

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983263

Luminaire Tested: S124IW-B770UB35-4F0-XX-W2A

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B770UB35-4F0-XX-W2A
Description: Define 4 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3139.0 lumens
Efficiency: N/A
Efficacy: 135.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983263

CATALOG NUMBER: S124IW-B770UB35-4F0-XX-W2A

Luminous Intensity Polar Plot



TEST NUMBER: P983263

CATALOG NUMBER: S124IW-B770UB35-4F0-XX-W2A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983263

CATALOG NUMBER: S124IW-B770UB35-4F0-XX-W2A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.1
90°-100°	33.7	1.1
100°-110°	221.6	7.1
110°-120°	423.2	13.5
120°-130°	537.2	17.1
130°-140°	574.7	18.3
140°-150°	537.4	17.1
150°-160°	433.4	13.8
160°-170°	279.5	8.9
170°-180°	96.3	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.1
90°-120°	678.5	21.6
90°-150°	2327.8	74.2
90°-180°	3137.0	99.9
0°-180°	3139.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	11	17	21	23	2
95°	42	16	17	21	22	51
105°	228	233	237	243	216	239
115°	426	428	428	429	429	419
125°	599	602	600	603	604	535
135°	743	742	745	747	748	573
145°	857	859	859	860	861	535
155°	939	940	938	941	939	433
165°	991	987	987	993	986	280
175°	1014	1009	1010	1017	1008	97
180°	1014	1014	1014	1014	1014	

TEST NUMBER: P983263

CATALOG NUMBER: S124IW-B770UB35-4F0-XX-W2A

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.3	10.6	16.7	21.2	22.7
92.5°	11.4	9.9	15.9	20.5	20.5
95°	41.7	15.9	16.7	21.2	22.0
97.5°	79.6	96.3	16.7	20.5	21.2
100°	124.3	138.0	33.4	20.5	21.2
102.5°	174.4	183.5	192.6	22.0	22.0
105°	228.2	232.8	236.6	243.4	216.1
107.5°	277.5	279.8	285.1	288.9	291.9
110°	327.6	329.8	334.4	335.9	338.2

TEST NUMBER: P983263

CATALOG NUMBER: S124IW-B770UB35-4F0-XX-W2A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.1	380.6	382.1	381.4	384.4
115°	426.1	428.4	427.6	429.2	429.2
117.5°	470.9	473.9	476.2	475.4	475.4
120°	516.4	519.4	518.6	520.1	518.6
122.5°	558.8	560.3	561.8	562.6	561.1
125°	599.0	602.0	600.5	602.8	603.6
127.5°	637.7	638.4	642.2	641.5	640.7
130°	674.8	675.6	677.9	678.6	678.6
132.5°	708.9	710.5	713.5	714.3	713.5
135°	743.1	742.3	745.3	746.9	748.4
137.5°	773.4	773.4	777.2	778.7	777.9
140°	803.0	804.5	806.0	808.3	809.0
142.5°	829.5	832.5	833.3	834.8	834.8
145°	856.8	859.1	859.1	859.8	861.3
147.5°	878.0	882.6	881.8	882.6	883.3
150°	901.5	904.6	903.8	903.8	904.6
152.5°	921.2	923.5	922.0	923.5	922.8
155°	939.4	940.2	937.9	941.0	938.7
157.5°	955.4	955.4	952.3	956.1	952.3
160°	969.0	966.7	966.0	970.5	966.0
162.5°	981.1	978.1	977.4	981.9	976.6
165°	991.0	987.2	987.2	993.3	986.5
167.5°	999.3	995.6	994.8	1001.6	994.0
170°	1006.2	1001.6	1002.4	1008.4	1000.9
172.5°	1010.7	1006.2	1006.9	1013.0	1004.7
175°	1013.8	1009.2	1010.0	1016.8	1007.7
177.5°	1016.0	1010.7	1012.2	1018.3	1009.2
180°	1013.8	1013.8	1013.8	1013.8	1013.8

(END OF REPORT)