

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034848

Luminaire Tested: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034848
REPORT IS A COMBINATION OF REPORTS P1006598 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6365.0 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034848

CATALOG NUMBER: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034848

CATALOG NUMBER: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	59	59	59	43	43	43
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	32	31
3	79	70	63	57	71	63	57	52	51	47	44	40	37	35	30	28	27
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	44	37	31	51	41	34	29	33	28	25	27	23	20	20	18	16
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	15	13
10	45	34	27	22	41	31	25	20	26	21	17	21	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6172	6172	6172
5°	6173	6018	6028
10°	6113	5867	5815
15°	6026	5654	5535
20°	5919	5399	5241
25°	5797	5149	4926
30°	5646	4876	4595
35°	5492	4597	4244
40°	5346	4311	3900
45°	5171	4002	3541
50°	4994	3675	3175
55°	4787	3352	2796
60°	4575	2983	2402
65°	4324	2571	1979
70°	4030	2093	1557
75°	3625	1574	1135
80°	3057	1020	765
85°	2287	548	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5171 cd/sqm

TEST NUMBER: P1034848

CATALOG NUMBER: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.7	1.4
10°-20°	253.4	4.0
20°-30°	367.4	5.8
30°-40°	418.6	6.6
40°-50°	408.0	6.4
50°-60°	343.3	5.4
60°-70°	240.6	3.8
70°-80°	123.3	1.9
80°-90°	32.7	0.5
90°-100°	45.2	0.7
100°-110°	300.3	4.7
110°-120°	540.7	8.5
120°-130°	694.1	10.9
130°-140°	746.5	11.7
140°-150°	700.6	11.0
150°-160°	566.7	8.9
160°-170°	366.5	5.8
170°-180°	126.4	2.0
0°-30°	711.4	11.2
0°-40°	1130.0	17.8
0°-60°	1881.3	29.6
0°-90°	2278.0	35.8
90°-120°	886.2	13.9
90°-150°	3027.4	47.6
90°-180°	4087.0	64.2
0°-180°	6365.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	963	963	963	963	963	
5°	962	959	951	958	957	91
15°	915	910	895	894	888	258
25°	830	818	792	782	774	382
35°	714	697	664	643	633	447
45°	585	564	524	495	484	451
55°	444	420	380	347	335	397
65°	300	276	237	208	197	298
75°	160	138	108	92	87	169
85°	40	27	23	23	22	44
90°	1	9	16	21	24	5
95°	56	53	16	21	21	69
105°	290	294	294	294	293	307
115°	544	549	550	546	540	540
125°	774	781	781	777	774	692
135°	966	972	970	968	962	744
145°	1119	1121	1121	1122	1116	700
155°	1233	1227	1229	1232	1224	568
165°	1301	1295	1296	1302	1294	367
175°	1330	1325	1326	1334	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1034848

CATALOG NUMBER: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	963.3	963.3	963.3	963.3	963.3
2.5°	965.5	963.3	956.1	963.3	962.6
5°	961.9	959.0	951.0	958.2	956.8
7.5°	954.6	951.7	942.2	948.0	946.6
10°	943.7	941.5	931.3	933.5	931.3
12.5°	931.3	928.4	913.9	915.3	911.7
15°	914.6	910.2	894.9	894.2	887.7
17.5°	897.1	890.6	872.4	868.7	863.6
20°	876.0	868.7	845.5	841.8	835.3
22.5°	852.7	845.5	820.7	812.7	807.6
25°	829.5	818.5	791.6	782.2	774.2
27.5°	803.3	790.2	761.8	749.4	741.4
30°	774.2	760.3	729.8	713.0	706.5
32.5°	745.8	729.0	697.8	678.8	670.1
35°	714.5	697.0	664.3	643.2	633.0
37.5°	684.7	663.6	630.1	605.4	595.2
40°	652.6	630.8	595.9	568.2	559.5
42.5°	619.2	596.6	560.2	534.1	520.2
45°	585.0	563.9	523.9	494.8	483.8
47.5°	549.3	527.5	487.5	457.7	445.3
50°	515.9	491.8	450.4	419.8	408.9
52.5°	479.5	454.7	416.2	382.7	371.8
55°	443.8	420.5	379.8	347.1	335.4
57.5°	407.4	382.7	343.4	311.4	301.2
60°	372.5	347.1	307.8	275.8	264.8
62.5°	335.4	311.4	271.4	242.3	231.4
65°	300.5	275.8	237.2	208.1	197.2
67.5°	265.6	240.8	203.7	176.1	167.3
70°	229.9	205.2	168.8	146.2	137.5
72.5°	195.0	171.0	137.5	117.1	112.0
75°	160.1	138.2	107.7	91.7	86.6
77.5°	124.4	107.0	81.5	69.1	64.8
80°	94.6	77.1	56.8	50.2	48.7
82.5°	65.5	50.2	37.8	35.7	34.9
85°	40.0	26.9	23.3	22.6	21.8
87.5°	16.7	11.6	10.9	10.9	10.2
90°	1.0	8.9	15.8	20.7	23.7
92.5°	18.7	9.9	15.8	20.7	21.7
95°	56.2	53.3	15.8	20.7	20.7
97.5°	105.5	111.5	17.8	19.7	20.7
100°	164.7	167.7	171.6	24.7	20.7
102.5°	224.9	228.8	230.8	232.8	149.9
105°	290.0	293.9	293.9	293.9	292.9
107.5°	357.0	357.0	359.0	360.0	356.1
110°	422.1	422.1	424.1	421.1	422.1

TEST NUMBER: P1034848

CATALOG NUMBER: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	483.3	486.2	487.2	483.3	481.3
115°	544.4	549.4	550.3	546.4	540.5
117.5°	608.5	608.5	612.5	606.6	604.6
120°	667.7	666.7	669.7	667.7	662.8
122.5°	720.0	724.9	725.9	723.9	718.0
125°	774.2	781.1	781.1	777.2	774.2
127.5°	826.5	831.4	830.5	828.5	820.6
130°	873.9	878.8	879.8	876.8	871.9
132.5°	921.2	927.1	924.2	924.2	919.2
135°	965.6	971.5	969.5	967.5	961.6
137.5°	1007.0	1012.9	1010.9	1010.9	1006.0
140°	1047.4	1049.4	1048.4	1050.4	1044.5
142.5°	1083.9	1084.9	1086.9	1086.9	1081.0
145°	1119.4	1121.4	1121.4	1122.4	1116.5
147.5°	1151.0	1151.0	1152.0	1153.0	1146.1
150°	1180.6	1178.6	1180.6	1182.6	1174.7
152.5°	1209.2	1204.3	1206.2	1208.2	1201.3
155°	1232.9	1226.9	1228.9	1231.9	1224.0
157.5°	1251.6	1248.6	1248.6	1251.6	1243.7
160°	1271.3	1265.4	1266.4	1270.3	1262.4
162.5°	1287.1	1281.2	1282.2	1288.1	1279.2
165°	1300.9	1295.0	1296.0	1301.9	1294.0
167.5°	1311.8	1305.8	1306.8	1313.7	1304.9
170°	1320.6	1313.7	1314.7	1322.6	1313.7
172.5°	1326.6	1319.7	1321.6	1328.5	1319.7
175°	1330.5	1324.6	1325.6	1333.5	1324.6
177.5°	1333.5	1327.5	1328.5	1335.4	1327.5
180°	1330.5	1330.5	1330.5	1330.5	1330.5

(END OF REPORT)