

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034854

Luminaire Tested: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034854
REPORT IS A COMBINATION OF REPORTS P1006636 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6754.0 lumens
Efficiency: N/A
Efficacy: 102.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034854

CATALOG NUMBER: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034854

CATALOG NUMBER: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	86	83	85	81	78	76	65	63	61	50	49	48	37	36	35
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25
4	72	61	54	48	64	56	49	44	45	40	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19
6	61	49	41	36	54	45	38	33	36	31	27	28	25	22	21	19	17
7	56	44	36	31	50	40	33	29	33	28	24	26	22	20	19	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14
9	48	36	29	24	44	33	27	23	27	22	19	22	18	16	16	14	12
10	45	33	26	22	41	30	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6172	6172	6172
5°	6173	6018	6028
10°	6113	5867	5815
15°	6026	5654	5535
20°	5919	5399	5241
25°	5797	5149	4926
30°	5646	4876	4595
35°	5492	4597	4244
40°	5346	4311	3900
45°	5171	4002	3541
50°	4994	3675	3175
55°	4787	3352	2796
60°	4575	2983	2402
65°	4324	2571	1979
70°	4030	2093	1557
75°	3625	1574	1135
80°	3057	1020	765
85°	2287	548	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5171 cd/sqm

TEST NUMBER: P1034854

CATALOG NUMBER: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.7	1.3
10°-20°	253.4	3.8
20°-30°	367.4	5.4
30°-40°	418.6	6.2
40°-50°	408.0	6.0
50°-60°	343.3	5.1
60°-70°	240.6	3.6
70°-80°	123.3	1.8
80°-90°	33.3	0.5
90°-100°	106.6	1.6
100°-110°	316.8	4.7
110°-120°	537.3	8.0
120°-130°	707.3	10.5
130°-140°	792.6	11.7
140°-150°	776.9	11.5
150°-160°	652.5	9.7
160°-170°	433.8	6.4
170°-180°	151.8	2.2
0°-30°	711.4	10.5
0°-40°	1130.0	16.7
0°-60°	1881.3	27.9
0°-90°	2278.5	33.7
90°-120°	960.7	14.2
90°-150°	3237.4	47.9
90°-180°	4475.0	66.3
0°-180°	6754.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	963	963	963	963	963	
5°	962	959	951	958	957	91
15°	915	910	895	894	888	258
25°	830	818	792	782	774	382
35°	714	697	664	643	633	447
45°	585	564	524	495	484	451
55°	444	420	380	347	335	397
65°	300	276	237	208	197	298
75°	160	138	108	92	87	169
85°	40	27	23	23	22	44
90°	1	11	20	26	30	8
95°	81	84	96	105	107	85
105°	284	291	298	306	310	303
115°	538	543	545	544	543	532
125°	785	792	794	791	790	703
135°	1021	1028	1030	1030	1025	787
145°	1237	1242	1245	1245	1242	773
155°	1415	1415	1416	1421	1415	652
165°	1539	1536	1538	1542	1535	434
175°	1600	1595	1595	1602	1594	152
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P1034854

CATALOG NUMBER: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	963.3	963.3	963.3	963.3	963.3
2.5°	965.5	963.3	956.1	963.3	962.6
5°	961.9	959.0	951.0	958.2	956.8
7.5°	954.6	951.7	942.2	948.0	946.6
10°	943.7	941.5	931.3	933.5	931.3
12.5°	931.3	928.4	913.9	915.3	911.7
15°	914.6	910.2	894.9	894.2	887.7
17.5°	897.1	890.6	872.4	868.7	863.6
20°	876.0	868.7	845.5	841.8	835.3
22.5°	852.7	845.5	820.7	812.7	807.6
25°	829.5	818.5	791.6	782.2	774.2
27.5°	803.3	790.2	761.8	749.4	741.4
30°	774.2	760.3	729.8	713.0	706.5
32.5°	745.8	729.0	697.8	678.8	670.1
35°	714.5	697.0	664.3	643.2	633.0
37.5°	684.7	663.6	630.1	605.4	595.2
40°	652.6	630.8	595.9	568.2	559.5
42.5°	619.2	596.6	560.2	534.1	520.2
45°	585.0	563.9	523.9	494.8	483.8
47.5°	549.3	527.5	487.5	457.7	445.3
50°	515.9	491.8	450.4	419.8	408.9
52.5°	479.5	454.7	416.2	382.7	371.8
55°	443.8	420.5	379.8	347.1	335.4
57.5°	407.4	382.7	343.4	311.4	301.2
60°	372.5	347.1	307.8	275.8	264.8
62.5°	335.4	311.4	271.4	242.3	231.4
65°	300.5	275.8	237.2	208.1	197.2
67.5°	265.6	240.8	203.7	176.1	167.3
70°	229.9	205.2	168.8	146.2	137.5
72.5°	195.0	171.0	137.5	117.1	112.0
75°	160.1	138.2	107.7	91.7	86.6
77.5°	124.4	107.0	81.5	69.1	64.8
80°	94.6	77.1	56.8	50.2	48.7
82.5°	65.5	50.2	37.8	35.7	34.9
85°	40.0	26.9	23.3	22.6	21.8
87.5°	16.7	11.6	10.9	10.9	10.2
90°	1.2	11.2	20.0	26.2	30.0
92.5°	37.4	43.7	54.9	63.6	66.1
95°	81.1	83.6	96.1	104.8	107.3
97.5°	124.8	126.0	143.5	151.0	152.2
100°	174.7	174.7	190.9	202.2	204.7
102.5°	228.4	234.6	240.9	253.3	257.1
105°	284.5	290.8	298.3	305.7	309.5
107.5°	345.7	351.9	358.2	361.9	361.9
110°	409.3	415.6	419.3	423.0	421.8

TEST NUMBER: P1034854

CATALOG NUMBER: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	474.2	476.7	481.7	483.0	480.5
115°	537.9	542.9	545.3	544.1	542.9
117.5°	602.8	604.0	606.5	607.7	602.8
120°	662.7	668.9	670.1	670.1	665.1
122.5°	727.5	728.8	732.5	731.3	727.5
125°	785.0	792.4	793.7	791.2	789.9
127.5°	848.6	852.3	853.6	852.3	849.8
130°	904.8	911.0	913.5	912.2	909.7
132.5°	960.9	972.1	970.9	969.6	965.9
135°	1020.8	1028.3	1029.5	1029.5	1024.6
137.5°	1077.0	1084.5	1087.0	1088.2	1082.0
140°	1130.6	1136.9	1140.6	1143.1	1136.9
142.5°	1184.3	1189.3	1194.3	1195.5	1189.3
145°	1236.7	1241.7	1245.4	1245.4	1241.7
147.5°	1285.4	1289.1	1291.6	1295.4	1285.4
150°	1334.0	1332.8	1337.8	1337.8	1335.3
152.5°	1374.0	1376.5	1377.7	1381.5	1376.5
155°	1415.2	1415.2	1416.4	1421.4	1415.2
157.5°	1452.6	1450.1	1451.3	1456.3	1447.6
160°	1485.0	1481.3	1482.5	1487.5	1481.3
162.5°	1513.7	1511.2	1511.2	1517.5	1510.0
165°	1538.7	1536.2	1537.5	1542.4	1535.0
167.5°	1561.2	1556.2	1556.2	1563.7	1556.2
170°	1578.6	1573.6	1573.6	1581.1	1572.4
172.5°	1591.1	1586.1	1586.1	1593.6	1586.1
175°	1599.9	1594.9	1594.9	1602.3	1593.6
177.5°	1606.1	1601.1	1599.9	1607.3	1598.6
180°	1603.6	1603.6	1603.6	1603.6	1603.6

(END OF REPORT)