

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034326

Luminaire Tested: S125DIW-B1090D1050UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034326
REPORT IS A COMBINATION OF REPORTS P1002745 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D1050UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8668.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034326

CATALOG NUMBER: S125DIW-B1090D1050UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034326

CATALOG NUMBER: S125DIW-B1090D1050UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	57
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	48	48	43
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40	40	40	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	34	34	30
4	74	64	56	49	68	59	52	47	50	45	41	42	38	35	35	32	30	30	30	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	32	28	26	26	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	23	23	20
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	20	20	18
8	54	42	34	28	50	39	32	27	34	28	24	29	24	21	24	21	18	18	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	16	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10868	10868	10868
5°	10869	10616	10636
10°	10779	10372	10340
15°	10637	10081	9991
20°	10446	9744	9591
25°	10241	9376	9163
30°	9993	8992	8711
35°	9728	8590	8205
40°	9454	8165	7755
45°	9158	7751	7278
50°	8833	7281	6721
55°	8511	6763	6209
60°	8126	6217	5613
65°	7666	5584	4997
70°	7199	4858	4285
75°	6412	4000	3466
80°	5465	2988	2549
85°	4220	1768	1405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9158 cd/sqm

TEST NUMBER: P1034326

CATALOG NUMBER: S125DIW-B1090D1050UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	1.8
10°-20°	452.1	5.2
20°-30°	667.5	7.7
30°-40°	778.8	9.0
40°-50°	782.2	9.0
50°-60°	686.6	7.9
60°-70°	511.4	5.9
70°-80°	292.1	3.4
80°-90°	86.4	1.0
90°-100°	47.0	0.5
100°-110°	312.3	3.6
110°-120°	562.4	6.5
120°-130°	721.9	8.3
130°-140°	776.4	9.0
140°-150°	728.7	8.4
150°-160°	589.5	6.8
160°-170°	381.2	4.4
170°-180°	131.5	1.5
0°-30°	1279.7	14.8
0°-40°	2058.4	23.7
0°-60°	3527.2	40.7
0°-90°	4417.1	51.0
90°-120°	921.7	10.6
90°-150°	3148.8	36.3
90°-180°	4251.0	49.0
0°-180°	8668.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1696	1696	1696	1696	1696	
5°	1694	1691	1678	1690	1688	161
15°	1614	1610	1596	1602	1602	455
25°	1466	1459	1441	1444	1440	674
35°	1266	1260	1241	1235	1224	792
45°	1036	1031	1014	998	994	798
55°	789	785	766	754	745	704
65°	533	530	515	503	498	528
75°	283	280	274	270	264	301
85°	74	75	75	74	71	81
90°	1	9	16	22	25	8
95°	58	55	16	22	22	72
105°	302	306	306	306	305	320
115°	566	571	572	568	562	561
125°	805	812	812	808	805	719
135°	1004	1010	1008	1006	1000	774
145°	1164	1166	1166	1167	1161	728
155°	1282	1276	1278	1281	1273	591
165°	1353	1347	1348	1354	1346	382
175°	1384	1378	1379	1387	1378	132
180°	1384	1384	1384	1384	1384	

TEST NUMBER: P1034326

CATALOG NUMBER: S125DIW-B1090D1050UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1696.3	1696.3	1696.3	1696.3	1696.3
2.5°	1701.6	1697.6	1684.2	1697.6	1696.3
5°	1693.6	1690.9	1677.5	1689.6	1688.2
7.5°	1681.5	1678.8	1664.1	1676.2	1674.8
10°	1664.1	1661.4	1646.6	1657.4	1656.0
12.5°	1642.6	1637.2	1623.8	1631.9	1631.9
15°	1614.4	1610.4	1595.6	1602.3	1602.3
17.5°	1584.9	1578.2	1563.4	1571.5	1564.8
20°	1546.0	1543.3	1525.8	1535.2	1528.5
22.5°	1507.1	1501.7	1485.6	1491.0	1486.9
25°	1465.5	1458.7	1441.3	1444.0	1440.0
27.5°	1417.1	1413.1	1395.7	1397.0	1393.0
30°	1370.2	1366.1	1346.0	1343.3	1339.3
32.5°	1319.2	1312.5	1295.0	1289.7	1281.6
35°	1265.5	1260.1	1241.3	1234.6	1223.9
37.5°	1210.5	1203.8	1186.3	1176.9	1170.2
40°	1154.1	1147.4	1128.6	1116.5	1112.5
42.5°	1093.7	1088.4	1069.6	1058.8	1052.1
45°	1036.0	1030.7	1014.5	998.4	994.4
47.5°	972.9	974.3	954.2	938.1	928.7
50°	912.6	908.5	892.4	875.0	865.6
52.5°	850.8	848.1	830.7	815.9	805.2
55°	789.1	785.1	766.3	754.2	744.8
57.5°	723.3	722.0	705.9	689.8	685.8
60°	661.6	656.2	641.5	628.1	618.7
62.5°	597.2	593.2	581.1	566.3	559.6
65°	532.8	530.1	515.3	503.2	497.9
67.5°	469.7	464.3	453.6	442.9	440.2
70°	410.7	403.9	391.9	383.8	378.4
72.5°	346.2	342.2	335.5	326.1	320.7
75°	283.2	280.5	273.8	269.7	264.4
77.5°	224.1	222.8	218.7	216.1	212.0
80°	169.1	169.1	166.4	165.1	162.4
82.5°	120.8	118.1	118.1	115.4	115.4
85°	73.8	75.2	75.2	73.8	71.1
87.5°	36.2	36.2	34.9	34.9	32.2
90°	1.0	9.2	16.4	21.5	24.6
92.5°	19.5	10.3	16.4	21.5	22.6
95°	58.5	55.4	16.4	21.5	21.5
97.5°	109.8	115.9	18.5	20.5	21.5
100°	171.3	174.4	178.5	25.6	21.5
102.5°	233.9	238.0	240.0	242.1	155.9
105°	301.6	305.7	305.7	305.7	304.7
107.5°	371.4	371.4	373.4	374.4	370.3
110°	439.1	439.1	441.1	438.0	439.1

TEST NUMBER: P1034326

CATALOG NUMBER: S125DIW-B1090D1050UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	502.7	505.7	506.8	502.7	500.6
115°	566.3	571.4	572.4	568.3	562.2
117.5°	632.9	632.9	637.1	630.9	628.8
120°	694.5	693.5	696.5	694.5	689.4
122.5°	748.9	754.0	755.0	753.0	746.8
125°	805.3	812.5	812.5	808.4	805.3
127.5°	859.7	864.8	863.8	861.7	853.5
130°	908.9	914.0	915.1	912.0	906.8
132.5°	958.1	964.3	961.2	961.2	956.1
135°	1004.3	1010.5	1008.4	1006.4	1000.2
137.5°	1047.4	1053.5	1051.5	1051.5	1046.4
140°	1089.4	1091.5	1090.5	1092.5	1086.4
142.5°	1127.4	1128.4	1130.5	1130.5	1124.3
145°	1164.3	1166.4	1166.4	1167.4	1161.3
147.5°	1197.2	1197.2	1198.2	1199.2	1192.0
150°	1227.9	1225.9	1227.9	1230.0	1221.8
152.5°	1257.7	1252.6	1254.6	1256.7	1249.5
155°	1282.3	1276.2	1278.2	1281.3	1273.1
157.5°	1301.8	1298.7	1298.7	1301.8	1293.6
160°	1322.3	1316.2	1317.2	1321.3	1313.1
162.5°	1338.7	1332.6	1333.6	1339.8	1330.5
165°	1353.1	1346.9	1348.0	1354.1	1345.9
167.5°	1364.4	1358.2	1359.2	1366.4	1357.2
170°	1373.6	1366.4	1367.5	1375.7	1366.4
172.5°	1379.8	1372.6	1374.6	1381.8	1372.6
175°	1383.9	1377.7	1378.7	1386.9	1377.7
177.5°	1386.9	1380.8	1381.8	1389.0	1380.8
180°	1383.9	1383.9	1383.9	1383.9	1383.9

(END OF REPORT)