

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034337

Luminaire Tested: S125DIW-B1090D1340UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034337
REPORT IS A COMBINATION OF REPORTS P1002805 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D1340UB2750-4F0-XX-W2A-D_3500K
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9651.0 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 88.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034337

CATALOG NUMBER: S125DIW-B1090D1340UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034337

CATALOG NUMBER: S125DIW-B1090D1340UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48
1	95	91	87	83	87	83	79	76	68	65	63	54	53	51	42	41	40
2	86	79	73	67	78	72	67	62	59	55	52	47	45	42	36	34	33
3	79	69	62	56	71	63	57	51	52	47	43	42	38	35	32	30	28
4	72	61	53	47	65	56	49	43	46	41	37	37	33	30	28	26	24
5	66	54	46	40	60	50	42	37	41	36	31	33	29	26	26	23	20
6	61	48	40	34	55	44	37	32	37	31	27	30	26	23	23	20	18
7	56	44	36	30	51	40	33	28	33	28	24	27	23	20	21	18	16
8	52	40	32	26	47	36	29	25	30	25	21	25	21	18	19	16	14
9	48	36	29	23	44	33	26	22	28	23	19	23	19	16	18	15	13
10	45	33	26	21	41	30	24	20	26	20	17	21	17	14	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8807	8807	8807
5°	8821	8622	8643
10°	8755	8446	8422
15°	8648	8241	8150
20°	8504	7994	7880
25°	8334	7731	7554
30°	8127	7445	7257
35°	7935	7180	6984
40°	7738	6902	6708
45°	7517	6661	6460
50°	7304	6399	6236
55°	7049	6149	5976
60°	6770	5864	5709
65°	6477	5564	5409
70°	6142	5162	5097
75°	5615	4765	4716
80°	4922	4282	4295
85°	4237	3899	4073

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7517 cd/sqm

TEST NUMBER: P1034337

CATALOG NUMBER: S125DIW-B1090D1340UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.1	1.3
10°-20°	369.2	3.8
20°-30°	549.1	5.7
30°-40°	650.3	6.7
40°-50°	672.3	7.0
50°-60°	619.3	6.4
60°-70°	500.6	5.2
70°-80°	335.0	3.5
80°-90°	175.8	1.8
90°-100°	157.1	1.6
100°-110°	467.9	4.8
110°-120°	761.3	7.9
120°-130°	942.7	9.8
130°-140°	996.5	10.3
140°-150°	926.4	9.6
150°-160°	747.5	7.7
160°-170°	483.4	5.0
170°-180°	166.7	1.7
0°-30°	1048.4	10.9
0°-40°	1698.6	17.6
0°-60°	2990.2	31.0
0°-90°	4001.5	41.5
90°-120°	1386.3	14.4
90°-150°	4251.9	44.1
90°-180°	5649.0	58.5
0°-180°	9651.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1374	1374	1374	1374	1374	
5°	1374	1372	1362	1373	1372	130
15°	1312	1314	1304	1312	1307	370
25°	1193	1197	1188	1194	1187	549
35°	1032	1042	1038	1042	1042	646
45°	850	865	872	881	883	656
55°	654	675	697	712	717	584
65°	450	481	513	534	539	447
75°	248	283	326	353	360	263
85°	74	119	166	195	206	77
90°	23	76	131	169	182	19
95°	92	123	119	155	165	105
105°	394	421	462	489	497	418
115°	726	742	778	798	798	720
125°	1026	1034	1061	1078	1080	917
135°	1276	1283	1290	1304	1303	984
145°	1478	1479	1479	1487	1485	924
155°	1626	1618	1621	1625	1614	749
165°	1716	1708	1709	1717	1707	485
175°	1755	1747	1748	1759	1747	167
180°	1755	1755	1755	1755	1755	

TEST NUMBER: P1034337

CATALOG NUMBER: S125DIW-B1090D1340UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1374.5	1374.5	1374.5	1374.5	1374.5
2.5°	1378.6	1375.9	1366.4	1375.9	1374.5
5°	1374.5	1371.8	1362.4	1373.2	1371.8
7.5°	1365.1	1363.7	1354.3	1363.7	1362.4
10°	1351.6	1351.6	1340.8	1350.3	1348.9
12.5°	1332.7	1334.1	1326.0	1332.7	1328.7
15°	1312.5	1313.9	1304.4	1312.5	1307.1
17.5°	1286.9	1289.6	1280.2	1286.9	1282.9
20°	1258.6	1261.3	1251.9	1255.9	1255.9
22.5°	1226.3	1231.7	1220.9	1226.3	1222.2
25°	1192.6	1196.6	1188.5	1193.9	1187.2
27.5°	1156.2	1161.6	1152.2	1156.2	1153.5
30°	1114.4	1122.5	1114.4	1117.1	1115.8
32.5°	1076.7	1083.4	1078.0	1080.7	1079.4
35°	1032.2	1041.7	1037.6	1041.7	1041.7
37.5°	989.1	997.2	995.8	1001.2	999.9
40°	944.6	955.4	954.1	959.5	962.2
42.5°	896.1	911.0	915.0	921.7	921.7
45°	850.3	865.1	871.9	881.3	882.7
47.5°	803.1	816.6	827.4	840.9	843.6
50°	754.6	769.5	784.3	799.1	803.1
52.5°	703.4	722.3	741.2	757.3	760.0
55°	653.6	675.1	696.7	711.5	716.9
57.5°	602.4	628.0	652.2	668.4	672.4
60°	551.2	578.1	605.1	625.3	629.3
62.5°	501.3	528.2	557.9	580.8	586.2
65°	450.1	481.1	513.4	533.6	539.0
67.5°	402.9	432.6	464.9	489.2	495.9
70°	350.4	381.4	416.4	442.0	450.1
72.5°	299.2	331.5	370.6	398.9	404.3
75°	248.0	283.0	326.1	353.1	359.8
77.5°	198.1	238.5	278.9	308.6	314.0
80°	152.3	192.7	238.5	268.2	273.6
82.5°	110.5	153.6	200.8	229.1	239.9
85°	74.1	118.6	165.8	195.4	206.2
87.5°	47.2	90.3	136.1	167.1	176.5
90°	22.9	76.4	131.3	168.8	182.1
92.5°	43.6	70.9	125.9	162.1	172.8
95°	91.6	122.8	119.2	155.3	164.8
97.5°	155.4	195.5	116.4	147.3	158.0
100°	232.0	264.2	312.5	147.0	149.9
102.5°	310.1	340.9	385.3	414.8	313.6
105°	394.5	421.3	461.7	488.7	496.8
107.5°	481.7	500.5	542.2	570.5	573.4
110°	566.2	582.4	622.7	644.4	655.2

TEST NUMBER: P1034337

CATALOG NUMBER: S125DIW-B1090D1340UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	646.8	662.9	700.5	719.6	726.4
115°	726.2	742.1	778.5	797.5	797.7
117.5°	809.3	816.1	855.0	870.1	876.9
120°	887.4	890.2	925.1	945.4	947.0
122.5°	955.0	962.8	993.8	1012.7	1013.0
125°	1026.5	1034.3	1061.3	1077.6	1080.4
127.5°	1094.1	1099.3	1120.9	1138.5	1136.2
130°	1156.5	1161.7	1181.9	1196.8	1197.1
132.5°	1217.7	1225.5	1235.1	1253.9	1252.8
135°	1276.2	1282.6	1289.5	1304.4	1303.3
137.5°	1330.8	1337.2	1340.0	1356.2	1355.1
140°	1382.8	1385.4	1385.5	1402.9	1400.5
142.5°	1430.9	1430.9	1433.5	1445.6	1443.2
145°	1477.7	1479.0	1479.0	1487.0	1484.6
147.5°	1518.1	1518.1	1519.4	1523.4	1517.0
150°	1557.1	1554.5	1557.1	1559.7	1550.6
152.5°	1594.8	1588.3	1590.9	1593.5	1584.4
155°	1626.0	1618.2	1620.8	1624.7	1614.3
157.5°	1650.7	1646.8	1646.8	1650.7	1640.3
160°	1676.8	1669.0	1670.3	1675.5	1665.1
162.5°	1697.6	1689.8	1691.1	1698.9	1687.2
165°	1715.8	1708.0	1709.3	1717.1	1706.7
167.5°	1730.1	1722.3	1723.6	1732.7	1721.0
170°	1741.8	1732.7	1734.0	1744.4	1732.7
172.5°	1749.6	1740.5	1743.1	1752.2	1740.5
175°	1754.8	1747.0	1748.3	1758.7	1747.0
177.5°	1758.7	1750.9	1752.2	1761.3	1750.9
180°	1754.8	1754.8	1754.8	1754.8	1754.8

(END OF REPORT)