

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034884

Luminaire Tested: S125RDIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034884
REPORT IS A COMBINATION OF REPORTS P1006768 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D770UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4880.9 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034884

CATALOG NUMBER: S125RDIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034884

CATALOG NUMBER: S125RDIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53			47
1	97	93	89	86	89	86	82	79	72	69	67	59	57	56	47	46	45			40
2	89	81	75	70	81	75	70	66	63	59	56	52	49	47	42	40	38			34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33			29
4	74	64	56	50	68	59	52	47	50	45	40	41	37	34	33	31	28			25
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25			22
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	27	24	22			19
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20			17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18			15
9	50	38	31	26	46	35	29	24	30	25	21	26	22	19	21	18	16			14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6172	6172	6172
5°	6173	6018	6028
10°	6113	5867	5815
15°	6026	5654	5535
20°	5919	5399	5241
25°	5797	5149	4926
30°	5646	4876	4595
35°	5492	4597	4244
40°	5346	4311	3900
45°	5171	4002	3541
50°	4994	3675	3175
55°	4787	3352	2796
60°	4575	2983	2402
65°	4324	2571	1979
70°	4030	2093	1557
75°	3625	1574	1135
80°	3057	1020	765
85°	2287	548	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5171 cd/sqm

TEST NUMBER: P1034884

CATALOG NUMBER: S125RDIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.7	1.9
10°-20°	253.4	5.2
20°-30°	367.4	7.5
30°-40°	418.6	8.6
40°-50°	408.0	8.4
50°-60°	343.3	7.0
60°-70°	240.6	4.9
70°-80°	123.3	2.5
80°-90°	32.2	0.7
90°-100°	62.0	1.3
100°-110°	184.3	3.8
110°-120°	312.5	6.4
120°-130°	411.4	8.4
130°-140°	461.1	9.4
140°-150°	451.9	9.3
150°-160°	379.6	7.8
160°-170°	252.3	5.2
170°-180°	88.3	1.8
0°-30°	711.4	14.6
0°-40°	1130.0	23.2
0°-60°	1881.3	38.5
0°-90°	2277.5	46.7
90°-120°	558.8	11.4
90°-150°	1883.3	38.6
90°-180°	2603.0	53.3
0°-180°	4880.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	963	963	963	963	963	
5°	962	959	951	958	957	91
15°	915	910	895	894	888	258
25°	830	818	792	782	774	382
35°	714	697	664	643	633	447
45°	585	564	524	495	484	451
55°	444	420	380	347	335	397
65°	300	276	237	208	197	298
75°	160	138	108	92	87	169
85°	40	27	23	23	22	44
90°	1	6	12	15	17	5
95°	47	49	56	61	62	49
105°	166	169	174	178	180	176
115°	313	316	317	316	316	310
125°	457	461	462	460	460	409
135°	594	598	599	599	596	458
145°	719	722	724	724	722	450
155°	823	823	824	827	823	379
165°	895	894	894	897	893	253
175°	931	928	928	932	927	88
180°	933	933	933	933	933	

TEST NUMBER: P1034884

CATALOG NUMBER: S125RDIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	963.3	963.3	963.3	963.3	963.3
2.5°	965.5	963.3	956.1	963.3	962.6
5°	961.9	959.0	951.0	958.2	956.8
7.5°	954.6	951.7	942.2	948.0	946.6
10°	943.7	941.5	931.3	933.5	931.3
12.5°	931.3	928.4	913.9	915.3	911.7
15°	914.6	910.2	894.9	894.2	887.7
17.5°	897.1	890.6	872.4	868.7	863.6
20°	876.0	868.7	845.5	841.8	835.3
22.5°	852.7	845.5	820.7	812.7	807.6
25°	829.5	818.5	791.6	782.2	774.2
27.5°	803.3	790.2	761.8	749.4	741.4
30°	774.2	760.3	729.8	713.0	706.5
32.5°	745.8	729.0	697.8	678.8	670.1
35°	714.5	697.0	664.3	643.2	633.0
37.5°	684.7	663.6	630.1	605.4	595.2
40°	652.6	630.8	595.9	568.2	559.5
42.5°	619.2	596.6	560.2	534.1	520.2
45°	585.0	563.9	523.9	494.8	483.8
47.5°	549.3	527.5	487.5	457.7	445.3
50°	515.9	491.8	450.4	419.8	408.9
52.5°	479.5	454.7	416.2	382.7	371.8
55°	443.8	420.5	379.8	347.1	335.4
57.5°	407.4	382.7	343.4	311.4	301.2
60°	372.5	347.1	307.8	275.8	264.8
62.5°	335.4	311.4	271.4	242.3	231.4
65°	300.5	275.8	237.2	208.1	197.2
67.5°	265.6	240.8	203.7	176.1	167.3
70°	229.9	205.2	168.8	146.2	137.5
72.5°	195.0	171.0	137.5	117.1	112.0
75°	160.1	138.2	107.7	91.7	86.6
77.5°	124.4	107.0	81.5	69.1	64.8
80°	94.6	77.1	56.8	50.2	48.7
82.5°	65.5	50.2	37.8	35.7	34.9
85°	40.0	26.9	23.3	22.6	21.8
87.5°	16.7	11.6	10.9	10.9	10.2
90°	0.7	6.5	11.6	15.2	17.4
92.5°	21.8	25.4	31.9	37.0	38.5
95°	47.2	48.6	55.9	61.0	62.4
97.5°	72.6	73.3	83.5	87.8	88.6
100°	101.6	101.6	111.1	117.6	119.1
102.5°	132.9	136.5	140.1	147.4	149.5
105°	165.5	169.1	173.5	177.9	180.0
107.5°	201.1	204.7	208.4	210.5	210.5
110°	238.1	241.7	243.9	246.1	245.4



TEST NUMBER: P1034884

CATALOG NUMBER: S125RDIW-B610D770UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	275.9	277.3	280.2	280.9	279.5
115°	312.9	315.8	317.2	316.5	315.8
117.5°	350.6	351.4	352.8	353.5	350.6
120°	385.5	389.1	389.8	389.8	386.9
122.5°	423.2	424.0	426.1	425.4	423.2
125°	456.6	461.0	461.7	460.3	459.5
127.5°	493.7	495.8	496.6	495.8	494.4
130°	526.3	530.0	531.4	530.7	529.2
132.5°	559.0	565.5	564.8	564.1	561.9
135°	593.8	598.2	598.9	598.9	596.0
137.5°	626.5	630.9	632.3	633.0	629.4
140°	657.7	661.4	663.5	665.0	661.4
142.5°	688.9	691.8	694.7	695.5	691.8
145°	719.4	722.3	724.5	724.5	722.3
147.5°	747.7	749.9	751.4	753.6	747.7
150°	776.1	775.3	778.2	778.2	776.8
152.5°	799.3	800.7	801.5	803.6	800.7
155°	823.2	823.2	824.0	826.9	823.2
157.5°	845.0	843.6	844.3	847.2	842.1
160°	863.9	861.7	862.4	865.3	861.7
162.5°	880.6	879.1	879.1	882.8	878.4
165°	895.1	893.7	894.4	897.3	892.9
167.5°	908.2	905.3	905.3	909.6	905.3
170°	918.3	915.4	915.4	919.8	914.7
172.5°	925.6	922.7	922.7	927.1	922.7
175°	930.7	927.8	927.8	932.1	927.1
177.5°	934.3	931.4	930.7	935.0	930.0
180°	932.9	932.9	932.9	932.9	932.9

(END OF REPORT)