

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034342

Luminaire Tested: S125DIW-B1090D1340UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034342
REPORT IS A COMBINATION OF REPORTS P1002812 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D1340UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9827.0 lumens
Efficiency: N/A
Efficacy: 110.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 88.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034342

CATALOG NUMBER: S125DIW-B1090D1340UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034342

CATALOG NUMBER: S125DIW-B1090D1340UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	88	85	88	85	81	78	71	68	66	58	56	54	46	45	44
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37
3	80	71	63	58	73	65	59	54	54	50	46	45	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10915	10915	10915
5°	10916	10662	10682
10°	10825	10417	10384
15°	10683	10125	10034
20°	10491	9786	9632
25°	10285	9416	9202
30°	10036	9031	8749
35°	9769	8627	8241
40°	9495	8200	7789
45°	9198	7784	7309
50°	8871	7313	6750
55°	8547	6792	6235
60°	8162	6243	5637
65°	7700	5608	5018
70°	7229	4878	4305
75°	6440	4017	3480
80°	5487	3000	2560
85°	4237	1775	1410

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9198 cd/sqm

TEST NUMBER: P1034342

CATALOG NUMBER: S125DIW-B1090D1340UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	1.6
10°-20°	454.1	4.6
20°-30°	670.4	6.8
30°-40°	782.1	8.0
40°-50°	785.5	8.0
50°-60°	689.5	7.0
60°-70°	513.6	5.2
70°-80°	293.3	3.0
80°-90°	87.3	0.9
90°-100°	59.5	0.6
100°-110°	396.0	4.0
110°-120°	713.2	7.3
120°-130°	915.4	9.3
130°-140°	984.6	10.0
140°-150°	924.1	9.4
150°-160°	747.5	7.6
160°-170°	483.4	4.9
170°-180°	166.7	1.7
0°-30°	1285.2	13.1
0°-40°	2067.3	21.0
0°-60°	3542.4	36.0
0°-90°	4436.6	45.1
90°-120°	1168.8	11.9
90°-150°	3992.8	40.6
90°-180°	5390.0	54.8
0°-180°	9827.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1704	1704	1704	1704	1704	
5°	1701	1698	1685	1697	1696	161
15°	1621	1617	1602	1609	1609	457
25°	1472	1465	1448	1450	1446	677
35°	1271	1266	1247	1240	1229	795
45°	1040	1035	1019	1003	999	802
55°	792	788	770	757	748	707
65°	535	532	518	505	500	531
75°	284	282	275	271	266	303
85°	74	76	76	74	71	81
90°	1	12	21	27	31	9
95°	74	70	21	27	27	91
105°	382	388	388	388	386	405
115°	718	725	726	721	713	712
125°	1021	1030	1030	1025	1021	912
135°	1274	1281	1279	1276	1268	982
145°	1476	1479	1479	1480	1472	923
155°	1626	1618	1621	1625	1614	749
165°	1716	1708	1709	1717	1707	485
175°	1755	1747	1748	1759	1747	167
180°	1755	1755	1755	1755	1755	

TEST NUMBER: P1034342

CATALOG NUMBER: S125DIW-B1090D1340UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1703.6	1703.6	1703.6	1703.6	1703.6
2.5°	1709.0	1704.9	1691.5	1704.9	1703.6
5°	1700.9	1698.2	1684.7	1696.8	1695.5
7.5°	1688.8	1686.1	1671.2	1683.4	1682.0
10°	1671.2	1668.5	1653.7	1664.5	1663.1
12.5°	1649.7	1644.3	1630.8	1638.9	1638.9
15°	1621.4	1617.3	1602.5	1609.2	1609.2
17.5°	1591.7	1585.0	1570.2	1578.2	1571.5
20°	1552.6	1549.9	1532.4	1541.8	1535.1
22.5°	1513.5	1508.2	1492.0	1497.4	1493.3
25°	1471.8	1465.0	1447.5	1450.2	1446.2
27.5°	1423.2	1419.2	1401.7	1403.0	1399.0
30°	1376.1	1372.0	1351.8	1349.1	1345.1
32.5°	1324.9	1318.1	1300.6	1295.2	1287.1
35°	1270.9	1265.6	1246.7	1239.9	1229.2
37.5°	1215.7	1208.9	1191.4	1182.0	1175.3
40°	1159.1	1152.3	1133.5	1121.3	1117.3
42.5°	1098.4	1093.0	1074.2	1063.4	1056.7
45°	1040.5	1035.1	1018.9	1002.7	998.7
47.5°	977.1	978.5	958.3	942.1	932.7
50°	916.5	912.4	896.3	878.7	869.3
52.5°	854.5	851.8	834.3	819.4	808.7
55°	792.5	788.4	769.6	757.4	748.0
57.5°	726.4	725.1	708.9	692.8	688.7
60°	664.5	659.1	644.2	630.8	621.3
62.5°	599.8	595.7	583.6	568.8	562.0
65°	535.1	532.4	517.5	505.4	500.0
67.5°	471.7	466.3	455.5	444.8	442.1
70°	412.4	405.7	393.5	385.5	380.1
72.5°	347.7	343.7	336.9	327.5	322.1
75°	284.4	281.7	274.9	270.9	265.5
77.5°	225.1	223.7	219.7	217.0	212.9
80°	169.8	169.8	167.1	165.8	163.1
82.5°	121.3	118.6	118.6	115.9	115.9
85°	74.1	75.5	75.5	74.1	71.4
87.5°	36.4	36.4	35.0	35.0	32.3
90°	1.3	11.7	20.8	27.3	31.2
92.5°	24.7	13.0	20.8	27.3	28.6
95°	74.1	70.2	20.8	27.3	27.3
97.5°	139.2	147.0	23.4	26.0	27.3
100°	217.2	221.1	226.3	32.5	27.3
102.5°	296.6	301.8	304.4	307.0	197.7
105°	382.4	387.6	387.6	387.6	386.3
107.5°	470.9	470.9	473.5	474.8	469.6
110°	556.8	556.8	559.4	555.5	556.8

TEST NUMBER: P1034342

CATALOG NUMBER: S125DIW-B1090D1340UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	637.4	641.3	642.6	637.4	634.8
115°	718.1	724.6	725.9	720.7	712.8
117.5°	802.6	802.6	807.8	800.0	797.4
120°	880.7	879.4	883.3	880.7	874.2
122.5°	949.6	956.1	957.4	954.8	947.0
125°	1021.1	1030.3	1030.3	1025.0	1021.1
127.5°	1090.1	1096.6	1095.3	1092.7	1082.3
130°	1152.5	1159.0	1160.3	1156.4	1149.9
132.5°	1215.0	1222.8	1218.9	1218.9	1212.4
135°	1273.5	1281.3	1278.7	1276.1	1268.3
137.5°	1328.1	1335.9	1333.3	1333.3	1326.8
140°	1381.5	1384.1	1382.8	1385.4	1377.6
142.5°	1429.6	1430.9	1433.5	1433.5	1425.7
145°	1476.4	1479.0	1479.0	1480.3	1472.5
147.5°	1518.1	1518.1	1519.4	1520.7	1511.6
150°	1557.1	1554.5	1557.1	1559.7	1549.3
152.5°	1594.8	1588.3	1590.9	1593.5	1584.4
155°	1626.0	1618.2	1620.8	1624.7	1614.3
157.5°	1650.7	1646.8	1646.8	1650.7	1640.3
160°	1676.8	1669.0	1670.3	1675.5	1665.1
162.5°	1697.6	1689.8	1691.1	1698.9	1687.2
165°	1715.8	1708.0	1709.3	1717.1	1706.7
167.5°	1730.1	1722.3	1723.6	1732.7	1721.0
170°	1741.8	1732.7	1734.0	1744.4	1732.7
172.5°	1749.6	1740.5	1743.1	1752.2	1740.5
175°	1754.8	1747.0	1748.3	1758.7	1747.0
177.5°	1758.7	1750.9	1752.2	1761.3	1750.9
180°	1754.8	1754.8	1754.8	1754.8	1754.8

(END OF REPORT)