

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034888

Luminaire Tested: S125RDIW-B610D770UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034888
REPORT IS A COMBINATION OF REPORTS P1006774 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D770UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5281.0 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034888

CATALOG NUMBER: S125RDIW-B610D770UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034888

CATALOG NUMBER: S125RDIW-B610D770UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	38	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	74	63	55	49	67	58	51	46	48	43	39	40	36	33	31	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23
6	62	50	42	37	57	46	39	34	39	34	30	32	28	25	26	23	21
7	58	45	38	32	52	42	35	30	35	30	26	29	25	22	23	21	18
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	16
9	50	38	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	35	27	23	42	32	26	21	27	22	19	23	19	16	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6172	6172	6172
5°	6173	6018	6028
10°	6113	5867	5815
15°	6026	5654	5535
20°	5919	5399	5241
25°	5797	5149	4926
30°	5646	4876	4595
35°	5492	4597	4244
40°	5346	4311	3900
45°	5171	4002	3541
50°	4994	3675	3175
55°	4787	3352	2796
60°	4575	2983	2402
65°	4324	2571	1979
70°	4030	2093	1557
75°	3625	1574	1135
80°	3057	1020	765
85°	2287	548	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5171 cd/sqm

TEST NUMBER: P1034888

CATALOG NUMBER: S125RDIW-B610D770UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.7	1.7
10°-20°	253.4	4.8
20°-30°	367.4	7.0
30°-40°	418.6	7.9
40°-50°	408.0	7.7
50°-60°	343.3	6.5
60°-70°	240.6	4.6
70°-80°	123.3	2.3
80°-90°	32.2	0.6
90°-100°	33.2	0.6
100°-110°	220.7	4.2
110°-120°	397.4	7.5
120°-130°	510.1	9.7
130°-140°	548.6	10.4
140°-150°	514.9	9.7
150°-160°	416.5	7.9
160°-170°	269.4	5.1
170°-180°	92.9	1.8
0°-30°	711.4	13.5
0°-40°	1130.0	21.4
0°-60°	1881.3	35.6
0°-90°	2277.5	43.1
90°-120°	651.2	12.3
90°-150°	2224.8	42.1
90°-180°	3004.0	56.9
0°-180°	5281.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	963	963	963	963	963	
5°	962	959	951	958	957	91
15°	915	910	895	894	888	258
25°	830	818	792	782	774	382
35°	714	697	664	643	633	447
45°	585	564	524	495	484	451
55°	444	420	380	347	335	397
65°	300	276	237	208	197	298
75°	160	138	108	92	87	169
85°	40	27	23	23	22	44
90°	1	6	12	15	17	4
95°	41	39	12	15	15	51
105°	213	216	216	216	215	226
115°	400	404	404	402	397	397
125°	569	574	574	571	569	508
135°	710	714	712	711	707	547
145°	823	824	824	825	820	515
155°	906	902	903	905	900	417
165°	956	952	952	957	951	270
175°	978	973	974	980	973	93
180°	978	978	978	978	978	

TEST NUMBER: P1034888

CATALOG NUMBER: S125RDIW-B610D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	963.3	963.3	963.3	963.3	963.3
2.5°	965.5	963.3	956.1	963.3	962.6
5°	961.9	959.0	951.0	958.2	956.8
7.5°	954.6	951.7	942.2	948.0	946.6
10°	943.7	941.5	931.3	933.5	931.3
12.5°	931.3	928.4	913.9	915.3	911.7
15°	914.6	910.2	894.9	894.2	887.7
17.5°	897.1	890.6	872.4	868.7	863.6
20°	876.0	868.7	845.5	841.8	835.3
22.5°	852.7	845.5	820.7	812.7	807.6
25°	829.5	818.5	791.6	782.2	774.2
27.5°	803.3	790.2	761.8	749.4	741.4
30°	774.2	760.3	729.8	713.0	706.5
32.5°	745.8	729.0	697.8	678.8	670.1
35°	714.5	697.0	664.3	643.2	633.0
37.5°	684.7	663.6	630.1	605.4	595.2
40°	652.6	630.8	595.9	568.2	559.5
42.5°	619.2	596.6	560.2	534.1	520.2
45°	585.0	563.9	523.9	494.8	483.8
47.5°	549.3	527.5	487.5	457.7	445.3
50°	515.9	491.8	450.4	419.8	408.9
52.5°	479.5	454.7	416.2	382.7	371.8
55°	443.8	420.5	379.8	347.1	335.4
57.5°	407.4	382.7	343.4	311.4	301.2
60°	372.5	347.1	307.8	275.8	264.8
62.5°	335.4	311.4	271.4	242.3	231.4
65°	300.5	275.8	237.2	208.1	197.2
67.5°	265.6	240.8	203.7	176.1	167.3
70°	229.9	205.2	168.8	146.2	137.5
72.5°	195.0	171.0	137.5	117.1	112.0
75°	160.1	138.2	107.7	91.7	86.6
77.5°	124.4	107.0	81.5	69.1	64.8
80°	94.6	77.1	56.8	50.2	48.7
82.5°	65.5	50.2	37.8	35.7	34.9
85°	40.0	26.9	23.3	22.6	21.8
87.5°	16.7	11.6	10.9	10.9	10.2
90°	0.7	6.5	11.6	15.2	17.4
92.5°	13.8	7.2	11.6	15.2	15.9
95°	41.3	39.1	11.6	15.2	15.2
97.5°	77.6	81.9	13.0	14.5	15.2
100°	121.0	123.2	126.1	18.1	15.2
102.5°	165.3	168.2	169.6	171.1	110.2
105°	213.1	216.0	216.0	216.0	215.3
107.5°	262.4	262.4	263.8	264.6	261.7
110°	310.2	310.2	311.7	309.5	310.2

TEST NUMBER: P1034888

CATALOG NUMBER: S125RDIW-B610D770UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.2	357.3	358.1	355.2	353.7
115°	400.1	403.7	404.5	401.6	397.2
117.5°	447.2	447.2	450.1	445.8	444.3
120°	490.7	490.0	492.2	490.7	487.1
122.5°	529.1	532.7	533.5	532.0	527.7
125°	569.0	574.1	574.1	571.2	569.0
127.5°	607.4	611.0	610.3	608.9	603.1
130°	642.2	645.8	646.5	644.4	640.7
132.5°	677.0	681.3	679.2	679.2	675.5
135°	709.6	713.9	712.5	711.1	706.7
137.5°	740.0	744.4	742.9	742.9	739.3
140°	769.8	771.2	770.5	771.9	767.6
142.5°	796.6	797.3	798.8	798.8	794.4
145°	822.7	824.1	824.1	824.8	820.5
147.5°	845.9	845.9	846.6	847.3	842.2
150°	867.6	866.2	867.6	869.1	863.3
152.5°	888.6	885.0	886.5	887.9	882.8
155°	906.0	901.7	903.1	905.3	899.5
157.5°	919.8	917.6	917.6	919.8	914.0
160°	934.3	929.9	930.7	933.6	927.8
162.5°	945.9	941.5	942.3	946.6	940.1
165°	956.0	951.7	952.4	956.8	951.0
167.5°	964.0	959.7	960.4	965.5	958.9
170°	970.5	965.5	966.2	972.0	965.5
172.5°	974.9	969.8	971.3	976.3	969.8
175°	977.8	973.4	974.2	980.0	973.4
177.5°	980.0	975.6	976.3	981.4	975.6
180°	977.8	977.8	977.8	977.8	977.8

(END OF REPORT)