

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034366

Luminaire Tested: S125DIW-B1090D470UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034366
REPORT IS A COMBINATION OF REPORTS P1002936 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D470UB2750-4F0-XX-W2A-D_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6136.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034366

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034366

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65		
1	100	95	91	87	94	90	86	82	79	76	73	69	67	65	60	59	57	53		
2	91	83	76	70	85	78	72	67	69	64	60	60	57	54	52	50	47	43		
3	83	72	65	58	77	68	61	55	60	55	50	53	49	45	46	43	40	36		
4	76	64	56	49	71	60	53	47	53	47	42	47	42	38	41	37	34	31		
5	69	57	48	42	65	54	46	40	48	41	37	42	37	33	37	33	30	27		
6	64	51	43	36	60	48	41	35	43	37	32	38	33	29	33	29	26	23		
7	59	46	38	32	55	44	36	31	39	33	28	35	29	26	31	26	23	21		
8	55	42	34	28	51	40	32	27	36	29	25	32	27	23	28	24	21	18		
9	51	38	31	25	48	36	29	24	33	27	22	29	24	20	26	22	19	16		
10	48	35	28	23	45	33	27	22	30	24	20	27	22	19	24	20	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8769	8769	8769
5°	8784	8585	8606
10°	8718	8411	8387
15°	8612	8207	8116
20°	8468	7961	7847
25°	8299	7699	7522
30°	8093	7414	7227
35°	7902	7150	6954
40°	7705	6873	6679
45°	7485	6633	6432
50°	7273	6372	6210
55°	7019	6122	5951
60°	6741	5839	5686
65°	6449	5541	5386
70°	6116	5140	5076
75°	5590	4744	4697
80°	4899	4264	4276
85°	4220	3880	4055

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7485 cd/sqm

TEST NUMBER: P1034366

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.5	2.1
10°-20°	367.7	6.0
20°-30°	546.7	8.9
30°-40°	647.5	10.6
40°-50°	669.4	10.9
50°-60°	616.7	10.0
60°-70°	498.5	8.1
70°-80°	333.6	5.4
80°-90°	173.3	2.8
90°-100°	118.1	1.9
100°-110°	210.8	3.4
110°-120°	298.7	4.9
120°-130°	349.0	5.7
130°-140°	358.0	5.8
140°-150°	327.2	5.3
150°-160°	262.8	4.3
160°-170°	170.0	2.8
170°-180°	58.6	1.0
0°-30°	1043.9	17.0
0°-40°	1691.5	27.6
0°-60°	2977.5	48.5
0°-90°	3982.9	64.9
90°-120°	627.5	10.2
90°-150°	1661.8	27.1
90°-180°	2153.0	35.1
0°-180°	6136.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1369	1369	1369	1369	1369	
5°	1369	1366	1357	1367	1366	130
15°	1307	1308	1299	1307	1302	368
25°	1188	1192	1184	1189	1182	547
35°	1028	1037	1033	1037	1037	643
45°	847	862	868	878	879	653
55°	651	672	694	708	714	582
65°	448	479	511	531	537	445
75°	247	282	325	352	358	262
85°	74	118	165	195	205	77
90°	22	68	117	150	161	16
95°	44	77	105	137	146	46
105°	147	170	210	237	246	155
115°	260	272	308	330	335	258
125°	364	366	393	413	418	325
135°	450	452	460	477	481	347
145°	520	520	520	527	530	325
155°	572	569	570	571	568	263
165°	603	600	601	604	600	170
175°	617	614	615	618	614	59
180°	617	617	617	617	617	

TEST NUMBER: P1034366

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1368.7	1368.7	1368.7	1368.7	1368.7
2.5°	1372.7	1370.0	1360.7	1370.0	1368.7
5°	1368.7	1366.0	1356.6	1367.4	1366.0
7.5°	1359.3	1358.0	1348.6	1358.0	1356.6
10°	1345.9	1345.9	1335.2	1344.5	1343.2
12.5°	1327.1	1328.4	1320.4	1327.1	1323.1
15°	1307.0	1308.3	1298.9	1307.0	1301.6
17.5°	1281.5	1284.2	1274.8	1281.5	1277.5
20°	1253.3	1256.0	1246.6	1250.6	1250.6
22.5°	1221.1	1226.5	1215.7	1221.1	1217.1
25°	1187.6	1191.6	1183.5	1188.9	1182.2
27.5°	1151.3	1156.7	1147.3	1151.3	1148.6
30°	1109.7	1117.8	1109.7	1112.4	1111.1
32.5°	1072.2	1078.9	1073.5	1076.2	1074.8
35°	1027.9	1037.3	1033.2	1037.3	1037.3
37.5°	984.9	993.0	991.6	997.0	995.7
40°	940.6	951.4	950.0	955.4	958.1
42.5°	892.3	907.1	911.1	917.8	917.8
45°	846.7	861.5	868.2	877.6	878.9
47.5°	799.8	813.2	823.9	837.3	840.0
50°	751.4	766.2	781.0	795.7	799.8
52.5°	700.5	719.2	738.0	754.1	756.8
55°	650.8	672.3	693.7	708.5	713.9
57.5°	599.8	625.3	649.5	665.6	669.6
60°	548.8	575.7	602.5	622.6	626.7
62.5°	499.2	526.0	555.5	578.3	583.7
65°	448.2	479.0	511.3	531.4	536.7
67.5°	401.2	430.7	462.9	487.1	493.8
70°	348.9	379.7	414.6	440.1	448.2
72.5°	297.9	330.1	369.0	397.2	402.6
75°	246.9	281.8	324.7	351.6	358.3
77.5°	197.3	237.5	277.8	307.3	312.7
80°	151.6	191.9	237.5	267.0	272.4
82.5°	110.0	153.0	199.9	228.1	238.9
85°	73.8	118.1	165.0	194.6	205.3
87.5°	47.0	89.9	135.5	166.4	175.8
90°	22.0	68.5	117.3	150.5	161.3
92.5°	27.5	62.3	112.0	143.8	153.7
95°	43.5	77.0	105.3	137.1	146.5
97.5°	65.0	100.0	100.8	129.9	139.8
100°	91.2	120.6	165.5	125.5	131.7
102.5°	117.7	145.0	187.5	215.2	184.9
105°	146.6	169.8	210.1	236.9	245.8
107.5°	176.3	195.1	234.9	262.2	268.4
110°	205.1	221.2	259.7	283.9	293.7



TEST NUMBER: P1034366

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	233.5	247.0	283.6	306.0	314.4
115°	260.5	272.1	307.5	329.9	335.1
117.5°	288.9	295.6	331.0	351.1	359.5
120°	316.3	319.9	352.1	374.0	379.8
122.5°	339.2	342.8	372.8	393.4	398.7
125°	364.4	366.2	393.1	412.7	418.0
127.5°	387.2	388.2	410.6	429.8	434.2
130°	409.2	410.2	429.4	446.9	451.3
132.5°	429.8	432.6	444.6	463.4	466.5
135°	450.4	451.8	460.3	476.8	480.8
137.5°	469.6	471.0	475.5	491.6	494.7
140°	487.0	487.9	488.8	504.5	507.1
142.5°	503.9	503.1	504.0	516.1	518.6
145°	520.4	520.0	520.0	527.1	529.8
147.5°	533.7	533.7	534.2	537.3	536.8
150°	547.4	546.5	547.4	548.3	546.0
152.5°	560.7	558.4	559.3	560.2	557.0
155°	571.7	568.9	569.8	571.2	567.5
157.5°	580.3	579.0	579.0	580.3	576.7
160°	589.5	586.7	587.2	589.0	585.4
162.5°	596.8	594.1	594.5	597.3	593.2
165°	603.2	600.5	600.9	603.7	600.0
167.5°	608.2	605.5	606.0	609.2	605.0
170°	612.4	609.2	609.6	613.3	609.2
172.5°	615.1	611.9	612.8	616.0	611.9
175°	616.9	614.2	614.6	618.3	614.2
177.5°	618.3	615.6	616.0	619.2	615.6
180°	616.9	616.9	616.9	616.9	616.9

(END OF REPORT)