

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034924

Luminaire Tested: S125RDIW-B850D470UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034924
REPORT IS A COMBINATION OF REPORTS P1006944 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B850D470UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4721.0 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 49.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034924

CATALOG NUMBER: S125RDIW-B850D470UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034924

CATALOG NUMBER: S125RDIW-B850D470UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	81	81	81	71	71	71	67		
1	102	97	94	90	96	92	89	86	82	79	77	72	70	69	64	62	61	57		
2	93	85	79	74	87	81	75	71	72	68	64	64	61	58	56	54	52	48		
3	85	75	68	62	80	71	65	59	64	59	54	57	53	49	50	47	44	41		
4	78	67	59	53	73	63	56	51	57	51	46	51	46	42	45	41	38	35		
5	72	60	52	46	67	57	49	44	51	45	40	46	41	37	41	37	34	31		
6	66	54	46	40	62	51	44	38	46	40	35	41	36	33	37	33	30	27		
7	61	49	41	35	58	46	39	34	42	36	31	38	33	29	34	30	27	24		
8	57	45	37	31	54	42	35	30	38	32	28	35	30	26	31	27	24	22		
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	29	25	22	20		
10	50	38	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8515	8515	8515
5°	8516	8303	8316
10°	8433	8094	8023
15°	8314	7801	7636
20°	8166	7448	7231
25°	7996	7104	6796
30°	7789	6726	6340
35°	7577	6342	5855
40°	7376	5948	5381
45°	7134	5521	4885
50°	6889	5069	4380
55°	6604	4625	3857
60°	6312	4115	3315
65°	5966	3546	2730
70°	5560	2887	2148
75°	4999	2171	1566
80°	4217	1406	1057
85°	3156	755	595

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7134 cd/sqm

TEST NUMBER: P1034924

CATALOG NUMBER: S125RDIW-B850D470UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.6
10°-20°	349.6	7.4
20°-30°	506.9	10.7
30°-40°	577.5	12.2
40°-50°	562.8	11.9
50°-60°	473.7	10.0
60°-70°	331.9	7.0
70°-80°	170.2	3.6
80°-90°	43.3	0.9
90°-100°	37.7	0.8
100°-110°	111.8	2.4
110°-120°	189.7	4.0
120°-130°	249.7	5.3
130°-140°	279.8	5.9
140°-150°	274.3	5.8
150°-160°	230.4	4.9
160°-170°	153.1	3.2
170°-180°	53.6	1.1
0°-30°	981.5	20.8
0°-40°	1559.0	33.0
0°-60°	2595.5	55.0
0°-90°	3140.9	66.5
90°-120°	339.2	7.2
90°-150°	1143.0	24.2
90°-180°	1580.0	33.5
0°-180°	4721.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1327	1323	1312	1322	1320	126
15°	1262	1256	1235	1234	1225	356
25°	1144	1129	1092	1079	1068	527
35°	986	962	916	887	873	617
45°	807	778	723	683	668	622
55°	612	580	524	479	463	548
65°	415	380	327	287	272	411
75°	221	191	149	126	120	233
85°	55	37	32	31	30	60
90°	0	4	7	9	11	5
95°	29	30	34	37	38	30
105°	100	103	105	108	109	107
115°	190	192	192	192	192	188
125°	277	280	280	279	279	248
135°	360	363	364	364	362	278
145°	437	438	440	440	438	273
155°	500	500	500	502	500	230
165°	543	542	543	545	542	153
175°	565	563	563	566	563	54
180°	566	566	566	566	566	

TEST NUMBER: P1034924

CATALOG NUMBER: S125RDIW-B850D470UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1329.0	1329.0	1329.0	1329.0	1329.0
2.5°	1332.0	1329.0	1319.0	1329.0	1328.0
5°	1327.0	1323.0	1312.0	1322.0	1320.0
7.5°	1317.0	1313.0	1299.9	1307.9	1305.9
10°	1301.9	1298.9	1284.9	1287.9	1284.9
12.5°	1284.9	1280.8	1260.8	1262.8	1257.8
15°	1261.8	1255.7	1234.7	1233.7	1224.6
17.5°	1237.7	1228.6	1203.5	1198.5	1191.5
20°	1208.6	1198.5	1166.4	1161.4	1152.4
22.5°	1176.4	1166.4	1132.3	1121.2	1114.2
25°	1144.3	1129.3	1092.1	1079.1	1068.0
27.5°	1108.2	1090.1	1051.0	1033.9	1022.9
30°	1068.0	1049.0	1006.8	983.7	974.7
32.5°	1028.9	1005.8	962.6	936.5	924.5
35°	985.7	961.6	916.5	887.4	873.3
37.5°	944.6	915.5	869.3	835.2	821.1
40°	900.4	870.3	822.1	784.0	771.9
42.5°	854.2	823.1	772.9	736.8	717.7
45°	807.0	777.9	722.7	682.6	667.5
47.5°	757.9	727.7	672.5	631.4	614.3
50°	711.7	678.6	621.3	579.2	564.1
52.5°	661.5	627.4	574.2	528.0	512.9
55°	612.3	580.2	524.0	478.8	462.7
57.5°	562.1	528.0	473.8	429.6	415.6
60°	513.9	478.8	424.6	380.4	365.4
62.5°	462.7	429.6	374.4	334.3	319.2
65°	414.6	380.4	327.2	287.1	272.0
67.5°	366.4	332.3	281.1	242.9	230.9
70°	317.2	283.1	232.9	201.8	189.7
72.5°	269.0	235.9	189.7	161.6	154.6
75°	220.8	190.7	148.6	126.5	119.5
77.5°	171.6	147.6	112.4	95.4	89.3
80°	130.5	106.4	78.3	69.3	67.3
82.5°	90.3	69.3	52.2	49.2	48.2
85°	55.2	37.1	32.1	31.1	30.1
87.5°	23.1	16.1	15.1	15.1	14.1
90°	0.4	4.0	7.0	9.3	10.6
92.5°	13.2	15.4	19.4	22.5	23.4
95°	28.6	29.5	33.9	37.0	37.9
97.5°	44.1	44.5	50.7	53.3	53.8
100°	61.7	61.7	67.4	71.4	72.3
102.5°	80.6	82.8	85.0	89.4	90.8
105°	100.5	102.7	105.3	107.9	109.3
107.5°	122.0	124.2	126.5	127.8	127.8
110°	144.5	146.7	148.0	149.4	148.9

TEST NUMBER: P1034924

CATALOG NUMBER: S125RDIW-B850D470UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	167.4	168.3	170.1	170.5	169.6
115°	189.9	191.7	192.5	192.1	191.7
117.5°	212.8	213.2	214.1	214.6	212.8
120°	234.0	236.2	236.6	236.6	234.8
122.5°	256.9	257.3	258.6	258.2	256.9
125°	277.1	279.8	280.2	279.3	278.9
127.5°	299.6	300.9	301.4	300.9	300.0
130°	319.4	321.6	322.5	322.1	321.2
132.5°	339.3	343.2	342.8	342.3	341.0
135°	360.4	363.1	363.5	363.5	361.7
137.5°	380.2	382.9	383.8	384.2	382.0
140°	399.2	401.4	402.7	403.6	401.4
142.5°	418.1	419.9	421.6	422.1	419.9
145°	436.6	438.4	439.7	439.7	438.4
147.5°	453.8	455.1	456.0	457.3	453.8
150°	471.0	470.6	472.3	472.3	471.4
152.5°	485.1	486.0	486.4	487.7	486.0
155°	499.6	499.6	500.1	501.8	499.6
157.5°	512.9	512.0	512.4	514.2	511.1
160°	524.3	523.0	523.4	525.2	523.0
162.5°	534.4	533.6	533.6	535.8	533.1
165°	543.3	542.4	542.8	544.6	541.9
167.5°	551.2	549.4	549.4	552.1	549.4
170°	557.4	555.6	555.6	558.2	555.1
172.5°	561.8	560.0	560.0	562.6	560.0
175°	564.8	563.1	563.1	565.7	562.6
177.5°	567.0	565.3	564.8	567.5	564.4
180°	566.2	566.2	566.2	566.2	566.2

(END OF REPORT)