

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034380

Luminaire Tested: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034380
REPORT IS A COMBINATION OF REPORTS P1003001 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_2700K
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7302.1 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034380

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034380

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	98	93	89	85	91	86	83	79	74	71	69	62	60	59	52	50	49
2	89	81	74	69	82	75	69	65	64	60	56	54	51	48	45	43	41
3	81	71	63	57	75	66	59	54	56	51	47	48	44	40	40	37	34
4	74	63	54	48	68	58	51	45	50	44	40	42	38	34	35	32	29
5	68	56	47	41	62	52	44	39	45	39	34	38	33	30	32	28	25
6	62	50	42	36	58	47	39	34	40	34	30	34	30	26	29	25	22
7	58	45	37	31	53	42	35	29	36	30	26	31	26	23	26	23	20
8	53	41	33	27	49	38	31	26	33	27	23	28	24	20	24	20	18
9	50	37	30	24	46	35	28	23	30	25	21	26	22	18	22	19	16
10	47	34	27	22	43	32	25	21	28	22	19	24	20	17	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8695	8695	8695
5°	8709	8513	8533
10°	8644	8339	8315
15°	8539	8137	8047
20°	8397	7893	7780
25°	8228	7634	7458
30°	8024	7351	7165
35°	7834	7090	6895
40°	7641	6815	6623
45°	7421	6576	6378
50°	7212	6317	6157
55°	6960	6071	5900
60°	6684	5790	5637
65°	6394	5493	5341
70°	6063	5096	5033
75°	5543	4705	4656
80°	4857	4228	4240
85°	4185	3847	4022

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7421 cd/sqm

TEST NUMBER: P1034380

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	1.8
10°-20°	364.6	5.0
20°-30°	542.1	7.4
30°-40°	642.0	8.8
40°-50°	663.7	9.1
50°-60°	611.4	8.4
60°-70°	494.3	6.8
70°-80°	330.7	4.5
80°-90°	172.4	2.4
90°-100°	130.5	1.8
100°-110°	298.5	4.1
110°-120°	457.2	6.3
120°-130°	552.8	7.6
130°-140°	577.4	7.9
140°-150°	533.2	7.3
150°-160°	429.4	5.9
160°-170°	277.7	3.8
170°-180°	95.8	1.3
0°-30°	1035.1	14.2
0°-40°	1677.1	23.0
0°-60°	2952.3	40.4
0°-90°	3949.7	54.1
90°-120°	886.2	12.1
90°-150°	2549.5	34.9
90°-180°	3352.0	45.9
0°-180°	7302.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1357	1357	1357	1357	1357	
5°	1357	1354	1345	1356	1354	129
15°	1296	1297	1288	1296	1291	365
25°	1178	1182	1174	1179	1172	542
35°	1019	1028	1024	1028	1028	638
45°	840	854	861	870	872	648
55°	645	667	688	702	708	577
65°	444	475	507	527	532	441
75°	245	279	322	349	355	259
85°	73	117	164	193	204	76
90°	22	71	121	155	167	17
95°	60	92	109	142	151	66
105°	232	256	296	322	331	245
115°	420	434	469	490	493	417
125°	592	596	622	641	645	528
135°	734	737	745	761	763	566
145°	849	850	850	857	858	531
155°	934	930	931	933	927	430
165°	986	981	982	986	980	278
175°	1008	1004	1004	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1034380

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1357.1	1357.1	1357.1	1357.1	1357.1
2.5°	1361.1	1358.4	1349.1	1358.4	1357.1
5°	1357.1	1354.4	1345.1	1355.8	1354.4
7.5°	1347.8	1346.4	1337.1	1346.4	1345.1
10°	1334.5	1334.5	1323.8	1333.1	1331.8
12.5°	1315.8	1317.2	1309.2	1315.8	1311.8
15°	1295.9	1297.2	1287.9	1295.9	1290.6
17.5°	1270.6	1273.3	1263.9	1270.6	1266.6
20°	1242.7	1245.3	1236.0	1240.0	1240.0
22.5°	1210.7	1216.1	1205.4	1210.7	1206.7
25°	1177.5	1181.5	1173.5	1178.8	1172.1
27.5°	1141.5	1146.9	1137.6	1141.5	1138.9
30°	1100.3	1108.3	1100.3	1103.0	1101.6
32.5°	1063.0	1069.7	1064.4	1067.0	1065.7
35°	1019.1	1028.5	1024.5	1028.5	1028.5
37.5°	976.6	984.5	983.2	988.5	987.2
40°	932.7	943.3	942.0	947.3	950.0
42.5°	884.8	899.4	903.4	910.0	910.0
45°	839.5	854.2	860.8	870.1	871.5
47.5°	793.0	806.3	816.9	830.2	832.9
50°	745.1	759.7	774.3	789.0	793.0
52.5°	694.5	713.1	731.8	747.7	750.4
55°	645.3	666.6	687.9	702.5	707.8
57.5°	594.7	620.0	643.9	659.9	663.9
60°	544.2	570.8	597.4	617.3	621.3
62.5°	494.9	521.5	550.8	573.4	578.8
65°	444.4	475.0	506.9	526.9	532.2
67.5°	397.8	427.1	459.0	483.0	489.6
70°	345.9	376.5	411.1	436.4	444.4
72.5°	295.4	327.3	365.9	393.8	399.1
75°	244.8	279.4	322.0	348.6	355.2
77.5°	195.6	235.5	275.4	304.7	310.0
80°	150.3	190.3	235.5	264.8	270.1
82.5°	109.1	151.7	198.2	226.2	236.8
85°	73.2	117.1	163.6	192.9	203.6
87.5°	46.6	89.1	134.4	165.0	174.3
90°	22.0	70.6	121.1	155.4	166.9
92.5°	32.8	64.7	115.8	148.7	158.8
95°	59.9	92.3	109.1	142.1	151.4
97.5°	96.0	132.3	105.3	134.6	144.8
100°	139.4	169.6	215.2	131.8	136.8
102.5°	183.7	212.0	254.7	282.8	228.0
105°	231.7	256.0	295.9	322.5	331.0
107.5°	281.1	299.8	339.9	367.2	372.2
110°	329.1	345.1	383.8	406.9	416.9

TEST NUMBER: P1034380

CATALOG NUMBER: S125DIW-B1090D770UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.5	389.7	426.3	447.4	455.2
115°	420.5	433.5	468.9	489.8	493.3
117.5°	467.8	474.4	510.6	528.8	536.6
120°	512.6	515.7	548.6	569.8	574.0
122.5°	550.8	555.9	585.9	605.7	609.2
125°	591.9	595.8	622.4	640.7	645.1
127.5°	630.2	632.6	654.5	672.9	674.9
130°	666.1	668.5	687.9	704.2	707.2
132.5°	700.6	705.1	716.2	734.8	736.3
135°	734.3	737.3	745.2	761.0	763.2
137.5°	765.6	768.7	772.6	788.5	790.1
140°	794.9	796.4	797.0	813.1	813.9
142.5°	822.5	822.0	823.5	835.5	836.3
145°	849.4	849.6	849.6	857.1	857.9
147.5°	872.0	872.0	872.8	876.2	873.6
150°	894.5	893.0	894.5	896.0	891.3
152.5°	916.1	912.4	913.9	915.4	910.2
155°	934.1	929.6	931.1	933.3	927.3
157.5°	948.3	946.0	946.0	948.3	942.3
160°	963.2	958.7	959.5	962.5	956.5
162.5°	975.2	970.7	971.4	975.9	969.2
165°	985.6	981.1	981.9	986.4	980.4
167.5°	993.8	989.4	990.1	995.3	988.6
170°	1000.6	995.3	996.1	1002.1	995.3
172.5°	1005.1	999.8	1001.3	1006.6	999.8
175°	1008.0	1003.6	1004.3	1010.3	1003.6
177.5°	1010.3	1005.8	1006.6	1011.8	1005.8
180°	1008.0	1008.0	1008.0	1008.0	1008.0

(END OF REPORT)