

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034960

Luminaire Tested: S125DIW-B1090D1050UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034960
REPORT IS A COMBINATION OF REPORTS P1002771 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D1050UB40-4F0-XX-W2A-D1
Description: Define 5 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7883.0 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034960

CATALOG NUMBER: S125DIW-B1090D1050UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1034960

CATALOG NUMBER: S125DIW-B1090D1050UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	82	78	72	69	67	60	58	56	49	47	46
2	88	80	74	68	81	74	69	64	63	59	55	52	49	46	42	40	38
3	80	70	63	57	74	65	58	53	55	50	46	46	42	39	37	35	32
4	73	62	54	48	67	57	50	45	49	43	39	41	37	33	33	30	28
5	67	55	47	41	62	51	44	38	44	38	33	36	32	29	30	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	28	25	27	24	21
7	57	45	36	31	52	41	34	29	35	30	25	30	25	22	25	21	19
8	53	40	33	27	49	38	31	26	32	27	23	27	23	20	23	19	17
9	49	37	29	24	45	34	28	23	30	24	20	25	21	18	21	17	15
10	46	34	26	22	42	32	25	20	27	22	18	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8720	8720	8720
5°	8734	8537	8558
10°	8669	8363	8339
15°	8563	8161	8070
20°	8420	7915	7802
25°	8251	7655	7480
30°	8047	7371	7186
35°	7857	7110	6914
40°	7662	6834	6641
45°	7442	6595	6396
50°	7232	6335	6174
55°	6979	6088	5917
60°	6702	5806	5653
65°	6412	5510	5356
70°	6081	5111	5046
75°	5559	4718	4669
80°	4873	4241	4253
85°	4197	3859	4032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7442 cd/sqm

TEST NUMBER: P1034960

CATALOG NUMBER: S125DIW-B1090D1050UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.8	1.6
10°-20°	365.6	4.6
20°-30°	543.6	6.9
30°-40°	643.8	8.2
40°-50°	665.6	8.4
50°-60°	613.2	7.8
60°-70°	495.7	6.3
70°-80°	331.7	4.2
80°-90°	173.5	2.2
90°-100°	183.9	2.3
100°-110°	330.6	4.2
110°-120°	487.6	6.2
120°-130°	606.2	7.7
130°-140°	660.8	8.4
140°-150°	638.5	8.1
150°-160°	534.4	6.8
160°-170°	355.2	4.5
170°-180°	124.3	1.6
0°-30°	1038.0	13.2
0°-40°	1681.9	21.3
0°-60°	2960.7	37.6
0°-90°	3961.5	50.3
90°-120°	1002.1	12.7
90°-150°	2907.6	36.9
90°-180°	3922.0	49.8
0°-180°	7883.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1361	1361	1361	1361	1361	
5°	1361	1358	1349	1360	1358	129
15°	1300	1301	1292	1300	1294	366
25°	1181	1185	1177	1182	1176	544
35°	1022	1031	1027	1031	1031	640
45°	842	857	863	873	874	650
55°	647	668	690	704	710	578
65°	446	476	508	528	534	442
75°	246	280	323	350	356	260
85°	73	117	164	194	204	77
90°	22	73	126	162	174	19
95°	84	120	176	213	224	83
105°	245	272	318	350	363	261
115°	448	462	499	522	529	444
125°	648	653	681	700	706	580
135°	839	843	854	871	874	646
145°	1014	1017	1020	1027	1029	634
155°	1159	1159	1160	1164	1159	534
165°	1260	1258	1259	1263	1257	356
175°	1310	1306	1306	1312	1305	125
180°	1313	1313	1313	1313	1313	

TEST NUMBER: P1034960

CATALOG NUMBER: S125DIW-B1090D1050UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1361.0	1361.0	1361.0	1361.0	1361.0
2.5°	1365.0	1362.3	1352.9	1362.3	1361.0
5°	1361.0	1358.3	1348.9	1359.6	1358.3
7.5°	1351.6	1350.3	1340.9	1350.3	1348.9
10°	1338.3	1338.3	1327.6	1336.9	1335.6
12.5°	1319.6	1320.9	1312.9	1319.6	1315.6
15°	1299.6	1300.9	1291.6	1299.6	1294.2
17.5°	1274.2	1276.9	1267.6	1274.2	1270.2
20°	1246.2	1248.9	1239.5	1243.5	1243.5
22.5°	1214.2	1219.5	1208.8	1214.2	1210.2
25°	1180.8	1184.8	1176.8	1182.2	1175.5
27.5°	1144.8	1150.1	1140.8	1144.8	1142.1
30°	1103.4	1111.4	1103.4	1106.1	1104.8
32.5°	1066.1	1072.8	1067.4	1070.1	1068.7
35°	1022.1	1031.4	1027.4	1031.4	1031.4
37.5°	979.4	987.4	986.0	991.4	990.0
40°	935.3	946.0	944.7	950.0	952.7
42.5°	887.3	902.0	906.0	912.6	912.6
45°	841.9	856.6	863.3	872.6	873.9
47.5°	795.2	808.6	819.2	832.6	835.3
50°	747.2	761.9	776.5	791.2	795.2
52.5°	696.5	715.2	733.8	749.9	752.5
55°	647.1	668.5	689.8	704.5	709.8
57.5°	596.4	621.8	645.8	661.8	665.8
60°	545.7	572.4	599.1	619.1	623.1
62.5°	496.3	523.0	552.4	575.1	580.4
65°	445.6	476.3	508.4	528.4	533.7
67.5°	398.9	428.3	460.3	484.3	491.0
70°	346.9	377.6	412.3	437.6	445.6
72.5°	296.2	328.2	366.9	394.9	400.3
75°	245.5	280.2	322.9	349.6	356.2
77.5°	196.1	236.2	276.2	305.5	310.9
80°	150.8	190.8	236.2	265.5	270.9
82.5°	109.4	152.1	198.8	226.8	237.5
85°	73.4	117.4	164.1	193.5	204.1
87.5°	46.7	89.4	134.8	165.4	174.8
90°	22.3	73.2	125.8	161.6	173.9
92.5°	49.4	93.2	149.1	185.5	197.0
95°	83.7	120.5	176.1	212.6	224.0
97.5°	118.2	151.2	209.6	243.8	254.1
100°	157.8	185.8	241.8	279.0	289.0
102.5°	200.3	230.8	277.3	314.2	325.2
105°	245.0	271.5	317.6	350.5	362.8
107.5°	293.8	317.6	361.3	391.1	399.1
110°	344.5	365.7	406.1	434.5	442.8



TEST NUMBER: P1034960

CATALOG NUMBER: S125DIW-B1090D1050UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	397.6	411.7	451.9	476.9	484.1
115°	448.4	461.8	498.6	521.7	528.6
117.5°	500.3	507.9	543.4	567.1	572.3
120°	549.3	558.5	590.2	612.8	616.8
122.5°	601.1	603.5	635.9	656.2	661.2
125°	648.1	652.9	680.6	699.9	705.6
127.5°	698.9	700.7	724.4	743.4	749.3
130°	744.9	748.7	769.3	787.0	791.7
132.5°	789.6	798.8	811.1	828.7	831.0
135°	838.6	843.4	853.8	871.1	873.7
137.5°	884.6	889.4	896.8	913.8	914.0
140°	927.2	932.3	936.7	953.4	953.7
142.5°	971.1	973.9	978.0	991.0	991.2
145°	1014.0	1016.8	1019.9	1026.6	1028.8
147.5°	1052.6	1055.6	1057.7	1063.5	1057.9
150°	1092.4	1091.4	1095.5	1095.5	1094.8
152.5°	1125.1	1127.2	1128.2	1131.3	1127.2
155°	1158.9	1158.9	1159.9	1164.0	1158.9
157.5°	1189.5	1187.5	1188.5	1192.6	1185.4
160°	1216.1	1213.0	1214.0	1218.1	1213.0
162.5°	1239.6	1237.5	1237.5	1242.7	1236.5
165°	1260.0	1258.0	1259.0	1263.1	1257.0
167.5°	1278.4	1274.3	1274.3	1280.5	1274.3
170°	1292.7	1288.6	1288.6	1294.8	1287.6
172.5°	1303.0	1298.9	1298.9	1305.0	1298.9
175°	1310.1	1306.0	1306.0	1312.1	1305.0
177.5°	1315.2	1311.1	1310.1	1316.2	1309.1
180°	1313.2	1313.2	1313.2	1313.2	1313.2

(END OF REPORT)