

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034491

Luminaire Tested: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034491
REPORT IS A COMBINATION OF REPORTS P1003471 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6850.0 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034491

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034491

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25
2	83	76	70	65	73	68	63	59	52	48	46	37	35	33	23	22	21
3	76	67	60	54	67	59	54	49	45	41	38	33	30	28	21	19	18
4	69	59	51	46	61	52	46	41	40	36	32	29	26	24	18	17	15
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	16	15	13
6	58	47	39	33	51	42	35	30	32	27	24	23	20	18	15	13	12
7	54	42	34	29	47	38	31	26	29	24	21	21	18	16	14	12	10
8	50	38	31	26	44	34	28	23	26	22	18	19	16	14	12	11	9
9	46	34	27	23	41	31	25	20	24	20	16	18	15	12	11	10	8
10	43	31	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3070 cd/sqm

TEST NUMBER: P1034491

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	0.8
10°-20°	151.6	2.2
20°-30°	223.8	3.3
30°-40°	261.1	3.8
40°-50°	262.2	3.8
50°-60°	230.2	3.4
60°-70°	171.4	2.5
70°-80°	97.9	1.4
80°-90°	30.9	0.5
90°-100°	59.3	0.9
100°-110°	394.4	5.8
110°-120°	710.2	10.4
120°-130°	911.5	13.3
130°-140°	980.4	14.3
140°-150°	920.1	13.4
150°-160°	744.3	10.9
160°-170°	481.3	7.0
170°-180°	166.0	2.4
0°-30°	429.0	6.3
0°-40°	690.0	10.1
0°-60°	1182.4	17.3
0°-90°	1482.6	21.6
90°-120°	1163.8	17.0
90°-150°	3975.8	58.0
90°-180°	5367.0	78.4
0°-180°	6850.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	1	12	21	27	31	5
95°	74	70	21	27	27	90
105°	381	386	386	386	385	403
115°	715	722	723	718	710	709
125°	1017	1026	1026	1021	1017	908
135°	1268	1276	1273	1271	1263	978
145°	1470	1473	1473	1474	1466	919
155°	1619	1611	1614	1618	1607	746
165°	1708	1701	1702	1710	1699	483
175°	1747	1740	1741	1751	1740	166
180°	1747	1747	1747	1747	1747	

TEST NUMBER: P1034491

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	1.3	11.7	20.7	27.2	31.1
92.5°	24.6	13.0	20.7	27.2	28.5
95°	73.8	69.9	20.7	27.2	27.2
97.5°	138.6	146.4	23.3	25.9	27.2
100°	216.3	220.2	225.4	32.4	27.2
102.5°	295.3	300.5	303.1	305.7	196.9
105°	380.8	386.0	386.0	386.0	384.7
107.5°	468.9	468.9	471.5	472.8	467.6
110°	554.4	554.4	557.0	553.1	554.4

TEST NUMBER: P1034491

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	634.7	638.6	639.9	634.7	632.1
115°	715.0	721.5	722.8	717.6	709.8
117.5°	799.2	799.2	804.4	796.6	794.0
120°	876.9	875.6	879.5	876.9	870.4
122.5°	945.5	952.0	953.3	950.7	943.0
125°	1016.8	1025.9	1025.9	1020.7	1016.8
127.5°	1085.4	1091.9	1090.6	1088.0	1077.7
130°	1147.6	1154.1	1155.4	1151.5	1145.0
132.5°	1209.8	1217.6	1213.7	1213.7	1207.2
135°	1268.1	1275.8	1273.3	1270.7	1262.9
137.5°	1322.5	1330.2	1327.7	1327.7	1321.2
140°	1375.6	1378.2	1376.9	1379.5	1371.7
142.5°	1423.5	1424.8	1427.4	1427.4	1419.6
145°	1470.1	1472.7	1472.7	1474.0	1466.2
147.5°	1511.6	1511.6	1512.9	1514.2	1505.1
150°	1550.4	1547.9	1550.4	1553.0	1542.7
152.5°	1588.0	1581.5	1584.1	1586.7	1577.6
155°	1619.1	1611.3	1613.9	1617.8	1607.4
157.5°	1643.7	1639.8	1639.8	1643.7	1633.3
160°	1669.6	1661.8	1663.1	1668.3	1657.9
162.5°	1690.3	1682.6	1683.9	1691.6	1680.0
165°	1708.5	1700.7	1702.0	1709.8	1699.4
167.5°	1722.7	1714.9	1716.2	1725.3	1713.6
170°	1734.4	1725.3	1726.6	1737.0	1725.3
172.5°	1742.1	1733.1	1735.7	1744.7	1733.1
175°	1747.3	1739.6	1740.8	1751.2	1739.6
177.5°	1751.2	1743.4	1744.7	1753.8	1743.4
180°	1747.3	1747.3	1747.3	1747.3	1747.3

(END OF REPORT)