

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034492

Luminaire Tested: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034492
REPORT IS A COMBINATION OF REPORTS P1003472 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6879.0 lumens
Efficiency: N/A
Efficacy: 124.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034492

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034492

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30			22
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25			18
2	83	76	70	65	73	68	63	59	52	48	46	37	35	33	23	22	21			15
3	76	67	60	54	67	59	54	49	45	41	38	33	30	28	21	19	18			13
4	69	59	51	46	61	52	46	41	40	36	32	29	26	24	18	17	15			11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	16	15	13			10
6	58	47	39	33	51	42	35	30	32	27	24	23	20	18	15	13	12			8
7	54	42	34	29	47	38	31	26	29	24	21	21	18	16	14	12	10			7
8	50	38	31	26	44	34	28	23	26	22	18	19	16	14	12	11	9			7
9	46	34	27	23	41	31	25	20	24	20	16	18	15	12	11	10	8			6
10	43	31	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8			5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3658	3658	3658
5°	3658	3573	3580
10°	3628	3491	3480
15°	3580	3393	3363
20°	3516	3280	3228
25°	3446	3156	3084
30°	3364	3026	2932
35°	3274	2891	2761
40°	3183	2748	2610
45°	3083	2609	2450
50°	2973	2451	2262
55°	2865	2276	2090
60°	2735	2092	1889
65°	2580	1879	1682
70°	2423	1635	1443
75°	2158	1346	1167
80°	1839	1005	859
85°	1418	595	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3083 cd/sqm

TEST NUMBER: P1034492

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	0.8
10°-20°	152.2	2.2
20°-30°	224.7	3.3
30°-40°	262.1	3.8
40°-50°	263.3	3.8
50°-60°	231.1	3.4
60°-70°	172.1	2.5
70°-80°	98.3	1.4
80°-90°	31.0	0.5
90°-100°	59.5	0.9
100°-110°	396.0	5.8
110°-120°	713.2	10.4
120°-130°	915.4	13.3
130°-140°	984.6	14.3
140°-150°	924.1	13.4
150°-160°	747.5	10.9
160°-170°	483.4	7.0
170°-180°	166.7	2.4
0°-30°	430.7	6.3
0°-40°	692.8	10.1
0°-60°	1187.2	17.3
0°-90°	1488.6	21.6
90°-120°	1168.8	17.0
90°-150°	3992.8	58.0
90°-180°	5390.0	78.4
0°-180°	6879.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	571	571	571	571	571	
5°	570	569	565	569	568	54
15°	543	542	537	539	539	153
25°	493	491	485	486	485	227
35°	426	424	418	416	412	266
45°	349	347	342	336	335	269
55°	266	264	258	254	251	237
65°	179	178	173	169	168	178
75°	95	94	92	91	89	101
85°	25	25	25	25	24	27
90°	1	12	21	27	31	5
95°	74	70	21	27	27	91
105°	382	388	388	388	386	405
115°	718	725	726	721	713	712
125°	1021	1030	1030	1025	1021	912
135°	1274	1281	1279	1276	1268	982
145°	1476	1479	1479	1480	1472	923
155°	1626	1618	1621	1625	1614	749
165°	1716	1708	1709	1717	1707	485
175°	1755	1747	1748	1759	1747	167
180°	1755	1755	1755	1755	1755	

TEST NUMBER: P1034492

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.9	570.9	570.9	570.9	570.9
2.5°	572.7	571.4	566.9	571.4	570.9
5°	570.0	569.1	564.6	568.7	568.2
7.5°	566.0	565.1	560.1	564.2	563.7
10°	560.1	559.2	554.2	557.8	557.4
12.5°	552.9	551.1	546.5	549.3	549.3
15°	543.4	542.0	537.1	539.3	539.3
17.5°	533.4	531.2	526.2	528.9	526.7
20°	520.3	519.4	513.6	516.7	514.5
22.5°	507.2	505.4	500.0	501.8	500.5
25°	493.2	491.0	485.1	486.0	484.7
27.5°	477.0	475.6	469.8	470.2	468.9
30°	461.2	459.8	453.0	452.1	450.8
32.5°	444.0	441.8	435.9	434.1	431.4
35°	425.9	424.1	417.8	415.6	411.9
37.5°	407.4	405.2	399.3	396.1	393.9
40°	388.5	386.2	379.9	375.8	374.4
42.5°	368.1	366.3	360.0	356.4	354.1
45°	348.7	346.9	341.5	336.1	334.7
47.5°	327.5	327.9	321.2	315.7	312.6
50°	307.1	305.8	300.4	294.5	291.3
52.5°	286.4	285.5	279.6	274.6	271.0
55°	265.6	264.2	257.9	253.8	250.7
57.5°	243.5	243.0	237.6	232.2	230.8
60°	222.7	220.9	215.9	211.4	208.2
62.5°	201.0	199.6	195.6	190.6	188.4
65°	179.3	178.4	173.4	169.4	167.6
67.5°	158.1	156.3	152.7	149.1	148.2
70°	138.2	136.0	131.9	129.2	127.4
72.5°	116.5	115.2	112.9	109.8	108.0
75°	95.3	94.4	92.1	90.8	89.0
77.5°	75.4	75.0	73.6	72.7	71.4
80°	56.9	56.9	56.0	55.6	54.7
82.5°	40.7	39.7	39.7	38.8	38.8
85°	24.8	25.3	25.3	24.8	23.9
87.5°	12.2	12.2	11.7	11.7	10.8
90°	1.3	11.7	20.8	27.3	31.2
92.5°	24.7	13.0	20.8	27.3	28.6
95°	74.1	70.2	20.8	27.3	27.3
97.5°	139.2	147.0	23.4	26.0	27.3
100°	217.2	221.1	226.3	32.5	27.3
102.5°	296.6	301.8	304.4	307.0	197.7
105°	382.4	387.6	387.6	387.6	386.3
107.5°	470.9	470.9	473.5	474.8	469.6
110°	556.8	556.8	559.4	555.5	556.8

TEST NUMBER: P1034492

CATALOG NUMBER: S125DIW-B375D1340UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	637.4	641.3	642.6	637.4	634.8
115°	718.1	724.6	725.9	720.7	712.8
117.5°	802.6	802.6	807.8	800.0	797.4
120°	880.7	879.4	883.3	880.7	874.2
122.5°	949.6	956.1	957.4	954.8	947.0
125°	1021.1	1030.3	1030.3	1025.0	1021.1
127.5°	1090.1	1096.6	1095.3	1092.7	1082.3
130°	1152.5	1159.0	1160.3	1156.4	1149.9
132.5°	1215.0	1222.8	1218.9	1218.9	1212.4
135°	1273.5	1281.3	1278.7	1276.1	1268.3
137.5°	1328.1	1335.9	1333.3	1333.3	1326.8
140°	1381.5	1384.1	1382.8	1385.4	1377.6
142.5°	1429.6	1430.9	1433.5	1433.5	1425.7
145°	1476.4	1479.0	1479.0	1480.3	1472.5
147.5°	1518.1	1518.1	1519.4	1520.7	1511.6
150°	1557.1	1554.5	1557.1	1559.7	1549.3
152.5°	1594.8	1588.3	1590.9	1593.5	1584.4
155°	1626.0	1618.2	1620.8	1624.7	1614.3
157.5°	1650.7	1646.8	1646.8	1650.7	1640.3
160°	1676.8	1669.0	1670.3	1675.5	1665.1
162.5°	1697.6	1689.8	1691.1	1698.9	1687.2
165°	1715.8	1708.0	1709.3	1717.1	1706.7
167.5°	1730.1	1722.3	1723.6	1732.7	1721.0
170°	1741.8	1732.7	1734.0	1744.4	1732.7
172.5°	1749.6	1740.5	1743.1	1752.2	1740.5
175°	1754.8	1747.0	1748.3	1758.7	1747.0
177.5°	1758.7	1750.9	1752.2	1761.3	1750.9
180°	1754.8	1754.8	1754.8	1754.8	1754.8

(END OF REPORT)