

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034505

Luminaire Tested: S125DIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034505
REPORT IS A COMBINATION OF REPORTS P1003536 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D1560UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7745.0 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034505

CATALOG NUMBER: S125DIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034505

CATALOG NUMBER: S125DIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19		
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16		
2	83	76	70	65	73	67	62	58	50	47	45	35	33	32	21	20	19	13		
3	75	66	59	54	66	59	53	48	44	41	37	31	29	27	19	18	17	11		
4	69	59	51	45	60	52	46	41	39	35	32	28	25	23	17	15	14	10		
5	63	52	44	39	55	46	40	35	35	31	27	25	22	20	15	14	12	8		
6	58	46	39	33	51	41	35	30	31	27	23	22	19	17	14	12	11	7		
7	53	42	34	29	47	37	31	26	28	24	20	20	17	15	12	11	10	7		
8	49	38	30	25	43	34	27	23	26	21	18	18	15	13	11	10	9	6		
9	46	34	27	22	40	30	24	20	23	19	16	17	14	12	10	9	8	5		
10	43	31	24	20	38	28	22	18	21	17	14	15	13	11	10	8	7	5		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3611	3611	3611
5°	3611	3528	3534
10°	3581	3446	3436
15°	3534	3350	3320
20°	3471	3238	3187
25°	3402	3115	3045
30°	3321	2988	2894
35°	3232	2855	2726
40°	3142	2713	2577
45°	3043	2575	2418
50°	2935	2419	2233
55°	2828	2247	2063
60°	2700	2065	1865
65°	2547	1855	1660
70°	2391	1614	1424
75°	2131	1330	1151
80°	1816	993	848
85°	1401	588	466

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3043 cd/sqm

TEST NUMBER: P1034505

CATALOG NUMBER: S125DIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.2	0.7
10°-20°	150.2	1.9
20°-30°	221.8	2.9
30°-40°	258.8	3.3
40°-50°	259.9	3.4
50°-60°	228.1	2.9
60°-70°	169.9	2.2
70°-80°	97.1	1.3
80°-90°	31.0	0.4
90°-100°	69.3	0.9
100°-110°	461.0	6.0
110°-120°	830.2	10.7
120°-130°	1065.6	13.8
130°-140°	1146.1	14.8
140°-150°	1075.7	13.9
150°-160°	870.1	11.2
160°-170°	562.7	7.3
170°-180°	194.1	2.5
0°-30°	425.2	5.5
0°-40°	684.0	8.8
0°-60°	1172.0	15.1
0°-90°	1470.0	19.0
90°-120°	1360.6	17.6
90°-150°	4648.1	60.0
90°-180°	6275.0	81.0
0°-180°	7745.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	564	564	564	564	564	
5°	563	562	557	561	561	53
15°	536	535	530	532	532	151
25°	487	485	479	480	478	224
35°	420	419	412	410	407	263
45°	344	342	337	332	330	265
55°	262	261	255	251	248	234
65°	177	176	171	167	165	176
75°	94	93	91	90	88	100
85°	24	25	25	24	24	27
90°	2	14	24	32	36	6
95°	86	82	24	32	32	106
105°	445	451	451	451	450	472
115°	836	844	845	839	830	829
125°	1189	1199	1199	1193	1189	1062
135°	1482	1492	1488	1486	1476	1143
145°	1719	1722	1722	1723	1714	1075
155°	1893	1884	1887	1891	1879	872
165°	1997	1988	1990	1999	1987	564
175°	2043	2034	2035	2047	2034	195
180°	2043	2043	2043	2043	2043	

TEST NUMBER: P1034505

CATALOG NUMBER: S125DIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	563.6	563.6	563.6	563.6	563.6
2.5°	565.4	564.1	559.6	564.1	563.6
5°	562.7	561.9	557.4	561.4	561.0
7.5°	558.7	557.8	552.9	556.9	556.5
10°	552.9	552.0	547.1	550.7	550.3
12.5°	545.8	544.0	539.6	542.2	542.2
15°	536.4	535.1	530.2	532.4	532.4
17.5°	526.6	524.4	519.5	522.2	519.9
20°	513.7	512.8	507.0	510.1	507.9
22.5°	500.8	499.0	493.6	495.4	494.1
25°	486.9	484.7	478.9	479.8	478.5
27.5°	470.9	469.5	463.7	464.2	462.9
30°	455.3	453.9	447.3	446.4	445.0
32.5°	438.3	436.1	430.3	428.5	425.8
35°	420.5	418.7	412.5	410.2	406.7
37.5°	402.2	400.0	394.2	391.1	388.8
40°	383.5	381.3	375.0	371.0	369.7
42.5°	363.4	361.6	355.4	351.8	349.6
45°	344.2	342.5	337.1	331.8	330.4
47.5°	323.3	323.7	317.0	311.7	308.6
50°	303.2	301.9	296.5	290.7	287.6
52.5°	282.7	281.8	276.0	271.1	267.5
55°	262.2	260.9	254.6	250.6	247.5
57.5°	240.3	239.9	234.6	229.2	227.9
60°	219.8	218.1	213.1	208.7	205.6
62.5°	198.4	197.1	193.1	188.2	185.9
65°	177.0	176.1	171.2	167.2	165.4
67.5°	156.1	154.3	150.7	147.2	146.3
70°	136.4	134.2	130.2	127.5	125.7
72.5°	115.0	113.7	111.5	108.4	106.6
75°	94.1	93.2	91.0	89.6	87.8
77.5°	74.5	74.0	72.7	71.8	70.5
80°	56.2	56.2	55.3	54.8	54.0
82.5°	40.1	39.2	39.2	38.3	38.3
85°	24.5	25.0	25.0	24.5	23.6
87.5°	12.0	12.0	11.6	11.6	10.7
90°	1.5	13.6	24.2	31.8	36.3
92.5°	28.8	15.1	24.2	31.8	33.3
95°	86.3	81.8	24.2	31.8	31.8
97.5°	162.0	171.1	27.3	30.3	31.8
100°	252.9	257.4	263.5	37.9	31.8
102.5°	345.3	351.3	354.3	357.4	230.2
105°	445.2	451.3	451.3	451.3	449.7
107.5°	548.2	548.2	551.2	552.7	546.7
110°	648.1	648.1	651.1	646.6	648.1

TEST NUMBER: P1034505

CATALOG NUMBER: S125DIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	742.0	746.5	748.1	742.0	739.0
115°	835.9	843.5	845.0	838.9	829.8
117.5°	934.3	934.3	940.4	931.3	928.3
120°	1025.2	1023.7	1028.2	1025.2	1017.6
122.5°	1105.4	1113.0	1114.5	1111.5	1102.4
125°	1188.7	1199.3	1199.3	1193.3	1188.7
127.5°	1269.0	1276.5	1275.0	1272.0	1259.9
130°	1341.7	1349.2	1350.7	1346.2	1338.6
132.5°	1414.3	1423.4	1418.9	1418.9	1411.3
135°	1482.5	1491.6	1488.5	1485.5	1476.4
137.5°	1546.1	1555.2	1552.1	1552.1	1544.6
140°	1608.2	1611.2	1609.7	1612.7	1603.6
142.5°	1664.2	1665.7	1668.7	1668.7	1659.7
145°	1718.7	1721.7	1721.7	1723.3	1714.2
147.5°	1767.2	1767.2	1768.7	1770.2	1759.6
150°	1812.6	1809.6	1812.6	1815.6	1803.5
152.5°	1856.5	1848.9	1852.0	1855.0	1844.4
155°	1892.9	1883.8	1886.8	1891.3	1879.2
157.5°	1921.6	1917.1	1917.1	1921.6	1909.5
160°	1951.9	1942.8	1944.3	1950.4	1938.3
162.5°	1976.1	1967.1	1968.6	1977.7	1964.0
165°	1997.3	1988.3	1989.8	1998.9	1986.7
167.5°	2014.0	2004.9	2006.4	2017.0	2003.4
170°	2027.6	2017.0	2018.5	2030.7	2017.0
172.5°	2036.7	2026.1	2029.1	2039.7	2026.1
175°	2042.8	2033.7	2035.2	2047.3	2033.7
177.5°	2047.3	2038.2	2039.7	2050.3	2038.2
180°	2042.8	2042.8	2042.8	2042.8	2042.8

(END OF REPORT)