

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034523

Luminaire Tested: S125DIW-B375D470UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034523
REPORT IS A COMBINATION OF REPORTS P1003606 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D470UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3246.0 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034523

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034523

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50
1	96	92	88	85	88	84	81	78	70	68	65	57	55	54	45	43	43
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	36
3	80	71	63	57	73	65	59	53	54	49	45	44	41	38	35	32	30
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26
5	67	56	47	42	61	51	44	39	43	37	33	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3503	3503	3503
5°	3503	3422	3428
10°	3474	3343	3333
15°	3428	3249	3221
20°	3367	3141	3091
25°	3300	3022	2953
30°	3221	2898	2808
35°	3136	2769	2645
40°	3047	2632	2500
45°	2952	2498	2346
50°	2847	2346	2166
55°	2743	2180	2001
60°	2619	2004	1809
65°	2471	1800	1611
70°	2321	1566	1382
75°	2067	1289	1117
80°	1761	962	821
85°	1361	569	452

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2952 cd/sqm

TEST NUMBER: P1034523

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.6	1.6
10°-20°	145.7	4.5
20°-30°	215.1	6.6
30°-40°	251.0	7.7
40°-50°	252.1	7.8
50°-60°	221.3	6.8
60°-70°	164.8	5.1
70°-80°	94.1	2.9
80°-90°	28.1	0.9
90°-100°	20.1	0.6
100°-110°	133.9	4.1
110°-120°	241.1	7.4
120°-130°	309.4	9.5
130°-140°	332.8	10.3
140°-150°	312.4	9.6
150°-160°	252.7	7.8
160°-170°	163.4	5.0
170°-180°	56.4	1.7
0°-30°	412.5	12.7
0°-40°	663.5	20.4
0°-60°	1136.8	35.0
0°-90°	1423.9	43.9
90°-120°	395.1	12.2
90°-150°	1349.7	41.6
90°-180°	1822.0	56.1
0°-180°	3246.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	547	547	547	547	547	
5°	546	545	541	545	544	52
15°	520	519	514	516	516	147
25°	472	470	464	465	464	217
35°	408	406	400	398	394	255
45°	334	332	327	322	320	257
55°	254	253	247	243	240	227
65°	172	171	166	162	160	170
75°	91	90	88	87	85	97
85°	24	24	24	24	23	26
90°	0	4	7	9	11	3
95°	25	24	7	9	9	31
105°	129	131	131	131	131	137
115°	243	245	245	244	241	241
125°	345	348	348	346	345	308
135°	430	433	432	431	429	332
145°	499	500	500	500	498	312
155°	550	547	548	549	546	253
165°	580	577	578	580	577	164
175°	593	590	591	594	590	56
180°	593	593	593	593	593	

TEST NUMBER: P1034523

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	546.7	546.7	546.7	546.7	546.7
2.5°	548.5	547.2	542.8	547.2	546.7
5°	545.9	545.0	540.7	544.6	544.1
7.5°	542.0	541.1	536.3	540.2	539.8
10°	536.3	535.5	530.7	534.2	533.8
12.5°	529.4	527.7	523.4	526.0	526.0
15°	520.3	519.0	514.3	516.5	516.5
17.5°	510.8	508.7	503.9	506.5	504.3
20°	498.3	497.4	491.8	494.8	492.7
22.5°	485.7	484.0	478.8	480.6	479.3
25°	472.3	470.2	464.5	465.4	464.1
27.5°	456.8	455.5	449.8	450.3	449.0
30°	441.6	440.3	433.8	433.0	431.7
32.5°	425.2	423.0	417.4	415.7	413.1
35°	407.9	406.2	400.1	397.9	394.5
37.5°	390.1	388.0	382.4	379.3	377.2
40°	372.0	369.8	363.8	359.9	358.6
42.5°	352.5	350.8	344.7	341.3	339.1
45°	333.9	332.2	327.0	321.8	320.5
47.5°	313.6	314.0	307.5	302.3	299.3
50°	294.1	292.8	287.6	282.0	279.0
52.5°	274.2	273.4	267.7	263.0	259.5
55°	254.3	253.0	247.0	243.1	240.1
57.5°	233.1	232.7	227.5	222.3	221.0
60°	213.2	211.5	206.8	202.4	199.4
62.5°	192.5	191.2	187.3	182.5	180.4
65°	171.7	170.9	166.1	162.2	160.5
67.5°	151.4	149.7	146.2	142.7	141.9
70°	132.4	130.2	126.3	123.7	122.0
72.5°	111.6	110.3	108.1	105.1	103.4
75°	91.3	90.4	88.2	86.9	85.2
77.5°	72.2	71.8	70.5	69.6	68.3
80°	54.5	54.5	53.6	53.2	52.3
82.5°	38.9	38.1	38.1	37.2	37.2
85°	23.8	24.2	24.2	23.8	22.9
87.5°	11.7	11.7	11.2	11.2	10.4
90°	0.4	4.0	7.0	9.2	10.6
92.5°	8.4	4.4	7.0	9.2	9.7
95°	25.1	23.7	7.0	9.2	9.2
97.5°	47.0	49.7	7.9	8.8	9.2
100°	73.4	74.8	76.5	11.0	9.2
102.5°	100.3	102.0	102.9	103.8	66.8
105°	129.3	131.0	131.0	131.0	130.6
107.5°	159.2	159.2	160.1	160.5	158.7
110°	188.2	188.2	189.1	187.8	188.2



TEST NUMBER: P1034523

CATALOG NUMBER: S125DIW-B375D470UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.5	216.8	217.2	215.5	214.6
115°	242.7	244.9	245.4	243.6	241.0
117.5°	271.3	271.3	273.1	270.4	269.5
120°	297.7	297.2	298.6	297.7	295.5
122.5°	321.0	323.2	323.6	322.8	320.1
125°	345.2	348.3	348.3	346.5	345.2
127.5°	368.5	370.7	370.2	369.4	365.8
130°	389.6	391.8	392.2	390.9	388.7
132.5°	410.7	413.3	412.0	412.0	409.8
135°	430.5	433.1	432.2	431.4	428.7
137.5°	449.0	451.6	450.7	450.7	448.5
140°	467.0	467.9	467.4	468.3	465.7
142.5°	483.2	483.7	484.6	484.6	481.9
145°	499.1	500.0	500.0	500.4	497.8
147.5°	513.2	513.2	513.6	514.0	511.0
150°	526.3	525.5	526.3	527.2	523.7
152.5°	539.1	536.9	537.8	538.7	535.6
155°	549.6	547.0	547.9	549.2	545.7
157.5°	558.0	556.7	556.7	558.0	554.5
160°	566.8	564.2	564.6	566.4	562.8
162.5°	573.8	571.2	571.6	574.3	570.3
165°	580.0	577.3	577.8	580.4	576.9
167.5°	584.8	582.2	582.6	585.7	581.7
170°	588.8	585.7	586.1	589.7	585.7
172.5°	591.4	588.3	589.2	592.3	588.3
175°	593.2	590.5	591.0	594.5	590.5
177.5°	594.5	591.9	592.3	595.4	591.9
180°	593.2	593.2	593.2	593.2	593.2

(END OF REPORT)