

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034536

Luminaire Tested: S125DIW-B375D770UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034536
REPORT IS A COMBINATION OF REPORTS P1003669 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D770UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4605.0 lumens
Efficiency: N/A
Efficacy: 127.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034536

CATALOG NUMBER: S125DIW-B375D770UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034536

CATALOG NUMBER: S125DIW-B375D770UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	82	84	81	78	75	64	62	60	49	48	46	35	34	33
2	85	78	72	67	77	70	65	61	56	53	50	43	41	39	31	29	28
3	78	69	61	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	21
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3643	3643	3643
5°	3643	3559	3565
10°	3613	3477	3466
15°	3566	3380	3349
20°	3501	3266	3215
25°	3433	3143	3071
30°	3350	3014	2920
35°	3261	2879	2751
40°	3169	2737	2600
45°	3070	2598	2439
50°	2961	2441	2253
55°	2853	2267	2081
60°	2724	2084	1882
65°	2570	1872	1675
70°	2414	1629	1437
75°	2149	1341	1161
80°	1832	1002	854
85°	1412	593	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3070 cd/sqm

TEST NUMBER: P1034536

CATALOG NUMBER: S125DIW-B375D770UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.2
10°-20°	151.6	3.3
20°-30°	223.8	4.9
30°-40°	261.1	5.7
40°-50°	262.2	5.7
50°-60°	230.2	5.0
60°-70°	171.4	3.7
70°-80°	97.9	2.1
80°-90°	29.8	0.6
90°-100°	34.5	0.7
100°-110°	229.5	5.0
110°-120°	413.3	9.0
120°-130°	530.4	11.5
130°-140°	570.5	12.4
140°-150°	535.5	11.6
150°-160°	433.1	9.4
160°-170°	280.1	6.1
170°-180°	96.6	2.1
0°-30°	429.0	9.3
0°-40°	690.0	15.0
0°-60°	1182.4	25.7
0°-90°	1481.5	32.2
90°-120°	677.3	14.7
90°-150°	2313.7	50.2
90°-180°	3124.0	67.8
0°-180°	4605.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	569	569	569	569	569	
5°	568	567	562	566	566	54
15°	541	540	535	537	537	153
25°	491	489	483	484	483	226
35°	424	422	416	414	410	265
45°	347	346	340	335	333	268
55°	264	263	257	253	250	236
65°	179	178	173	169	167	177
75°	95	94	92	90	89	101
85°	25	25	25	25	24	27
90°	1	7	12	16	18	4
95°	43	41	12	16	16	53
105°	222	225	225	225	224	235
115°	416	420	421	418	413	412
125°	592	597	597	594	592	529
135°	738	742	741	739	735	569
145°	856	857	857	858	853	535
155°	942	938	939	942	935	434
165°	994	990	990	995	989	281
175°	1017	1012	1013	1019	1012	97
180°	1017	1017	1017	1017	1017	

TEST NUMBER: P1034536

CATALOG NUMBER: S125DIW-B375D770UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	568.6	568.6	568.6	568.6	568.6
2.5°	570.4	569.1	564.6	569.1	568.6
5°	567.7	566.8	562.3	566.4	565.9
7.5°	563.7	562.8	557.8	561.9	561.4
10°	557.8	556.9	552.0	555.6	555.1
12.5°	550.6	548.8	544.3	547.0	547.0
15°	541.2	539.8	534.9	537.1	537.1
17.5°	531.3	529.0	524.1	526.8	524.5
20°	518.2	517.3	511.5	514.6	512.4
22.5°	505.2	503.4	498.0	499.8	498.4
25°	491.3	489.0	483.2	484.1	482.7
27.5°	475.1	473.7	467.9	468.3	467.0
30°	459.3	458.0	451.2	450.3	449.0
32.5°	442.2	440.0	434.1	432.3	429.6
35°	424.2	422.4	416.1	413.9	410.3
37.5°	405.8	403.5	397.7	394.5	392.3
40°	386.9	384.6	378.3	374.3	372.9
42.5°	366.6	364.8	358.5	354.9	352.7
45°	347.3	345.5	340.1	334.7	333.3
47.5°	326.2	326.6	319.9	314.5	311.3
50°	305.9	304.6	299.2	293.3	290.2
52.5°	285.2	284.3	278.5	273.5	269.9
55°	264.5	263.2	256.9	252.8	249.7
57.5°	242.5	242.0	236.6	231.2	229.9
60°	221.8	220.0	215.0	210.5	207.4
62.5°	200.2	198.8	194.8	189.8	187.6
65°	178.6	177.7	172.7	168.7	166.9
67.5°	157.5	155.7	152.1	148.5	147.6
70°	137.7	135.4	131.4	128.7	126.9
72.5°	116.1	114.7	112.5	109.3	107.5
75°	94.9	94.0	91.8	90.4	88.6
77.5°	75.1	74.7	73.3	72.4	71.1
80°	56.7	56.7	55.8	55.3	54.4
82.5°	40.5	39.6	39.6	38.7	38.7
85°	24.7	25.2	25.2	24.7	23.8
87.5°	12.1	12.1	11.7	11.7	10.8
90°	0.8	6.8	12.1	15.8	18.1
92.5°	14.3	7.5	12.1	15.8	16.6
95°	43.0	40.7	12.1	15.8	15.8
97.5°	80.7	85.2	13.6	15.1	15.8
100°	125.9	128.1	131.2	18.8	15.8
102.5°	171.9	174.9	176.4	177.9	114.6
105°	221.6	224.6	224.6	224.6	223.9
107.5°	272.9	272.9	274.4	275.1	272.1
110°	322.6	322.6	324.1	321.9	322.6

TEST NUMBER: P1034536

CATALOG NUMBER: S125DIW-B375D770UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	369.3	371.6	372.4	369.3	367.8
115°	416.1	419.8	420.6	417.6	413.1
117.5°	465.1	465.1	468.1	463.6	462.1
120°	510.3	509.5	511.8	510.3	506.5
122.5°	550.2	554.0	554.8	553.3	548.7
125°	591.7	597.0	597.0	594.0	591.7
127.5°	631.7	635.4	634.7	633.2	627.1
130°	667.8	671.6	672.4	670.1	666.3
132.5°	704.0	708.5	706.3	706.3	702.5
135°	737.9	742.5	741.0	739.4	734.9
137.5°	769.6	774.1	772.6	772.6	768.8
140°	800.5	802.0	801.3	802.8	798.2
142.5°	828.4	829.1	830.7	830.7	826.1
145°	855.5	857.0	857.0	857.8	853.3
147.5°	879.6	879.6	880.4	881.2	875.9
150°	902.3	900.8	902.3	903.8	897.7
152.5°	924.1	920.3	921.9	923.4	918.1
155°	942.2	937.7	939.2	941.5	935.4
157.5°	956.5	954.3	954.3	956.5	950.5
160°	971.6	967.1	967.8	970.9	964.8
162.5°	983.7	979.1	979.9	984.4	977.6
165°	994.2	989.7	990.4	995.0	988.9
167.5°	1002.5	998.0	998.7	1004.0	997.2
170°	1009.3	1004.0	1004.8	1010.8	1004.0
172.5°	1013.8	1008.5	1010.0	1015.3	1008.5
175°	1016.8	1012.3	1013.1	1019.1	1012.3
177.5°	1019.1	1014.6	1015.3	1020.6	1014.6
180°	1016.8	1016.8	1016.8	1016.8	1016.8

(END OF REPORT)