

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034560

Luminaire Tested: S125DIW-B610D1340UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034560
REPORT IS A COMBINATION OF REPORTS P1003793 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D1340UB2750-4F0-XX-W2A-D_2700K
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7694.1 lumens
Efficiency: N/A
Efficacy: 116.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034560

CATALOG NUMBER: S125DIW-B610D1340UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034560

CATALOG NUMBER: S125DIW-B610D1340UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	93	88	84	81	83	79	76	73	62	60	58	46	45	44	32	31	30
2	84	77	71	66	75	69	64	59	54	50	47	40	38	36	28	26	25
3	77	67	60	54	68	60	54	49	47	43	40	36	33	30	24	23	21
4	70	59	52	46	62	53	47	42	42	37	33	31	28	26	22	20	18
5	64	53	45	39	57	47	41	35	37	32	29	28	25	22	19	17	16
6	59	47	39	33	52	42	36	31	34	29	25	25	22	19	18	15	14
7	54	42	35	29	48	38	31	27	30	25	22	23	19	17	16	14	12
8	50	38	31	26	45	35	28	23	28	23	19	21	17	15	15	12	11
9	47	35	27	23	42	31	25	21	25	20	17	19	16	13	14	11	10
10	43	32	25	20	39	29	23	18	23	18	15	18	14	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4902	4902	4902
5°	4910	4799	4811
10°	4873	4701	4688
15°	4814	4588	4537
20°	4733	4450	4386
25°	4639	4303	4205
30°	4524	4144	4039
35°	4416	3996	3887
40°	4307	3842	3733
45°	4184	3708	3596
50°	4065	3561	3471
55°	3924	3423	3326
60°	3768	3264	3178
65°	3604	3097	3011
70°	3418	2874	2837
75°	3125	2652	2625
80°	2740	2384	2391
85°	2361	2170	2268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4184 cd/sqm

TEST NUMBER: P1034560

CATALOG NUMBER: S125DIW-B610D1340UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.4	0.9
10°-20°	205.5	2.7
20°-30°	305.6	4.0
30°-40°	361.9	4.7
40°-50°	374.2	4.9
50°-60°	344.7	4.5
60°-70°	278.7	3.6
70°-80°	186.5	2.4
80°-90°	99.0	1.3
90°-100°	113.1	1.5
100°-110°	431.0	5.6
110°-120°	730.9	9.5
120°-130°	918.9	11.9
130°-140°	978.6	12.7
140°-150°	913.6	11.9
150°-160°	737.9	9.6
160°-170°	477.2	6.2
170°-180°	164.6	2.1
0°-30°	583.5	7.6
0°-40°	945.4	12.3
0°-60°	1664.3	21.6
0°-90°	2228.4	29.0
90°-120°	1275.0	16.6
90°-150°	4086.1	53.1
90°-180°	5466.0	71.0
0°-180°	7694.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	765	765	765	765	765	
5°	765	764	758	764	764	73
15°	731	731	726	731	728	206
25°	664	666	662	664	661	306
35°	574	580	578	580	580	360
45°	473	482	485	490	491	365
55°	364	376	388	396	399	325
65°	250	268	286	297	300	249
75°	138	158	182	196	200	146
85°	41	66	92	109	115	43
90°	13	48	82	106	115	12
95°	83	99	75	98	104	97
105°	384	402	424	439	443	407
115°	713	725	746	754	751	707
125°	1011	1019	1034	1041	1041	903
135°	1259	1266	1268	1276	1272	970
145°	1458	1460	1460	1465	1460	912
155°	1605	1598	1600	1604	1594	740
165°	1694	1686	1687	1695	1685	478
175°	1732	1725	1726	1736	1725	165
180°	1732	1732	1732	1732	1732	

TEST NUMBER: P1034560

CATALOG NUMBER: S125DIW-B610D1340UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	765.1	765.1	765.1	765.1	765.1
2.5°	767.3	765.8	760.6	765.8	765.1
5°	765.1	763.6	758.3	764.3	763.6
7.5°	759.8	759.1	753.8	759.1	758.3
10°	752.3	752.3	746.3	751.6	750.8
12.5°	741.8	742.6	738.1	741.8	739.6
15°	730.6	731.3	726.1	730.6	727.6
17.5°	716.3	717.8	712.5	716.3	714.0
20°	700.5	702.0	696.8	699.0	699.0
22.5°	682.5	685.5	679.5	682.5	680.3
25°	663.8	666.0	661.5	664.5	660.8
27.5°	643.5	646.5	641.3	643.5	642.0
30°	620.3	624.8	620.3	621.8	621.0
32.5°	599.3	603.0	600.0	601.5	600.8
35°	574.5	579.8	577.5	579.8	579.8
37.5°	550.5	555.0	554.3	557.3	556.5
40°	525.8	531.8	531.0	534.0	535.5
42.5°	498.8	507.0	509.3	513.0	513.0
45°	473.3	481.5	485.3	490.5	491.3
47.5°	447.0	454.5	460.5	468.0	469.5
50°	420.0	428.3	436.5	444.8	447.0
52.5°	391.5	402.0	412.5	421.5	423.0
55°	363.8	375.8	387.8	396.0	399.0
57.5°	335.3	349.5	363.0	372.0	374.3
60°	306.8	321.8	336.8	348.0	350.3
62.5°	279.0	294.0	310.5	323.3	326.3
65°	250.5	267.8	285.8	297.0	300.0
67.5°	224.3	240.8	258.8	272.3	276.0
70°	195.0	212.3	231.8	246.0	250.5
72.5°	166.5	184.5	206.3	222.0	225.0
75°	138.0	157.5	181.5	196.5	200.3
77.5°	110.3	132.8	155.3	171.8	174.8
80°	84.8	107.3	132.8	149.3	152.3
82.5°	61.5	85.5	111.8	127.5	133.5
85°	41.3	66.0	92.3	108.8	114.8
87.5°	26.3	50.3	75.8	93.0	98.3
90°	13.3	47.6	82.0	105.8	114.8
92.5°	34.9	45.1	79.0	102.0	108.6
95°	83.0	98.6	75.3	98.3	103.5
97.5°	146.4	172.1	74.9	93.2	99.8
100°	222.8	242.3	271.4	95.9	95.3
102.5°	300.3	319.7	345.5	363.1	259.7
105°	384.3	401.5	424.0	439.0	442.9
107.5°	470.9	481.4	505.7	522.0	521.4
110°	554.9	563.9	587.5	597.8	604.4

TEST NUMBER: P1034560

CATALOG NUMBER: S125DIW-B610D1340UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	634.5	645.1	666.7	675.0	677.7
115°	713.4	725.1	745.9	754.2	751.0
117.5°	796.1	799.8	823.8	828.8	831.5
120°	873.2	874.1	895.3	905.4	903.5
122.5°	940.4	947.7	965.5	974.9	971.7
125°	1011.1	1019.4	1034.4	1041.2	1041.1
127.5°	1078.4	1084.1	1095.6	1104.2	1098.4
130°	1140.1	1145.7	1157.5	1164.1	1161.5
132.5°	1200.9	1208.6	1212.3	1222.8	1219.4
135°	1258.7	1265.7	1268.3	1275.6	1271.6
137.5°	1312.6	1319.7	1320.1	1329.1	1325.7
140°	1364.6	1367.2	1366.6	1377.4	1372.7
142.5°	1412.1	1412.6	1415.2	1422.0	1417.3
145°	1458.3	1460.1	1460.1	1465.2	1460.5
147.5°	1498.6	1498.6	1499.9	1502.7	1495.2
150°	1537.2	1534.6	1537.2	1539.7	1530.3
152.5°	1574.4	1568.0	1570.5	1573.1	1564.1
155°	1605.2	1597.5	1600.1	1603.9	1593.7
157.5°	1629.6	1625.8	1625.8	1629.6	1619.3
160°	1655.3	1647.6	1648.9	1654.0	1643.7
162.5°	1675.9	1668.1	1669.4	1677.1	1665.6
165°	1693.8	1686.1	1687.4	1695.1	1684.8
167.5°	1708.0	1700.3	1701.5	1710.5	1699.0
170°	1719.5	1710.5	1711.8	1722.1	1710.5
172.5°	1727.2	1718.2	1720.8	1729.8	1718.2
175°	1732.4	1724.7	1725.9	1736.2	1724.7
177.5°	1736.2	1728.5	1729.8	1738.8	1728.5
180°	1732.4	1732.4	1732.4	1732.4	1732.4

(END OF REPORT)