

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035097

Luminaire Tested: S125DIW-B1270D1050UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035097
REPORT IS A COMBINATION OF REPORTS P1003086 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1050UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8829.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035097

CATALOG NUMBER: S125DIW-B1270D1050UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035097

CATALOG NUMBER: S125DIW-B1270D1050UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	85	82	77	74	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	67	67	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	60	54	50	51	47	44	44	41	38
4	76	65	57	50	70	61	53	48	53	47	43	46	41	38	39	36	33
5	69	58	49	43	65	54	47	41	47	41	37	41	36	33	35	32	29
6	64	52	43	38	59	49	41	36	43	37	32	37	32	29	32	28	25
7	59	47	39	33	55	44	37	31	39	33	28	34	29	25	29	25	23
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	32	27	23	29	24	20	25	21	18
10	48	36	28	23	45	34	27	22	30	24	20	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12655	12655	12655
5°	12656	12362	12385
10°	12551	12078	12040
15°	12387	11739	11634
20°	12164	11346	11168
25°	11924	10918	10669
30°	11636	10471	10143
35°	11328	10003	9554
40°	11009	9508	9031
45°	10665	9026	8474
50°	10285	8479	7826
55°	9911	7875	7230
60°	9462	7239	6536
65°	8927	6503	5819
70°	8382	5657	4991
75°	7465	4658	4035
80°	6363	3480	2969
85°	4911	2057	1636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10665 cd/sqm

TEST NUMBER: P1035097

CATALOG NUMBER: S125DIW-B1270D1050UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	2.1
10°-20°	526.5	6.0
20°-30°	777.2	8.8
30°-40°	906.8	10.3
40°-50°	910.8	10.3
50°-60°	799.5	9.1
60°-70°	595.5	6.7
70°-80°	340.1	3.9
80°-90°	100.2	1.1
90°-100°	87.8	1.0
100°-110°	260.9	3.0
110°-120°	442.5	5.0
120°-130°	582.5	6.6
130°-140°	652.7	7.4
140°-150°	639.8	7.2
150°-160°	537.4	6.1
160°-170°	357.2	4.0
170°-180°	125.0	1.4
0°-30°	1490.1	16.9
0°-40°	2396.9	27.1
0°-60°	4107.2	46.5
0°-90°	5143.1	58.3
90°-120°	791.2	9.0
90°-150°	2666.2	30.2
90°-180°	3686.0	41.7
0°-180°	8829.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1972	1969	1953	1967	1966	187
15°	1880	1875	1858	1866	1866	530
25°	1706	1699	1678	1681	1677	785
35°	1474	1467	1446	1438	1425	922
45°	1206	1200	1181	1163	1158	929
55°	919	914	892	878	867	820
65°	620	617	600	586	580	615
75°	330	327	319	314	308	351
85°	86	88	88	86	83	94
90°	1	9	16	22	25	10
95°	67	69	79	86	88	70
105°	234	240	246	252	255	250
115°	443	447	449	448	447	438
125°	646	653	654	652	651	579
135°	841	847	848	848	844	648
145°	1018	1023	1026	1026	1023	637
155°	1166	1166	1166	1171	1166	537
165°	1267	1265	1266	1270	1264	358
175°	1318	1314	1314	1320	1312	125
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1035097

CATALOG NUMBER: S125DIW-B1270D1050UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1981.5	1976.8	1961.2	1976.8	1975.2
5°	1972.1	1969.0	1953.3	1967.4	1965.8
7.5°	1958.0	1954.9	1937.7	1951.8	1950.2
10°	1937.7	1934.6	1917.4	1929.9	1928.3
12.5°	1912.7	1906.5	1890.8	1900.2	1900.2
15°	1879.9	1875.2	1858.0	1865.8	1865.8
17.5°	1845.5	1837.7	1820.5	1829.9	1822.1
20°	1800.2	1797.1	1776.8	1787.7	1779.9
22.5°	1754.9	1748.6	1729.9	1736.1	1731.4
25°	1706.4	1698.6	1678.3	1681.4	1676.7
27.5°	1650.2	1645.5	1625.2	1626.7	1622.1
30°	1595.5	1590.8	1567.4	1564.2	1559.5
32.5°	1536.1	1528.3	1508.0	1501.7	1492.4
35°	1473.6	1467.3	1445.5	1437.7	1425.2
37.5°	1409.5	1401.7	1381.4	1370.5	1362.6
40°	1343.9	1336.1	1314.2	1300.1	1295.5
42.5°	1273.6	1267.3	1245.4	1232.9	1225.1
45°	1206.4	1200.1	1181.4	1162.6	1157.9
47.5°	1132.9	1134.5	1111.1	1092.3	1081.4
50°	1062.6	1057.9	1039.2	1018.9	1007.9
52.5°	990.7	987.6	967.3	950.1	937.6
55°	918.9	914.2	892.3	878.2	867.3
57.5°	842.3	840.7	822.0	803.2	798.5
60°	770.4	764.1	747.0	731.3	720.4
62.5°	695.4	690.7	676.6	659.4	651.6
65°	620.4	617.3	600.1	586.0	579.8
67.5°	546.9	540.7	528.2	515.7	512.6
70°	478.2	470.4	456.3	446.9	440.7
72.5°	403.2	398.5	390.7	379.7	373.5
75°	329.7	326.6	318.8	314.1	307.8
77.5°	261.0	259.4	254.7	251.6	246.9
80°	196.9	196.9	193.8	192.2	189.1
82.5°	140.6	137.5	137.5	134.4	134.4
85°	85.9	87.5	87.5	85.9	82.8
87.5°	42.2	42.2	40.6	40.6	37.5
90°	1.0	9.2	16.4	21.6	24.7
92.5°	30.8	36.0	45.2	52.4	54.5
95°	66.8	68.9	79.1	86.3	88.4
97.5°	102.8	103.8	118.2	124.4	125.4
100°	143.9	143.9	157.2	166.5	168.6
102.5°	188.1	193.2	198.4	208.6	211.7
105°	234.3	239.5	245.6	251.8	254.9
107.5°	284.7	289.8	295.0	298.1	298.1
110°	337.1	342.2	345.3	348.4	347.4

TEST NUMBER: P1035097

CATALOG NUMBER: S125DIW-B1270D1050UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	390.6	392.6	396.7	397.7	395.7
115°	443.0	447.1	449.1	448.1	447.1
117.5°	496.4	497.4	499.5	500.5	496.4
120°	545.7	550.9	551.9	551.9	547.8
122.5°	599.2	600.2	603.3	602.3	599.2
125°	646.5	652.6	653.7	651.6	650.6
127.5°	698.9	702.0	703.0	702.0	699.9
130°	745.1	750.3	752.3	751.3	749.2
132.5°	791.4	800.6	799.6	798.6	795.5
135°	840.7	846.9	847.9	847.9	843.8
137.5°	887.0	893.1	895.2	896.2	891.1
140°	931.2	936.3	939.4	941.4	936.3
142.5°	975.4	979.5	983.6	984.6	979.5
145°	1018.5	1022.6	1025.7	1025.7	1022.6
147.5°	1058.6	1061.7	1063.7	1066.8	1058.6
150°	1098.7	1097.7	1101.8	1101.8	1099.7
152.5°	1131.6	1133.6	1134.7	1137.7	1133.6
155°	1165.5	1165.5	1166.5	1170.6	1165.5
157.5°	1196.3	1194.3	1195.3	1199.4	1192.2
160°	1223.1	1220.0	1221.0	1225.1	1220.0
162.5°	1246.7	1244.6	1244.6	1249.8	1243.6
165°	1267.2	1265.2	1266.2	1270.3	1264.2
167.5°	1285.7	1281.6	1281.6	1287.8	1281.6
170°	1300.1	1296.0	1296.0	1302.2	1295.0
172.5°	1310.4	1306.3	1306.3	1312.5	1306.3
175°	1317.6	1313.5	1313.5	1319.7	1312.5
177.5°	1322.7	1318.6	1317.6	1323.8	1316.6
180°	1320.7	1320.7	1320.7	1320.7	1320.7

(END OF REPORT)