

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035107

Luminaire Tested: S125DIW-B1270D1050UB40-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035107
REPORT IS A COMBINATION OF REPORTS P1003101 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1050UB40-4F0-XX-W2A-D1
Description: Define 5 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8576.1 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035107

CATALOG NUMBER: S125DIW-B1270D1050UB40-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1035107

CATALOG NUMBER: S125DIW-B1270D1050UB40-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60
1	98	93	89	85	90	86	83	79	74	71	69	62	60	58	51	50	49
2	89	81	74	69	82	75	69	65	64	60	56	54	51	48	45	42	40
3	81	71	63	57	74	66	59	54	56	51	47	48	44	40	39	37	34
4	74	63	54	48	68	58	51	45	50	44	40	42	38	34	35	32	29
5	68	56	47	41	62	52	44	39	45	39	34	38	33	30	32	28	25
6	62	50	41	35	57	46	39	34	40	34	30	34	29	26	29	25	22
7	58	45	37	31	53	42	35	29	36	30	26	31	26	23	26	22	20
8	53	41	33	27	49	38	31	26	33	27	23	28	24	20	24	20	18
9	50	37	30	24	46	35	28	23	30	25	21	26	22	18	22	18	16
10	46	34	27	22	43	32	25	21	28	22	19	24	20	16	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10153	10153	10153
5°	10170	9940	9965
10°	10093	9737	9710
15°	9970	9502	9397
20°	9805	9217	9085
25°	9608	8914	8709
30°	9370	8583	8367
35°	9148	8279	8051
40°	8922	7957	7733
45°	8666	7679	7447
50°	8421	7377	7189
55°	8127	7089	6890
60°	7804	6761	6582
65°	7466	6414	6236
70°	7080	5952	5876
75°	6473	5494	5437
80°	5675	4937	4951
85°	4883	4493	4696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8666 cd/sqm

TEST NUMBER: P1035107

CATALOG NUMBER: S125DIW-B1270D1050UB40-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.0	1.7
10°-20°	425.7	5.0
20°-30°	633.0	7.4
30°-40°	749.7	8.7
40°-50°	775.0	9.0
50°-60°	714.0	8.3
60°-70°	577.2	6.7
70°-80°	386.2	4.5
80°-90°	201.7	2.4
90°-100°	199.8	2.3
100°-110°	342.3	4.0
110°-120°	495.5	5.8
120°-130°	610.6	7.1
130°-140°	662.8	7.7
140°-150°	638.9	7.4
150°-160°	534.4	6.2
160°-170°	355.2	4.1
170°-180°	124.3	1.4
0°-30°	1208.7	14.1
0°-40°	1958.3	22.8
0°-60°	3447.3	40.2
0°-90°	4612.4	53.8
90°-120°	1037.5	12.1
90°-150°	2949.8	34.4
90°-180°	3964.0	46.2
0°-180°	8576.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1585	1585	1585	1585	1585	
5°	1585	1582	1571	1583	1582	150
15°	1513	1515	1504	1513	1507	426
25°	1375	1380	1370	1376	1369	633
35°	1190	1201	1196	1201	1201	745
45°	980	997	1005	1016	1018	756
55°	754	778	803	820	826	673
65°	519	555	592	615	621	515
75°	286	326	376	407	415	303
85°	85	137	191	225	238	89
90°	26	84	144	185	198	22
95°	87	129	192	233	246	85
105°	247	277	330	367	381	263
115°	450	465	507	534	542	445
125°	649	654	686	708	715	581
135°	839	844	856	876	879	647
145°	1014	1017	1020	1028	1031	634
155°	1159	1159	1160	1164	1159	534
165°	1260	1258	1259	1263	1257	356
175°	1310	1306	1306	1312	1305	125
180°	1313	1313	1313	1313	1313	

TEST NUMBER: P1035107

CATALOG NUMBER: S125DIW-B1270D1050UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1584.7	1584.7	1584.7	1584.7	1584.7
2.5°	1589.3	1586.2	1575.3	1586.2	1584.7
5°	1584.7	1581.6	1570.7	1583.1	1581.6
7.5°	1573.8	1572.2	1561.4	1572.2	1570.7
10°	1558.2	1558.2	1545.8	1556.7	1555.1
12.5°	1536.5	1538.1	1528.7	1536.5	1531.8
15°	1513.2	1514.7	1503.9	1513.2	1507.0
17.5°	1483.7	1486.8	1475.9	1483.7	1479.0
20°	1451.1	1454.2	1443.3	1447.9	1447.9
22.5°	1413.8	1420.0	1407.6	1413.8	1409.1
25°	1374.9	1379.6	1370.3	1376.5	1368.7
27.5°	1333.0	1339.2	1328.3	1333.0	1329.9
30°	1284.8	1294.1	1284.8	1287.9	1286.4
32.5°	1241.3	1249.1	1242.9	1246.0	1244.4
35°	1190.0	1200.9	1196.3	1200.9	1200.9
37.5°	1140.3	1149.7	1148.1	1154.3	1152.8
40°	1089.1	1101.5	1099.9	1106.2	1109.3
42.5°	1033.1	1050.2	1054.9	1062.7	1062.7
45°	980.3	997.4	1005.2	1016.0	1017.6
47.5°	925.9	941.5	953.9	969.4	972.5
50°	870.0	887.1	904.2	921.3	925.9
52.5°	811.0	832.7	854.5	873.1	876.2
55°	753.5	778.3	803.2	820.3	826.5
57.5°	694.5	724.0	751.9	770.6	775.2
60°	635.4	666.5	697.6	720.9	725.5
62.5°	577.9	609.0	643.2	669.6	675.8
65°	518.9	554.6	591.9	615.2	621.4
67.5°	464.5	498.7	536.0	564.0	571.7
70°	403.9	439.7	480.1	509.6	518.9
72.5°	344.9	382.2	427.2	459.9	466.1
75°	285.9	326.3	376.0	407.0	414.8
77.5°	228.4	275.0	321.6	355.8	362.0
80°	175.6	222.2	275.0	309.2	315.4
82.5°	127.4	177.1	231.5	264.1	276.5
85°	85.4	136.7	191.1	225.3	237.7
87.5°	54.4	104.1	156.9	192.6	203.5
90°	25.9	83.8	143.8	184.6	198.5
92.5°	52.5	102.6	166.2	207.5	220.4
95°	86.6	129.1	192.1	233.4	246.4
97.5°	120.8	159.1	224.7	263.5	275.4
100°	160.2	192.8	255.8	297.7	309.0
102.5°	202.5	237.2	290.4	331.8	344.1
105°	247.0	276.9	329.6	366.9	380.8
107.5°	295.5	322.4	372.5	406.7	416.0
110°	346.1	369.8	416.4	448.9	458.8



TEST NUMBER: P1035107

CATALOG NUMBER: S125DIW-B1270D1050UB40-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	399.2	415.3	461.3	490.3	499.0
115°	449.7	464.7	507.2	534.2	542.4
117.5°	501.4	510.1	551.1	578.5	585.3
120°	550.4	560.2	597.0	623.4	628.6
122.5°	602.0	604.6	641.8	665.6	671.9
125°	649.0	653.6	685.6	708.5	715.3
127.5°	699.6	701.1	728.5	750.8	758.0
130°	745.6	749.1	772.9	793.6	799.4
132.5°	790.0	799.2	813.7	834.4	837.6
135°	839.0	843.7	855.5	875.7	879.4
137.5°	885.0	889.7	897.9	917.5	918.6
140°	927.5	932.6	937.1	956.3	957.4
142.5°	971.4	973.9	978.0	993.0	994.1
145°	1014.3	1016.8	1019.9	1027.7	1030.8
147.5°	1052.6	1055.6	1057.7	1063.9	1058.8
150°	1092.4	1091.4	1095.5	1095.5	1095.1
152.5°	1125.1	1127.2	1128.2	1131.3	1127.2
155°	1158.9	1158.9	1159.9	1164.0	1158.9
157.5°	1189.5	1187.5	1188.5	1192.6	1185.4
160°	1216.1	1213.0	1214.0	1218.1	1213.0
162.5°	1239.6	1237.5	1237.5	1242.7	1236.5
165°	1260.0	1258.0	1259.0	1263.1	1257.0
167.5°	1278.4	1274.3	1274.3	1280.5	1274.3
170°	1292.7	1288.6	1288.6	1294.8	1287.6
172.5°	1303.0	1298.9	1298.9	1305.0	1298.9
175°	1310.1	1306.0	1306.0	1312.1	1305.0
177.5°	1315.2	1311.1	1310.1	1316.2	1309.1
180°	1313.2	1313.2	1313.2	1313.2	1313.2

(END OF REPORT)