

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034578

Luminaire Tested: S125DIW-B610D1560UB2750-4F0-XX-W2A-D_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034578
REPORT IS A COMBINATION OF REPORTS P1003863 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D1560UB2750-4F0-XX-W2A-D_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8388.0 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034578

CATALOG NUMBER: S125DIW-B610D1560UB2750-4F0-XX-W2A-D_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034578

CATALOG NUMBER: S125DIW-B610D1560UB2750-4F0-XX-W2A-D_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	84	80	82	78	75	72	61	58	56	44	43	42	29	28	28
2	84	76	70	65	74	68	63	59	53	49	46	39	36	34	26	24	23
3	76	67	60	54	67	60	54	49	46	42	39	34	31	29	22	21	19
4	69	59	51	45	62	53	46	41	41	36	33	30	27	25	20	18	17
5	64	52	44	39	56	47	40	35	37	32	28	27	24	21	18	16	14
6	58	47	39	33	52	42	35	30	33	28	24	24	21	18	16	14	13
7	54	42	34	29	48	38	31	26	30	25	21	22	19	16	15	13	11
8	50	38	30	25	44	34	28	23	27	22	19	20	17	14	14	11	10
9	46	34	27	22	41	31	25	20	24	20	16	18	15	13	12	10	9
10	43	31	24	20	38	28	22	18	22	18	15	17	14	11	12	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4755	4755	4755
5°	4762	4655	4667
10°	4727	4560	4547
15°	4670	4450	4401
20°	4592	4316	4255
25°	4500	4174	4079
30°	4388	4020	3918
35°	4284	3877	3770
40°	4178	3727	3622
45°	4058	3596	3488
50°	3943	3455	3367
55°	3806	3320	3227
60°	3655	3166	3083
65°	3497	3004	2920
70°	3316	2787	2752
75°	3032	2573	2547
80°	2656	2312	2319
85°	2287	2104	2199

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4058 cd/sqm

TEST NUMBER: P1034578

CATALOG NUMBER: S125DIW-B610D1560UB2750-4F0-XX-W2A-D_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.2	0.8
10°-20°	199.4	2.4
20°-30°	296.5	3.5
30°-40°	351.1	4.2
40°-50°	363.0	4.3
50°-60°	334.4	4.0
60°-70°	270.3	3.2
70°-80°	180.9	2.2
80°-90°	96.4	1.1
90°-100°	119.9	1.4
100°-110°	486.0	5.8
110°-120°	831.2	9.9
120°-130°	1048.3	12.5
130°-140°	1118.1	13.3
140°-150°	1044.6	12.5
150°-160°	843.9	10.1
160°-170°	545.8	6.5
170°-180°	188.2	2.2
0°-30°	566.0	6.7
0°-40°	917.1	10.9
0°-60°	1614.5	19.2
0°-90°	2162.0	25.8
90°-120°	1437.1	17.1
90°-150°	4648.0	55.4
90°-180°	6226.0	74.2
0°-180°	8388.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	742	742	742	742	742	
5°	742	741	736	741	741	70
15°	709	709	704	709	706	200
25°	644	646	642	645	641	296
35°	557	562	560	562	562	349
45°	459	467	471	476	477	354
55°	353	364	376	384	387	315
65°	243	260	277	288	291	241
75°	134	153	176	191	194	142
85°	40	64	90	106	111	42
90°	13	48	83	107	117	12
95°	93	108	77	100	105	110
105°	438	456	478	492	496	464
115°	815	828	848	855	851	808
125°	1156	1165	1180	1186	1185	1032
135°	1439	1447	1450	1456	1451	1110
145°	1668	1670	1670	1675	1669	1043
155°	1836	1827	1830	1834	1823	846
165°	1937	1928	1930	1939	1927	547
175°	1981	1972	1974	1986	1972	189
180°	1981	1981	1981	1981	1981	

TEST NUMBER: P1034578

CATALOG NUMBER: S125DIW-B610D1560UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	742.1	742.1	742.1	742.1	742.1
2.5°	744.3	742.9	737.8	742.9	742.1
5°	742.1	740.7	735.6	741.4	740.7
7.5°	737.0	736.3	731.2	736.3	735.6
10°	729.8	729.8	723.9	729.0	728.3
12.5°	719.6	720.3	715.9	719.6	717.4
15°	708.7	709.4	704.3	708.7	705.8
17.5°	694.8	696.3	691.2	694.8	692.7
20°	679.6	681.0	675.9	678.1	678.1
22.5°	662.1	665.0	659.2	662.1	659.9
25°	643.9	646.1	641.7	644.6	641.0
27.5°	624.3	627.2	622.1	624.3	622.8
30°	601.7	606.1	601.7	603.2	602.4
32.5°	581.3	585.0	582.1	583.5	582.8
35°	557.3	562.4	560.2	562.4	562.4
37.5°	534.0	538.4	537.7	540.6	539.9
40°	510.0	515.9	515.1	518.0	519.5
42.5°	483.8	491.8	494.0	497.7	497.7
45°	459.1	467.1	470.7	475.8	476.6
47.5°	433.6	440.9	446.7	454.0	455.5
50°	407.4	415.4	423.5	431.5	433.6
52.5°	379.8	390.0	400.2	408.9	410.4
55°	352.9	364.5	376.2	384.2	387.1
57.5°	325.2	339.1	352.1	360.9	363.1
60°	297.6	312.1	326.7	337.6	339.8
62.5°	270.7	285.2	301.2	313.6	316.5
65°	243.0	259.7	277.2	288.1	291.0
67.5°	217.5	233.6	251.0	264.1	267.8
70°	189.2	205.9	224.8	238.6	243.0
72.5°	161.5	179.0	200.1	215.4	218.3
75°	133.9	152.8	176.1	190.6	194.3
77.5°	107.0	128.8	150.6	166.6	169.5
80°	82.2	104.0	128.8	144.8	147.7
82.5°	59.7	82.9	108.4	123.7	129.5
85°	40.0	64.0	89.5	105.5	111.3
87.5°	25.5	48.7	73.5	90.2	95.3
90°	13.1	48.1	83.2	107.2	116.7
92.5°	38.1	46.0	80.3	103.6	110.2
95°	93.2	107.7	76.6	99.9	105.0
97.5°	165.9	192.2	76.6	94.9	101.4
100°	253.3	273.0	302.2	98.5	97.0
102.5°	342.2	361.8	387.4	404.8	285.8
105°	438.3	455.9	477.7	492.3	495.9
107.5°	537.5	547.7	571.7	587.8	586.2
110°	633.7	642.4	665.7	675.1	681.7

TEST NUMBER: P1034578

CATALOG NUMBER: S125DIW-B610D1560UB2750-4F0-XX-W2A-D_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	724.8	735.7	756.8	764.1	766.2
115°	815.1	827.6	847.9	855.2	850.6
117.5°	909.8	913.5	937.6	941.1	943.2
120°	997.9	998.6	1019.8	1029.2	1026.3
122.5°	1075.1	1083.1	1100.6	1109.3	1104.9
125°	1155.8	1165.4	1179.9	1185.7	1184.9
127.5°	1233.0	1239.6	1250.4	1258.4	1251.1
130°	1303.5	1310.1	1321.7	1327.5	1323.8
132.5°	1373.3	1382.1	1384.9	1395.1	1390.6
135°	1439.4	1447.4	1449.5	1456.1	1450.9
137.5°	1501.0	1509.1	1509.0	1517.8	1513.4
140°	1560.5	1563.4	1562.7	1573.7	1567.8
142.5°	1614.8	1615.6	1618.5	1625.0	1619.2
145°	1667.7	1669.9	1669.9	1675.0	1669.1
147.5°	1714.0	1714.0	1715.4	1718.4	1709.5
150°	1758.0	1755.1	1758.0	1761.0	1749.9
152.5°	1800.6	1793.3	1796.2	1799.2	1788.9
155°	1835.9	1827.1	1830.0	1834.4	1822.7
157.5°	1863.8	1859.4	1859.4	1863.8	1852.0
160°	1893.2	1884.3	1885.8	1891.7	1879.9
162.5°	1916.7	1907.8	1909.3	1918.1	1904.9
165°	1937.2	1928.4	1929.9	1938.7	1926.9
167.5°	1953.4	1944.6	1946.0	1956.3	1943.1
170°	1966.6	1956.3	1957.8	1969.5	1956.3
172.5°	1975.4	1965.1	1968.1	1978.3	1965.1
175°	1981.3	1972.5	1973.9	1985.7	1972.5
177.5°	1985.7	1976.9	1978.3	1988.6	1976.9
180°	1981.3	1981.3	1981.3	1981.3	1981.3

(END OF REPORT)