

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034579

Luminaire Tested: S125DIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034579
REPORT IS A COMBINATION OF REPORTS P1003864 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7674.0 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034579

CATALOG NUMBER: S125DIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034579

CATALOG NUMBER: S125DIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	89	86	82	84	80	77	74	64	62	60	48	47	46	34	33	33
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	29	27
3	78	68	61	56	69	62	56	51	49	45	41	37	35	32	27	25	23
4	71	60	53	47	63	55	48	43	44	39	35	33	30	27	24	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	32	28	32	27	23	24	21	18	18	15	14
8	51	39	32	26	46	36	29	24	29	24	20	22	19	16	16	14	12
9	47	36	28	23	43	32	26	22	26	21	18	20	17	14	15	13	11
10	44	33	26	21	40	30	23	19	24	19	16	19	15	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5893	5893	5893
5°	5893	5756	5767
10°	5845	5625	5607
15°	5768	5466	5418
20°	5664	5284	5200
25°	5553	5084	4968
30°	5419	4876	4723
35°	5275	4658	4449
40°	5127	4428	4206
45°	4966	4203	3946
50°	4789	3948	3645
55°	4615	3667	3367
60°	4406	3371	3044
65°	4157	3028	2710
70°	3904	2634	2324
75°	3476	2168	1880
80°	2963	1619	1381
85°	2287	959	763

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4966 cd/sqm

TEST NUMBER: P1034579

CATALOG NUMBER: S125DIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.1
10°-20°	245.2	3.2
20°-30°	361.9	4.7
30°-40°	422.3	5.5
40°-50°	424.1	5.5
50°-60°	372.3	4.9
60°-70°	277.3	3.6
70°-80°	158.4	2.1
80°-90°	48.7	0.6
90°-100°	125.7	1.6
100°-110°	373.5	4.9
110°-120°	633.5	8.3
120°-130°	834.0	10.9
130°-140°	934.5	12.2
140°-150°	916.0	11.9
150°-160°	769.4	10.0
160°-170°	511.5	6.7
170°-180°	179.0	2.3
0°-30°	693.9	9.0
0°-40°	1116.2	14.5
0°-60°	1912.6	24.9
0°-90°	2396.9	31.2
90°-120°	1132.7	14.8
90°-150°	3817.2	49.7
90°-180°	5277.0	68.8
0°-180°	7674.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	918	917	910	916	915	87
15°	875	873	865	869	869	247
25°	795	791	782	783	781	366
35°	686	683	673	670	664	429
45°	562	559	550	541	539	433
55°	428	426	416	409	404	382
65°	289	287	279	273	270	287
75°	154	152	148	146	143	163
85°	40	41	41	40	39	44
90°	2	13	24	31	35	9
95°	96	99	113	124	126	100
105°	336	343	352	360	365	358
115°	634	640	643	642	640	627
125°	926	934	936	933	931	829
135°	1204	1212	1214	1214	1208	928
145°	1458	1464	1468	1468	1464	912
155°	1669	1669	1670	1676	1669	769
165°	1814	1811	1813	1819	1810	512
175°	1886	1880	1880	1889	1879	179
180°	1891	1891	1891	1891	1891	

TEST NUMBER: P1034579

CATALOG NUMBER: S125DIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	919.8	919.8	919.8	919.8	919.8
2.5°	922.7	920.5	913.2	920.5	919.8
5°	918.3	916.9	909.6	916.2	915.4
7.5°	911.8	910.3	902.3	908.9	908.2
10°	902.3	900.9	892.9	898.7	898.0
12.5°	890.7	887.8	880.5	884.9	884.9
15°	875.4	873.2	865.2	868.9	868.9
17.5°	859.4	855.8	847.8	852.1	848.5
20°	838.3	836.8	827.4	832.5	828.8
22.5°	817.2	814.3	805.5	808.5	806.3
25°	794.6	791.0	781.5	783.0	780.8
27.5°	768.4	766.3	756.8	757.5	755.3
30°	743.0	740.8	729.9	728.4	726.2
32.5°	715.3	711.7	702.2	699.3	694.9
35°	686.2	683.3	673.1	669.5	663.6
37.5°	656.4	652.7	643.3	638.2	634.5
40°	625.8	622.2	612.0	605.4	603.3
42.5°	593.1	590.2	580.0	574.1	570.5
45°	561.8	558.9	550.1	541.4	539.2
47.5°	527.6	528.3	517.4	508.7	503.6
50°	494.8	492.6	483.9	474.5	469.4
52.5°	461.4	459.9	450.4	442.4	436.6
55°	427.9	425.7	415.5	409.0	403.9
57.5°	392.2	391.5	382.8	374.0	371.8
60°	358.7	355.8	347.8	340.6	335.5
62.5°	323.8	321.6	315.1	307.1	303.4
65°	288.9	287.4	279.4	272.9	270.0
67.5°	254.7	251.8	246.0	240.1	238.7
70°	222.7	219.0	212.5	208.1	205.2
72.5°	187.7	185.6	181.9	176.8	173.9
75°	153.5	152.1	148.4	146.3	143.4
77.5°	121.5	120.8	118.6	117.2	115.0
80°	91.7	91.7	90.2	89.5	88.0
82.5°	65.5	64.0	64.0	62.6	62.6
85°	40.0	40.8	40.8	40.0	38.6
87.5°	19.6	19.6	18.9	18.9	17.5
90°	1.5	13.2	23.5	30.9	35.3
92.5°	44.1	51.5	64.7	75.0	78.0
95°	95.6	98.6	113.3	123.6	126.5
97.5°	147.1	148.6	169.2	178.0	179.5
100°	206.0	206.0	225.1	238.4	241.3
102.5°	269.3	276.6	284.0	298.7	303.1
105°	335.5	342.8	351.7	360.5	364.9
107.5°	407.6	414.9	422.3	426.7	426.7
110°	482.6	490.0	494.4	498.8	497.3

TEST NUMBER: P1034579

CATALOG NUMBER: S125DIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	559.1	562.1	568.0	569.4	566.5
115°	634.2	640.1	643.0	641.5	640.1
117.5°	710.7	712.2	715.1	716.6	710.7
120°	781.3	788.7	790.2	790.2	784.3
122.5°	857.8	859.3	863.7	862.3	857.8
125°	925.5	934.4	935.8	932.9	931.4
127.5°	1000.6	1005.0	1006.5	1005.0	1002.0
130°	1066.8	1074.1	1077.1	1075.6	1072.7
132.5°	1133.0	1146.2	1144.8	1143.3	1138.9
135°	1203.6	1212.5	1213.9	1213.9	1208.0
137.5°	1269.8	1278.7	1281.6	1283.1	1275.7
140°	1333.1	1340.5	1344.9	1347.8	1340.5
142.5°	1396.4	1402.3	1408.2	1409.6	1402.3
145°	1458.2	1464.1	1468.5	1468.5	1464.1
147.5°	1515.6	1520.0	1522.9	1527.4	1515.6
150°	1573.0	1571.5	1577.4	1577.4	1574.4
152.5°	1620.1	1623.0	1624.5	1628.9	1623.0
155°	1668.6	1668.6	1670.1	1676.0	1668.6
157.5°	1712.8	1709.8	1711.3	1717.2	1706.9
160°	1751.0	1746.6	1748.1	1754.0	1746.6
162.5°	1784.9	1781.9	1781.9	1789.3	1780.4
165°	1814.3	1811.3	1812.8	1818.7	1809.9
167.5°	1840.8	1834.9	1834.9	1843.7	1834.9
170°	1861.4	1855.5	1855.5	1864.3	1854.0
172.5°	1876.1	1870.2	1870.2	1879.0	1870.2
175°	1886.4	1880.5	1880.5	1889.3	1879.0
177.5°	1893.7	1887.9	1886.4	1895.2	1884.9
180°	1890.8	1890.8	1890.8	1890.8	1890.8

(END OF REPORT)