

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034598

Luminaire Tested: S125DIW-B610D470UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034598
REPORT IS A COMBINATION OF REPORTS P1003936 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D470UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4217.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034598

CATALOG NUMBER: S125DIW-B610D470UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034598

CATALOG NUMBER: S125DIW-B610D470UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	109	109	109	109		101	101	101	101		87	87	87		74	74	74		62	62	62
1	99	95	91	87		92	88	85	82		76	74	71		65	63	62		55	54	53
2	90	83	77	71		84	77	72	67		67	63	59		57	54	51		48	46	44
3	82	73	65	59		76	68	61	56		59	54	50		51	47	44		43	40	38
4	75	64	56	50		70	60	53	48		52	47	42		45	41	37		38	35	32
5	69	57	49	43		64	54	46	41		47	41	37		40	36	32		34	31	28
6	64	52	43	37		59	48	41	36		42	36	32		37	32	28		31	28	25
7	59	47	38	33		55	44	36	31		38	32	28		33	29	25		29	25	22
8	55	42	34	29		51	40	33	28		35	29	25		30	26	22		26	23	20
9	51	39	31	26		47	36	29	25		32	26	22		28	23	20		24	21	18
10	48	35	28	23		44	33	27	22		30	24	20		26	21	18		23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5893	5893	5893
5°	5893	5756	5767
10°	5845	5625	5607
15°	5768	5466	5418
20°	5664	5284	5200
25°	5553	5084	4968
30°	5419	4876	4723
35°	5275	4658	4449
40°	5127	4428	4206
45°	4966	4203	3946
50°	4789	3948	3645
55°	4615	3667	3367
60°	4406	3371	3044
65°	4157	3028	2710
70°	3904	2634	2324
75°	3476	2168	1880
80°	2963	1619	1381
85°	2287	959	763

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4966 cd/sqm

TEST NUMBER: P1034598

CATALOG NUMBER: S125DIW-B610D470UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	2.1
10°-20°	245.2	5.8
20°-30°	361.9	8.6
30°-40°	422.3	10.0
40°-50°	424.1	10.1
50°-60°	372.3	8.8
60°-70°	277.3	6.6
70°-80°	158.4	3.8
80°-90°	46.6	1.1
90°-100°	20.1	0.5
100°-110°	133.9	3.2
110°-120°	241.1	5.7
120°-130°	309.4	7.3
130°-140°	332.8	7.9
140°-150°	312.4	7.4
150°-160°	252.7	6.0
160°-170°	163.4	3.9
170°-180°	56.4	1.3
0°-30°	693.9	16.5
0°-40°	1116.2	26.5
0°-60°	1912.6	45.4
0°-90°	2394.9	56.8
90°-120°	395.1	9.4
90°-150°	1349.7	32.0
90°-180°	1822.0	43.2
0°-180°	4217.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	920	920	920	920	920	
5°	918	917	910	916	915	87
15°	875	873	865	869	869	247
25°	795	791	782	783	781	366
35°	686	683	673	670	664	429
45°	562	559	550	541	539	433
55°	428	426	416	409	404	382
65°	289	287	279	273	270	287
75°	154	152	148	146	143	163
85°	40	41	41	40	39	44
90°	0	4	7	9	11	4
95°	25	24	7	9	9	31
105°	129	131	131	131	131	137
115°	243	245	245	244	241	241
125°	345	348	348	346	345	308
135°	430	433	432	431	429	332
145°	499	500	500	500	498	312
155°	550	547	548	549	546	253
165°	580	577	578	580	577	164
175°	593	590	591	594	590	56
180°	593	593	593	593	593	

TEST NUMBER: P1034598

CATALOG NUMBER: S125DIW-B610D470UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	919.8	919.8	919.8	919.8	919.8
2.5°	922.7	920.5	913.2	920.5	919.8
5°	918.3	916.9	909.6	916.2	915.4
7.5°	911.8	910.3	902.3	908.9	908.2
10°	902.3	900.9	892.9	898.7	898.0
12.5°	890.7	887.8	880.5	884.9	884.9
15°	875.4	873.2	865.2	868.9	868.9
17.5°	859.4	855.8	847.8	852.1	848.5
20°	838.3	836.8	827.4	832.5	828.8
22.5°	817.2	814.3	805.5	808.5	806.3
25°	794.6	791.0	781.5	783.0	780.8
27.5°	768.4	766.3	756.8	757.5	755.3
30°	743.0	740.8	729.9	728.4	726.2
32.5°	715.3	711.7	702.2	699.3	694.9
35°	686.2	683.3	673.1	669.5	663.6
37.5°	656.4	652.7	643.3	638.2	634.5
40°	625.8	622.2	612.0	605.4	603.3
42.5°	593.1	590.2	580.0	574.1	570.5
45°	561.8	558.9	550.1	541.4	539.2
47.5°	527.6	528.3	517.4	508.7	503.6
50°	494.8	492.6	483.9	474.5	469.4
52.5°	461.4	459.9	450.4	442.4	436.6
55°	427.9	425.7	415.5	409.0	403.9
57.5°	392.2	391.5	382.8	374.0	371.8
60°	358.7	355.8	347.8	340.6	335.5
62.5°	323.8	321.6	315.1	307.1	303.4
65°	288.9	287.4	279.4	272.9	270.0
67.5°	254.7	251.8	246.0	240.1	238.7
70°	222.7	219.0	212.5	208.1	205.2
72.5°	187.7	185.6	181.9	176.8	173.9
75°	153.5	152.1	148.4	146.3	143.4
77.5°	121.5	120.8	118.6	117.2	115.0
80°	91.7	91.7	90.2	89.5	88.0
82.5°	65.5	64.0	64.0	62.6	62.6
85°	40.0	40.8	40.8	40.0	38.6
87.5°	19.6	19.6	18.9	18.9	17.5
90°	0.4	4.0	7.0	9.2	10.6
92.5°	8.4	4.4	7.0	9.2	9.7
95°	25.1	23.7	7.0	9.2	9.2
97.5°	47.0	49.7	7.9	8.8	9.2
100°	73.4	74.8	76.5	11.0	9.2
102.5°	100.3	102.0	102.9	103.8	66.8
105°	129.3	131.0	131.0	131.0	130.6
107.5°	159.2	159.2	160.1	160.5	158.7
110°	188.2	188.2	189.1	187.8	188.2



TEST NUMBER: P1034598

CATALOG NUMBER: S125DIW-B610D470UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.5	216.8	217.2	215.5	214.6
115°	242.7	244.9	245.4	243.6	241.0
117.5°	271.3	271.3	273.1	270.4	269.5
120°	297.7	297.2	298.6	297.7	295.5
122.5°	321.0	323.2	323.6	322.8	320.1
125°	345.2	348.3	348.3	346.5	345.2
127.5°	368.5	370.7	370.2	369.4	365.8
130°	389.6	391.8	392.2	390.9	388.7
132.5°	410.7	413.3	412.0	412.0	409.8
135°	430.5	433.1	432.2	431.4	428.7
137.5°	449.0	451.6	450.7	450.7	448.5
140°	467.0	467.9	467.4	468.3	465.7
142.5°	483.2	483.7	484.6	484.6	481.9
145°	499.1	500.0	500.0	500.4	497.8
147.5°	513.2	513.2	513.6	514.0	511.0
150°	526.3	525.5	526.3	527.2	523.7
152.5°	539.1	536.9	537.8	538.7	535.6
155°	549.6	547.0	547.9	549.2	545.7
157.5°	558.0	556.7	556.7	558.0	554.5
160°	566.8	564.2	564.6	566.4	562.8
162.5°	573.8	571.2	571.6	574.3	570.3
165°	580.0	577.3	577.8	580.4	576.9
167.5°	584.8	582.2	582.6	585.7	581.7
170°	588.8	585.7	586.1	589.7	585.7
172.5°	591.4	588.3	589.2	592.3	588.3
175°	593.2	590.5	591.0	594.5	590.5
177.5°	594.5	591.9	592.3	595.4	591.9
180°	593.2	593.2	593.2	593.2	593.2

(END OF REPORT)