

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034604

Luminaire Tested: S125DIW-B610D770UB2750-4F0-XX-W2A-D1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034604
REPORT IS A COMBINATION OF REPORTS P1003989 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D770UB2750-4F0-XX-W2A-D1_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4903.9 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034604

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034604

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	96	91	87	83	87	84	80	77	69	67	64	56	54	53	44	43	41
2	87	79	73	68	79	73	67	63	60	56	53	49	46	43	38	36	34
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29
4	72	61	53	47	66	56	49	44	47	41	37	38	34	31	30	27	25
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	21
6	61	49	41	35	55	45	38	32	38	32	28	31	26	23	24	21	19
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	22	19	17
8	52	40	32	27	48	37	30	25	31	25	22	25	21	18	20	17	15
9	49	36	29	24	44	34	27	22	28	23	19	23	19	16	19	16	13
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4755	4755	4755
5°	4762	4655	4667
10°	4727	4560	4547
15°	4670	4450	4401
20°	4592	4316	4255
25°	4500	4174	4079
30°	4388	4020	3918
35°	4284	3877	3770
40°	4178	3727	3622
45°	4058	3596	3488
50°	3943	3455	3367
55°	3806	3320	3227
60°	3655	3166	3083
65°	3497	3004	2920
70°	3316	2787	2752
75°	3032	2573	2547
80°	2656	2312	2319
85°	2287	2104	2199

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4058 cd/sqm

TEST NUMBER: P1034604

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.2	1.4
10°-20°	199.4	4.1
20°-30°	296.5	6.0
30°-40°	351.1	7.2
40°-50°	363.0	7.4
50°-60°	334.4	6.8
60°-70°	270.3	5.5
70°-80°	180.9	3.7
80°-90°	94.9	1.9
90°-100°	114.7	2.3
100°-110°	223.1	4.5
110°-120°	338.5	6.9
120°-130°	426.2	8.7
130°-140°	467.5	9.5
140°-150°	453.2	9.2
150°-160°	379.6	7.7
160°-170°	252.3	5.1
170°-180°	88.3	1.8
0°-30°	566.0	11.5
0°-40°	917.1	18.7
0°-60°	1614.5	32.9
0°-90°	2160.5	44.1
90°-120°	676.3	13.8
90°-150°	2023.2	41.3
90°-180°	2743.0	55.9
0°-180°	4903.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	742	742	742	742	742	
5°	742	741	736	741	741	70
15°	709	709	704	709	706	200
25°	644	646	642	645	641	296
35°	557	562	560	562	562	349
45°	459	467	471	476	477	354
55°	353	364	376	384	387	315
65°	243	260	277	288	291	241
75°	134	153	176	191	194	142
85°	40	64	90	106	111	42
90°	12	41	71	92	99	11
95°	57	77	109	130	137	57
105°	172	187	214	232	240	183
115°	317	325	346	358	362	314
125°	460	463	478	489	492	412
135°	595	599	605	614	615	459
145°	720	722	724	728	729	450
155°	823	823	824	827	823	379
165°	895	894	894	897	893	253
175°	931	928	928	932	927	88
180°	933	933	933	933	933	

TEST NUMBER: P1034604

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	742.1	742.1	742.1	742.1	742.1
2.5°	744.3	742.9	737.8	742.9	742.1
5°	742.1	740.7	735.6	741.4	740.7
7.5°	737.0	736.3	731.2	736.3	735.6
10°	729.8	729.8	723.9	729.0	728.3
12.5°	719.6	720.3	715.9	719.6	717.4
15°	708.7	709.4	704.3	708.7	705.8
17.5°	694.8	696.3	691.2	694.8	692.7
20°	679.6	681.0	675.9	678.1	678.1
22.5°	662.1	665.0	659.2	662.1	659.9
25°	643.9	646.1	641.7	644.6	641.0
27.5°	624.3	627.2	622.1	624.3	622.8
30°	601.7	606.1	601.7	603.2	602.4
32.5°	581.3	585.0	582.1	583.5	582.8
35°	557.3	562.4	560.2	562.4	562.4
37.5°	534.0	538.4	537.7	540.6	539.9
40°	510.0	515.9	515.1	518.0	519.5
42.5°	483.8	491.8	494.0	497.7	497.7
45°	459.1	467.1	470.7	475.8	476.6
47.5°	433.6	440.9	446.7	454.0	455.5
50°	407.4	415.4	423.5	431.5	433.6
52.5°	379.8	390.0	400.2	408.9	410.4
55°	352.9	364.5	376.2	384.2	387.1
57.5°	325.2	339.1	352.1	360.9	363.1
60°	297.6	312.1	326.7	337.6	339.8
62.5°	270.7	285.2	301.2	313.6	316.5
65°	243.0	259.7	277.2	288.1	291.0
67.5°	217.5	233.6	251.0	264.1	267.8
70°	189.2	205.9	224.8	238.6	243.0
72.5°	161.5	179.0	200.1	215.4	218.3
75°	133.9	152.8	176.1	190.6	194.3
77.5°	107.0	128.8	150.6	166.6	169.5
80°	82.2	104.0	128.8	144.8	147.7
82.5°	59.7	82.9	108.4	123.7	129.5
85°	40.0	64.0	89.5	105.5	111.3
87.5°	25.5	48.7	73.5	90.2	95.3
90°	12.3	41.4	71.3	91.6	98.9
92.5°	32.0	56.7	88.7	109.8	116.4
95°	56.7	77.0	109.0	130.1	136.6
97.5°	81.3	99.5	133.7	153.3	159.2
100°	109.6	124.9	157.7	179.4	185.3
102.5°	140.2	157.6	183.8	205.6	212.1
105°	172.0	187.3	213.5	232.5	239.7
107.5°	206.9	220.7	245.5	262.2	266.5
110°	243.2	255.5	278.1	294.1	298.5

TEST NUMBER: P1034604

CATALOG NUMBER: S125DIW-B610D770UB2750-4F0-XX-W2A-D1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.0	288.9	311.5	325.3	329.0
115°	317.3	325.3	345.6	358.0	361.6
117.5°	354.2	358.7	378.3	391.3	393.5
120°	389.1	394.9	412.4	424.7	426.2
122.5°	426.1	427.6	445.7	456.7	458.9
125°	459.5	463.2	478.4	488.7	491.5
127.5°	495.9	497.3	510.4	520.5	523.5
130°	528.5	531.5	543.0	552.5	554.7
132.5°	560.5	567.0	573.5	583.0	583.7
135°	595.3	598.9	604.7	614.2	614.9
137.5°	628.0	631.6	635.9	645.4	644.7
140°	658.4	662.1	665.0	674.5	673.8
142.5°	689.6	691.8	694.7	702.0	701.3
145°	720.1	722.3	724.5	728.1	728.8
147.5°	747.7	749.9	751.4	755.1	750.6
150°	776.1	775.3	778.2	778.2	777.5
152.5°	799.3	800.7	801.5	803.6	800.7
155°	823.2	823.2	824.0	826.9	823.2
157.5°	845.0	843.6	844.3	847.2	842.1
160°	863.9	861.7	862.4	865.3	861.7
162.5°	880.6	879.1	879.1	882.8	878.4
165°	895.1	893.7	894.4	897.3	892.9
167.5°	908.2	905.3	905.3	909.6	905.3
170°	918.3	915.4	915.4	919.8	914.7
172.5°	925.6	922.7	922.7	927.1	922.7
175°	930.7	927.8	927.8	932.1	927.1
177.5°	934.3	931.4	930.7	935.0	930.0
180°	932.9	932.9	932.9	932.9	932.9

(END OF REPORT)