

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035153

Luminaire Tested: S125DIW-B1270D1560UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035153
REPORT IS A COMBINATION OF REPORTS P1003217 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1560UB30-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11473.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035153

CATALOG NUMBER: S125DIW-B1270D1560UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035153

CATALOG NUMBER: S125DIW-B1270D1560UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27
5	67	56	48	42	61	51	44	39	43	38	34	36	31	28	28	25	23
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	19	22	19	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12655	12655	12655
5°	12656	12362	12385
10°	12551	12078	12040
15°	12387	11739	11634
20°	12164	11346	11168
25°	11924	10918	10669
30°	11636	10471	10143
35°	11328	10003	9554
40°	11009	9508	9031
45°	10665	9026	8474
50°	10285	8479	7826
55°	9911	7875	7230
60°	9462	7239	6536
65°	8927	6503	5819
70°	8382	5657	4991
75°	7465	4658	4035
80°	6363	3480	2969
85°	4911	2057	1636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10665 cd/sqm

TEST NUMBER: P1035153

CATALOG NUMBER: S125DIW-B1270D1560UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.4	1.6
10°-20°	526.5	4.6
20°-30°	777.2	6.8
30°-40°	906.8	7.9
40°-50°	910.8	7.9
50°-60°	799.5	7.0
60°-70°	595.5	5.2
70°-80°	340.1	3.0
80°-90°	101.2	0.9
90°-100°	69.9	0.6
100°-110°	465.0	4.1
110°-120°	837.4	7.3
120°-130°	1074.8	9.4
130°-140°	1156.0	10.1
140°-150°	1084.9	9.5
150°-160°	877.6	7.6
160°-170°	567.6	4.9
170°-180°	195.7	1.7
0°-30°	1490.1	13.0
0°-40°	2396.9	20.9
0°-60°	4107.2	35.8
0°-90°	5144.1	44.8
90°-120°	1372.3	12.0
90°-150°	4688.0	40.9
90°-180°	6329.0	55.2
0°-180°	11473.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1975	1975	1975	1975	1975	
5°	1972	1969	1953	1967	1966	187
15°	1880	1875	1858	1866	1866	530
25°	1706	1699	1678	1681	1677	785
35°	1474	1467	1446	1438	1425	922
45°	1206	1200	1181	1163	1158	929
55°	919	914	892	878	867	820
65°	620	617	600	586	580	615
75°	330	327	319	314	308	351
85°	86	88	88	86	83	94
90°	2	14	24	32	37	10
95°	87	82	24	32	32	107
105°	449	455	455	455	454	476
115°	843	851	852	846	837	836
125°	1199	1210	1210	1204	1199	1071
135°	1495	1504	1501	1498	1489	1153
145°	1734	1737	1737	1738	1729	1084
155°	1909	1900	1903	1908	1895	880
165°	2014	2005	2007	2016	2004	569
175°	2060	2051	2053	2065	2051	196
180°	2060	2060	2060	2060	2060	

TEST NUMBER: P1035153

CATALOG NUMBER: S125DIW-B1270D1560UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1975.2	1975.2	1975.2	1975.2	1975.2
2.5°	1981.5	1976.8	1961.2	1976.8	1975.2
5°	1972.1	1969.0	1953.3	1967.4	1965.8
7.5°	1958.0	1954.9	1937.7	1951.8	1950.2
10°	1937.7	1934.6	1917.4	1929.9	1928.3
12.5°	1912.7	1906.5	1890.8	1900.2	1900.2
15°	1879.9	1875.2	1858.0	1865.8	1865.8
17.5°	1845.5	1837.7	1820.5	1829.9	1822.1
20°	1800.2	1797.1	1776.8	1787.7	1779.9
22.5°	1754.9	1748.6	1729.9	1736.1	1731.4
25°	1706.4	1698.6	1678.3	1681.4	1676.7
27.5°	1650.2	1645.5	1625.2	1626.7	1622.1
30°	1595.5	1590.8	1567.4	1564.2	1559.5
32.5°	1536.1	1528.3	1508.0	1501.7	1492.4
35°	1473.6	1467.3	1445.5	1437.7	1425.2
37.5°	1409.5	1401.7	1381.4	1370.5	1362.6
40°	1343.9	1336.1	1314.2	1300.1	1295.5
42.5°	1273.6	1267.3	1245.4	1232.9	1225.1
45°	1206.4	1200.1	1181.4	1162.6	1157.9
47.5°	1132.9	1134.5	1111.1	1092.3	1081.4
50°	1062.6	1057.9	1039.2	1018.9	1007.9
52.5°	990.7	987.6	967.3	950.1	937.6
55°	918.9	914.2	892.3	878.2	867.3
57.5°	842.3	840.7	822.0	803.2	798.5
60°	770.4	764.1	747.0	731.3	720.4
62.5°	695.4	690.7	676.6	659.4	651.6
65°	620.4	617.3	600.1	586.0	579.8
67.5°	546.9	540.7	528.2	515.7	512.6
70°	478.2	470.4	456.3	446.9	440.7
72.5°	403.2	398.5	390.7	379.7	373.5
75°	329.7	326.6	318.8	314.1	307.8
77.5°	261.0	259.4	254.7	251.6	246.9
80°	196.9	196.9	193.8	192.2	189.1
82.5°	140.6	137.5	137.5	134.4	134.4
85°	85.9	87.5	87.5	85.9	82.8
87.5°	42.2	42.2	40.6	40.6	37.5
90°	1.5	13.7	24.4	32.1	36.7
92.5°	29.0	15.3	24.4	32.1	33.6
95°	87.1	82.5	24.4	32.1	32.1
97.5°	163.4	172.6	27.5	30.5	32.1
100°	255.1	259.6	265.8	38.2	32.1
102.5°	348.2	354.3	357.4	360.4	232.2
105°	449.0	455.1	455.1	455.1	453.6
107.5°	552.9	552.9	555.9	557.5	551.4
110°	653.7	653.7	656.7	652.2	653.7

TEST NUMBER: P1035153

CATALOG NUMBER: S125DIW-B1270D1560UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	748.4	753.0	754.5	748.4	745.3
115°	843.1	850.7	852.2	846.1	837.0
117.5°	942.4	942.4	948.5	939.3	936.2
120°	1034.0	1032.5	1037.0	1034.0	1026.4
122.5°	1114.9	1122.6	1124.1	1121.0	1111.9
125°	1198.9	1209.6	1209.6	1203.5	1198.9
127.5°	1279.9	1287.5	1286.0	1282.9	1270.7
130°	1353.2	1360.8	1362.4	1357.8	1350.1
132.5°	1426.5	1435.7	1431.1	1431.1	1423.5
135°	1495.2	1504.4	1501.3	1498.3	1489.1
137.5°	1559.4	1568.6	1565.5	1565.5	1557.9
140°	1622.0	1625.1	1623.5	1626.6	1617.4
142.5°	1678.5	1680.0	1683.1	1683.1	1673.9
145°	1733.5	1736.6	1736.6	1738.1	1728.9
147.5°	1782.4	1782.4	1783.9	1785.4	1774.7
150°	1828.2	1825.1	1828.2	1831.2	1819.0
152.5°	1872.5	1864.8	1867.9	1871.0	1860.3
155°	1909.1	1900.0	1903.0	1907.6	1895.4
157.5°	1938.2	1933.6	1933.6	1938.2	1925.9
160°	1968.7	1959.5	1961.1	1967.2	1955.0
162.5°	1993.1	1984.0	1985.5	1994.7	1980.9
165°	2014.5	2005.4	2006.9	2016.1	2003.8
167.5°	2031.3	2022.2	2023.7	2034.4	2020.6
170°	2045.1	2034.4	2035.9	2048.1	2034.4
172.5°	2054.2	2043.5	2046.6	2057.3	2043.5
175°	2060.3	2051.2	2052.7	2064.9	2051.2
177.5°	2064.9	2055.8	2057.3	2068.0	2055.8
180°	2060.3	2060.3	2060.3	2060.3	2060.3

(END OF REPORT)