

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035157

Luminaire Tested: S125DIW-B1270D1560UB35-4F0-XX-W2A-D

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035157
REPORT IS A COMBINATION OF REPORTS P1003223 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D1560UB35-4F0-XX-W2A-D
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11318.9 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035157

CATALOG NUMBER: S125DIW-B1270D1560UB35-4F0-XX-W2A-D

Luminous Intensity Polar Plot



TEST NUMBER: P1035157

CATALOG NUMBER: S125DIW-B1270D1560UB35-4F0-XX-W2A-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41		
1	95	91	87	83	87	83	79	76	68	65	63	54	52	51	41	40	39	33		
2	86	79	73	67	78	72	67	62	59	55	52	47	44	42	36	34	33	28		
3	79	69	62	56	71	63	57	51	52	47	43	41	38	35	32	29	27	23		
4	72	61	53	47	65	56	49	43	46	41	37	37	33	30	28	26	24	20		
5	66	54	46	40	60	50	42	37	41	36	31	33	29	26	25	23	20	17		
6	61	48	40	34	55	44	37	32	37	31	27	30	26	22	23	20	18	15		
7	56	44	36	30	51	40	33	28	33	28	24	27	23	20	21	18	16	13		
8	52	40	32	26	47	36	29	25	30	25	21	25	21	18	19	16	14	12		
9	48	36	29	23	44	33	26	22	28	22	19	23	19	16	18	15	13	10		
10	45	33	26	21	41	30	24	20	25	20	17	21	17	14	16	14	12	9		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10256	10256	10256
5°	10273	10042	10066
10°	10196	9837	9809
15°	10072	9599	9492
20°	9904	9311	9178
25°	9706	9004	8798
30°	9466	8671	8452
35°	9241	8362	8133
40°	9013	8038	7812
45°	8754	7757	7523
50°	8507	7452	7263
55°	8210	7161	6960
60°	7884	6830	6649
65°	7543	6479	6301
70°	7152	6011	5936
75°	6539	5549	5492
80°	5729	4988	5002
85°	4934	4538	4743

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8754 cd/sqm

TEST NUMBER: P1035157

CATALOG NUMBER: S125DIW-B1270D1560UB35-4F0-XX-W2A-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.5	1.3
10°-20°	430.0	3.8
20°-30°	639.5	5.6
30°-40°	757.3	6.7
40°-50°	782.9	6.9
50°-60°	721.2	6.4
60°-70°	583.0	5.2
70°-80°	390.1	3.4
80°-90°	204.7	1.8
90°-100°	183.8	1.6
100°-110°	550.8	4.9
110°-120°	897.1	7.9
120°-130°	1111.3	9.8
130°-140°	1175.0	10.4
140°-150°	1092.5	9.7
150°-160°	881.5	7.8
160°-170°	570.1	5.0
170°-180°	196.6	1.7
0°-30°	1221.0	10.8
0°-40°	1978.3	17.5
0°-60°	3482.4	30.8
0°-90°	4660.3	41.2
90°-120°	1631.7	14.4
90°-150°	5010.5	44.3
90°-180°	6659.0	58.8
0°-180°	11318.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1601	1601	1601	1601	1601	
5°	1601	1598	1587	1599	1598	152
15°	1529	1530	1519	1529	1522	431
25°	1389	1394	1384	1390	1383	639
35°	1202	1213	1208	1213	1213	753
45°	990	1008	1015	1026	1028	764
55°	761	786	811	829	835	680
65°	524	560	598	622	628	520
75°	289	330	380	411	419	306
85°	86	138	193	228	240	90
90°	27	89	153	197	213	22
95°	108	144	139	181	192	123
105°	465	496	544	575	584	493
115°	856	875	917	939	940	849
125°	1210	1220	1251	1270	1273	1081
135°	1505	1513	1521	1538	1536	1160
145°	1743	1744	1744	1754	1751	1090
155°	1918	1908	1911	1916	1904	884
165°	2023	2014	2016	2025	2013	572
175°	2070	2060	2062	2074	2060	197
180°	2070	2070	2070	2070	2070	

TEST NUMBER: P1035157

CATALOG NUMBER: S125DIW-B1270D1560UB35-4F0-XX-W2A-D

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1600.8	1600.8	1600.8	1600.8	1600.8
2.5°	1605.5	1602.4	1591.4	1602.4	1600.8
5°	1600.8	1597.7	1586.7	1599.2	1597.7
7.5°	1589.8	1588.2	1577.3	1588.2	1586.7
10°	1574.1	1574.1	1561.6	1572.6	1571.0
12.5°	1552.1	1553.7	1544.3	1552.1	1547.4
15°	1528.6	1530.2	1519.2	1528.6	1522.3
17.5°	1498.8	1501.9	1490.9	1498.8	1494.1
20°	1465.8	1469.0	1458.0	1462.7	1462.7
22.5°	1428.2	1434.4	1421.9	1428.2	1423.5
25°	1388.9	1393.6	1384.2	1390.5	1382.7
27.5°	1346.6	1352.8	1341.8	1346.6	1343.4
30°	1297.9	1307.3	1297.9	1301.0	1299.5
32.5°	1254.0	1261.8	1255.5	1258.7	1257.1
35°	1202.2	1213.2	1208.4	1213.2	1213.2
37.5°	1151.9	1161.4	1159.8	1166.1	1164.5
40°	1100.2	1112.7	1111.1	1117.4	1120.6
42.5°	1043.7	1060.9	1065.6	1073.5	1073.5
45°	990.3	1007.6	1015.4	1026.4	1028.0
47.5°	935.4	951.1	963.6	979.3	982.5
50°	878.9	896.1	913.4	930.7	935.4
52.5°	819.2	841.2	863.2	882.0	885.1
55°	761.2	786.3	811.4	828.6	834.9
57.5°	701.5	731.3	759.6	778.4	783.1
60°	641.9	673.3	704.7	728.2	732.9
62.5°	583.8	615.2	649.7	676.4	682.7
65°	524.2	560.3	597.9	621.5	627.8
67.5°	469.3	503.8	541.4	569.7	577.5
70°	408.0	444.1	484.9	514.8	524.2
72.5°	348.4	386.1	431.6	464.5	470.8
75°	288.8	329.6	379.8	411.2	419.0
77.5°	230.7	277.8	324.9	359.4	365.7
80°	177.3	224.4	277.8	312.3	318.6
82.5°	128.7	178.9	233.8	266.8	279.4
85°	86.3	138.1	193.0	227.6	240.1
87.5°	54.9	105.2	158.5	194.6	205.6
90°	26.6	89.1	153.2	197.0	212.6
92.5°	51.1	82.8	146.9	189.1	201.6
95°	107.8	144.0	139.1	181.3	192.3
97.5°	182.9	229.8	135.9	171.9	184.4
100°	273.5	311.0	367.3	171.8	175.0
102.5°	365.5	401.4	453.2	487.6	368.2
105°	465.1	496.4	543.5	574.9	584.3
107.5°	567.9	589.8	638.4	671.3	674.6
110°	667.6	686.4	733.4	758.6	771.2

TEST NUMBER: P1035157

CATALOG NUMBER: S125DIW-B1270D1560UB35-4F0-XX-W2A-D

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	762.7	781.4	825.3	847.4	855.3
115°	856.2	874.9	917.2	939.4	939.6
117.5°	954.3	962.2	1007.6	1025.1	1033.0
120°	1046.4	1049.6	1090.3	1113.9	1115.6
122.5°	1126.2	1135.3	1171.5	1193.5	1193.7
125°	1210.5	1219.7	1251.1	1270.0	1273.3
127.5°	1290.2	1296.3	1321.5	1342.0	1339.1
130°	1363.9	1370.0	1393.5	1410.9	1411.0
132.5°	1435.9	1445.1	1456.2	1478.2	1476.8
135°	1505.0	1512.7	1520.6	1537.9	1536.5
137.5°	1569.4	1577.1	1580.2	1599.1	1597.7
140°	1630.8	1633.8	1633.8	1654.2	1651.3
142.5°	1687.5	1687.5	1690.5	1704.6	1701.7
145°	1742.8	1744.2	1744.2	1753.6	1750.7
147.5°	1790.3	1790.3	1791.8	1796.4	1788.9
150°	1836.3	1833.2	1836.3	1839.3	1828.7
152.5°	1880.8	1873.1	1876.2	1879.2	1868.5
155°	1917.6	1908.4	1911.4	1916.0	1903.8
157.5°	1946.7	1942.1	1942.1	1946.7	1934.5
160°	1977.4	1968.2	1969.7	1975.9	1963.6
162.5°	2002.0	1992.8	1994.3	2003.5	1989.7
165°	2023.4	2014.2	2015.8	2025.0	2012.7
167.5°	2040.3	2031.1	2032.6	2043.4	2029.6
170°	2054.1	2043.4	2044.9	2057.2	2043.4
172.5°	2063.3	2052.6	2055.6	2066.4	2052.6
175°	2069.5	2060.3	2061.8	2074.1	2060.3
177.5°	2074.1	2064.9	2066.4	2077.1	2064.9
180°	2069.5	2069.5	2069.5	2069.5	2069.5

(END OF REPORT)