

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034626

Luminaire Tested: S125DIW-B850D1050UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034626
REPORT IS A COMBINATION OF REPORTS P1004065 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B850D1050UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7688.0 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034626

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034626

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43
2	88	80	74	69	80	74	69	64	62	58	54	50	48	45	40	38	36
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	31	29	27
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	26	23	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	27	22	19	22	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8456	8456	8456
5°	8456	8259	8275
10°	8386	8070	8045
15°	8276	7843	7774
20°	8127	7581	7462
25°	7968	7295	7128
30°	7774	6996	6777
35°	7569	6683	6384
40°	7356	6353	6034
45°	7126	6030	5662
50°	6872	5665	5229
55°	6621	5262	4831
60°	6322	4837	4367
65°	5964	4345	3888
70°	5601	3780	3334
75°	4988	3112	2696
80°	4253	2325	1983
85°	3282	1376	1092

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7126 cd/sqm

TEST NUMBER: P1034626

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.5	1.6
10°-20°	351.8	4.6
20°-30°	519.3	6.8
30°-40°	605.9	7.9
40°-50°	608.5	7.9
50°-60°	534.2	6.9
60°-70°	397.9	5.2
70°-80°	227.2	3.0
80°-90°	67.7	0.9
90°-100°	47.0	0.6
100°-110°	312.3	4.1
110°-120°	562.4	7.3
120°-130°	721.9	9.4
130°-140°	776.4	10.1
140°-150°	728.7	9.5
150°-160°	589.5	7.7
160°-170°	381.2	5.0
170°-180°	131.5	1.7
0°-30°	995.6	13.0
0°-40°	1601.5	20.8
0°-60°	2744.3	35.7
0°-90°	3437.1	44.7
90°-120°	921.7	12.0
90°-150°	3148.8	41.0
90°-180°	4251.0	55.3
0°-180°	7688.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1320	1320	1320	1320	1320	
5°	1318	1316	1305	1314	1314	125
15°	1256	1253	1241	1247	1247	354
25°	1140	1135	1121	1124	1120	525
35°	985	980	966	961	952	616
45°	806	802	789	777	774	621
55°	614	611	596	587	580	548
65°	414	412	401	392	387	411
75°	220	218	213	210	206	235
85°	57	58	58	57	55	63
90°	1	9	16	22	25	7
95°	58	55	16	22	22	72
105°	302	306	306	306	305	320
115°	566	571	572	568	562	561
125°	805	812	812	808	805	719
135°	1004	1010	1008	1006	1000	774
145°	1164	1166	1166	1167	1161	728
155°	1282	1276	1278	1281	1273	591
165°	1353	1347	1348	1354	1346	382
175°	1384	1378	1379	1387	1378	132
180°	1384	1384	1384	1384	1384	

TEST NUMBER: P1034626

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1319.8	1319.8	1319.8	1319.8	1319.8
2.5°	1323.9	1320.8	1310.4	1320.8	1319.8
5°	1317.7	1315.6	1305.1	1314.5	1313.5
7.5°	1308.3	1306.2	1294.7	1304.1	1303.1
10°	1294.7	1292.6	1281.1	1289.5	1288.4
12.5°	1278.0	1273.8	1263.4	1269.6	1269.6
15°	1256.1	1252.9	1241.4	1246.7	1246.7
17.5°	1233.1	1227.9	1216.4	1222.7	1217.4
20°	1202.8	1200.7	1187.2	1194.5	1189.2
22.5°	1172.5	1168.4	1155.8	1160.0	1156.9
25°	1140.2	1134.9	1121.4	1123.5	1120.3
27.5°	1102.6	1099.4	1085.9	1086.9	1083.8
30°	1066.0	1062.9	1047.2	1045.2	1042.0
32.5°	1026.4	1021.1	1007.6	1003.4	997.1
35°	984.6	980.4	965.8	960.6	952.2
37.5°	941.8	936.6	923.0	915.7	910.5
40°	897.9	892.7	878.1	868.7	865.6
42.5°	851.0	846.8	832.2	823.8	818.6
45°	806.1	801.9	789.3	776.8	773.7
47.5°	757.0	758.0	742.4	729.8	722.5
50°	710.0	706.9	694.3	680.8	673.5
52.5°	662.0	659.9	646.3	634.8	626.5
55°	613.9	610.8	596.2	586.8	579.5
57.5°	562.8	561.7	549.2	536.7	533.5
60°	514.7	510.6	499.1	488.6	481.3
62.5°	464.6	461.5	452.1	440.6	435.4
65°	414.5	412.4	400.9	391.5	387.4
67.5°	365.4	361.3	352.9	344.6	342.5
70°	319.5	314.3	304.9	298.6	294.4
72.5°	269.4	266.2	261.0	253.7	249.5
75°	220.3	218.2	213.0	209.9	205.7
77.5°	174.4	173.3	170.2	168.1	165.0
80°	131.6	131.6	129.5	128.4	126.3
82.5°	94.0	91.9	91.9	89.8	89.8
85°	57.4	58.5	58.5	57.4	55.3
87.5°	28.2	28.2	27.1	27.1	25.1
90°	1.0	9.2	16.4	21.5	24.6
92.5°	19.5	10.3	16.4	21.5	22.6
95°	58.5	55.4	16.4	21.5	21.5
97.5°	109.8	115.9	18.5	20.5	21.5
100°	171.3	174.4	178.5	25.6	21.5
102.5°	233.9	238.0	240.0	242.1	155.9
105°	301.6	305.7	305.7	305.7	304.7
107.5°	371.4	371.4	373.4	374.4	370.3
110°	439.1	439.1	441.1	438.0	439.1

TEST NUMBER: P1034626

CATALOG NUMBER: S125DIW-B850D1050UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	502.7	505.7	506.8	502.7	500.6
115°	566.3	571.4	572.4	568.3	562.2
117.5°	632.9	632.9	637.1	630.9	628.8
120°	694.5	693.5	696.5	694.5	689.4
122.5°	748.9	754.0	755.0	753.0	746.8
125°	805.3	812.5	812.5	808.4	805.3
127.5°	859.7	864.8	863.8	861.7	853.5
130°	908.9	914.0	915.1	912.0	906.8
132.5°	958.1	964.3	961.2	961.2	956.1
135°	1004.3	1010.5	1008.4	1006.4	1000.2
137.5°	1047.4	1053.5	1051.5	1051.5	1046.4
140°	1089.4	1091.5	1090.5	1092.5	1086.4
142.5°	1127.4	1128.4	1130.5	1130.5	1124.3
145°	1164.3	1166.4	1166.4	1167.4	1161.3
147.5°	1197.2	1197.2	1198.2	1199.2	1192.0
150°	1227.9	1225.9	1227.9	1230.0	1221.8
152.5°	1257.7	1252.6	1254.6	1256.7	1249.5
155°	1282.3	1276.2	1278.2	1281.3	1273.1
157.5°	1301.8	1298.7	1298.7	1301.8	1293.6
160°	1322.3	1316.2	1317.2	1321.3	1313.1
162.5°	1338.7	1332.6	1333.6	1339.8	1330.5
165°	1353.1	1346.9	1348.0	1354.1	1345.9
167.5°	1364.4	1358.2	1359.2	1366.4	1357.2
170°	1373.6	1366.4	1367.5	1375.7	1366.4
172.5°	1379.8	1372.6	1374.6	1381.8	1372.6
175°	1383.9	1377.7	1378.7	1386.9	1377.7
177.5°	1386.9	1380.8	1381.8	1389.0	1380.8
180°	1383.9	1383.9	1383.9	1383.9	1383.9

(END OF REPORT)