

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034639

Luminaire Tested: S125DIW-B850D1340UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034639
REPORT IS A COMBINATION OF REPORTS P1004128 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B850D1340UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7781.0 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034639

CATALOG NUMBER: S125DIW-B850D1340UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034639

CATALOG NUMBER: S125DIW-B850D1340UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	47	42	38	39	35	32	30	28	25
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8131	8131	8131
5°	8131	7942	7957
10°	8064	7760	7735
15°	7958	7542	7475
20°	7815	7289	7175
25°	7662	7014	6855
30°	7476	6727	6517
35°	7278	6427	6138
40°	7073	6109	5802
45°	6852	5799	5445
50°	6608	5448	5028
55°	6367	5060	4645
60°	6080	4651	4199
65°	5735	4178	3738
70°	5385	3635	3206
75°	4796	2992	2593
80°	4088	2235	1907
85°	3156	1321	1051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6852 cd/sqm

TEST NUMBER: P1034639

CATALOG NUMBER: S125DIW-B850D1340UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	1.5
10°-20°	338.2	4.3
20°-30°	499.4	6.4
30°-40°	582.6	7.5
40°-50°	585.2	7.5
50°-60°	513.6	6.6
60°-70°	382.6	4.9
70°-80°	218.5	2.8
80°-90°	65.6	0.8
90°-100°	106.6	1.4
100°-110°	316.8	4.1
110°-120°	537.3	6.9
120°-130°	707.3	9.1
130°-140°	792.6	10.2
140°-150°	776.9	10.0
150°-160°	652.5	8.4
160°-170°	433.8	5.6
170°-180°	151.8	2.0
0°-30°	957.4	12.3
0°-40°	1540.0	19.8
0°-60°	2638.8	33.9
0°-90°	3305.5	42.5
90°-120°	960.7	12.3
90°-150°	3237.4	41.6
90°-180°	4475.0	57.5
0°-180°	7781.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1267	1265	1255	1264	1263	120
15°	1208	1205	1194	1199	1199	341
25°	1096	1091	1078	1080	1077	504
35°	947	943	929	924	916	592
45°	775	771	759	747	744	597
55°	590	587	573	564	557	527
65°	399	397	386	376	372	395
75°	212	210	205	202	198	226
85°	55	56	56	55	53	60
90°	1	11	20	26	30	9
95°	81	84	96	105	107	85
105°	284	291	298	306	310	303
115°	538	543	545	544	543	532
125°	785	792	794	791	790	703
135°	1021	1028	1030	1030	1025	787
145°	1237	1242	1245	1245	1242	773
155°	1415	1415	1416	1421	1415	652
165°	1539	1536	1538	1542	1535	434
175°	1600	1595	1595	1602	1594	152
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P1034639

CATALOG NUMBER: S125DIW-B850D1340UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1269.0	1269.0	1269.0	1269.0	1269.0
2.5°	1273.1	1270.0	1260.0	1270.0	1269.0
5°	1267.0	1265.0	1255.0	1264.0	1263.0
7.5°	1258.0	1256.0	1244.9	1254.0	1253.0
10°	1244.9	1242.9	1231.9	1239.9	1238.9
12.5°	1228.9	1224.9	1214.8	1220.8	1220.8
15°	1207.8	1204.8	1193.7	1198.8	1198.8
17.5°	1185.7	1180.7	1169.6	1175.7	1170.6
20°	1156.6	1154.6	1141.5	1148.6	1143.5
22.5°	1127.5	1123.5	1111.4	1115.4	1112.4
25°	1096.4	1091.3	1078.3	1080.3	1077.3
27.5°	1060.2	1057.2	1044.1	1045.2	1042.1
30°	1025.1	1022.1	1007.0	1005.0	1002.0
32.5°	986.9	981.9	968.8	964.8	958.8
35°	946.8	942.7	928.7	923.7	915.6
37.5°	905.6	900.6	887.5	880.5	875.5
40°	863.4	858.4	844.4	835.3	832.3
42.5°	818.2	814.2	800.2	792.1	787.1
45°	775.1	771.1	759.0	747.0	744.0
47.5°	727.9	728.9	713.8	701.8	694.8
50°	682.7	679.7	667.7	654.6	647.6
52.5°	636.5	634.5	621.5	610.4	602.4
55°	590.3	587.3	573.3	564.2	557.2
57.5°	541.1	540.1	528.1	516.0	513.0
60°	495.0	490.9	479.9	469.9	462.8
62.5°	446.8	443.8	434.7	423.7	418.7
65°	398.6	396.6	385.5	376.5	372.5
67.5°	351.4	347.4	339.3	331.3	329.3
70°	307.2	302.2	293.2	287.1	283.1
72.5°	259.0	256.0	251.0	244.0	240.0
75°	211.8	209.8	204.8	201.8	197.8
77.5°	167.7	166.7	163.6	161.6	158.6
80°	126.5	126.5	124.5	123.5	121.5
82.5°	90.4	88.4	88.4	86.3	86.3
85°	55.2	56.2	56.2	55.2	53.2
87.5°	27.1	27.1	26.1	26.1	24.1
90°	1.2	11.2	20.0	26.2	30.0
92.5°	37.4	43.7	54.9	63.6	66.1
95°	81.1	83.6	96.1	104.8	107.3
97.5°	124.8	126.0	143.5	151.0	152.2
100°	174.7	174.7	190.9	202.2	204.7
102.5°	228.4	234.6	240.9	253.3	257.1
105°	284.5	290.8	298.3	305.7	309.5
107.5°	345.7	351.9	358.2	361.9	361.9
110°	409.3	415.6	419.3	423.0	421.8

TEST NUMBER: P1034639

CATALOG NUMBER: S125DIW-B850D1340UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	474.2	476.7	481.7	483.0	480.5
115°	537.9	542.9	545.3	544.1	542.9
117.5°	602.8	604.0	606.5	607.7	602.8
120°	662.7	668.9	670.1	670.1	665.1
122.5°	727.5	728.8	732.5	731.3	727.5
125°	785.0	792.4	793.7	791.2	789.9
127.5°	848.6	852.3	853.6	852.3	849.8
130°	904.8	911.0	913.5	912.2	909.7
132.5°	960.9	972.1	970.9	969.6	965.9
135°	1020.8	1028.3	1029.5	1029.5	1024.6
137.5°	1077.0	1084.5	1087.0	1088.2	1082.0
140°	1130.6	1136.9	1140.6	1143.1	1136.9
142.5°	1184.3	1189.3	1194.3	1195.5	1189.3
145°	1236.7	1241.7	1245.4	1245.4	1241.7
147.5°	1285.4	1289.1	1291.6	1295.4	1285.4
150°	1334.0	1332.8	1337.8	1337.8	1335.3
152.5°	1374.0	1376.5	1377.7	1381.5	1376.5
155°	1415.2	1415.2	1416.4	1421.4	1415.2
157.5°	1452.6	1450.1	1451.3	1456.3	1447.6
160°	1485.0	1481.3	1482.5	1487.5	1481.3
162.5°	1513.7	1511.2	1511.2	1517.5	1510.0
165°	1538.7	1536.2	1537.5	1542.4	1535.0
167.5°	1561.2	1556.2	1556.2	1563.7	1556.2
170°	1578.6	1573.6	1573.6	1581.1	1572.4
172.5°	1591.1	1586.1	1586.1	1593.6	1586.1
175°	1599.9	1594.9	1594.9	1602.3	1593.6
177.5°	1606.1	1601.1	1599.9	1607.3	1598.6
180°	1603.6	1603.6	1603.6	1603.6	1603.6

(END OF REPORT)