

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035189

Luminaire Tested: S125DIW-B1270D470UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035189
REPORT IS A COMBINATION OF REPORTS P1003292 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D470UB35-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7067.0 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035189

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035189

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	82	79	76	74	72	68	67	65
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	85	76	68	62	81	72	65	59	65	60	55	59	55	51	53	50	47
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31
7	61	49	40	35	58	47	39	34	43	36	31	39	34	29	36	31	27
8	57	44	36	31	54	42	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12710	12710	12710
5°	12710	12415	12439
10°	12605	12130	12092
15°	12439	11790	11684
20°	12216	11395	11216
25°	11975	10964	10715
30°	11686	10516	10187
35°	11376	10046	9595
40°	11056	9548	9069
45°	10710	9064	8511
50°	10330	8515	7859
55°	9953	7909	7261
60°	9503	7270	6564
65°	8964	6530	5843
70°	8417	5681	5012
75°	7497	4677	4053
80°	6389	3494	2981
85°	4934	2067	1644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10710 cd/sqm

TEST NUMBER: P1035189

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.6
10°-20°	528.7	7.5
20°-30°	780.6	11.0
30°-40°	910.7	12.9
40°-50°	914.7	12.9
50°-60°	802.9	11.4
60°-70°	598.0	8.5
70°-80°	341.6	4.8
80°-90°	99.5	1.4
90°-100°	21.0	0.3
100°-110°	139.8	2.0
110°-120°	251.8	3.6
120°-130°	323.2	4.6
130°-140°	347.6	4.9
140°-150°	326.2	4.6
150°-160°	263.9	3.7
160°-170°	170.7	2.4
170°-180°	58.9	0.8
0°-30°	1496.5	21.2
0°-40°	2407.2	34.1
0°-60°	4124.8	58.4
0°-90°	5163.9	73.1
90°-120°	412.6	5.8
90°-150°	1409.7	19.9
90°-180°	1903.0	26.9
0°-180°	7067.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1984	1984	1984	1984	1984	
5°	1980	1977	1962	1976	1974	188
15°	1888	1883	1866	1874	1874	532
25°	1714	1706	1686	1689	1684	789
35°	1480	1474	1452	1444	1431	926
45°	1212	1205	1186	1168	1163	933
55°	923	918	896	882	871	824
65°	623	620	603	588	582	618
75°	331	328	320	315	309	353
85°	86	88	88	86	83	95
90°	0	4	7	10	11	7
95°	26	25	7	10	10	32
105°	135	137	137	137	136	143
115°	254	256	256	254	252	251
125°	360	364	364	362	360	322
135°	450	452	451	450	448	347
145°	521	522	522	523	520	326
155°	574	571	572	574	570	265
165°	606	603	604	606	602	171
175°	620	617	617	621	617	59
180°	620	620	620	620	620	

TEST NUMBER: P1035189

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1983.7	1983.7	1983.7	1983.7	1983.7
2.5°	1989.9	1985.2	1969.5	1985.2	1983.7
5°	1980.5	1977.4	1961.7	1975.8	1974.3
7.5°	1966.4	1963.3	1946.0	1960.1	1958.6
10°	1946.0	1942.9	1925.6	1938.2	1936.6
12.5°	1920.9	1914.6	1898.9	1908.3	1908.3
15°	1887.9	1883.2	1866.0	1873.8	1873.8
17.5°	1853.4	1845.6	1828.3	1837.7	1829.9
20°	1807.9	1804.8	1784.4	1795.3	1787.5
22.5°	1762.4	1756.1	1737.3	1743.6	1738.8
25°	1713.7	1705.9	1685.5	1688.6	1683.9
27.5°	1657.2	1652.5	1632.1	1633.7	1629.0
30°	1602.3	1597.6	1574.1	1570.9	1566.2
32.5°	1542.7	1534.8	1514.4	1508.2	1498.7
35°	1479.9	1473.6	1451.7	1443.8	1431.3
37.5°	1415.6	1407.7	1387.3	1376.3	1368.5
40°	1349.6	1341.8	1319.8	1305.7	1301.0
42.5°	1279.0	1272.7	1250.8	1238.2	1230.4
45°	1211.5	1205.3	1186.4	1167.6	1162.9
47.5°	1137.8	1139.4	1115.8	1097.0	1086.0
50°	1067.2	1062.5	1043.6	1023.2	1012.2
52.5°	995.0	991.8	971.4	954.2	941.6
55°	922.8	918.1	896.1	882.0	871.0
57.5°	845.9	844.3	825.5	806.6	801.9
60°	773.7	767.4	750.2	734.5	723.5
62.5°	698.4	693.7	679.5	662.3	654.4
65°	623.0	619.9	602.6	588.5	582.2
67.5°	549.3	543.0	530.4	517.9	514.7
70°	480.2	472.4	458.3	448.8	442.6
72.5°	404.9	400.2	392.3	381.4	375.1
75°	331.1	328.0	320.1	315.4	309.2
77.5°	262.1	260.5	255.8	252.7	248.0
80°	197.7	197.7	194.6	193.0	189.9
82.5°	141.2	138.1	138.1	135.0	135.0
85°	86.3	87.9	87.9	86.3	83.2
87.5°	42.4	42.4	40.8	40.8	37.7
90°	0.5	4.1	7.3	9.6	11.0
92.5°	8.7	4.6	7.3	9.6	10.1
95°	26.2	24.8	7.3	9.6	9.6
97.5°	49.1	51.9	8.3	9.2	9.6
100°	76.7	78.1	79.9	11.5	9.6
102.5°	104.7	106.5	107.5	108.4	69.8
105°	135.0	136.9	136.9	136.9	136.4
107.5°	166.3	166.3	167.2	167.6	165.8
110°	196.6	196.6	197.5	196.1	196.6

TEST NUMBER: P1035189

CATALOG NUMBER: S125DIW-B1270D470UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.0	226.4	226.9	225.0	224.1
115°	253.5	255.8	256.3	254.4	251.7
117.5°	283.4	283.4	285.2	282.4	281.5
120°	310.9	310.5	311.8	310.9	308.6
122.5°	335.3	337.6	338.0	337.1	334.3
125°	360.5	363.7	363.7	361.9	360.5
127.5°	384.9	387.2	386.7	385.8	382.1
130°	406.9	409.2	409.7	408.3	406.0
132.5°	428.9	431.7	430.3	430.3	428.0
135°	449.6	452.4	451.4	450.5	447.8
137.5°	468.9	471.7	470.7	470.7	468.4
140°	487.7	488.6	488.2	489.1	486.4
142.5°	504.7	505.2	506.1	506.1	503.3
145°	521.3	522.2	522.2	522.6	519.9
147.5°	536.0	536.0	536.4	536.9	533.7
150°	549.7	548.8	549.7	550.6	547.0
152.5°	563.0	560.8	561.7	562.6	559.4
155°	574.1	571.3	572.2	573.6	569.9
157.5°	582.8	581.4	581.4	582.8	579.1
160°	592.0	589.2	589.7	591.5	587.8
162.5°	599.3	596.6	597.0	599.8	595.7
165°	605.8	603.0	603.5	606.2	602.5
167.5°	610.8	608.1	608.5	611.7	607.6
170°	614.9	611.7	612.2	615.9	611.7
172.5°	617.7	614.5	615.4	618.6	614.5
175°	619.5	616.8	617.2	620.9	616.8
177.5°	620.9	618.2	618.6	621.8	618.2
180°	619.5	619.5	619.5	619.5	619.5

(END OF REPORT)