

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034640

Luminaire Tested: S125DIW-B850D1340UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034640
REPORT IS A COMBINATION OF REPORTS P1004130 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B850D1340UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8729.0 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034640

CATALOG NUMBER: S125DIW-B850D1340UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034640

CATALOG NUMBER: S125DIW-B850D1340UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46			39
1	95	91	87	84	86	83	80	77	68	65	63	54	52	51	41	40	39			33
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33			27
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	30	28			23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24			20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21			17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18			15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16			13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	17	14			12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13			11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8382	8382	8382
5°	8383	8187	8203
10°	8313	7999	7975
15°	8204	7775	7706
20°	8056	7515	7397
25°	7898	7231	7066
30°	7707	6935	6718
35°	7503	6625	6328
40°	7292	6297	5981
45°	7063	5978	5613
50°	6812	5616	5184
55°	6564	5216	4788
60°	6268	4794	4329
65°	5912	4307	3854
70°	5551	3746	3306
75°	4945	3084	2673
80°	4214	2304	1965
85°	3253	1364	1084

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7063 cd/sqm

TEST NUMBER: P1034640

CATALOG NUMBER: S125DIW-B850D1340UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.4	1.4
10°-20°	348.7	4.0
20°-30°	514.8	5.9
30°-40°	600.6	6.9
40°-50°	603.2	6.9
50°-60°	529.5	6.1
60°-70°	394.4	4.5
70°-80°	225.2	2.6
80°-90°	67.6	0.8
90°-100°	58.8	0.7
100°-110°	391.0	4.5
110°-120°	704.1	8.1
120°-130°	903.7	10.4
130°-140°	972.0	11.1
140°-150°	912.2	10.5
150°-160°	737.9	8.5
160°-170°	477.2	5.5
170°-180°	164.6	1.9
0°-30°	986.9	11.3
0°-40°	1587.5	18.2
0°-60°	2720.3	31.2
0°-90°	3407.6	39.0
90°-120°	1153.8	13.2
90°-150°	3941.7	45.2
90°-180°	5321.0	61.0
0°-180°	8729.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1306	1304	1294	1303	1302	124
15°	1245	1242	1231	1236	1236	351
25°	1130	1125	1112	1114	1110	520
35°	976	972	957	952	944	611
45°	799	795	782	770	767	616
55°	609	606	591	582	574	543
65°	411	409	397	388	384	408
75°	218	216	211	208	204	232
85°	57	58	58	57	55	62
90°	1	12	20	27	31	8
95°	73	69	20	27	27	90
105°	378	383	383	383	381	400
115°	709	715	717	711	704	703
125°	1008	1017	1017	1012	1008	900
135°	1257	1265	1262	1260	1252	969
145°	1458	1460	1460	1461	1454	912
155°	1605	1598	1600	1604	1594	740
165°	1694	1686	1687	1695	1685	478
175°	1732	1725	1726	1736	1725	165
180°	1732	1732	1732	1732	1732	

TEST NUMBER: P1034640

CATALOG NUMBER: S125DIW-B850D1340UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1308.2	1308.2	1308.2	1308.2	1308.2
2.5°	1312.4	1309.3	1298.9	1309.3	1308.2
5°	1306.2	1304.1	1293.7	1303.1	1302.0
7.5°	1296.8	1294.8	1283.4	1292.7	1291.7
10°	1283.4	1281.3	1269.9	1278.2	1277.2
12.5°	1266.8	1262.7	1252.3	1258.6	1258.6
15°	1245.1	1242.0	1230.6	1235.8	1235.8
17.5°	1222.3	1217.2	1205.8	1212.0	1206.8
20°	1192.3	1190.2	1176.8	1184.0	1178.9
22.5°	1162.3	1158.2	1145.7	1149.9	1146.8
25°	1130.2	1125.0	1111.6	1113.7	1110.5
27.5°	1093.0	1089.8	1076.4	1077.4	1074.3
30°	1056.7	1053.6	1038.1	1036.0	1032.9
32.5°	1017.4	1012.2	998.8	994.6	988.4
35°	976.0	971.9	957.4	952.2	943.9
37.5°	933.6	928.4	914.9	907.7	902.5
40°	890.1	884.9	870.4	861.1	858.0
42.5°	843.5	839.4	824.9	816.6	811.4
45°	799.0	794.9	782.5	770.0	766.9
47.5°	750.4	751.4	735.9	723.5	716.2
50°	703.8	700.7	688.3	674.8	667.6
52.5°	656.2	654.1	640.7	629.3	621.0
55°	608.6	605.5	591.0	581.7	574.4
57.5°	557.9	556.8	544.4	532.0	528.9
60°	510.3	506.1	494.7	484.4	477.1
62.5°	460.6	457.5	448.2	436.8	431.6
65°	410.9	408.8	397.4	388.1	384.0
67.5°	362.2	358.1	349.8	341.5	339.5
70°	316.7	311.5	302.2	296.0	291.9
72.5°	267.0	263.9	258.7	251.5	247.4
75°	218.4	216.3	211.1	208.0	203.9
77.5°	172.8	171.8	168.7	166.6	163.5
80°	130.4	130.4	128.3	127.3	125.2
82.5°	93.1	91.1	91.1	89.0	89.0
85°	56.9	58.0	58.0	56.9	54.9
87.5°	27.9	27.9	26.9	26.9	24.8
90°	1.3	11.6	20.5	27.0	30.8
92.5°	24.4	12.8	20.5	27.0	28.3
95°	73.2	69.3	20.5	27.0	27.0
97.5°	137.4	145.1	23.1	25.7	27.0
100°	214.5	218.3	223.4	32.1	27.0
102.5°	292.8	297.9	300.5	303.1	195.2
105°	377.5	382.7	382.7	382.7	381.4
107.5°	464.9	464.9	467.4	468.7	463.6
110°	549.6	549.6	552.2	548.3	549.6

TEST NUMBER: P1034640

CATALOG NUMBER: S125DIW-B850D1340UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	629.2	633.1	634.4	629.2	626.7
115°	708.9	715.3	716.6	711.4	703.7
117.5°	792.3	792.3	797.5	789.8	787.2
120°	869.4	868.1	872.0	869.4	863.0
122.5°	937.4	943.9	945.2	942.6	934.9
125°	1008.1	1017.1	1017.1	1011.9	1008.1
127.5°	1076.1	1082.6	1081.3	1078.7	1068.4
130°	1137.8	1144.2	1145.5	1141.6	1135.2
132.5°	1199.4	1207.1	1203.3	1203.3	1196.9
135°	1257.2	1264.9	1262.3	1259.8	1252.1
137.5°	1311.1	1318.9	1316.3	1316.3	1309.9
140°	1363.8	1366.4	1365.1	1367.6	1359.9
142.5°	1411.3	1412.6	1415.2	1415.2	1407.5
145°	1457.5	1460.1	1460.1	1461.4	1453.7
147.5°	1498.6	1498.6	1499.9	1501.2	1492.2
150°	1537.2	1534.6	1537.2	1539.7	1529.5
152.5°	1574.4	1568.0	1570.5	1573.1	1564.1
155°	1605.2	1597.5	1600.1	1603.9	1593.7
157.5°	1629.6	1625.8	1625.8	1629.6	1619.3
160°	1655.3	1647.6	1648.9	1654.0	1643.7
162.5°	1675.9	1668.1	1669.4	1677.1	1665.6
165°	1693.8	1686.1	1687.4	1695.1	1684.8
167.5°	1708.0	1700.3	1701.5	1710.5	1699.0
170°	1719.5	1710.5	1711.8	1722.1	1710.5
172.5°	1727.2	1718.2	1720.8	1729.8	1718.2
175°	1732.4	1724.7	1725.9	1736.2	1724.7
177.5°	1736.2	1728.5	1729.8	1738.8	1728.5
180°	1732.4	1732.4	1732.4	1732.4	1732.4

(END OF REPORT)