

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035219

Luminaire Tested: S125DIW-B1270D770UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035219
REPORT IS A COMBINATION OF REPORTS P1003358 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1270D770UB35-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8301.0 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 84.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035219
CATALOG NUMBER: S125DIW-B1270D770UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot





TEST NUMBER: P1035219

CATALOG NUMBER: S125DIW-B1270D770UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	57	52
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	52	50	48	44
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	41	37
4	76	65	57	51	71	61	54	49	54	48	44	48	43	39	41	38	35	32
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	34	30	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	49	37	30	25	33	27	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12710	12710	12710
5°	12710	12415	12439
10°	12605	12130	12092
15°	12439	11790	11684
20°	12216	11395	11216
25°	11975	10964	10715
30°	11686	10516	10187
35°	11376	10046	9595
40°	11056	9548	9069
45°	10710	9064	8511
50°	10330	8515	7859
55°	9953	7909	7261
60°	9503	7270	6564
65°	8964	6530	5843
70°	8417	5681	5012
75°	7497	4677	4053
80°	6389	3494	2981
85°	4934	2067	1644

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10710 cd/sqm



TEST NUMBER: P1035219

CATALOG NUMBER: S125DIW-B1270D770UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.3
10°-20°	528.7	6.4
20°-30°	780.6	9.4
30°-40°	910.7	11.0
40°-50°	914.7	11.0
50°-60°	802.9	9.7
60°-70°	598.0	7.2
70°-80°	341.6	4.1
80°-90°	100.1	1.2
90°-100°	34.7	0.4
100°-110°	230.4	2.8
110°-120°	415.0	5.0
120°-130°	532.7	6.4
130°-140°	572.9	6.9
140°-150°	537.7	6.5
150°-160°	434.9	5.2
160°-170°	281.3	3.4
170°-180°	97.0	1.2
0°-30°	1496.5	18.0
0°-40°	2407.2	29.0
0°-60°	4124.8	49.7
0°-90°	5164.5	62.2
90°-120°	680.1	8.2
90°-150°	2323.3	28.0
90°-180°	3136.0	37.8
0°-180°	8301.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1984	1984	1984	1984	1984	
5°	1980	1977	1962	1976	1974	188
15°	1888	1883	1866	1874	1874	532
25°	1714	1706	1686	1689	1684	789
35°	1480	1474	1452	1444	1431	926
45°	1212	1205	1186	1168	1163	933
55°	923	918	896	882	871	824
65°	623	620	603	588	582	618
75°	331	328	320	315	309	353
85°	86	88	88	86	83	95
90°	1	7	12	16	18	8
95°	43	41	12	16	16	53
105°	222	226	226	226	225	236
115°	418	422	422	419	415	414
125°	594	600	600	596	594	531
135°	741	746	744	742	738	571
145°	859	861	861	861	857	537
155°	946	942	943	945	939	436
165°	998	994	995	999	993	282
175°	1021	1016	1017	1023	1016	97
180°	1021	1021	1021	1021	1021	



TEST NUMBER: P1035219

CATALOG NUMBER: S125DIW-B1270D770UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1983.7	1983.7	1983.7	1983.7	1983.7
2.5°	1989.9	1985.2	1969.5	1985.2	1983.7
5°	1980.5	1977.4	1961.7	1975.8	1974.3
7.5°	1966.4	1963.3	1946.0	1960.1	1958.6
10°	1946.0	1942.9	1925.6	1938.2	1936.6
12.5°	1920.9	1914.6	1898.9	1908.3	1908.3
15°	1887.9	1883.2	1866.0	1873.8	1873.8
17.5°	1853.4	1845.6	1828.3	1837.7	1829.9
20°	1807.9	1804.8	1784.4	1795.3	1787.5
22.5°	1762.4	1756.1	1737.3	1743.6	1738.8
25°	1713.7	1705.9	1685.5	1688.6	1683.9
27.5°	1657.2	1652.5	1632.1	1633.7	1629.0
30°	1602.3	1597.6	1574.1	1570.9	1566.2
32.5°	1542.7	1534.8	1514.4	1508.2	1498.7
35°	1479.9	1473.6	1451.7	1443.8	1431.3
37.5°	1415.6	1407.7	1387.3	1376.3	1368.5
40°	1349.6	1341.8	1319.8	1305.7	1301.0
42.5°	1279.0	1272.7	1250.8	1238.2	1230.4
45°	1211.5	1205.3	1186.4	1167.6	1162.9
47.5°	1137.8	1139.4	1115.8	1097.0	1086.0
50°	1067.2	1062.5	1043.6	1023.2	1012.2
52.5°	995.0	991.8	971.4	954.2	941.6
55°	922.8	918.1	896.1	882.0	871.0
57.5°	845.9	844.3	825.5	806.6	801.9
60°	773.7	767.4	750.2	734.5	723.5
62.5°	698.4	693.7	679.5	662.3	654.4
65°	623.0	619.9	602.6	588.5	582.2
67.5°	549.3	543.0	530.4	517.9	514.7
70°	480.2	472.4	458.3	448.8	442.6
72.5°	404.9	400.2	392.3	381.4	375.1
75°	331.1	328.0	320.1	315.4	309.2
77.5°	262.1	260.5	255.8	252.7	248.0
80°	197.7	197.7	194.6	193.0	189.9
82.5°	141.2	138.1	138.1	135.0	135.0
85°	86.3	87.9	87.9	86.3	83.2
87.5°	42.4	42.4	40.8	40.8	37.7
90°	0.8	6.8	12.1	15.9	18.2
92.5°	14.4	7.6	12.1	15.9	16.7
95°	43.1	40.9	12.1	15.9	15.9
97.5°	81.0	85.5	13.6	15.1	15.9
100°	126.4	128.7	131.7	18.9	15.9
102.5°	172.6	175.6	177.1	178.6	115.0
105°	222.5	225.6	225.6	225.6	224.8
107.5°	274.0	274.0	275.5	276.3	273.2
110°	324.0	324.0	325.5	323.2	324.0



TEST NUMBER: P1035219

CATALOG NUMBER: S125DIW-B1270D770UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	370.9	373.2	373.9	370.9	369.4
115°	417.8	421.6	422.4	419.3	414.8
117.5°	467.0	467.0	470.0	465.5	464.0
120°	512.4	511.7	513.9	512.4	508.6
122.5°	552.5	556.3	557.1	555.6	551.0
125°	594.2	599.5	599.5	596.4	594.2
127.5°	634.3	638.1	637.3	635.8	629.7
130°	670.6	674.4	675.2	672.9	669.1
132.5°	706.9	711.5	709.2	709.2	705.4
135°	741.0	745.5	744.0	742.5	738.0
137.5°	772.8	777.3	775.8	775.8	772.0
140°	803.8	805.3	804.6	806.1	801.6
142.5°	831.8	832.6	834.1	834.1	829.6
145°	859.1	860.6	860.6	861.4	856.8
147.5°	883.3	883.3	884.1	884.8	879.5
150°	906.0	904.5	906.0	907.5	901.5
152.5°	928.0	924.2	925.7	927.2	921.9
155°	946.1	941.6	943.1	945.4	939.3
157.5°	960.5	958.2	958.2	960.5	954.5
160°	975.6	971.1	971.9	974.9	968.8
162.5°	987.8	983.2	984.0	988.5	981.7
165°	998.4	993.8	994.6	999.1	993.1
167.5°	1006.7	1002.1	1002.9	1008.2	1001.4
170°	1013.5	1008.2	1009.0	1015.0	1008.2
172.5°	1018.0	1012.7	1014.2	1019.5	1012.7
175°	1021.1	1016.5	1017.3	1023.3	1016.5
177.5°	1023.3	1018.8	1019.5	1024.8	1018.8
180°	1021.1	1021.1	1021.1	1021.1	1021.1

(END OF REPORT)