

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034687

Luminaire Tested: S125DIW-B850D770UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034687
REPORT IS A COMBINATION OF REPORTS P1004330 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B850D770UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6588.0 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034687

CATALOG NUMBER: S125DIW-B850D770UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034687

CATALOG NUMBER: S125DIW-B850D770UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	51	50	49
2	89	82	76	71	82	76	71	66	65	61	57	55	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30
5	68	57	49	43	63	53	46	40	46	40	35	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	18
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8493	8493	8493
5°	8493	8295	8311
10°	8423	8105	8080
15°	8313	7878	7807
20°	8163	7614	7494
25°	8002	7327	7160
30°	7809	7027	6807
35°	7602	6713	6412
40°	7388	6380	6060
45°	7157	6057	5687
50°	6902	5690	5252
55°	6650	5285	4852
60°	6350	4858	4386
65°	5990	4364	3905
70°	5625	3796	3349
75°	5011	3125	2708
80°	4269	2334	1992
85°	3299	1380	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7157 cd/sqm

TEST NUMBER: P1034687

CATALOG NUMBER: S125DIW-B850D770UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	1.9
10°-20°	353.3	5.4
20°-30°	521.6	7.9
30°-40°	608.6	9.2
40°-50°	611.2	9.3
50°-60°	536.5	8.1
60°-70°	399.6	6.1
70°-80°	228.2	3.5
80°-90°	67.4	1.0
90°-100°	34.7	0.5
100°-110°	230.4	3.5
110°-120°	415.0	6.3
120°-130°	532.7	8.1
130°-140°	572.9	8.7
140°-150°	537.7	8.2
150°-160°	434.9	6.6
160°-170°	281.3	4.3
170°-180°	97.0	1.5
0°-30°	1000.0	15.2
0°-40°	1608.5	24.4
0°-60°	2756.3	41.8
0°-90°	3451.5	52.4
90°-120°	680.1	10.3
90°-150°	2323.3	35.3
90°-180°	3136.0	47.6
0°-180°	6588.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1326	1326	1326	1326	1326	
5°	1323	1321	1311	1320	1319	126
15°	1262	1258	1247	1252	1252	356
25°	1145	1140	1126	1128	1125	527
35°	989	985	970	965	956	619
45°	810	805	793	780	777	624
55°	617	614	599	589	582	550
65°	416	414	403	393	389	413
75°	221	219	214	211	207	236
85°	58	59	59	58	56	63
90°	1	7	12	16	18	6
95°	43	41	12	16	16	53
105°	222	226	226	226	225	236
115°	418	422	422	419	415	414
125°	594	600	600	596	594	531
135°	741	746	744	742	738	571
145°	859	861	861	861	857	537
155°	946	942	943	945	939	436
165°	998	994	995	999	993	282
175°	1021	1016	1017	1023	1016	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1034687

CATALOG NUMBER: S125DIW-B850D770UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1325.5	1325.5	1325.5	1325.5	1325.5
2.5°	1329.7	1326.6	1316.1	1326.6	1325.5
5°	1323.4	1321.3	1310.8	1320.3	1319.2
7.5°	1314.0	1311.9	1300.4	1309.8	1308.7
10°	1300.4	1298.3	1286.7	1295.1	1294.1
12.5°	1283.6	1279.4	1268.9	1275.2	1275.2
15°	1261.6	1258.4	1246.9	1252.1	1252.1
17.5°	1238.5	1233.2	1221.7	1228.0	1222.7
20°	1208.1	1206.0	1192.3	1199.7	1194.4
22.5°	1177.7	1173.5	1160.9	1165.1	1161.9
25°	1145.1	1139.9	1126.3	1128.4	1125.2
27.5°	1107.4	1104.2	1090.6	1091.7	1088.5
30°	1070.7	1067.5	1051.8	1049.7	1046.6
32.5°	1030.8	1025.6	1012.0	1007.8	1001.5
35°	988.9	984.7	970.0	964.8	956.4
37.5°	945.9	940.7	927.0	919.7	914.4
40°	901.9	896.6	881.9	872.5	869.3
42.5°	854.7	850.5	835.8	827.4	822.2
45°	809.6	805.4	792.8	780.2	777.1
47.5°	760.3	761.3	745.6	733.0	725.7
50°	713.1	709.9	697.4	683.7	676.4
52.5°	664.9	662.8	649.1	637.6	629.2
55°	616.6	613.5	598.8	589.4	582.0
57.5°	565.2	564.2	551.6	539.0	535.9
60°	517.0	512.8	501.3	490.8	483.4
62.5°	466.7	463.5	454.1	442.5	437.3
65°	416.3	414.2	402.7	393.3	389.1
67.5°	367.0	362.8	354.5	346.1	344.0
70°	320.9	315.6	306.2	299.9	295.7
72.5°	270.6	267.4	262.2	254.8	250.6
75°	221.3	219.2	213.9	210.8	206.6
77.5°	175.1	174.1	170.9	168.8	165.7
80°	132.1	132.1	130.0	129.0	126.9
82.5°	94.4	92.3	92.3	90.2	90.2
85°	57.7	58.7	58.7	57.7	55.6
87.5°	28.3	28.3	27.3	27.3	25.2
90°	0.8	6.8	12.1	15.9	18.2
92.5°	14.4	7.6	12.1	15.9	16.7
95°	43.1	40.9	12.1	15.9	15.9
97.5°	81.0	85.5	13.6	15.1	15.9
100°	126.4	128.7	131.7	18.9	15.9
102.5°	172.6	175.6	177.1	178.6	115.0
105°	222.5	225.6	225.6	225.6	224.8
107.5°	274.0	274.0	275.5	276.3	273.2
110°	324.0	324.0	325.5	323.2	324.0



TEST NUMBER: P1034687

CATALOG NUMBER: S125DIW-B850D770UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	370.9	373.2	373.9	370.9	369.4
115°	417.8	421.6	422.4	419.3	414.8
117.5°	467.0	467.0	470.0	465.5	464.0
120°	512.4	511.7	513.9	512.4	508.6
122.5°	552.5	556.3	557.1	555.6	551.0
125°	594.2	599.5	599.5	596.4	594.2
127.5°	634.3	638.1	637.3	635.8	629.7
130°	670.6	674.4	675.2	672.9	669.1
132.5°	706.9	711.5	709.2	709.2	705.4
135°	741.0	745.5	744.0	742.5	738.0
137.5°	772.8	777.3	775.8	775.8	772.0
140°	803.8	805.3	804.6	806.1	801.6
142.5°	831.8	832.6	834.1	834.1	829.6
145°	859.1	860.6	860.6	861.4	856.8
147.5°	883.3	883.3	884.1	884.8	879.5
150°	906.0	904.5	906.0	907.5	901.5
152.5°	928.0	924.2	925.7	927.2	921.9
155°	946.1	941.6	943.1	945.4	939.3
157.5°	960.5	958.2	958.2	960.5	954.5
160°	975.6	971.1	971.9	974.9	968.8
162.5°	987.8	983.2	984.0	988.5	981.7
165°	998.4	993.8	994.6	999.1	993.1
167.5°	1006.7	1002.1	1002.9	1008.2	1001.4
170°	1013.5	1008.2	1009.0	1015.0	1008.2
172.5°	1018.0	1012.7	1014.2	1019.5	1012.7
175°	1021.1	1016.5	1017.3	1023.3	1016.5
177.5°	1023.3	1018.8	1019.5	1024.8	1018.8
180°	1021.1	1021.1	1021.1	1021.1	1021.1

(END OF REPORT)