

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034748

Luminaire Tested: S125RDIW-B1270D1050UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034748
REPORT IS A COMBINATION OF REPORTS P1006158 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D1050UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8789.0 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034748

CATALOG NUMBER: S125RDIW-B1270D1050UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034748

CATALOG NUMBER: S125RDIW-B1270D1050UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	87	91	88	85	82	75	73	71	64	62	60	53	52	51
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	66	60	76	68	62	56	59	54	50	50	46	43	42	39	37
4	75	65	57	51	70	60	53	48	52	47	43	44	40	37	37	34	32
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	30	28
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	31	27	25
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20
9	51	39	32	27	48	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12746	12746	12746
5°	12747	12428	12448
10°	12622	12115	12008
15°	12444	11677	11429
20°	12223	11149	10823
25°	11969	10634	10172
30°	11659	10068	9489
35°	11341	9493	8763
40°	11040	8902	8054
45°	10679	8265	7313
50°	10311	7588	6556
55°	9885	6922	5773
60°	9449	6160	4962
65°	8928	5308	4087
70°	8323	4322	3216
75°	7483	3249	2344
80°	6311	2104	1581
85°	4723	1131	891

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10679 cd/sqm

TEST NUMBER: P1034748

CATALOG NUMBER: S125RDIW-B1270D1050UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	2.1
10°-20°	523.2	6.0
20°-30°	758.7	8.6
30°-40°	864.3	9.8
40°-50°	842.5	9.6
50°-60°	709.0	8.1
60°-70°	496.8	5.7
70°-80°	254.7	2.9
80°-90°	65.5	0.7
90°-100°	45.2	0.5
100°-110°	300.3	3.4
110°-120°	540.7	6.2
120°-130°	694.1	7.9
130°-140°	746.5	8.5
140°-150°	700.6	8.0
150°-160°	566.7	6.4
160°-170°	366.5	4.2
170°-180°	126.4	1.4
0°-30°	1469.1	16.7
0°-40°	2333.5	26.5
0°-60°	3884.9	44.2
0°-90°	4702.0	53.5
90°-120°	886.2	10.1
90°-150°	3027.4	34.4
90°-180°	4087.0	46.5
0°-180°	8789.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1989	1989	1989	1989	1989	
5°	1986	1980	1964	1979	1976	188
15°	1889	1880	1848	1847	1833	533
25°	1713	1690	1635	1615	1599	788
35°	1475	1439	1372	1328	1307	924
45°	1208	1164	1082	1022	999	932
55°	916	868	784	717	693	820
65°	620	569	490	430	407	614
75°	330	286	222	189	179	349
85°	83	56	48	47	45	90
90°	1	9	16	21	24	8
95°	56	53	16	21	21	69
105°	290	294	294	294	293	307
115°	544	549	550	546	540	540
125°	774	781	781	777	774	692
135°	966	972	970	968	962	744
145°	1119	1121	1121	1122	1116	700
155°	1233	1227	1229	1232	1224	568
165°	1301	1295	1296	1302	1294	367
175°	1330	1325	1326	1334	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1034748

CATALOG NUMBER: S125RDIW-B1270D1050UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1989.3	1989.3	1989.3	1989.3	1989.3
2.5°	1993.8	1989.3	1974.3	1989.3	1987.8
5°	1986.3	1980.3	1963.8	1978.8	1975.8
7.5°	1971.3	1965.3	1945.7	1957.7	1954.7
10°	1948.7	1944.2	1923.2	1927.7	1923.2
12.5°	1923.2	1917.2	1887.1	1890.1	1882.6
15°	1888.6	1879.6	1848.1	1846.6	1833.0
17.5°	1852.6	1839.0	1801.5	1794.0	1783.5
20°	1809.0	1794.0	1745.9	1738.4	1724.9
22.5°	1760.9	1745.9	1694.8	1678.3	1667.8
25°	1712.8	1690.3	1634.7	1615.2	1598.6
27.5°	1658.7	1631.7	1573.1	1547.6	1531.0
30°	1598.6	1570.1	1507.0	1472.4	1458.9
32.5°	1540.1	1505.5	1440.9	1401.8	1383.8
35°	1475.4	1439.4	1371.8	1328.2	1307.2
37.5°	1413.8	1370.3	1301.2	1250.1	1229.0
40°	1347.7	1302.7	1230.5	1173.4	1155.4
42.5°	1278.6	1232.0	1156.9	1102.8	1074.3
45°	1208.0	1164.4	1081.8	1021.7	999.2
47.5°	1134.4	1089.3	1006.7	945.1	919.5
50°	1065.3	1015.7	930.0	866.9	844.4
52.5°	990.1	939.1	859.4	790.3	767.8
55°	916.5	868.4	784.3	716.7	692.6
57.5°	841.4	790.3	709.2	643.1	622.0
60°	769.3	716.7	635.6	569.4	546.9
62.5°	692.6	643.1	560.4	500.3	477.8
65°	620.5	569.4	489.8	429.7	407.2
67.5°	548.4	497.3	420.7	363.6	345.6
70°	474.8	423.7	348.6	302.0	284.0
72.5°	402.7	353.1	284.0	241.9	231.4
75°	330.5	285.5	222.4	189.3	178.8
77.5°	256.9	220.9	168.3	142.7	133.7
80°	195.3	159.3	117.2	103.7	100.7
82.5°	135.2	103.7	78.1	73.6	72.1
85°	82.6	55.6	48.1	46.6	45.1
87.5°	34.6	24.0	22.5	22.5	21.0
90°	1.0	8.9	15.8	20.7	23.7
92.5°	18.7	9.9	15.8	20.7	21.7
95°	56.2	53.3	15.8	20.7	20.7
97.5°	105.5	111.5	17.8	19.7	20.7
100°	164.7	167.7	171.6	24.7	20.7
102.5°	224.9	228.8	230.8	232.8	149.9
105°	290.0	293.9	293.9	293.9	292.9
107.5°	357.0	357.0	359.0	360.0	356.1
110°	422.1	422.1	424.1	421.1	422.1



TEST NUMBER: P1034748

CATALOG NUMBER: S125RDIW-B1270D1050UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	483.3	486.2	487.2	483.3	481.3
115°	544.4	549.4	550.3	546.4	540.5
117.5°	608.5	608.5	612.5	606.6	604.6
120°	667.7	666.7	669.7	667.7	662.8
122.5°	720.0	724.9	725.9	723.9	718.0
125°	774.2	781.1	781.1	777.2	774.2
127.5°	826.5	831.4	830.5	828.5	820.6
130°	873.9	878.8	879.8	876.8	871.9
132.5°	921.2	927.1	924.2	924.2	919.2
135°	965.6	971.5	969.5	967.5	961.6
137.5°	1007.0	1012.9	1010.9	1010.9	1006.0
140°	1047.4	1049.4	1048.4	1050.4	1044.5
142.5°	1083.9	1084.9	1086.9	1086.9	1081.0
145°	1119.4	1121.4	1121.4	1122.4	1116.5
147.5°	1151.0	1151.0	1152.0	1153.0	1146.1
150°	1180.6	1178.6	1180.6	1182.6	1174.7
152.5°	1209.2	1204.3	1206.2	1208.2	1201.3
155°	1232.9	1226.9	1228.9	1231.9	1224.0
157.5°	1251.6	1248.6	1248.6	1251.6	1243.7
160°	1271.3	1265.4	1266.4	1270.3	1262.4
162.5°	1287.1	1281.2	1282.2	1288.1	1279.2
165°	1300.9	1295.0	1296.0	1301.9	1294.0
167.5°	1311.8	1305.8	1306.8	1313.7	1304.9
170°	1320.6	1313.7	1314.7	1322.6	1313.7
172.5°	1326.6	1319.7	1321.6	1328.5	1319.7
175°	1330.5	1324.6	1325.6	1333.5	1324.6
177.5°	1333.5	1327.5	1328.5	1335.4	1327.5
180°	1330.5	1330.5	1330.5	1330.5	1330.5

(END OF REPORT)