

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034767

Luminaire Tested: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034767
REPORT IS A COMBINATION OF REPORTS P1006244 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11269.0 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034767

CATALOG NUMBER: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034767

CATALOG NUMBER: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	24
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13313	13313	13313
5°	13314	12981	13001
10°	13184	12653	12542
15°	12997	12195	11938
20°	12766	11645	11304
25°	12501	11107	10624
30°	12177	10515	9911
35°	11847	9915	9153
40°	11532	9299	8413
45°	11153	8632	7638
50°	10769	7925	6848
55°	10325	7230	6030
60°	9869	6433	5182
65°	9326	5544	4268
70°	8693	4514	3359
75°	7816	3394	2447
80°	6592	2198	1650
85°	4934	1180	930

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11153 cd/sqm

TEST NUMBER: P1034767

CATALOG NUMBER: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.6	1.7
10°-20°	546.5	4.8
20°-30°	792.4	7.0
30°-40°	902.8	8.0
40°-50°	879.9	7.8
50°-60°	740.5	6.6
60°-70°	518.9	4.6
70°-80°	266.0	2.4
80°-90°	69.4	0.6
90°-100°	70.2	0.6
100°-110°	467.1	4.1
110°-120°	841.1	7.5
120°-130°	1079.6	9.6
130°-140°	1161.1	10.3
140°-150°	1089.7	9.7
150°-160°	881.5	7.8
160°-170°	570.1	5.1
170°-180°	196.6	1.7
0°-30°	1534.4	13.6
0°-40°	2437.2	21.6
0°-60°	4057.7	36.0
0°-90°	4912.1	43.6
90°-120°	1378.3	12.2
90°-150°	4708.7	41.8
90°-180°	6357.0	56.4
0°-180°	11269.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2078	2078	2078	2078	2078	
5°	2075	2068	2051	2067	2064	197
15°	1973	1963	1930	1929	1914	556
25°	1789	1766	1707	1687	1670	823
35°	1541	1503	1433	1387	1365	965
45°	1262	1216	1130	1067	1044	973
55°	957	907	819	749	723	856
65°	648	595	512	449	425	642
75°	345	298	232	198	187	365
85°	86	58	50	49	47	95
90°	2	14	24	32	37	9
95°	87	83	24	32	32	107
105°	451	457	457	457	456	478
115°	847	854	856	850	841	839
125°	1204	1215	1215	1209	1204	1076
135°	1502	1511	1508	1505	1496	1158
145°	1741	1744	1744	1746	1737	1089
155°	1918	1908	1911	1916	1904	884
165°	2023	2014	2016	2025	2013	572
175°	2070	2060	2062	2074	2060	197
180°	2070	2070	2070	2070	2070	

TEST NUMBER: P1034767

CATALOG NUMBER: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2077.8	2077.8	2077.8	2077.8	2077.8
2.5°	2082.5	2077.8	2062.1	2077.8	2076.2
5°	2074.6	2068.3	2051.1	2066.8	2063.6
7.5°	2058.9	2052.6	2032.2	2044.8	2041.7
10°	2035.4	2030.7	2008.7	2013.4	2008.7
12.5°	2008.7	2002.4	1971.0	1974.2	1966.3
15°	1972.6	1963.2	1930.2	1928.7	1914.5
17.5°	1935.0	1920.8	1881.6	1873.7	1862.8
20°	1889.4	1873.7	1823.5	1815.7	1801.6
22.5°	1839.2	1823.5	1770.2	1752.9	1741.9
25°	1789.0	1765.5	1707.4	1687.0	1669.7
27.5°	1732.5	1704.3	1643.1	1616.4	1599.1
30°	1669.7	1639.9	1574.0	1537.9	1523.8
32.5°	1608.5	1572.4	1505.0	1464.2	1445.3
35°	1541.1	1503.4	1432.8	1387.3	1365.3
37.5°	1476.7	1431.2	1359.0	1305.7	1283.7
40°	1407.7	1360.6	1285.3	1225.6	1206.8
42.5°	1335.5	1286.8	1208.4	1151.9	1122.1
45°	1261.7	1216.2	1129.9	1067.1	1043.6
47.5°	1184.8	1137.7	1051.4	987.1	960.4
50°	1112.6	1060.8	971.4	905.5	881.9
52.5°	1034.2	980.8	897.6	825.5	801.9
55°	957.3	907.1	819.2	748.6	723.4
57.5°	878.8	825.5	740.7	671.7	649.7
60°	803.5	748.6	663.8	594.8	571.2
62.5°	723.4	671.7	585.3	522.6	499.0
65°	648.1	594.8	511.6	448.8	425.3
67.5°	572.8	519.4	439.4	379.8	360.9
70°	495.9	442.5	364.1	315.4	296.6
72.5°	420.6	368.8	296.6	252.7	241.7
75°	345.2	298.2	232.3	197.7	186.7
77.5°	268.4	230.7	175.8	149.1	139.7
80°	204.0	166.3	122.4	108.3	105.1
82.5°	141.2	108.3	81.6	76.9	75.3
85°	86.3	58.1	50.2	48.6	47.1
87.5°	36.1	25.1	23.5	23.5	22.0
90°	1.5	13.8	24.5	32.2	36.8
92.5°	29.1	15.3	24.5	32.2	33.7
95°	87.4	82.8	24.5	32.2	32.2
97.5°	164.1	173.3	27.6	30.7	32.2
100°	256.2	260.8	266.9	38.4	32.2
102.5°	349.8	355.9	359.0	362.0	233.2
105°	451.0	457.2	457.2	457.2	455.6
107.5°	555.3	555.3	558.4	559.9	553.8
110°	656.6	656.6	659.6	655.0	656.6

TEST NUMBER: P1034767

CATALOG NUMBER: S125RDIW-B1270D1560UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	751.7	756.3	757.8	751.7	748.6
115°	846.8	854.5	856.0	849.9	840.7
117.5°	946.5	946.5	952.7	943.5	940.4
120°	1038.6	1037.0	1041.6	1038.6	1030.9
122.5°	1119.9	1127.5	1129.1	1126.0	1116.8
125°	1204.2	1215.0	1215.0	1208.8	1204.2
127.5°	1285.5	1293.2	1291.7	1288.6	1276.3
130°	1359.2	1366.9	1368.4	1363.8	1356.1
132.5°	1432.8	1442.0	1437.4	1437.4	1429.7
135°	1501.9	1511.1	1508.0	1504.9	1495.7
137.5°	1566.3	1575.5	1572.4	1572.4	1564.7
140°	1629.2	1632.2	1630.7	1633.8	1624.6
142.5°	1685.9	1687.5	1690.5	1690.5	1681.3
145°	1741.2	1744.2	1744.2	1745.8	1736.6
147.5°	1790.3	1790.3	1791.8	1793.3	1782.6
150°	1836.3	1833.2	1836.3	1839.3	1827.1
152.5°	1880.8	1873.1	1876.2	1879.2	1868.5
155°	1917.6	1908.4	1911.4	1916.0	1903.8
157.5°	1946.7	1942.1	1942.1	1946.7	1934.5
160°	1977.4	1968.2	1969.7	1975.9	1963.6
162.5°	2002.0	1992.8	1994.3	2003.5	1989.7
165°	2023.4	2014.2	2015.8	2025.0	2012.7
167.5°	2040.3	2031.1	2032.6	2043.4	2029.6
170°	2054.1	2043.4	2044.9	2057.2	2043.4
172.5°	2063.3	2052.6	2055.6	2066.4	2052.6
175°	2069.5	2060.3	2061.8	2074.1	2060.3
177.5°	2074.1	2064.9	2066.4	2077.1	2064.9
180°	2069.5	2069.5	2069.5	2069.5	2069.5

(END OF REPORT)