

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034805

Luminaire Tested: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034805
REPORT IS A COMBINATION OF REPORTS P1006418 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6719.0 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034805

CATALOG NUMBER: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034805

CATALOG NUMBER: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	42	41	39	26	25	25
2	83	76	70	66	73	68	63	59	52	48	46	37	35	33	23	22	21
3	76	67	60	55	67	60	54	49	45	42	38	32	30	28	20	19	18
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	18	17	16
5	64	53	45	39	56	47	40	35	36	31	28	26	23	21	16	15	14
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	15	13	12
7	54	42	35	29	47	38	31	27	29	25	21	21	18	16	14	12	11
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	11	9
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	11	10	8
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3783	3783	3783
5°	3783	3689	3695
10°	3747	3596	3564
15°	3694	3466	3393
20°	3628	3309	3213
25°	3553	3156	3019
30°	3461	2988	2816
35°	3366	2818	2601
40°	3277	2642	2390
45°	3169	2453	2171
50°	3061	2252	1946
55°	2934	2055	1714
60°	2804	1828	1472
65°	2650	1576	1213
70°	2470	1283	955
75°	2221	964	696
80°	1874	625	469
85°	1401	336	265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3169 cd/sqm

TEST NUMBER: P1034805

CATALOG NUMBER: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	0.8
10°-20°	155.3	2.3
20°-30°	225.2	3.4
30°-40°	256.5	3.8
40°-50°	250.0	3.7
50°-60°	210.4	3.1
60°-70°	147.5	2.2
70°-80°	75.6	1.1
80°-90°	21.4	0.3
90°-100°	58.8	0.9
100°-110°	391.0	5.8
110°-120°	704.1	10.5
120°-130°	903.7	13.5
130°-140°	972.0	14.5
140°-150°	912.2	13.6
150°-160°	737.9	11.0
160°-170°	477.2	7.1
170°-180°	164.6	2.4
0°-30°	436.0	6.5
0°-40°	692.6	10.3
0°-60°	1153.1	17.2
0°-90°	1397.6	20.8
90°-120°	1153.8	17.2
90°-150°	3941.7	58.7
90°-180°	5321.0	79.2
0°-180°	6719.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	590	588	583	587	586	56
15°	561	558	548	548	544	158
25°	508	502	485	479	474	234
35°	438	427	407	394	388	274
45°	358	346	321	303	297	277
55°	272	258	233	213	206	243
65°	184	169	145	128	121	182
75°	98	85	66	56	53	104
85°	24	16	14	14	13	27
90°	1	12	20	27	31	5
95°	73	69	20	27	27	90
105°	378	383	383	383	381	400
115°	709	715	717	711	704	703
125°	1008	1017	1017	1012	1008	900
135°	1257	1265	1262	1260	1252	969
145°	1458	1460	1460	1461	1454	912
155°	1605	1598	1600	1604	1594	740
165°	1694	1686	1687	1695	1685	478
175°	1732	1725	1726	1736	1725	165
180°	1732	1732	1732	1732	1732	

TEST NUMBER: P1034805

CATALOG NUMBER: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	590.4	590.4	590.4	590.4	590.4
2.5°	591.8	590.4	586.0	590.4	590.0
5°	589.5	587.8	582.9	587.3	586.4
7.5°	585.1	583.3	577.5	581.1	580.2
10°	578.4	577.1	570.8	572.2	570.8
12.5°	570.8	569.0	560.1	561.0	558.8
15°	560.6	557.9	548.5	548.1	544.1
17.5°	549.9	545.8	534.7	532.5	529.3
20°	536.9	532.5	518.2	516.0	512.0
22.5°	522.7	518.2	503.0	498.1	495.0
25°	508.4	501.7	485.2	479.4	474.5
27.5°	492.3	484.3	466.9	459.3	454.4
30°	474.5	466.0	447.3	437.0	433.0
32.5°	457.1	446.8	427.7	416.1	410.7
35°	437.9	427.2	407.2	394.2	388.0
37.5°	419.6	406.7	386.2	371.0	364.8
40°	400.0	386.6	365.2	348.3	342.9
42.5°	379.5	365.7	343.4	327.3	318.9
45°	358.5	345.6	321.1	303.2	296.6
47.5°	336.7	323.3	298.8	280.5	272.9
50°	316.2	301.5	276.0	257.3	250.6
52.5°	293.9	278.7	255.1	234.6	227.9
55°	272.0	257.8	232.8	212.7	205.6
57.5°	249.7	234.6	210.5	190.9	184.6
60°	228.3	212.7	188.6	169.0	162.3
62.5°	205.6	190.9	166.3	148.5	141.8
65°	184.2	169.0	145.4	127.5	120.9
67.5°	162.8	147.6	124.9	107.9	102.6
70°	140.9	125.8	103.5	89.6	84.3
72.5°	119.5	104.8	84.3	71.8	68.7
75°	98.1	84.7	66.0	56.2	53.1
77.5°	76.3	65.6	49.9	42.4	39.7
80°	58.0	47.3	34.8	30.8	29.9
82.5°	40.1	30.8	23.2	21.9	21.4
85°	24.5	16.5	14.3	13.8	13.4
87.5°	10.3	7.1	6.7	6.7	6.2
90°	1.3	11.6	20.5	27.0	30.8
92.5°	24.4	12.8	20.5	27.0	28.3
95°	73.2	69.3	20.5	27.0	27.0
97.5°	137.4	145.1	23.1	25.7	27.0
100°	214.5	218.3	223.4	32.1	27.0
102.5°	292.8	297.9	300.5	303.1	195.2
105°	377.5	382.7	382.7	382.7	381.4
107.5°	464.9	464.9	467.4	468.7	463.6
110°	549.6	549.6	552.2	548.3	549.6

TEST NUMBER: P1034805

CATALOG NUMBER: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	629.2	633.1	634.4	629.2	626.7
115°	708.9	715.3	716.6	711.4	703.7
117.5°	792.3	792.3	797.5	789.8	787.2
120°	869.4	868.1	872.0	869.4	863.0
122.5°	937.4	943.9	945.2	942.6	934.9
125°	1008.1	1017.1	1017.1	1011.9	1008.1
127.5°	1076.1	1082.6	1081.3	1078.7	1068.4
130°	1137.8	1144.2	1145.5	1141.6	1135.2
132.5°	1199.4	1207.1	1203.3	1203.3	1196.9
135°	1257.2	1264.9	1262.3	1259.8	1252.1
137.5°	1311.1	1318.9	1316.3	1316.3	1309.9
140°	1363.8	1366.4	1365.1	1367.6	1359.9
142.5°	1411.3	1412.6	1415.2	1415.2	1407.5
145°	1457.5	1460.1	1460.1	1461.4	1453.7
147.5°	1498.6	1498.6	1499.9	1501.2	1492.2
150°	1537.2	1534.6	1537.2	1539.7	1529.5
152.5°	1574.4	1568.0	1570.5	1573.1	1564.1
155°	1605.2	1597.5	1600.1	1603.9	1593.7
157.5°	1629.6	1625.8	1625.8	1629.6	1619.3
160°	1655.3	1647.6	1648.9	1654.0	1643.7
162.5°	1675.9	1668.1	1669.4	1677.1	1665.6
165°	1693.8	1686.1	1687.4	1695.1	1684.8
167.5°	1708.0	1700.3	1701.5	1710.5	1699.0
170°	1719.5	1710.5	1711.8	1722.1	1710.5
172.5°	1727.2	1718.2	1720.8	1729.8	1718.2
175°	1732.4	1724.7	1725.9	1736.2	1724.7
177.5°	1736.2	1728.5	1729.8	1738.8	1728.5
180°	1732.4	1732.4	1732.4	1732.4	1732.4

(END OF REPORT)