

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034806

Luminaire Tested: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034806
REPORT IS A COMBINATION OF REPORTS P1006419 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6777.0 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034806

CATALOG NUMBER: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034806

CATALOG NUMBER: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	42	41	39	26	25	25
2	83	76	70	66	73	68	63	59	52	48	46	37	35	33	23	22	21
3	76	67	60	55	67	60	54	49	45	42	38	32	30	28	20	19	18
4	69	59	52	46	61	53	46	41	40	36	33	29	26	24	18	17	16
5	64	53	45	39	56	47	40	35	36	31	28	26	23	21	16	15	14
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	15	13	12
7	54	42	35	29	47	38	31	27	29	25	21	21	18	16	14	12	11
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	11	9
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	11	10	8
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3815	3815	3815
5°	3816	3721	3727
10°	3779	3627	3595
15°	3725	3495	3421
20°	3659	3338	3240
25°	3583	3184	3045
30°	3490	3014	2840
35°	3395	2842	2623
40°	3305	2665	2411
45°	3197	2474	2189
50°	3087	2271	1963
55°	2959	2072	1729
60°	2829	1844	1485
65°	2673	1589	1223
70°	2491	1294	963
75°	2242	973	701
80°	1890	630	473
85°	1412	339	267

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3197 cd/sqm

TEST NUMBER: P1034806

CATALOG NUMBER: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.0	0.8
10°-20°	156.6	2.3
20°-30°	227.1	3.4
30°-40°	258.7	3.8
40°-50°	252.2	3.7
50°-60°	212.2	3.1
60°-70°	148.7	2.2
70°-80°	76.3	1.1
80°-90°	21.6	0.3
90°-100°	59.3	0.9
100°-110°	394.4	5.8
110°-120°	710.2	10.5
120°-130°	911.5	13.5
130°-140°	980.4	14.5
140°-150°	920.1	13.6
150°-160°	744.3	11.0
160°-170°	481.3	7.1
170°-180°	166.0	2.4
0°-30°	439.8	6.5
0°-40°	698.5	10.3
0°-60°	1163.0	17.2
0°-90°	1409.6	20.8
90°-120°	1163.8	17.2
90°-150°	3975.8	58.7
90°-180°	5367.0	79.2
0°-180°	6777.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	596	596	596	596	596	
5°	595	593	588	592	592	56
15°	565	563	553	553	549	159
25°	513	506	489	484	479	236
35°	442	431	411	398	391	277
45°	362	349	324	306	299	279
55°	274	260	235	214	207	245
65°	186	170	147	129	122	184
75°	99	86	67	57	54	105
85°	25	17	14	14	14	27
90°	1	12	21	27	31	5
95°	74	70	21	27	27	90
105°	381	386	386	386	385	403
115°	715	722	723	718	710	709
125°	1017	1026	1026	1021	1017	908
135°	1268	1276	1273	1271	1263	978
145°	1470	1473	1473	1474	1466	919
155°	1619	1611	1614	1618	1607	746
165°	1708	1701	1702	1710	1699	483
175°	1747	1740	1741	1751	1740	166
180°	1747	1747	1747	1747	1747	

TEST NUMBER: P1034806

CATALOG NUMBER: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	595.5	595.5	595.5	595.5	595.5
2.5°	596.9	595.5	591.0	595.5	595.1
5°	594.6	592.8	587.9	592.4	591.5
7.5°	590.1	588.3	582.5	586.1	585.2
10°	583.4	582.0	575.7	577.1	575.7
12.5°	575.7	573.9	564.9	565.8	563.6
15°	565.4	562.7	553.2	552.8	548.7
17.5°	554.6	550.5	539.3	537.0	533.9
20°	541.5	537.0	522.7	520.4	516.4
22.5°	527.2	522.7	507.4	502.4	499.3
25°	512.8	506.0	489.4	483.5	478.6
27.5°	496.6	488.5	470.9	463.3	458.3
30°	478.6	470.0	451.1	440.8	436.7
32.5°	461.0	450.7	431.3	419.7	414.3
35°	441.7	430.9	410.7	397.6	391.3
37.5°	423.3	410.2	389.5	374.2	367.9
40°	403.5	390.0	368.4	351.3	345.9
42.5°	382.8	368.8	346.3	330.1	321.6
45°	361.6	348.6	323.8	305.9	299.1
47.5°	339.6	326.1	301.4	282.9	275.3
50°	318.9	304.1	278.4	259.5	252.8
52.5°	296.4	281.1	257.3	236.6	229.8
55°	274.4	260.0	234.8	214.5	207.4
57.5°	251.9	236.6	212.3	192.5	186.2
60°	230.3	214.5	190.3	170.5	163.7
62.5°	207.4	192.5	167.8	149.8	143.0
65°	185.8	170.5	146.6	128.6	121.9
67.5°	164.2	148.9	125.9	108.8	103.5
70°	142.1	126.8	104.4	90.4	85.0
72.5°	120.5	105.7	85.0	72.4	69.3
75°	99.0	85.5	66.6	56.7	53.5
77.5°	76.9	66.1	50.4	42.7	40.0
80°	58.5	47.7	35.1	31.0	30.1
82.5°	40.5	31.0	23.4	22.0	21.6
85°	24.7	16.6	14.4	13.9	13.5
87.5°	10.3	7.2	6.7	6.7	6.3
90°	1.3	11.7	20.7	27.2	31.1
92.5°	24.6	13.0	20.7	27.2	28.5
95°	73.8	69.9	20.7	27.2	27.2
97.5°	138.6	146.4	23.3	25.9	27.2
100°	216.3	220.2	225.4	32.4	27.2
102.5°	295.3	300.5	303.1	305.7	196.9
105°	380.8	386.0	386.0	386.0	384.7
107.5°	468.9	468.9	471.5	472.8	467.6
110°	554.4	554.4	557.0	553.1	554.4

TEST NUMBER: P1034806

CATALOG NUMBER: S125RDIW-B375D1340UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	634.7	638.6	639.9	634.7	632.1
115°	715.0	721.5	722.8	717.6	709.8
117.5°	799.2	799.2	804.4	796.6	794.0
120°	876.9	875.6	879.5	876.9	870.4
122.5°	945.5	952.0	953.3	950.7	943.0
125°	1016.8	1025.9	1025.9	1020.7	1016.8
127.5°	1085.4	1091.9	1090.6	1088.0	1077.7
130°	1147.6	1154.1	1155.4	1151.5	1145.0
132.5°	1209.8	1217.6	1213.7	1213.7	1207.2
135°	1268.1	1275.8	1273.3	1270.7	1262.9
137.5°	1322.5	1330.2	1327.7	1327.7	1321.2
140°	1375.6	1378.2	1376.9	1379.5	1371.7
142.5°	1423.5	1424.8	1427.4	1427.4	1419.6
145°	1470.1	1472.7	1472.7	1474.0	1466.2
147.5°	1511.6	1511.6	1512.9	1514.2	1505.1
150°	1550.4	1547.9	1550.4	1553.0	1542.7
152.5°	1588.0	1581.5	1584.1	1586.7	1577.6
155°	1619.1	1611.3	1613.9	1617.8	1607.4
157.5°	1643.7	1639.8	1639.8	1643.7	1633.3
160°	1669.6	1661.8	1663.1	1668.3	1657.9
162.5°	1690.3	1682.6	1683.9	1691.6	1680.0
165°	1708.5	1700.7	1702.0	1709.8	1699.4
167.5°	1722.7	1714.9	1716.2	1725.3	1713.6
170°	1734.4	1725.3	1726.6	1737.0	1725.3
172.5°	1742.1	1733.1	1735.7	1744.7	1733.1
175°	1747.3	1739.6	1740.8	1751.2	1739.6
177.5°	1751.2	1743.4	1744.7	1753.8	1743.4
180°	1747.3	1747.3	1747.3	1747.3	1747.3

(END OF REPORT)