

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035337

Luminaire Tested: S125DIW-B375D470UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035337
REPORT IS A COMBINATION OF REPORTS P1003623 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B375D470UB35-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3137.0 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035337

CATALOG NUMBER: S125DIW-B375D470UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035337

CATALOG NUMBER: S125DIW-B375D470UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3658	3658	3658
5°	3658	3573	3580
10°	3628	3491	3480
15°	3580	3393	3363
20°	3516	3280	3228
25°	3446	3156	3084
30°	3364	3026	2932
35°	3274	2891	2761
40°	3183	2748	2610
45°	3083	2609	2450
50°	2973	2451	2262
55°	2865	2276	2090
60°	2735	2092	1889
65°	2580	1879	1682
70°	2423	1635	1443
75°	2158	1346	1167
80°	1839	1005	859
85°	1418	595	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3083 cd/sqm

TEST NUMBER: P1035337

CATALOG NUMBER: S125DIW-B375D470UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.7
10°-20°	152.2	4.9
20°-30°	224.7	7.2
30°-40°	262.1	8.4
40°-50°	263.3	8.4
50°-60°	231.1	7.4
60°-70°	172.1	5.5
70°-80°	98.3	3.1
80°-90°	29.3	0.9
90°-100°	39.3	1.3
100°-110°	116.8	3.7
110°-120°	198.1	6.3
120°-130°	260.8	8.3
130°-140°	292.2	9.3
140°-150°	286.4	9.1
150°-160°	240.6	7.7
160°-170°	159.9	5.1
170°-180°	56.0	1.8
0°-30°	430.7	13.7
0°-40°	692.8	22.1
0°-60°	1187.2	37.8
0°-90°	1486.9	47.4
90°-120°	354.2	11.3
90°-150°	1193.6	38.0
90°-180°	1650.0	52.6
0°-180°	3137.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	571	571	571	571	571	
5°	570	569	565	569	568	54
15°	543	542	537	539	539	153
25°	493	491	485	486	485	227
35°	426	424	418	416	412	266
45°	349	347	342	336	335	269
55°	266	264	258	254	251	237
65°	179	178	173	169	168	178
75°	95	94	92	91	89	101
85°	25	25	25	25	24	27
90°	0	4	7	10	11	4
95°	30	31	35	39	40	31
105°	105	107	110	113	114	112
115°	198	200	201	201	200	196
125°	289	292	293	292	291	259
135°	376	379	380	380	378	290
145°	456	458	459	459	458	285
155°	522	522	522	524	522	240
165°	567	566	567	569	566	160
175°	590	588	588	591	588	56
180°	591	591	591	591	591	

TEST NUMBER: P1035337

CATALOG NUMBER: S125DIW-B375D470UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.9	570.9	570.9	570.9	570.9
2.5°	572.7	571.4	566.9	571.4	570.9
5°	570.0	569.1	564.6	568.7	568.2
7.5°	566.0	565.1	560.1	564.2	563.7
10°	560.1	559.2	554.2	557.8	557.4
12.5°	552.9	551.1	546.5	549.3	549.3
15°	543.4	542.0	537.1	539.3	539.3
17.5°	533.4	531.2	526.2	528.9	526.7
20°	520.3	519.4	513.6	516.7	514.5
22.5°	507.2	505.4	500.0	501.8	500.5
25°	493.2	491.0	485.1	486.0	484.7
27.5°	477.0	475.6	469.8	470.2	468.9
30°	461.2	459.8	453.0	452.1	450.8
32.5°	444.0	441.8	435.9	434.1	431.4
35°	425.9	424.1	417.8	415.6	411.9
37.5°	407.4	405.2	399.3	396.1	393.9
40°	388.5	386.2	379.9	375.8	374.4
42.5°	368.1	366.3	360.0	356.4	354.1
45°	348.7	346.9	341.5	336.1	334.7
47.5°	327.5	327.9	321.2	315.7	312.6
50°	307.1	305.8	300.4	294.5	291.3
52.5°	286.4	285.5	279.6	274.6	271.0
55°	265.6	264.2	257.9	253.8	250.7
57.5°	243.5	243.0	237.6	232.2	230.8
60°	222.7	220.9	215.9	211.4	208.2
62.5°	201.0	199.6	195.6	190.6	188.4
65°	179.3	178.4	173.4	169.4	167.6
67.5°	158.1	156.3	152.7	149.1	148.2
70°	138.2	136.0	131.9	129.2	127.4
72.5°	116.5	115.2	112.9	109.8	108.0
75°	95.3	94.4	92.1	90.8	89.0
77.5°	75.4	75.0	73.6	72.7	71.4
80°	56.9	56.9	56.0	55.6	54.7
82.5°	40.7	39.7	39.7	38.8	38.8
85°	24.8	25.3	25.3	24.8	23.9
87.5°	12.2	12.2	11.7	11.7	10.8
90°	0.5	4.1	7.4	9.7	11.0
92.5°	13.8	16.1	20.2	23.5	24.4
95°	29.9	30.8	35.4	38.6	39.6
97.5°	46.0	46.5	52.9	55.7	56.1
100°	64.4	64.4	70.4	74.5	75.5
102.5°	84.2	86.5	88.8	93.4	94.8
105°	104.9	107.2	110.0	112.7	114.1
107.5°	127.4	129.7	132.0	133.4	133.4
110°	150.9	153.2	154.6	156.0	155.5

TEST NUMBER: P1035337

CATALOG NUMBER: S125DIW-B375D470UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.8	175.8	177.6	178.1	177.1
115°	198.3	200.1	201.1	200.6	200.1
117.5°	222.2	222.7	223.6	224.1	222.2
120°	244.3	246.6	247.1	247.1	245.2
122.5°	268.2	268.7	270.1	269.6	268.2
125°	289.4	292.2	292.6	291.7	291.2
127.5°	312.9	314.2	314.7	314.2	313.3
130°	333.6	335.9	336.8	336.3	335.4
132.5°	354.3	358.4	358.0	357.5	356.1
135°	376.4	379.1	379.6	379.6	377.7
137.5°	397.1	399.8	400.7	401.2	398.9
140°	416.9	419.2	420.5	421.5	419.2
142.5°	436.6	438.5	440.3	440.8	438.5
145°	456.0	457.8	459.2	459.2	457.8
147.5°	473.9	475.3	476.2	477.6	473.9
150°	491.8	491.4	493.2	493.2	492.3
152.5°	506.6	507.5	508.0	509.3	507.5
155°	521.8	521.8	522.2	524.1	521.8
157.5°	535.6	534.6	535.1	536.9	533.7
160°	547.5	546.1	546.6	548.4	546.1
162.5°	558.1	557.2	557.2	559.5	556.7
165°	567.3	566.4	566.8	568.7	565.9
167.5°	575.6	573.7	573.7	576.5	573.7
170°	582.0	580.2	580.2	582.9	579.7
172.5°	586.6	584.8	584.8	587.6	584.8
175°	589.9	588.0	588.0	590.8	587.6
177.5°	592.2	590.3	589.9	592.6	589.4
180°	591.2	591.2	591.2	591.2	591.2

(END OF REPORT)