

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034815

Luminaire Tested: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034815
REPORT IS A COMBINATION OF REPORTS P1006462 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7673.0 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034815

CATALOG NUMBER: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034815

CATALOG NUMBER: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	88	88	88	88	66	66	66	45	45	45	27	27	27	15	15	15
1	91	87	83	80	80	76	73	71	57	56	54	40	39	38	24	23	23	15	15	15
2	83	76	70	65	73	67	62	58	50	47	45	35	33	32	21	20	19	13	13	13
3	75	66	60	54	66	59	53	48	44	41	37	31	29	27	19	18	16	11	11	11
4	69	59	51	46	60	52	46	41	39	35	32	28	25	23	17	15	14	10	10	10
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	14	12	8	8	8
6	58	47	39	33	51	41	35	30	31	27	24	22	19	17	14	12	11	7	7	7
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	12	11	10	7	7	7
8	49	38	31	25	43	34	27	23	26	21	18	18	15	13	11	10	9	6	6	6
9	46	34	27	22	40	31	25	20	23	19	16	17	14	12	10	9	8	5	5	5
10	43	31	24	20	38	28	22	18	22	17	14	15	13	11	10	8	7	5	5	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3783	3783	3783
5°	3783	3689	3695
10°	3747	3596	3564
15°	3694	3466	3393
20°	3628	3309	3213
25°	3553	3156	3019
30°	3461	2988	2816
35°	3366	2818	2601
40°	3277	2642	2390
45°	3169	2453	2171
50°	3061	2252	1946
55°	2934	2055	1714
60°	2804	1828	1472
65°	2650	1576	1213
70°	2470	1283	955
75°	2221	964	696
80°	1874	625	469
85°	1401	336	265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3169 cd/sqm

TEST NUMBER: P1034815

CATALOG NUMBER: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	0.7
10°-20°	155.3	2.0
20°-30°	225.2	2.9
30°-40°	256.5	3.3
40°-50°	250.0	3.3
50°-60°	210.4	2.7
60°-70°	147.5	1.9
70°-80°	75.6	1.0
80°-90°	21.9	0.3
90°-100°	69.3	0.9
100°-110°	461.0	6.0
110°-120°	830.2	10.8
120°-130°	1065.6	13.9
130°-140°	1146.1	14.9
140°-150°	1075.7	14.0
150°-160°	870.1	11.3
160°-170°	562.7	7.3
170°-180°	194.1	2.5
0°-30°	436.0	5.7
0°-40°	692.6	9.0
0°-60°	1153.1	15.0
0°-90°	1398.0	18.2
90°-120°	1360.6	17.7
90°-150°	4648.1	60.6
90°-180°	6275.0	81.8
0°-180°	7673.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	590	588	583	587	586	56
15°	561	558	548	548	544	158
25°	508	502	485	479	474	234
35°	438	427	407	394	388	274
45°	358	346	321	303	297	277
55°	272	258	233	213	206	243
65°	184	169	145	128	121	182
75°	98	85	66	56	53	104
85°	24	16	14	14	13	27
90°	2	14	24	32	36	6
95°	86	82	24	32	32	106
105°	445	451	451	451	450	472
115°	836	844	845	839	830	829
125°	1189	1199	1199	1193	1189	1062
135°	1482	1492	1488	1486	1476	1143
145°	1719	1722	1722	1723	1714	1075
155°	1893	1884	1887	1891	1879	872
165°	1997	1988	1990	1999	1987	564
175°	2043	2034	2035	2047	2034	195
180°	2043	2043	2043	2043	2043	

TEST NUMBER: P1034815

CATALOG NUMBER: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	590.4	590.4	590.4	590.4	590.4
2.5°	591.8	590.4	586.0	590.4	590.0
5°	589.5	587.8	582.9	587.3	586.4
7.5°	585.1	583.3	577.5	581.1	580.2
10°	578.4	577.1	570.8	572.2	570.8
12.5°	570.8	569.0	560.1	561.0	558.8
15°	560.6	557.9	548.5	548.1	544.1
17.5°	549.9	545.8	534.7	532.5	529.3
20°	536.9	532.5	518.2	516.0	512.0
22.5°	522.7	518.2	503.0	498.1	495.0
25°	508.4	501.7	485.2	479.4	474.5
27.5°	492.3	484.3	466.9	459.3	454.4
30°	474.5	466.0	447.3	437.0	433.0
32.5°	457.1	446.8	427.7	416.1	410.7
35°	437.9	427.2	407.2	394.2	388.0
37.5°	419.6	406.7	386.2	371.0	364.8
40°	400.0	386.6	365.2	348.3	342.9
42.5°	379.5	365.7	343.4	327.3	318.9
45°	358.5	345.6	321.1	303.2	296.6
47.5°	336.7	323.3	298.8	280.5	272.9
50°	316.2	301.5	276.0	257.3	250.6
52.5°	293.9	278.7	255.1	234.6	227.9
55°	272.0	257.8	232.8	212.7	205.6
57.5°	249.7	234.6	210.5	190.9	184.6
60°	228.3	212.7	188.6	169.0	162.3
62.5°	205.6	190.9	166.3	148.5	141.8
65°	184.2	169.0	145.4	127.5	120.9
67.5°	162.8	147.6	124.9	107.9	102.6
70°	140.9	125.8	103.5	89.6	84.3
72.5°	119.5	104.8	84.3	71.8	68.7
75°	98.1	84.7	66.0	56.2	53.1
77.5°	76.3	65.6	49.9	42.4	39.7
80°	58.0	47.3	34.8	30.8	29.9
82.5°	40.1	30.8	23.2	21.9	21.4
85°	24.5	16.5	14.3	13.8	13.4
87.5°	10.3	7.1	6.7	6.7	6.2
90°	1.5	13.6	24.2	31.8	36.3
92.5°	28.8	15.1	24.2	31.8	33.3
95°	86.3	81.8	24.2	31.8	31.8
97.5°	162.0	171.1	27.3	30.3	31.8
100°	252.9	257.4	263.5	37.9	31.8
102.5°	345.3	351.3	354.3	357.4	230.2
105°	445.2	451.3	451.3	451.3	449.7
107.5°	548.2	548.2	551.2	552.7	546.7
110°	648.1	648.1	651.1	646.6	648.1

TEST NUMBER: P1034815

CATALOG NUMBER: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	742.0	746.5	748.1	742.0	739.0
115°	835.9	843.5	845.0	838.9	829.8
117.5°	934.3	934.3	940.4	931.3	928.3
120°	1025.2	1023.7	1028.2	1025.2	1017.6
122.5°	1105.4	1113.0	1114.5	1111.5	1102.4
125°	1188.7	1199.3	1199.3	1193.3	1188.7
127.5°	1269.0	1276.5	1275.0	1272.0	1259.9
130°	1341.7	1349.2	1350.7	1346.2	1338.6
132.5°	1414.3	1423.4	1418.9	1418.9	1411.3
135°	1482.5	1491.6	1488.5	1485.5	1476.4
137.5°	1546.1	1555.2	1552.1	1552.1	1544.6
140°	1608.2	1611.2	1609.7	1612.7	1603.6
142.5°	1664.2	1665.7	1668.7	1668.7	1659.7
145°	1718.7	1721.7	1721.7	1723.3	1714.2
147.5°	1767.2	1767.2	1768.7	1770.2	1759.6
150°	1812.6	1809.6	1812.6	1815.6	1803.5
152.5°	1856.5	1848.9	1852.0	1855.0	1844.4
155°	1892.9	1883.8	1886.8	1891.3	1879.2
157.5°	1921.6	1917.1	1917.1	1921.6	1909.5
160°	1951.9	1942.8	1944.3	1950.4	1938.3
162.5°	1976.1	1967.1	1968.6	1977.7	1964.0
165°	1997.3	1988.3	1989.8	1998.9	1986.7
167.5°	2014.0	2004.9	2006.4	2017.0	2003.4
170°	2027.6	2017.0	2018.5	2030.7	2017.0
172.5°	2036.7	2026.1	2029.1	2039.7	2026.1
175°	2042.8	2033.7	2035.2	2047.3	2033.7
177.5°	2047.3	2038.2	2039.7	2050.3	2038.2
180°	2042.8	2042.8	2042.8	2042.8	2042.8

(END OF REPORT)