

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034817

Luminaire Tested: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034817
REPORT IS A COMBINATION OF REPORTS P1006464 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_3500K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7773.0 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034817

CATALOG NUMBER: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1034817

CATALOG NUMBER: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	88	88	88	88	66	66	66	45	45	45	27	27	27	15	15	15
1	91	87	83	80	80	76	73	71	57	56	54	40	39	38	24	23	23	15	15	15
2	83	76	70	65	73	67	62	58	50	47	45	35	33	32	21	20	19	13	13	13
3	75	66	60	54	66	59	53	48	44	41	37	31	29	27	19	18	16	11	11	11
4	69	59	51	46	60	52	46	41	39	35	32	28	25	23	17	15	14	10	10	10
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	14	12	8	8	8
6	58	47	39	33	51	41	35	30	31	27	24	22	19	17	14	12	11	7	7	7
7	53	42	34	29	47	37	31	26	28	24	21	20	17	15	12	11	10	7	7	7
8	49	38	31	25	43	34	27	23	26	21	18	18	15	13	11	10	9	6	6	6
9	46	34	27	22	40	31	25	20	23	19	16	17	14	12	10	9	8	5	5	5
10	43	31	24	20	38	28	22	18	22	17	14	15	13	11	10	8	7	5	5	5

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3832	3832	3832
5°	3833	3736	3742
10°	3795	3642	3610
15°	3741	3510	3436
20°	3675	3352	3254
25°	3598	3197	3058
30°	3505	3027	2853
35°	3410	2854	2635
40°	3319	2676	2422
45°	3211	2484	2198
50°	3100	2281	1971
55°	2971	2081	1736
60°	2841	1852	1492
65°	2685	1596	1228
70°	2501	1299	967
75°	2251	977	705
80°	1897	632	476
85°	1418	341	269

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3211 cd/sqm

TEST NUMBER: P1034817

CATALOG NUMBER: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	0.7
10°-20°	157.3	2.0
20°-30°	228.1	2.9
30°-40°	259.9	3.3
40°-50°	253.3	3.3
50°-60°	213.2	2.7
60°-70°	149.4	1.9
70°-80°	76.6	1.0
80°-90°	22.2	0.3
90°-100°	70.2	0.9
100°-110°	467.1	6.0
110°-120°	841.1	10.8
120°-130°	1079.6	13.9
130°-140°	1161.1	14.9
140°-150°	1089.7	14.0
150°-160°	881.5	11.3
160°-170°	570.1	7.3
170°-180°	196.6	2.5
0°-30°	441.7	5.7
0°-40°	701.5	9.0
0°-60°	1168.0	15.0
0°-90°	1416.1	18.2
90°-120°	1378.3	17.7
90°-150°	4708.7	60.6
90°-180°	6357.0	81.8
0°-180°	7773.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	597	595	590	595	594	57
15°	568	565	556	555	551	160
25°	515	508	492	486	481	237
35°	444	433	412	399	393	278
45°	363	350	325	307	300	280
55°	276	261	236	216	208	246
65°	187	171	147	129	122	185
75°	99	86	67	57	54	105
85°	25	17	14	14	14	27
90°	2	14	24	32	37	6
95°	87	83	24	32	32	107
105°	451	457	457	457	456	478
115°	847	854	856	850	841	839
125°	1204	1215	1215	1209	1204	1076
135°	1502	1511	1508	1505	1496	1158
145°	1741	1744	1744	1746	1737	1089
155°	1918	1908	1911	1916	1904	884
165°	2023	2014	2016	2025	2013	572
175°	2070	2060	2062	2074	2060	197
180°	2070	2070	2070	2070	2070	

TEST NUMBER: P1034817

CATALOG NUMBER: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	598.1	598.1	598.1	598.1	598.1
2.5°	599.4	598.1	593.5	598.1	597.6
5°	597.2	595.3	590.4	594.9	594.0
7.5°	592.6	590.8	585.0	588.6	587.7
10°	585.9	584.5	578.2	579.5	578.2
12.5°	578.2	576.4	567.3	568.2	566.0
15°	567.8	565.1	555.6	555.1	551.1
17.5°	557.0	552.9	541.6	539.3	536.2
20°	543.9	539.3	524.9	522.6	518.6
22.5°	529.4	524.9	509.5	504.6	501.4
25°	514.9	508.2	491.5	485.6	480.6
27.5°	498.7	490.6	472.9	465.3	460.3
30°	480.6	472.0	453.1	442.7	438.6
32.5°	463.0	452.6	433.2	421.4	416.0
35°	443.6	432.7	412.4	399.3	393.0
37.5°	425.1	412.0	391.2	375.8	369.5
40°	405.2	391.6	369.9	352.8	347.4
42.5°	384.4	370.4	347.8	331.6	323.0
45°	363.2	350.1	325.2	307.2	300.4
47.5°	341.0	327.5	302.6	284.1	276.4
50°	320.3	305.4	279.6	260.6	253.9
52.5°	297.7	282.3	258.4	237.6	230.8
55°	275.5	261.1	235.8	215.5	208.2
57.5°	253.0	237.6	213.2	193.3	187.0
60°	231.3	215.5	191.1	171.2	164.4
62.5°	208.2	193.3	168.5	150.4	143.6
65°	186.6	171.2	147.3	129.2	122.4
67.5°	164.9	149.5	126.5	109.3	103.9
70°	142.7	127.4	104.8	90.8	85.4
72.5°	121.1	106.2	85.4	72.7	69.6
75°	99.4	85.8	66.9	56.9	53.8
77.5°	77.2	66.4	50.6	42.9	40.2
80°	58.7	47.9	35.2	31.2	30.3
82.5°	40.7	31.2	23.5	22.1	21.7
85°	24.8	16.7	14.5	14.0	13.6
87.5°	10.4	7.2	6.8	6.8	6.3
90°	1.5	13.8	24.5	32.2	36.8
92.5°	29.1	15.3	24.5	32.2	33.7
95°	87.4	82.8	24.5	32.2	32.2
97.5°	164.1	173.3	27.6	30.7	32.2
100°	256.2	260.8	266.9	38.4	32.2
102.5°	349.8	355.9	359.0	362.0	233.2
105°	451.0	457.2	457.2	457.2	455.6
107.5°	555.3	555.3	558.4	559.9	553.8
110°	656.6	656.6	659.6	655.0	656.6

TEST NUMBER: P1034817

CATALOG NUMBER: S125RDIW-B375D1560UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	751.7	756.3	757.8	751.7	748.6
115°	846.8	854.5	856.0	849.9	840.7
117.5°	946.5	946.5	952.7	943.5	940.4
120°	1038.6	1037.0	1041.6	1038.6	1030.9
122.5°	1119.9	1127.5	1129.1	1126.0	1116.8
125°	1204.2	1215.0	1215.0	1208.8	1204.2
127.5°	1285.5	1293.2	1291.7	1288.6	1276.3
130°	1359.2	1366.9	1368.4	1363.8	1356.1
132.5°	1432.8	1442.0	1437.4	1437.4	1429.7
135°	1501.9	1511.1	1508.0	1504.9	1495.7
137.5°	1566.3	1575.5	1572.4	1572.4	1564.7
140°	1629.2	1632.2	1630.7	1633.8	1624.6
142.5°	1685.9	1687.5	1690.5	1690.5	1681.3
145°	1741.2	1744.2	1744.2	1745.8	1736.6
147.5°	1790.3	1790.3	1791.8	1793.3	1782.6
150°	1836.3	1833.2	1836.3	1839.3	1827.1
152.5°	1880.8	1873.1	1876.2	1879.2	1868.5
155°	1917.6	1908.4	1911.4	1916.0	1903.8
157.5°	1946.7	1942.1	1942.1	1946.7	1934.5
160°	1977.4	1968.2	1969.7	1975.9	1963.6
162.5°	2002.0	1992.8	1994.3	2003.5	1989.7
165°	2023.4	2014.2	2015.8	2025.0	2012.7
167.5°	2040.3	2031.1	2032.6	2043.4	2029.6
170°	2054.1	2043.4	2044.9	2057.2	2043.4
172.5°	2063.3	2052.6	2055.6	2066.4	2052.6
175°	2069.5	2060.3	2061.8	2074.1	2060.3
177.5°	2074.1	2064.9	2066.4	2077.1	2064.9
180°	2069.5	2069.5	2069.5	2069.5	2069.5

(END OF REPORT)