

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034835

Luminaire Tested: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034835
REPORT IS A COMBINATION OF REPORTS P1006550 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_2700K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4493.0 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034835

CATALOG NUMBER: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1034835

CATALOG NUMBER: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39
1	94	90	86	82	84	81	78	75	64	62	60	49	47	46	34	34	33	33	33	33
2	85	78	72	68	77	71	66	61	56	53	50	43	41	39	30	29	28	28	28	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24	24	24	24
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21	21	21	21
5	65	54	46	41	59	49	42	37	39	34	31	30	27	24	22	20	18	18	18	18
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	16	16	16
7	56	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	14	14	14
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	13	13	13
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11	11	11	11
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	10	10	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3783	3783	3783
5°	3783	3689	3695
10°	3747	3596	3564
15°	3694	3466	3393
20°	3628	3309	3213
25°	3553	3156	3019
30°	3461	2988	2816
35°	3366	2818	2601
40°	3277	2642	2390
45°	3169	2453	2171
50°	3061	2252	1946
55°	2934	2055	1714
60°	2804	1828	1472
65°	2650	1576	1213
70°	2470	1283	955
75°	2221	964	696
80°	1874	625	469
85°	1401	336	265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3169 cd/sqm

TEST NUMBER: P1034835

CATALOG NUMBER: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	1.2
10°-20°	155.3	3.5
20°-30°	225.2	5.0
30°-40°	256.5	5.7
40°-50°	250.0	5.6
50°-60°	210.4	4.7
60°-70°	147.5	3.3
70°-80°	75.6	1.7
80°-90°	20.4	0.5
90°-100°	34.2	0.8
100°-110°	227.5	5.1
110°-120°	409.7	9.1
120°-130°	525.9	11.7
130°-140°	565.6	12.6
140°-150°	530.8	11.8
150°-160°	429.4	9.6
160°-170°	277.7	6.2
170°-180°	95.8	2.1
0°-30°	436.0	9.7
0°-40°	692.6	15.4
0°-60°	1153.1	25.7
0°-90°	1396.5	31.1
90°-120°	671.4	14.9
90°-150°	2293.7	51.0
90°-180°	3097.0	68.9
0°-180°	4493.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	590	590	590	590	590	
5°	590	588	583	587	586	56
15°	561	558	548	548	544	158
25°	508	502	485	479	474	234
35°	438	427	407	394	388	274
45°	358	346	321	303	297	277
55°	272	258	233	213	206	243
65°	184	169	145	128	121	182
75°	98	85	66	56	53	104
85°	24	16	14	14	13	27
90°	1	7	12	16	18	4
95°	43	40	12	16	16	52
105°	220	223	223	223	222	233
115°	412	416	417	414	410	409
125°	587	592	592	589	587	524
135°	732	736	735	733	729	564
145°	848	850	850	850	846	530
155°	934	930	931	933	927	430
165°	986	981	982	986	980	278
175°	1008	1004	1004	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1034835

CATALOG NUMBER: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	590.4	590.4	590.4	590.4	590.4
2.5°	591.8	590.4	586.0	590.4	590.0
5°	589.5	587.8	582.9	587.3	586.4
7.5°	585.1	583.3	577.5	581.1	580.2
10°	578.4	577.1	570.8	572.2	570.8
12.5°	570.8	569.0	560.1	561.0	558.8
15°	560.6	557.9	548.5	548.1	544.1
17.5°	549.9	545.8	534.7	532.5	529.3
20°	536.9	532.5	518.2	516.0	512.0
22.5°	522.7	518.2	503.0	498.1	495.0
25°	508.4	501.7	485.2	479.4	474.5
27.5°	492.3	484.3	466.9	459.3	454.4
30°	474.5	466.0	447.3	437.0	433.0
32.5°	457.1	446.8	427.7	416.1	410.7
35°	437.9	427.2	407.2	394.2	388.0
37.5°	419.6	406.7	386.2	371.0	364.8
40°	400.0	386.6	365.2	348.3	342.9
42.5°	379.5	365.7	343.4	327.3	318.9
45°	358.5	345.6	321.1	303.2	296.6
47.5°	336.7	323.3	298.8	280.5	272.9
50°	316.2	301.5	276.0	257.3	250.6
52.5°	293.9	278.7	255.1	234.6	227.9
55°	272.0	257.8	232.8	212.7	205.6
57.5°	249.7	234.6	210.5	190.9	184.6
60°	228.3	212.7	188.6	169.0	162.3
62.5°	205.6	190.9	166.3	148.5	141.8
65°	184.2	169.0	145.4	127.5	120.9
67.5°	162.8	147.6	124.9	107.9	102.6
70°	140.9	125.8	103.5	89.6	84.3
72.5°	119.5	104.8	84.3	71.8	68.7
75°	98.1	84.7	66.0	56.2	53.1
77.5°	76.3	65.6	49.9	42.4	39.7
80°	58.0	47.3	34.8	30.8	29.9
82.5°	40.1	30.8	23.2	21.9	21.4
85°	24.5	16.5	14.3	13.8	13.4
87.5°	10.3	7.1	6.7	6.7	6.2
90°	0.7	6.7	12.0	15.7	17.9
92.5°	14.2	7.5	12.0	15.7	16.4
95°	42.6	40.4	12.0	15.7	15.7
97.5°	80.0	84.4	13.5	14.9	15.7
100°	124.8	127.0	130.0	18.7	15.7
102.5°	170.4	173.4	174.9	176.4	113.6
105°	219.7	222.7	222.7	222.7	221.9
107.5°	270.5	270.5	272.0	272.7	269.8
110°	319.8	319.8	321.3	319.1	319.8

TEST NUMBER: P1034835

CATALOG NUMBER: S125RDIW-B375D770UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	366.2	368.4	369.1	366.2	364.7
115°	412.5	416.2	417.0	414.0	409.5
117.5°	461.1	461.1	464.0	459.6	458.1
120°	505.9	505.1	507.4	505.9	502.2
122.5°	545.5	549.2	550.0	548.5	544.0
125°	586.6	591.8	591.8	588.8	586.6
127.5°	626.2	629.9	629.2	627.7	621.7
130°	662.1	665.8	666.6	664.3	660.6
132.5°	697.9	702.4	700.2	700.2	696.4
135°	731.6	736.0	734.6	733.1	728.6
137.5°	762.9	767.4	765.9	765.9	762.2
140°	793.6	795.1	794.3	795.8	791.3
142.5°	821.2	822.0	823.5	823.5	819.0
145°	848.1	849.6	849.6	850.4	845.9
147.5°	872.0	872.0	872.8	873.5	868.3
150°	894.5	893.0	894.5	896.0	890.0
152.5°	916.1	912.4	913.9	915.4	910.2
155°	934.1	929.6	931.1	933.3	927.3
157.5°	948.3	946.0	946.0	948.3	942.3
160°	963.2	958.7	959.5	962.5	956.5
162.5°	975.2	970.7	971.4	975.9	969.2
165°	985.6	981.1	981.9	986.4	980.4
167.5°	993.8	989.4	990.1	995.3	988.6
170°	1000.6	995.3	996.1	1002.1	995.3
172.5°	1005.1	999.8	1001.3	1006.6	999.8
175°	1008.0	1003.6	1004.3	1010.3	1003.6
177.5°	1010.3	1005.8	1006.6	1011.8	1005.8
180°	1008.0	1008.0	1008.0	1008.0	1008.0

(END OF REPORT)