

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034844

Luminaire Tested: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034844
REPORT IS A COMBINATION OF REPORTS P1006592 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5822.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034844

CATALOG NUMBER: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034844

CATALOG NUMBER: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46			39
1	96	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39			33
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33			28
3	80	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	29			24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25			21
5	67	55	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22			18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19			16
7	57	45	37	32	52	41	34	30	34	29	25	28	24	21	22	19	17			14
8	53	41	33	28	48	37	31	26	31	26	22	25	22	19	20	17	15			13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14			12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	14	13			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6172	6172	6172
5°	6173	6018	6028
10°	6113	5867	5815
15°	6026	5654	5535
20°	5919	5399	5241
25°	5797	5149	4926
30°	5646	4876	4595
35°	5492	4597	4244
40°	5346	4311	3900
45°	5171	4002	3541
50°	4994	3675	3175
55°	4787	3352	2796
60°	4575	2983	2402
65°	4324	2571	1979
70°	4030	2093	1557
75°	3625	1574	1135
80°	3057	1020	765
85°	2287	548	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5171 cd/sqm

TEST NUMBER: P1034844

CATALOG NUMBER: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.7	1.6
10°-20°	253.4	4.4
20°-30°	367.4	6.3
30°-40°	418.6	7.2
40°-50°	408.0	7.0
50°-60°	343.3	5.9
60°-70°	240.6	4.1
70°-80°	123.3	2.1
80°-90°	32.7	0.6
90°-100°	84.4	1.5
100°-110°	250.9	4.3
110°-120°	425.4	7.3
120°-130°	560.1	9.6
130°-140°	627.6	10.8
140°-150°	615.2	10.6
150°-160°	516.7	8.9
160°-170°	343.5	5.9
170°-180°	120.2	2.1
0°-30°	711.4	12.2
0°-40°	1130.0	19.4
0°-60°	1881.3	32.3
0°-90°	2278.0	39.1
90°-120°	760.7	13.1
90°-150°	2563.6	44.0
90°-180°	3544.0	60.9
0°-180°	5822.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	963	963	963	963	963	
5°	962	959	951	958	957	91
15°	915	910	895	894	888	258
25°	830	818	792	782	774	382
35°	714	697	664	643	633	447
45°	585	564	524	495	484	451
55°	444	420	380	347	335	397
65°	300	276	237	208	197	298
75°	160	138	108	92	87	169
85°	40	27	23	23	22	44
90°	1	9	16	21	24	7
95°	64	66	76	83	85	67
105°	225	230	236	242	245	240
115°	426	430	432	431	430	421
125°	622	628	628	626	626	557
135°	808	814	815	815	811	623
145°	979	983	986	986	983	612
155°	1121	1121	1122	1126	1121	516
165°	1218	1216	1218	1221	1216	344
175°	1267	1263	1263	1269	1262	120
180°	1270	1270	1270	1270	1270	

TEST NUMBER: P1034844

CATALOG NUMBER: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	963.3	963.3	963.3	963.3	963.3
2.5°	965.5	963.3	956.1	963.3	962.6
5°	961.9	959.0	951.0	958.2	956.8
7.5°	954.6	951.7	942.2	948.0	946.6
10°	943.7	941.5	931.3	933.5	931.3
12.5°	931.3	928.4	913.9	915.3	911.7
15°	914.6	910.2	894.9	894.2	887.7
17.5°	897.1	890.6	872.4	868.7	863.6
20°	876.0	868.7	845.5	841.8	835.3
22.5°	852.7	845.5	820.7	812.7	807.6
25°	829.5	818.5	791.6	782.2	774.2
27.5°	803.3	790.2	761.8	749.4	741.4
30°	774.2	760.3	729.8	713.0	706.5
32.5°	745.8	729.0	697.8	678.8	670.1
35°	714.5	697.0	664.3	643.2	633.0
37.5°	684.7	663.6	630.1	605.4	595.2
40°	652.6	630.8	595.9	568.2	559.5
42.5°	619.2	596.6	560.2	534.1	520.2
45°	585.0	563.9	523.9	494.8	483.8
47.5°	549.3	527.5	487.5	457.7	445.3
50°	515.9	491.8	450.4	419.8	408.9
52.5°	479.5	454.7	416.2	382.7	371.8
55°	443.8	420.5	379.8	347.1	335.4
57.5°	407.4	382.7	343.4	311.4	301.2
60°	372.5	347.1	307.8	275.8	264.8
62.5°	335.4	311.4	271.4	242.3	231.4
65°	300.5	275.8	237.2	208.1	197.2
67.5°	265.6	240.8	203.7	176.1	167.3
70°	229.9	205.2	168.8	146.2	137.5
72.5°	195.0	171.0	137.5	117.1	112.0
75°	160.1	138.2	107.7	91.7	86.6
77.5°	124.4	107.0	81.5	69.1	64.8
80°	94.6	77.1	56.8	50.2	48.7
82.5°	65.5	50.2	37.8	35.7	34.9
85°	40.0	26.9	23.3	22.6	21.8
87.5°	16.7	11.6	10.9	10.9	10.2
90°	1.0	8.9	15.8	20.8	23.7
92.5°	29.6	34.6	43.5	50.4	52.4
95°	64.2	66.2	76.1	83.0	85.0
97.5°	98.8	99.8	113.6	119.6	120.6
100°	138.3	138.3	151.2	160.1	162.1
102.5°	180.8	185.8	190.7	200.6	203.6
105°	225.3	230.3	236.2	242.1	245.1
107.5°	273.7	278.7	283.6	286.6	286.6
110°	324.1	329.1	332.0	335.0	334.0

TEST NUMBER: P1034844

CATALOG NUMBER: S125RDIW-B610D1050UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.5	377.5	381.4	382.4	380.5
115°	425.9	429.9	431.8	430.9	429.9
117.5°	477.3	478.3	480.3	481.3	477.3
120°	524.7	529.7	530.7	530.7	526.7
122.5°	576.1	577.1	580.1	579.1	576.1
125°	621.6	627.5	628.5	626.5	625.5
127.5°	672.0	674.9	675.9	674.9	673.0
130°	716.4	721.4	723.4	722.4	720.4
132.5°	760.9	769.8	768.8	767.8	764.9
135°	808.4	814.3	815.3	815.3	811.3
137.5°	852.8	858.7	860.7	861.7	856.8
140°	895.3	900.3	903.2	905.2	900.3
142.5°	937.8	941.8	945.7	946.7	941.8
145°	979.3	983.3	986.2	986.2	983.3
147.5°	1017.8	1020.8	1022.8	1025.8	1017.8
150°	1056.4	1055.4	1059.4	1059.4	1057.4
152.5°	1088.0	1090.0	1091.0	1093.9	1090.0
155°	1120.6	1120.6	1121.6	1125.6	1120.6
157.5°	1150.3	1148.3	1149.3	1153.2	1146.3
160°	1176.0	1173.0	1174.0	1177.9	1173.0
162.5°	1198.7	1196.7	1196.7	1201.7	1195.7
165°	1218.5	1216.5	1217.5	1221.4	1215.5
167.5°	1236.2	1232.3	1232.3	1238.2	1232.3
170°	1250.1	1246.1	1246.1	1252.1	1245.1
172.5°	1260.0	1256.0	1256.0	1261.9	1256.0
175°	1266.9	1262.9	1262.9	1268.9	1261.9
177.5°	1271.8	1267.9	1266.9	1272.8	1265.9
180°	1269.8	1269.8	1269.8	1269.8	1269.8

(END OF REPORT)