

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034856

Luminaire Tested: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034856
REPORT IS A COMBINATION OF REPORTS P1006639 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7737.0 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034856

CATALOG NUMBER: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034856

CATALOG NUMBER: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	38	38	38
1	94	89	86	82	84	80	77	75	64	62	60	48	47	46	34	33	33
2	85	78	72	67	76	70	66	61	56	53	50	43	40	38	30	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	48	43	44	39	36	34	30	28	24	22	20
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6419	6419	6419
5°	6419	6259	6269
10°	6357	6101	6047
15°	6267	5880	5756
20°	6155	5615	5451
25°	6028	5356	5123
30°	5872	5070	4779
35°	5712	4780	4413
40°	5560	4483	4057
45°	5378	4162	3683
50°	5193	3822	3302
55°	4979	3486	2908
60°	4758	3102	2499
65°	4497	2673	2058
70°	4191	2176	1619
75°	3770	1636	1180
80°	3180	1059	796
85°	2378	569	448

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5378 cd/sqm

TEST NUMBER: P1034856

CATALOG NUMBER: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	1.2
10°-20°	263.5	3.4
20°-30°	382.1	4.9
30°-40°	435.3	5.6
40°-50°	424.3	5.5
50°-60°	357.1	4.6
60°-70°	250.2	3.2
70°-80°	128.3	1.7
80°-90°	34.6	0.4
90°-100°	59.3	0.8
100°-110°	394.4	5.1
110°-120°	710.2	9.2
120°-130°	911.5	11.8
130°-140°	980.4	12.7
140°-150°	920.1	11.9
150°-160°	744.3	9.6
160°-170°	481.3	6.2
170°-180°	166.0	2.1
0°-30°	739.9	9.6
0°-40°	1175.2	15.2
0°-60°	1956.5	25.3
0°-90°	2369.6	30.6
90°-120°	1163.8	15.0
90°-150°	3975.8	51.4
90°-180°	5367.0	69.4
0°-180°	7737.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1002	1002	1002	1002	1002	
5°	1000	997	989	996	995	95
15°	951	947	931	930	923	268
25°	863	851	823	813	805	397
35°	743	725	691	669	658	465
45°	608	586	545	514	503	469
55°	462	437	395	361	349	413
65°	312	287	247	216	205	309
75°	166	144	112	95	90	176
85°	42	28	24	24	23	46
90°	1	12	21	27	31	6
95°	74	70	21	27	27	90
105°	381	386	386	386	385	403
115°	715	722	723	718	710	709
125°	1017	1026	1026	1021	1017	908
135°	1268	1276	1273	1271	1263	978
145°	1470	1473	1473	1474	1466	919
155°	1619	1611	1614	1618	1607	746
165°	1708	1701	1702	1710	1699	483
175°	1747	1740	1741	1751	1740	166
180°	1747	1747	1747	1747	1747	

TEST NUMBER: P1034856

CATALOG NUMBER: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1001.8	1001.8	1001.8	1001.8	1001.8
2.5°	1004.1	1001.8	994.3	1001.8	1001.1
5°	1000.3	997.3	989.0	996.5	995.0
7.5°	992.8	989.7	979.9	986.0	984.4
10°	981.4	979.1	968.5	970.8	968.5
12.5°	968.5	965.5	950.4	951.9	948.1
15°	951.1	946.6	930.7	930.0	923.1
17.5°	933.0	926.2	907.3	903.5	898.2
20°	911.0	903.5	879.3	875.5	868.7
22.5°	886.8	879.3	853.5	845.2	839.9
25°	862.6	851.3	823.3	813.4	805.1
27.5°	835.4	821.8	792.2	779.4	771.1
30°	805.1	790.7	758.9	741.5	734.7
32.5°	775.6	758.2	725.7	706.0	696.9
35°	743.1	724.9	690.8	668.9	658.3
37.5°	712.0	690.1	655.3	629.6	619.0
40°	678.7	656.0	619.7	591.0	581.9
42.5°	643.9	620.5	582.6	555.4	541.0
45°	608.4	586.4	544.8	514.5	503.2
47.5°	571.3	548.6	507.0	476.0	463.1
50°	536.5	511.5	468.4	436.6	425.3
52.5°	498.7	472.9	432.8	398.0	386.7
55°	461.6	437.4	395.0	360.9	348.8
57.5°	423.7	398.0	357.2	323.9	313.3
60°	387.4	360.9	320.1	286.8	275.4
62.5°	348.8	323.9	282.2	252.0	240.6
65°	312.5	286.8	246.7	216.4	205.1
67.5°	276.2	250.5	211.9	183.1	174.0
70°	239.1	213.4	175.5	152.1	143.0
72.5°	202.8	177.8	143.0	121.8	116.5
75°	166.5	143.8	112.0	95.3	90.0
77.5°	129.4	111.2	84.7	71.9	67.3
80°	98.4	80.2	59.0	52.2	50.7
82.5°	68.1	52.2	39.3	37.1	36.3
85°	41.6	28.0	24.2	23.5	22.7
87.5°	17.4	12.1	11.4	11.4	10.6
90°	1.3	11.7	20.7	27.2	31.1
92.5°	24.6	13.0	20.7	27.2	28.5
95°	73.8	69.9	20.7	27.2	27.2
97.5°	138.6	146.4	23.3	25.9	27.2
100°	216.3	220.2	225.4	32.4	27.2
102.5°	295.3	300.5	303.1	305.7	196.9
105°	380.8	386.0	386.0	386.0	384.7
107.5°	468.9	468.9	471.5	472.8	467.6
110°	554.4	554.4	557.0	553.1	554.4

TEST NUMBER: P1034856

CATALOG NUMBER: S125RDIW-B610D1340UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	634.7	638.6	639.9	634.7	632.1
115°	715.0	721.5	722.8	717.6	709.8
117.5°	799.2	799.2	804.4	796.6	794.0
120°	876.9	875.6	879.5	876.9	870.4
122.5°	945.5	952.0	953.3	950.7	943.0
125°	1016.8	1025.9	1025.9	1020.7	1016.8
127.5°	1085.4	1091.9	1090.6	1088.0	1077.7
130°	1147.6	1154.1	1155.4	1151.5	1145.0
132.5°	1209.8	1217.6	1213.7	1213.7	1207.2
135°	1268.1	1275.8	1273.3	1270.7	1262.9
137.5°	1322.5	1330.2	1327.7	1327.7	1321.2
140°	1375.6	1378.2	1376.9	1379.5	1371.7
142.5°	1423.5	1424.8	1427.4	1427.4	1419.6
145°	1470.1	1472.7	1472.7	1474.0	1466.2
147.5°	1511.6	1511.6	1512.9	1514.2	1505.1
150°	1550.4	1547.9	1550.4	1553.0	1542.7
152.5°	1588.0	1581.5	1584.1	1586.7	1577.6
155°	1619.1	1611.3	1613.9	1617.8	1607.4
157.5°	1643.7	1639.8	1639.8	1643.7	1633.3
160°	1669.6	1661.8	1663.1	1668.3	1657.9
162.5°	1690.3	1682.6	1683.9	1691.6	1680.0
165°	1708.5	1700.7	1702.0	1709.8	1699.4
167.5°	1722.7	1714.9	1716.2	1725.3	1713.6
170°	1734.4	1725.3	1726.6	1737.0	1725.3
172.5°	1742.1	1733.1	1735.7	1744.7	1733.1
175°	1747.3	1739.6	1740.8	1751.2	1739.6
177.5°	1751.2	1743.4	1744.7	1753.8	1743.4
180°	1747.3	1747.3	1747.3	1747.3	1747.3

(END OF REPORT)