

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034864

Luminaire Tested: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034864
REPORT IS A COMBINATION OF REPORTS P1006680 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7556.0 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034864

CATALOG NUMBER: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034864

CATALOG NUMBER: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38
1	93	89	86	82	84	80	77	74	63	61	59	48	47	45	34	33	32
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	30	28	27
3	78	69	62	56	70	62	56	51	49	45	42	37	35	32	26	25	23
4	71	61	53	47	64	55	48	43	44	39	35	33	30	28	24	22	20
5	65	54	46	41	58	49	42	37	39	34	30	30	27	24	21	19	18
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	19	17	16
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6172	6172	6172
5°	6173	6018	6028
10°	6113	5867	5815
15°	6026	5654	5535
20°	5919	5399	5241
25°	5797	5149	4926
30°	5646	4876	4595
35°	5492	4597	4244
40°	5346	4311	3900
45°	5171	4002	3541
50°	4994	3675	3175
55°	4787	3352	2796
60°	4575	2983	2402
65°	4324	2571	1979
70°	4030	2093	1557
75°	3625	1574	1135
80°	3057	1020	765
85°	2287	548	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5171 cd/sqm

TEST NUMBER: P1034864

CATALOG NUMBER: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.7	1.2
10°-20°	253.4	3.4
20°-30°	367.4	4.9
30°-40°	418.6	5.5
40°-50°	408.0	5.4
50°-60°	343.3	4.5
60°-70°	240.6	3.2
70°-80°	123.3	1.6
80°-90°	33.7	0.4
90°-100°	125.7	1.7
100°-110°	373.5	4.9
110°-120°	633.5	8.4
120°-130°	834.0	11.0
130°-140°	934.5	12.4
140°-150°	916.0	12.1
150°-160°	769.4	10.2
160°-170°	511.5	6.8
170°-180°	179.0	2.4
0°-30°	711.4	9.4
0°-40°	1130.0	15.0
0°-60°	1881.3	24.9
0°-90°	2278.9	30.2
90°-120°	1132.7	15.0
90°-150°	3817.2	50.5
90°-180°	5277.0	69.8
0°-180°	7556.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	963	963	963	963	963	
5°	962	959	951	958	957	91
15°	915	910	895	894	888	258
25°	830	818	792	782	774	382
35°	714	697	664	643	633	447
45°	585	564	524	495	484	451
55°	444	420	380	347	335	397
65°	300	276	237	208	197	298
75°	160	138	108	92	87	169
85°	40	27	23	23	22	44
90°	2	13	24	31	35	9
95°	96	99	113	124	126	100
105°	336	343	352	360	365	358
115°	634	640	643	642	640	627
125°	926	934	936	933	931	829
135°	1204	1212	1214	1214	1208	928
145°	1458	1464	1468	1468	1464	912
155°	1669	1669	1670	1676	1669	769
165°	1814	1811	1813	1819	1810	512
175°	1886	1880	1880	1889	1879	179
180°	1891	1891	1891	1891	1891	

TEST NUMBER: P1034864

CATALOG NUMBER: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	963.3	963.3	963.3	963.3	963.3
2.5°	965.5	963.3	956.1	963.3	962.6
5°	961.9	959.0	951.0	958.2	956.8
7.5°	954.6	951.7	942.2	948.0	946.6
10°	943.7	941.5	931.3	933.5	931.3
12.5°	931.3	928.4	913.9	915.3	911.7
15°	914.6	910.2	894.9	894.2	887.7
17.5°	897.1	890.6	872.4	868.7	863.6
20°	876.0	868.7	845.5	841.8	835.3
22.5°	852.7	845.5	820.7	812.7	807.6
25°	829.5	818.5	791.6	782.2	774.2
27.5°	803.3	790.2	761.8	749.4	741.4
30°	774.2	760.3	729.8	713.0	706.5
32.5°	745.8	729.0	697.8	678.8	670.1
35°	714.5	697.0	664.3	643.2	633.0
37.5°	684.7	663.6	630.1	605.4	595.2
40°	652.6	630.8	595.9	568.2	559.5
42.5°	619.2	596.6	560.2	534.1	520.2
45°	585.0	563.9	523.9	494.8	483.8
47.5°	549.3	527.5	487.5	457.7	445.3
50°	515.9	491.8	450.4	419.8	408.9
52.5°	479.5	454.7	416.2	382.7	371.8
55°	443.8	420.5	379.8	347.1	335.4
57.5°	407.4	382.7	343.4	311.4	301.2
60°	372.5	347.1	307.8	275.8	264.8
62.5°	335.4	311.4	271.4	242.3	231.4
65°	300.5	275.8	237.2	208.1	197.2
67.5°	265.6	240.8	203.7	176.1	167.3
70°	229.9	205.2	168.8	146.2	137.5
72.5°	195.0	171.0	137.5	117.1	112.0
75°	160.1	138.2	107.7	91.7	86.6
77.5°	124.4	107.0	81.5	69.1	64.8
80°	94.6	77.1	56.8	50.2	48.7
82.5°	65.5	50.2	37.8	35.7	34.9
85°	40.0	26.9	23.3	22.6	21.8
87.5°	16.7	11.6	10.9	10.9	10.2
90°	1.5	13.2	23.5	30.9	35.3
92.5°	44.1	51.5	64.7	75.0	78.0
95°	95.6	98.6	113.3	123.6	126.5
97.5°	147.1	148.6	169.2	178.0	179.5
100°	206.0	206.0	225.1	238.4	241.3
102.5°	269.3	276.6	284.0	298.7	303.1
105°	335.5	342.8	351.7	360.5	364.9
107.5°	407.6	414.9	422.3	426.7	426.7
110°	482.6	490.0	494.4	498.8	497.3

TEST NUMBER: P1034864

CATALOG NUMBER: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	559.1	562.1	568.0	569.4	566.5
115°	634.2	640.1	643.0	641.5	640.1
117.5°	710.7	712.2	715.1	716.6	710.7
120°	781.3	788.7	790.2	790.2	784.3
122.5°	857.8	859.3	863.7	862.3	857.8
125°	925.5	934.4	935.8	932.9	931.4
127.5°	1000.6	1005.0	1006.5	1005.0	1002.0
130°	1066.8	1074.1	1077.1	1075.6	1072.7
132.5°	1133.0	1146.2	1144.8	1143.3	1138.9
135°	1203.6	1212.5	1213.9	1213.9	1208.0
137.5°	1269.8	1278.7	1281.6	1283.1	1275.7
140°	1333.1	1340.5	1344.9	1347.8	1340.5
142.5°	1396.4	1402.3	1408.2	1409.6	1402.3
145°	1458.2	1464.1	1468.5	1468.5	1464.1
147.5°	1515.6	1520.0	1522.9	1527.4	1515.6
150°	1573.0	1571.5	1577.4	1577.4	1574.4
152.5°	1620.1	1623.0	1624.5	1628.9	1623.0
155°	1668.6	1668.6	1670.1	1676.0	1668.6
157.5°	1712.8	1709.8	1711.3	1717.2	1706.9
160°	1751.0	1746.6	1748.1	1754.0	1746.6
162.5°	1784.9	1781.9	1781.9	1789.3	1780.4
165°	1814.3	1811.3	1812.8	1818.7	1809.9
167.5°	1840.8	1834.9	1834.9	1843.7	1834.9
170°	1861.4	1855.5	1855.5	1864.3	1854.0
172.5°	1876.1	1870.2	1870.2	1879.0	1870.2
175°	1886.4	1880.5	1880.5	1889.3	1879.0
177.5°	1893.7	1887.9	1886.4	1895.2	1884.9
180°	1890.8	1890.8	1890.8	1890.8	1890.8

(END OF REPORT)