

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034868

Luminaire Tested: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034868
REPORT IS A COMBINATION OF REPORTS P1006686 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8365.0 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034868

CATALOG NUMBER: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034868

CATALOG NUMBER: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	102	102	102	102		91	91	91	91		71	71	71		52	52	52		35	35	35
1	93	89	85	82		83	79	76	74		62	60	58		46	45	44		31	31	30
2	85	78	72	67		75	69	65	60		54	51	48		41	38	37		28	26	25
3	77	68	61	56		69	61	55	51		48	44	41		36	33	31		25	23	22
4	71	60	53	47		63	54	48	43		43	38	35		32	29	27		22	20	19
5	65	54	46	40		58	48	42	37		38	33	30		29	25	23		20	18	16
6	59	48	40	35		53	43	37	32		34	29	26		26	23	20		18	16	14
7	55	43	36	30		49	39	32	28		31	26	23		23	20	18		16	14	13
8	51	39	32	27		45	35	29	24		28	23	20		21	18	16		15	13	11
9	47	36	28	24		42	32	26	22		26	21	18		20	16	14		14	12	10
10	44	32	26	21		39	29	23	19		24	19	16		18	15	13		13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6172	6172	6172
5°	6173	6018	6028
10°	6113	5867	5815
15°	6026	5654	5535
20°	5919	5399	5241
25°	5797	5149	4926
30°	5646	4876	4595
35°	5492	4597	4244
40°	5346	4311	3900
45°	5171	4002	3541
50°	4994	3675	3175
55°	4787	3352	2796
60°	4575	2983	2402
65°	4324	2571	1979
70°	4030	2093	1557
75°	3625	1574	1135
80°	3057	1020	765
85°	2287	548	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5171 cd/sqm

TEST NUMBER: P1034868

CATALOG NUMBER: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.7	1.1
10°-20°	253.4	3.0
20°-30°	367.4	4.4
30°-40°	418.6	5.0
40°-50°	408.0	4.9
50°-60°	343.3	4.1
60°-70°	240.6	2.9
70°-80°	123.3	1.5
80°-90°	33.7	0.4
90°-100°	67.2	0.8
100°-110°	447.2	5.3
110°-120°	805.2	9.6
120°-130°	1033.6	12.4
130°-140°	1111.6	13.3
140°-150°	1043.3	12.5
150°-160°	843.9	10.1
160°-170°	545.8	6.5
170°-180°	188.2	2.3
0°-30°	711.4	8.5
0°-40°	1130.0	13.5
0°-60°	1881.3	22.5
0°-90°	2278.9	27.2
90°-120°	1319.6	15.8
90°-150°	4508.1	53.9
90°-180°	6086.0	72.8
0°-180°	8365.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	963	963	963	963	963	
5°	962	959	951	958	957	91
15°	915	910	895	894	888	258
25°	830	818	792	782	774	382
35°	714	697	664	643	633	447
45°	585	564	524	495	484	451
55°	444	420	380	347	335	397
65°	300	276	237	208	197	298
75°	160	138	108	92	87	169
85°	40	27	23	23	22	44
90°	2	13	24	31	35	7
95°	84	79	24	31	31	103
105°	432	438	438	438	436	457
115°	811	818	820	814	805	804
125°	1153	1163	1163	1157	1153	1030
135°	1438	1447	1444	1441	1432	1109
145°	1667	1670	1670	1671	1663	1043
155°	1836	1827	1830	1834	1823	846
165°	1937	1928	1930	1939	1927	547
175°	1981	1972	1974	1986	1972	189
180°	1981	1981	1981	1981	1981	

TEST NUMBER: P1034868

CATALOG NUMBER: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	963.3	963.3	963.3	963.3	963.3
2.5°	965.5	963.3	956.1	963.3	962.6
5°	961.9	959.0	951.0	958.2	956.8
7.5°	954.6	951.7	942.2	948.0	946.6
10°	943.7	941.5	931.3	933.5	931.3
12.5°	931.3	928.4	913.9	915.3	911.7
15°	914.6	910.2	894.9	894.2	887.7
17.5°	897.1	890.6	872.4	868.7	863.6
20°	876.0	868.7	845.5	841.8	835.3
22.5°	852.7	845.5	820.7	812.7	807.6
25°	829.5	818.5	791.6	782.2	774.2
27.5°	803.3	790.2	761.8	749.4	741.4
30°	774.2	760.3	729.8	713.0	706.5
32.5°	745.8	729.0	697.8	678.8	670.1
35°	714.5	697.0	664.3	643.2	633.0
37.5°	684.7	663.6	630.1	605.4	595.2
40°	652.6	630.8	595.9	568.2	559.5
42.5°	619.2	596.6	560.2	534.1	520.2
45°	585.0	563.9	523.9	494.8	483.8
47.5°	549.3	527.5	487.5	457.7	445.3
50°	515.9	491.8	450.4	419.8	408.9
52.5°	479.5	454.7	416.2	382.7	371.8
55°	443.8	420.5	379.8	347.1	335.4
57.5°	407.4	382.7	343.4	311.4	301.2
60°	372.5	347.1	307.8	275.8	264.8
62.5°	335.4	311.4	271.4	242.3	231.4
65°	300.5	275.8	237.2	208.1	197.2
67.5°	265.6	240.8	203.7	176.1	167.3
70°	229.9	205.2	168.8	146.2	137.5
72.5°	195.0	171.0	137.5	117.1	112.0
75°	160.1	138.2	107.7	91.7	86.6
77.5°	124.4	107.0	81.5	69.1	64.8
80°	94.6	77.1	56.8	50.2	48.7
82.5°	65.5	50.2	37.8	35.7	34.9
85°	40.0	26.9	23.3	22.6	21.8
87.5°	16.7	11.6	10.9	10.9	10.2
90°	1.5	13.2	23.5	30.8	35.2
92.5°	27.9	14.7	23.5	30.8	32.3
95°	83.7	79.3	23.5	30.8	30.8
97.5°	157.2	166.0	26.4	29.4	30.8
100°	245.3	249.7	255.6	36.7	30.8
102.5°	334.9	340.7	343.7	346.6	223.2
105°	431.8	437.7	437.7	437.7	436.2
107.5°	531.7	531.7	534.6	536.1	530.2
110°	628.6	628.6	631.5	627.1	628.6

TEST NUMBER: P1034868

CATALOG NUMBER: S125RDIW-B610D1560UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	719.7	724.1	725.5	719.7	716.7
115°	810.7	818.1	819.5	813.7	804.8
117.5°	906.2	906.2	912.1	903.3	900.3
120°	994.3	992.8	997.2	994.3	987.0
122.5°	1072.2	1079.5	1081.0	1078.0	1069.2
125°	1152.9	1163.2	1163.2	1157.3	1152.9
127.5°	1230.8	1238.1	1236.6	1233.7	1222.0
130°	1301.3	1308.6	1310.1	1305.7	1298.3
132.5°	1371.8	1380.6	1376.2	1376.2	1368.8
135°	1437.9	1446.7	1443.7	1440.8	1432.0
137.5°	1499.5	1508.4	1505.4	1505.4	1498.1
140°	1559.8	1562.7	1561.2	1564.2	1555.4
142.5°	1614.1	1615.6	1618.5	1618.5	1609.7
145°	1667.0	1669.9	1669.9	1671.4	1662.6
147.5°	1714.0	1714.0	1715.4	1716.9	1706.6
150°	1758.0	1755.1	1758.0	1761.0	1749.2
152.5°	1800.6	1793.3	1796.2	1799.2	1788.9
155°	1835.9	1827.1	1830.0	1834.4	1822.7
157.5°	1863.8	1859.4	1859.4	1863.8	1852.0
160°	1893.2	1884.3	1885.8	1891.7	1879.9
162.5°	1916.7	1907.8	1909.3	1918.1	1904.9
165°	1937.2	1928.4	1929.9	1938.7	1926.9
167.5°	1953.4	1944.6	1946.0	1956.3	1943.1
170°	1966.6	1956.3	1957.8	1969.5	1956.3
172.5°	1975.4	1965.1	1968.1	1978.3	1965.1
175°	1981.3	1972.5	1973.9	1985.7	1972.5
177.5°	1985.7	1976.9	1978.3	1988.6	1976.9
180°	1981.3	1981.3	1981.3	1981.3	1981.3

(END OF REPORT)