

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034898

Luminaire Tested: S125RDIW-B850D1050UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034898
REPORT IS A COMBINATION OF REPORTS P1006818 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B850D1050UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7229.0 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034898

CATALOG NUMBER: S125RDIW-B850D1050UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034898

CATALOG NUMBER: S125RDIW-B850D1050UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	45	44	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36
3	80	71	64	58	73	65	59	54	55	50	46	44	41	38	35	33	31
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	31	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	18
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8515	8515	8515
5°	8516	8303	8316
10°	8433	8094	8023
15°	8314	7801	7636
20°	8166	7448	7231
25°	7996	7104	6796
30°	7789	6726	6340
35°	7577	6342	5855
40°	7376	5948	5381
45°	7134	5521	4885
50°	6889	5069	4380
55°	6604	4625	3857
60°	6312	4115	3315
65°	5966	3546	2730
70°	5560	2887	2148
75°	4999	2171	1566
80°	4217	1406	1057
85°	3156	755	595

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7134 cd/sqm

TEST NUMBER: P1034898

CATALOG NUMBER: S125RDIW-B850D1050UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	1.7
10°-20°	349.6	4.8
20°-30°	506.9	7.0
30°-40°	577.5	8.0
40°-50°	562.8	7.8
50°-60°	473.7	6.6
60°-70°	331.9	4.6
70°-80°	170.2	2.4
80°-90°	44.4	0.6
90°-100°	45.2	0.6
100°-110°	300.3	4.2
110°-120°	540.7	7.5
120°-130°	694.1	9.6
130°-140°	746.5	10.3
140°-150°	700.6	9.7
150°-160°	566.7	7.8
160°-170°	366.5	5.1
170°-180°	126.4	1.7
0°-30°	981.5	13.6
0°-40°	1559.0	21.6
0°-60°	2595.5	35.9
0°-90°	3142.0	43.5
90°-120°	886.2	12.3
90°-150°	3027.4	41.9
90°-180°	4087.0	56.5
0°-180°	7229.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1327	1323	1312	1322	1320	126
15°	1262	1256	1235	1234	1225	356
25°	1144	1129	1092	1079	1068	527
35°	986	962	916	887	873	617
45°	807	778	723	683	668	622
55°	612	580	524	479	463	548
65°	415	380	327	287	272	411
75°	221	191	149	126	120	233
85°	55	37	32	31	30	60
90°	1	9	16	21	24	6
95°	56	53	16	21	21	69
105°	290	294	294	294	293	307
115°	544	549	550	546	540	540
125°	774	781	781	777	774	692
135°	966	972	970	968	962	744
145°	1119	1121	1121	1122	1116	700
155°	1233	1227	1229	1232	1224	568
165°	1301	1295	1296	1302	1294	367
175°	1330	1325	1326	1334	1325	127
180°	1330	1330	1330	1330	1330	

TEST NUMBER: P1034898

CATALOG NUMBER: S125RDIW-B850D1050UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1329.0	1329.0	1329.0	1329.0	1329.0
2.5°	1332.0	1329.0	1319.0	1329.0	1328.0
5°	1327.0	1323.0	1312.0	1322.0	1320.0
7.5°	1317.0	1313.0	1299.9	1307.9	1305.9
10°	1301.9	1298.9	1284.9	1287.9	1284.9
12.5°	1284.9	1280.8	1260.8	1262.8	1257.8
15°	1261.8	1255.7	1234.7	1233.7	1224.6
17.5°	1237.7	1228.6	1203.5	1198.5	1191.5
20°	1208.6	1198.5	1166.4	1161.4	1152.4
22.5°	1176.4	1166.4	1132.3	1121.2	1114.2
25°	1144.3	1129.3	1092.1	1079.1	1068.0
27.5°	1108.2	1090.1	1051.0	1033.9	1022.9
30°	1068.0	1049.0	1006.8	983.7	974.7
32.5°	1028.9	1005.8	962.6	936.5	924.5
35°	985.7	961.6	916.5	887.4	873.3
37.5°	944.6	915.5	869.3	835.2	821.1
40°	900.4	870.3	822.1	784.0	771.9
42.5°	854.2	823.1	772.9	736.8	717.7
45°	807.0	777.9	722.7	682.6	667.5
47.5°	757.9	727.7	672.5	631.4	614.3
50°	711.7	678.6	621.3	579.2	564.1
52.5°	661.5	627.4	574.2	528.0	512.9
55°	612.3	580.2	524.0	478.8	462.7
57.5°	562.1	528.0	473.8	429.6	415.6
60°	513.9	478.8	424.6	380.4	365.4
62.5°	462.7	429.6	374.4	334.3	319.2
65°	414.6	380.4	327.2	287.1	272.0
67.5°	366.4	332.3	281.1	242.9	230.9
70°	317.2	283.1	232.9	201.8	189.7
72.5°	269.0	235.9	189.7	161.6	154.6
75°	220.8	190.7	148.6	126.5	119.5
77.5°	171.6	147.6	112.4	95.4	89.3
80°	130.5	106.4	78.3	69.3	67.3
82.5°	90.3	69.3	52.2	49.2	48.2
85°	55.2	37.1	32.1	31.1	30.1
87.5°	23.1	16.1	15.1	15.1	14.1
90°	1.0	8.9	15.8	20.7	23.7
92.5°	18.7	9.9	15.8	20.7	21.7
95°	56.2	53.3	15.8	20.7	20.7
97.5°	105.5	111.5	17.8	19.7	20.7
100°	164.7	167.7	171.6	24.7	20.7
102.5°	224.9	228.8	230.8	232.8	149.9
105°	290.0	293.9	293.9	293.9	292.9
107.5°	357.0	357.0	359.0	360.0	356.1
110°	422.1	422.1	424.1	421.1	422.1

TEST NUMBER: P1034898

CATALOG NUMBER: S125RDIW-B850D1050UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	483.3	486.2	487.2	483.3	481.3
115°	544.4	549.4	550.3	546.4	540.5
117.5°	608.5	608.5	612.5	606.6	604.6
120°	667.7	666.7	669.7	667.7	662.8
122.5°	720.0	724.9	725.9	723.9	718.0
125°	774.2	781.1	781.1	777.2	774.2
127.5°	826.5	831.4	830.5	828.5	820.6
130°	873.9	878.8	879.8	876.8	871.9
132.5°	921.2	927.1	924.2	924.2	919.2
135°	965.6	971.5	969.5	967.5	961.6
137.5°	1007.0	1012.9	1010.9	1010.9	1006.0
140°	1047.4	1049.4	1048.4	1050.4	1044.5
142.5°	1083.9	1084.9	1086.9	1086.9	1081.0
145°	1119.4	1121.4	1121.4	1122.4	1116.5
147.5°	1151.0	1151.0	1152.0	1153.0	1146.1
150°	1180.6	1178.6	1180.6	1182.6	1174.7
152.5°	1209.2	1204.3	1206.2	1208.2	1201.3
155°	1232.9	1226.9	1228.9	1231.9	1224.0
157.5°	1251.6	1248.6	1248.6	1251.6	1243.7
160°	1271.3	1265.4	1266.4	1270.3	1262.4
162.5°	1287.1	1281.2	1282.2	1288.1	1279.2
165°	1300.9	1295.0	1296.0	1301.9	1294.0
167.5°	1311.8	1305.8	1306.8	1313.7	1304.9
170°	1320.6	1313.7	1314.7	1322.6	1313.7
172.5°	1326.6	1319.7	1321.6	1328.5	1319.7
175°	1330.5	1324.6	1325.6	1333.5	1324.6
177.5°	1333.5	1327.5	1328.5	1335.4	1327.5
180°	1330.5	1330.5	1330.5	1330.5	1330.5

(END OF REPORT)