

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034906

Luminaire Tested: S125RDIW-B850D1340UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034906
REPORT IS A COMBINATION OF REPORTS P1006859 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIW-B850D1340UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8636.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034906

CATALOG NUMBER: S125RDIW-B850D1340UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034906

CATALOG NUMBER: S125RDIW-B850D1340UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45			38
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38			32
2	87	80	74	69	79	73	67	63	59	56	52	47	44	42	35	34	32			27
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28			23
4	73	62	54	49	66	57	50	45	46	42	38	37	34	31	28	26	24			20
5	67	55	47	42	60	51	44	39	42	36	33	33	30	27	25	23	21			18
6	61	50	42	36	55	45	38	33	37	32	28	30	26	23	23	21	19			15
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	19	17			14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15			12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13			11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8857	8857	8857
5°	8858	8636	8650
10°	8772	8418	8344
15°	8647	8114	7943
20°	8494	7747	7521
25°	8317	7389	7069
30°	8102	6996	6594
35°	7882	6596	6089
40°	7672	6186	5597
45°	7420	5743	5081
50°	7165	5273	4556
55°	6869	4810	4012
60°	6566	4280	3448
65°	6205	3689	2839
70°	5783	3002	2234
75°	5201	2257	1628
80°	4385	1461	1099
85°	3282	785	618

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7420 cd/sqm

TEST NUMBER: P1034906

CATALOG NUMBER: S125RDIW-B850D1340UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.1	1.5
10°-20°	363.6	4.2
20°-30°	527.2	6.1
30°-40°	600.6	7.0
40°-50°	585.4	6.8
50°-60°	492.7	5.7
60°-70°	345.2	4.0
70°-80°	177.0	2.0
80°-90°	46.7	0.5
90°-100°	59.3	0.7
100°-110°	394.4	4.6
110°-120°	710.2	8.2
120°-130°	911.5	10.6
130°-140°	980.4	11.4
140°-150°	920.1	10.7
150°-160°	744.3	8.6
160°-170°	481.3	5.6
170°-180°	166.0	1.9
0°-30°	1020.9	11.8
0°-40°	1621.5	18.8
0°-60°	2699.6	31.3
0°-90°	3268.6	37.8
90°-120°	1163.8	13.5
90°-150°	3975.8	46.0
90°-180°	5367.0	62.1
0°-180°	8636.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1382	1382	1382	1382	1382	
5°	1380	1376	1365	1375	1373	131
15°	1312	1306	1284	1283	1274	370
25°	1190	1175	1136	1122	1111	548
35°	1025	1000	953	923	908	642
45°	839	809	752	710	694	647
55°	637	604	545	498	481	570
65°	431	396	340	299	283	427
75°	230	198	154	132	124	243
85°	57	39	33	32	31	63
90°	1	12	21	27	31	7
95°	74	70	21	27	27	90
105°	381	386	386	386	385	403
115°	715	722	723	718	710	709
125°	1017	1026	1026	1021	1017	908
135°	1268	1276	1273	1271	1263	978
145°	1470	1473	1473	1474	1466	919
155°	1619	1611	1614	1618	1607	746
165°	1708	1701	1702	1710	1699	483
175°	1747	1740	1741	1751	1740	166
180°	1747	1747	1747	1747	1747	

TEST NUMBER: P1034906

CATALOG NUMBER: S125RDIW-B850D1340UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1382.3	1382.3	1382.3	1382.3	1382.3
2.5°	1385.5	1382.3	1371.9	1382.3	1381.3
5°	1380.3	1376.1	1364.6	1375.0	1373.0
7.5°	1369.8	1365.6	1352.1	1360.4	1358.3
10°	1354.2	1351.0	1336.4	1339.5	1336.4
12.5°	1336.4	1332.2	1311.4	1313.4	1308.2
15°	1312.4	1306.1	1284.2	1283.2	1273.8
17.5°	1287.3	1277.9	1251.8	1246.6	1239.3
20°	1257.1	1246.6	1213.2	1208.0	1198.6
22.5°	1223.7	1213.2	1177.7	1166.2	1158.9
25°	1190.2	1174.6	1135.9	1122.4	1110.9
27.5°	1152.7	1133.9	1093.1	1075.4	1063.9
30°	1110.9	1091.1	1047.2	1023.2	1013.8
32.5°	1070.2	1046.2	1001.3	974.1	961.6
35°	1025.3	1000.2	953.2	923.0	908.3
37.5°	982.5	952.2	904.2	868.7	854.0
40°	936.5	905.2	855.1	815.4	802.9
42.5°	888.5	856.1	803.9	766.3	746.5
45°	839.4	809.2	751.7	710.0	694.3
47.5°	788.3	757.0	699.5	656.7	639.0
50°	740.2	705.8	646.3	602.4	586.8
52.5°	688.0	652.5	597.2	549.2	533.5
55°	636.9	603.5	545.0	498.0	481.3
57.5°	584.7	549.2	492.8	446.9	432.2
60°	534.6	498.0	441.6	395.7	380.0
62.5°	481.3	446.9	389.4	347.7	332.0
65°	431.2	395.7	340.4	298.6	282.9
67.5°	381.1	345.6	292.3	252.7	240.1
70°	329.9	294.4	242.2	209.9	197.3
72.5°	279.8	245.4	197.3	168.1	160.8
75°	229.7	198.4	154.5	131.6	124.2
77.5°	178.5	153.5	116.9	99.2	92.9
80°	135.7	110.7	81.4	72.0	70.0
82.5°	94.0	72.0	54.3	51.2	50.1
85°	57.4	38.6	33.4	32.4	31.3
87.5°	24.0	16.7	15.7	15.7	14.6
90°	1.3	11.7	20.7	27.2	31.1
92.5°	24.6	13.0	20.7	27.2	28.5
95°	73.8	69.9	20.7	27.2	27.2
97.5°	138.6	146.4	23.3	25.9	27.2
100°	216.3	220.2	225.4	32.4	27.2
102.5°	295.3	300.5	303.1	305.7	196.9
105°	380.8	386.0	386.0	386.0	384.7
107.5°	468.9	468.9	471.5	472.8	467.6
110°	554.4	554.4	557.0	553.1	554.4

TEST NUMBER: P1034906

CATALOG NUMBER: S125RDIW-B850D1340UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	634.7	638.6	639.9	634.7	632.1
115°	715.0	721.5	722.8	717.6	709.8
117.5°	799.2	799.2	804.4	796.6	794.0
120°	876.9	875.6	879.5	876.9	870.4
122.5°	945.5	952.0	953.3	950.7	943.0
125°	1016.8	1025.9	1025.9	1020.7	1016.8
127.5°	1085.4	1091.9	1090.6	1088.0	1077.7
130°	1147.6	1154.1	1155.4	1151.5	1145.0
132.5°	1209.8	1217.6	1213.7	1213.7	1207.2
135°	1268.1	1275.8	1273.3	1270.7	1262.9
137.5°	1322.5	1330.2	1327.7	1327.7	1321.2
140°	1375.6	1378.2	1376.9	1379.5	1371.7
142.5°	1423.5	1424.8	1427.4	1427.4	1419.6
145°	1470.1	1472.7	1472.7	1474.0	1466.2
147.5°	1511.6	1511.6	1512.9	1514.2	1505.1
150°	1550.4	1547.9	1550.4	1553.0	1542.7
152.5°	1588.0	1581.5	1584.1	1586.7	1577.6
155°	1619.1	1611.3	1613.9	1617.8	1607.4
157.5°	1643.7	1639.8	1639.8	1643.7	1633.3
160°	1669.6	1661.8	1663.1	1668.3	1657.9
162.5°	1690.3	1682.6	1683.9	1691.6	1680.0
165°	1708.5	1700.7	1702.0	1709.8	1699.4
167.5°	1722.7	1714.9	1716.2	1725.3	1713.6
170°	1734.4	1725.3	1726.6	1737.0	1725.3
172.5°	1742.1	1733.1	1735.7	1744.7	1733.1
175°	1747.3	1739.6	1740.8	1751.2	1739.6
177.5°	1751.2	1743.4	1744.7	1753.8	1743.4
180°	1747.3	1747.3	1747.3	1747.3	1747.3

(END OF REPORT)