

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035453

Luminaire Tested: S125DIW-B610D1560UB35-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035453
REPORT IS A COMBINATION OF REPORTS P1003886 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D1560UB35-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8860.0 lumens
Efficiency: N/A
Efficacy: 116.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035453

CATALOG NUMBER: S125DIW-B610D1560UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035453

CATALOG NUMBER: S125DIW-B610D1560UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	36	36	28
1	93	89	85	82	83	79	76	73	62	60	58	46	45	44	32	31	30	30	30	24
2	85	77	71	66	75	69	64	60	54	51	48	41	39	37	28	27	26	26	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	22	22	17
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19	19	19	14
5	64	53	45	40	57	48	41	36	38	33	29	29	25	23	20	18	16	16	16	12
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	14	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13	13	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	11	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	10	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	9	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6154	6154	6154
5°	6154	6012	6023
10°	6104	5873	5855
15°	6024	5708	5657
20°	5915	5517	5431
25°	5799	5309	5188
30°	5659	5092	4933
35°	5509	4864	4646
40°	5353	4624	4392
45°	5186	4389	4121
50°	5001	4123	3805
55°	4819	3829	3515
60°	4601	3520	3178
65°	4341	3162	2829
70°	4076	2751	2427
75°	3630	2265	1962
80°	3093	1691	1443
85°	2390	1002	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5186 cd/sqm

TEST NUMBER: P1035453

CATALOG NUMBER: S125DIW-B610D1560UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.0
10°-20°	256.0	2.9
20°-30°	378.0	4.3
30°-40°	441.0	5.0
40°-50°	442.9	5.0
50°-60°	388.8	4.4
60°-70°	289.6	3.3
70°-80°	165.4	1.9
80°-90°	50.8	0.6
90°-100°	70.2	0.8
100°-110°	467.1	5.3
110°-120°	841.1	9.5
120°-130°	1079.6	12.2
130°-140°	1161.1	13.1
140°-150°	1089.7	12.3
150°-160°	881.5	9.9
160°-170°	570.1	6.4
170°-180°	196.6	2.2
0°-30°	724.6	8.2
0°-40°	1165.6	13.2
0°-60°	1997.3	22.5
0°-90°	2503.1	28.3
90°-120°	1378.3	15.6
90°-150°	4708.7	53.1
90°-180°	6357.0	71.7
0°-180°	8860.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	960	960	960	960	960	
5°	959	958	950	957	956	91
15°	914	912	904	907	907	258
25°	830	826	816	818	815	382
35°	717	714	703	699	693	448
45°	587	584	574	565	563	452
55°	447	444	434	427	422	399
65°	302	300	292	285	282	299
75°	160	159	155	153	150	171
85°	42	43	43	42	40	46
90°	2	14	24	32	37	7
95°	87	83	24	32	32	107
105°	451	457	457	457	456	478
115°	847	854	856	850	841	839
125°	1204	1215	1215	1209	1204	1076
135°	1502	1511	1508	1505	1496	1158
145°	1741	1744	1744	1746	1737	1089
155°	1918	1908	1911	1916	1904	884
165°	2023	2014	2016	2025	2013	572
175°	2070	2060	2062	2074	2060	197
180°	2070	2070	2070	2070	2070	

TEST NUMBER: P1035453

CATALOG NUMBER: S125DIW-B610D1560UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	960.5	960.5	960.5	960.5	960.5
2.5°	963.6	961.3	953.7	961.3	960.5
5°	959.0	957.5	949.9	956.7	956.0
7.5°	952.2	950.6	942.3	949.1	948.4
10°	942.3	940.8	932.4	938.5	937.7
12.5°	930.1	927.1	919.5	924.0	924.0
15°	914.2	911.9	903.5	907.3	907.3
17.5°	897.4	893.6	885.3	889.8	886.1
20°	875.4	873.9	864.0	869.3	865.5
22.5°	853.4	850.3	841.2	844.3	842.0
25°	829.8	826.0	816.1	817.7	815.4
27.5°	802.5	800.2	790.3	791.1	788.8
30°	775.9	773.6	762.2	760.7	758.4
32.5°	747.0	743.2	733.3	730.3	725.7
35°	716.6	713.6	702.9	699.1	693.0
37.5°	685.4	681.6	671.8	666.4	662.6
40°	653.5	649.7	639.1	632.2	630.0
42.5°	619.3	616.3	605.6	599.6	595.8
45°	586.6	583.6	574.5	565.4	563.1
47.5°	550.9	551.7	540.3	531.2	525.9
50°	516.7	514.5	505.3	495.5	490.1
52.5°	481.8	480.3	470.4	462.0	455.9
55°	446.8	444.5	433.9	427.1	421.7
57.5°	409.6	408.8	399.7	390.6	388.3
60°	374.6	371.6	363.2	355.6	350.3
62.5°	338.2	335.9	329.0	320.7	316.9
65°	301.7	300.2	291.8	285.0	281.9
67.5°	266.0	262.9	256.8	250.8	249.2
70°	232.5	228.7	221.9	217.3	214.3
72.5°	196.1	193.8	190.0	184.7	181.6
75°	160.3	158.8	155.0	152.7	149.7
77.5°	126.9	126.1	123.9	122.3	120.1
80°	95.7	95.7	94.2	93.5	91.9
82.5°	68.4	66.9	66.9	65.4	65.4
85°	41.8	42.6	42.6	41.8	40.3
87.5°	20.5	20.5	19.8	19.8	18.2
90°	1.5	13.8	24.5	32.2	36.8
92.5°	29.1	15.3	24.5	32.2	33.7
95°	87.4	82.8	24.5	32.2	32.2
97.5°	164.1	173.3	27.6	30.7	32.2
100°	256.2	260.8	266.9	38.4	32.2
102.5°	349.8	355.9	359.0	362.0	233.2
105°	451.0	457.2	457.2	457.2	455.6
107.5°	555.3	555.3	558.4	559.9	553.8
110°	656.6	656.6	659.6	655.0	656.6

TEST NUMBER: P1035453

CATALOG NUMBER: S125DIW-B610D1560UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	751.7	756.3	757.8	751.7	748.6
115°	846.8	854.5	856.0	849.9	840.7
117.5°	946.5	946.5	952.7	943.5	940.4
120°	1038.6	1037.0	1041.6	1038.6	1030.9
122.5°	1119.9	1127.5	1129.1	1126.0	1116.8
125°	1204.2	1215.0	1215.0	1208.8	1204.2
127.5°	1285.5	1293.2	1291.7	1288.6	1276.3
130°	1359.2	1366.9	1368.4	1363.8	1356.1
132.5°	1432.8	1442.0	1437.4	1437.4	1429.7
135°	1501.9	1511.1	1508.0	1504.9	1495.7
137.5°	1566.3	1575.5	1572.4	1572.4	1564.7
140°	1629.2	1632.2	1630.7	1633.8	1624.6
142.5°	1685.9	1687.5	1690.5	1690.5	1681.3
145°	1741.2	1744.2	1744.2	1745.8	1736.6
147.5°	1790.3	1790.3	1791.8	1793.3	1782.6
150°	1836.3	1833.2	1836.3	1839.3	1827.1
152.5°	1880.8	1873.1	1876.2	1879.2	1868.5
155°	1917.6	1908.4	1911.4	1916.0	1903.8
157.5°	1946.7	1942.1	1942.1	1946.7	1934.5
160°	1977.4	1968.2	1969.7	1975.9	1963.6
162.5°	2002.0	1992.8	1994.3	2003.5	1989.7
165°	2023.4	2014.2	2015.8	2025.0	2012.7
167.5°	2040.3	2031.1	2032.6	2043.4	2029.6
170°	2054.1	2043.4	2044.9	2057.2	2043.4
172.5°	2063.3	2052.6	2055.6	2066.4	2052.6
175°	2069.5	2060.3	2061.8	2074.1	2060.3
177.5°	2074.1	2064.9	2066.4	2077.1	2064.9
180°	2069.5	2069.5	2069.5	2069.5	2069.5

(END OF REPORT)