

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035471

Luminaire Tested: S125DIW-B610D470UB27-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035471
REPORT IS A COMBINATION OF REPORTS P1003913 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D470UB27-4F0-XX-W2A-F
Description: Define 5 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4348.0 lumens
Efficiency: N/A
Efficacy: 116.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035471

CATALOG NUMBER: S125DIW-B610D470UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1035471

CATALOG NUMBER: S125DIW-B610D470UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	99	95	91	87	92	88	85	82	76	74	71	65	63	62	55	54	53
2	90	83	77	71	84	77	72	67	67	63	59	57	54	51	48	46	44
3	82	73	65	59	76	68	61	56	59	54	50	51	47	44	43	40	38
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	37	40	36	32	34	31	28
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25
7	59	47	38	33	55	44	36	31	38	32	28	33	29	25	29	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	23	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	21	18
10	48	35	28	23	44	33	27	22	30	24	20	26	21	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6075	6075	6075
5°	6075	5934	5946
10°	6025	5799	5780
15°	5947	5636	5585
20°	5839	5447	5362
25°	5725	5241	5122
30°	5586	5027	4870
35°	5438	4802	4587
40°	5285	4564	4335
45°	5119	4332	4068
50°	4937	4070	3757
55°	4757	3781	3470
60°	4542	3475	3137
65°	4285	3122	2793
70°	4025	2716	2396
75°	3584	2235	1937
80°	3054	1670	1425
85°	2361	988	786

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5119 cd/sqm

TEST NUMBER: P1035471

CATALOG NUMBER: S125DIW-B610D470UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.5	2.1
10°-20°	252.7	5.8
20°-30°	373.1	8.6
30°-40°	435.3	10.0
40°-50°	437.2	10.1
50°-60°	383.8	8.8
60°-70°	285.9	6.6
70°-80°	163.3	3.8
80°-90°	48.0	1.1
90°-100°	20.8	0.5
100°-110°	138.1	3.2
110°-120°	248.6	5.7
120°-130°	319.1	7.3
130°-140°	343.2	7.9
140°-150°	322.1	7.4
150°-160°	260.6	6.0
160°-170°	168.5	3.9
170°-180°	58.1	1.3
0°-30°	715.3	16.5
0°-40°	1150.7	26.5
0°-60°	1971.7	45.3
0°-90°	2468.9	56.8
90°-120°	407.4	9.4
90°-150°	1391.9	32.0
90°-180°	1879.0	43.2
0°-180°	4348.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	948	948	948	948	948	
5°	947	945	938	944	944	90
15°	902	900	892	896	896	254
25°	819	815	806	807	805	377
35°	707	704	694	690	684	443
45°	579	576	567	558	556	446
55°	441	439	428	422	416	394
65°	298	296	288	281	278	295
75°	158	157	153	151	148	169
85°	41	42	42	41	40	45
90°	0	4	7	10	11	4
95°	26	24	7	10	10	32
105°	133	135	135	135	135	141
115°	250	253	253	251	248	248
125°	356	359	359	357	356	318
135°	444	447	446	445	442	342
145°	515	516	516	516	513	322
155°	567	564	565	566	563	261
165°	598	595	596	599	595	169
175°	612	609	610	613	609	58
180°	612	612	612	612	612	

TEST NUMBER: P1035471

CATALOG NUMBER: S125DIW-B610D470UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	948.2	948.2	948.2	948.2	948.2
2.5°	951.2	949.0	941.5	949.0	948.2
5°	946.7	945.2	937.7	944.5	943.7
7.5°	940.0	938.5	930.2	937.0	936.2
10°	930.2	928.7	920.5	926.5	925.7
12.5°	918.2	915.2	907.7	912.2	912.2
15°	902.5	900.2	892.0	895.7	895.7
17.5°	886.0	882.2	874.0	878.5	874.7
20°	864.2	862.7	853.0	858.2	854.5
22.5°	842.5	839.5	830.4	833.4	831.2
25°	819.2	815.4	805.7	807.2	804.9
27.5°	792.2	789.9	780.2	780.9	778.7
30°	765.9	763.7	752.4	750.9	748.7
32.5°	737.4	733.7	723.9	720.9	716.4
35°	707.4	704.4	693.9	690.2	684.2
37.5°	676.7	672.9	663.2	657.9	654.2
40°	645.2	641.4	630.9	624.1	621.9
42.5°	611.4	608.4	597.9	591.9	588.1
45°	579.1	576.1	567.1	558.1	555.9
47.5°	543.9	544.6	533.4	524.4	519.1
50°	510.1	507.9	498.9	489.1	483.9
52.5°	475.6	474.1	464.4	456.1	450.1
55°	441.1	438.9	428.4	421.6	416.3
57.5°	404.3	403.6	394.6	385.6	383.3
60°	369.8	366.8	358.6	351.1	345.8
62.5°	333.8	331.6	324.8	316.6	312.8
65°	297.8	296.3	288.1	281.3	278.3
67.5°	262.6	259.6	253.6	247.6	246.1
70°	229.6	225.8	219.1	214.6	211.6
72.5°	193.5	191.3	187.5	182.3	179.3
75°	158.3	156.8	153.0	150.8	147.8
77.5°	125.3	124.5	122.3	120.8	118.5
80°	94.5	94.5	93.0	92.3	90.8
82.5°	67.5	66.0	66.0	64.5	64.5
85°	41.3	42.0	42.0	41.3	39.8
87.5°	20.3	20.3	19.5	19.5	18.0
90°	0.5	4.1	7.3	9.5	10.9
92.5°	8.6	4.5	7.3	9.5	10.0
95°	25.8	24.5	7.3	9.5	9.5
97.5°	48.5	51.2	8.2	9.1	9.5
100°	75.7	77.1	78.9	11.3	9.5
102.5°	103.4	105.2	106.1	107.0	68.9
105°	133.3	135.1	135.1	135.1	134.7
107.5°	164.2	164.2	165.1	165.5	163.7
110°	194.1	194.1	195.0	193.6	194.1

TEST NUMBER: P1035471

CATALOG NUMBER: S125DIW-B610D470UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	222.2	223.6	224.0	222.2	221.3
115°	250.3	252.6	253.0	251.2	248.5
117.5°	279.8	279.8	281.6	278.9	278.0
120°	307.0	306.5	307.9	307.0	304.7
122.5°	331.0	333.3	333.8	332.8	330.1
125°	356.0	359.1	359.1	357.3	356.0
127.5°	380.0	382.3	381.8	380.9	377.3
130°	401.8	404.0	404.5	403.1	400.9
132.5°	423.5	426.3	424.9	424.9	422.6
135°	443.9	446.7	445.8	444.9	442.1
137.5°	463.0	465.7	464.8	464.8	462.5
140°	481.6	482.5	482.0	482.9	480.2
142.5°	498.4	498.8	499.7	499.7	497.0
145°	514.7	515.6	515.6	516.0	513.3
147.5°	529.2	529.2	529.6	530.1	526.9
150°	542.8	541.9	542.8	543.7	540.1
152.5°	555.9	553.7	554.6	555.5	552.3
155°	566.8	564.1	565.0	566.4	562.8
157.5°	575.4	574.1	574.1	575.4	571.8
160°	584.5	581.8	582.3	584.1	580.4
162.5°	591.8	589.1	589.5	592.2	588.1
165°	598.1	595.4	595.9	598.6	594.9
167.5°	603.1	600.4	600.8	604.0	599.9
170°	607.2	604.0	604.5	608.1	604.0
172.5°	609.9	606.7	607.6	610.8	606.7
175°	611.7	609.0	609.5	613.1	609.0
177.5°	613.1	610.4	610.8	614.0	610.4
180°	611.7	611.7	611.7	611.7	611.7

(END OF REPORT)