

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035478

Luminaire Tested: S125DIW-B610D470UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1035478
REPORT IS A COMBINATION OF REPORTS P1003944 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B610D470UB30-4F0-XX-W2A-F1
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4133.0 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1035478

CATALOG NUMBER: S125DIW-B610D470UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1035478

CATALOG NUMBER: S125DIW-B610D470UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	66	66	66
1	100	96	92	88	93	89	86	83	78	75	73	68	66	64	58	56	55
2	91	83	77	72	85	78	73	68	68	64	60	59	56	53	51	49	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34
5	70	58	50	43	65	54	47	41	48	42	37	42	37	33	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6127	6127	6127
5°	6127	5985	5997
10°	6076	5848	5829
15°	5997	5684	5632
20°	5889	5493	5407
25°	5773	5285	5165
30°	5634	5069	4911
35°	5484	4843	4626
40°	5330	4603	4372
45°	5163	4370	4103
50°	4980	4105	3789
55°	4798	3813	3500
60°	4581	3504	3165
65°	4322	3148	2817
70°	4058	2738	2417
75°	3614	2254	1953
80°	3080	1684	1436
85°	2378	997	792

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5163 cd/sqm

TEST NUMBER: P1035478

CATALOG NUMBER: S125DIW-B610D470UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.2	2.2
10°-20°	254.9	6.2
20°-30°	376.3	9.1
30°-40°	439.0	10.6
40°-50°	440.9	10.7
50°-60°	387.1	9.4
60°-70°	288.3	7.0
70°-80°	164.6	4.0
80°-90°	48.5	1.2
90°-100°	39.1	0.9
100°-110°	116.3	2.8
110°-120°	197.2	4.8
120°-130°	259.7	6.3
130°-140°	291.0	7.0
140°-150°	285.2	6.9
150°-160°	239.6	5.8
160°-170°	159.2	3.9
170°-180°	55.7	1.3
0°-30°	721.4	17.5
0°-40°	1160.5	28.1
0°-60°	1988.5	48.1
0°-90°	2489.9	60.2
90°-120°	352.7	8.5
90°-150°	1188.5	28.8
90°-180°	1643.0	39.8
0°-180°	4133.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	956	956	956	956	956	
5°	955	953	946	952	952	91
15°	910	908	900	903	903	257
25°	826	822	812	814	812	380
35°	713	710	700	696	690	446
45°	584	581	572	563	561	450
55°	445	443	432	425	420	397
65°	300	299	290	284	281	298
75°	160	158	154	152	149	170
85°	42	42	42	42	40	46
90°	0	4	7	10	11	5
95°	30	31	35	38	39	31
105°	104	107	110	112	114	111
115°	198	199	200	200	199	195
125°	288	291	291	290	290	258
135°	375	378	378	378	376	289
145°	454	456	457	457	456	284
155°	520	520	520	522	520	239
165°	565	564	564	566	564	159
175°	587	586	586	588	585	56
180°	589	589	589	589	589	

TEST NUMBER: P1035478

CATALOG NUMBER: S125DIW-B610D470UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	956.3	956.3	956.3	956.3	956.3
2.5°	959.3	957.1	949.5	957.1	956.3
5°	954.8	953.3	945.7	952.5	951.8
7.5°	948.0	946.5	938.1	944.9	944.2
10°	938.1	936.6	928.3	934.4	933.6
12.5°	926.0	923.0	915.4	920.0	920.0
15°	910.1	907.9	899.6	903.3	903.3
17.5°	893.5	889.7	881.4	885.9	882.2
20°	871.6	870.0	860.2	865.5	861.7
22.5°	849.6	846.6	837.5	840.5	838.3
25°	826.2	822.4	812.5	814.1	811.8
27.5°	798.9	796.7	786.8	787.6	785.3
30°	772.5	770.2	758.8	757.3	755.0
32.5°	743.7	739.9	730.1	727.1	722.5
35°	713.4	710.4	699.8	696.0	690.0
37.5°	682.4	678.6	668.8	663.5	659.7
40°	650.6	646.9	636.3	629.5	627.2
42.5°	616.6	613.6	603.0	596.9	593.1
45°	584.1	581.0	572.0	562.9	560.6
47.5°	548.5	549.3	537.9	528.8	523.5
50°	514.5	512.2	503.1	493.3	488.0
52.5°	479.7	478.1	468.3	460.0	453.9
55°	444.9	442.6	432.0	425.2	419.9
57.5°	407.8	407.0	398.0	388.9	386.6
60°	373.0	370.0	361.6	354.1	348.8
62.5°	336.7	334.4	327.6	319.3	315.5
65°	300.4	298.8	290.5	283.7	280.7
67.5°	264.8	261.8	255.7	249.7	248.2
70°	231.5	227.7	220.9	216.4	213.4
72.5°	195.2	192.9	189.1	183.8	180.8
75°	159.6	158.1	154.3	152.1	149.0
77.5°	126.3	125.6	123.3	121.8	119.5
80°	95.3	95.3	93.8	93.1	91.5
82.5°	68.1	66.6	66.6	65.1	65.1
85°	41.6	42.4	42.4	41.6	40.1
87.5°	20.4	20.4	19.7	19.7	18.2
90°	0.5	4.1	7.3	9.6	11.0
92.5°	13.7	16.0	20.2	23.4	24.3
95°	29.8	30.7	35.3	38.5	39.4
97.5°	45.8	46.3	52.7	55.4	55.9
100°	64.1	64.1	70.1	74.2	75.1
102.5°	83.8	86.1	88.4	93.0	94.4
105°	104.5	106.7	109.5	112.2	113.6
107.5°	126.9	129.2	131.5	132.9	132.9
110°	150.3	152.6	153.9	155.3	154.9



TEST NUMBER: P1035478

CATALOG NUMBER: S125DIW-B610D470UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	174.1	175.0	176.8	177.3	176.4
115°	197.5	199.3	200.2	199.8	199.3
117.5°	221.3	221.7	222.7	223.1	221.3
120°	243.3	245.6	246.0	246.0	244.2
122.5°	267.1	267.6	268.9	268.5	267.1
125°	288.2	290.9	291.4	290.5	290.0
127.5°	311.5	312.9	313.4	312.9	312.0
130°	332.2	334.5	335.4	334.9	334.0
132.5°	352.8	356.9	356.4	356.0	354.6
135°	374.8	377.5	378.0	378.0	376.1
137.5°	395.4	398.1	399.1	399.5	397.2
140°	415.1	417.4	418.8	419.7	417.4
142.5°	434.8	436.6	438.5	438.9	436.6
145°	454.0	455.9	457.2	457.2	455.9
147.5°	471.9	473.3	474.2	475.6	471.9
150°	489.8	489.3	491.1	491.1	490.2
152.5°	504.4	505.3	505.8	507.2	505.3
155°	519.5	519.5	520.0	521.8	519.5
157.5°	533.3	532.4	532.8	534.7	531.5
160°	545.2	543.8	544.3	546.1	543.8
162.5°	555.7	554.8	554.8	557.1	554.4
165°	564.9	564.0	564.4	566.3	563.5
167.5°	573.1	571.3	571.3	574.1	571.3
170°	579.6	577.7	577.7	580.5	577.3
172.5°	584.1	582.3	582.3	585.1	582.3
175°	587.4	585.5	585.5	588.3	585.1
177.5°	589.6	587.8	587.4	590.1	586.9
180°	588.7	588.7	588.7	588.7	588.7

(END OF REPORT)