Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1035579

Luminaire Tested: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1035579
	REPORT IS A COMBINATION OF REPORTS P1004163 AND P1007351
Test Lab:	INNOVATION CENTER
Issue Date:	5/6/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	NEO-RAY
Catalog Number:	S125DIW-B850D1340UB50-4F0-XX-W2A-A1
Description:	Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	7815.0 lumens
Efficiency:	N/A
Efficacy:	100.2 lumens/watt
Spacing Criteria (0/90/45):	1.23 / 1.43 / 1.52
Luminous Opening:	Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type:	General Diffuse

Input Watts (W):	78
Input Voltage (V):	
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43
1	96	92	88	85	88	84	81	78	70	68	65	56	55	53	44	43	42	36
2	88	81	75	70	80	74	69	64	61	58	54	50	47	45	39	37	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	32	31	26
4	73	63	55	49	67	58	51	46	48	43	39	39	36	33	31	29	26	23
5	67	56	48	42	61	52	45	39	43	38	34	35	31	28	28	25	23	20
6	62	50	42	37	57	46	39	34	39	33	29	32	28	25	25	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	26	22	20	21	18	16	14
9	49	37	30	25	45	35	28	24	29	24	21	24	20	18	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7577	7577	7577	7577
5°	7583	8596	7589	6521
10°	7536	9797	7523	5598
15°	7481	10622	7434	5057
20°	7387	11640	7319	4617
25°	7302	13337	7170	4356
30°	7182	14070	7057	4120
35°	6991	11279	6845	3931
40°	6694	7796	6595	3730
45°	6319	5804	6247	3563
50°	5888	4778	5791	3430
55°	5424	4075	5381	3314
60°	4969	3488	4882	3224
65°	4478	3013	4406	3093
70°	3960	2502	3907	2865
75°	3410	1935	3365	2487
80°	2692	1308	2595	1827
85°	1721	654	1664	932

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°
Vertical Angle: 45°
Luminance: 11573 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.8	1.5
10°-20°	339.0	4.3
20°-30°	550.7	7.0
30°-40°	673.0	8.6
40°-50°	610.5	7.8
50°-60°	486.2	6.2
60°-70°	338.7	4.3
70°-80°	180.4	2.3
80°-90°	47.2	0.6
90°-100°	106.6	1.4
100°-110°	316.8	4.1
110°-120°	537.3	6.9
120°-130°	707.3	9.1
130°-140°	792.6	10.1
140°-150°	776.9	9.9
150°-160°	652.5	8.3
160°-170°	433.8	5.6
170°-180°	151.8	1.9
0°-30°	1003.5	12.8
0°-40°	1676.5	21.5
0°-60°	2773.2	35.5
0°-90°	3339.5	42.7
90°-120°	960.7	12.3
90°-150°	3237.4	41.4
90°-180°	4475.0	57.3
0°-180°	7815.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1183	1183	1183	1183	1183	
5°	1182	1364	1183	1035	1182	112
15°	1135	1704	1128	811	1135	320
25°	1045	2096	1026	685	1045	481
35°	910	1682	890	586	910	568
45°	715	793	707	487	715	551
55°	503	489	499	398	503	450
65°	311	300	306	308	311	309
75°	151	148	149	190	151	160
85°	30	33	29	47	30	36
90°	1	30	1	30	1	8
95°	81	107	81	107	81	85
105°	284	310	284	310	284	303
115°	538	543	538	543	538	532
125°	785	790	785	790	785	703
135°	1021	1025	1021	1025	1021	787
145°	1237	1242	1237	1242	1237	773
155°	1415	1415	1415	1415	1415	652
165°	1539	1535	1539	1535	1539	434
175°	1600	1594	1600	1594	1600	152
180°	1604	1604	1604	1604	1604	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6
2.5°	1184.6	1191.6	1199.6	1205.6	1215.7	1218.7	1223.7	1226.7	1229.7	1232.7	1234.8
5°	1181.6	1198.6	1213.7	1224.7	1243.8	1250.8	1259.9	1270.9	1283.9	1295.0	1302.0
7.5°	1173.5	1200.6	1220.7	1242.8	1268.9	1286.0	1295.0	1318.1	1339.2	1355.2	1376.3
10°	1163.5	1195.6	1226.7	1259.9	1297.0	1316.1	1334.1	1366.3	1395.4	1421.5	1442.6
12.5°	1152.4	1191.6	1228.7	1271.9	1322.1	1345.2	1357.2	1412.4	1448.6	1462.6	1503.8
15°	1135.4	1181.6	1234.8	1288.0	1330.1	1357.2	1390.4	1434.5	1470.7	1501.8	1534.9
17.5°	1119.3	1169.5	1223.7	1282.9	1344.2	1379.3	1404.4	1443.6	1482.7	1522.9	1554.0
20°	1093.2	1158.5	1213.7	1276.9	1349.2	1374.3	1400.4	1446.6	1488.7	1531.9	1571.1
22.5°	1072.1	1134.4	1209.7	1269.9	1331.1	1356.2	1388.3	1436.5	1486.7	1535.9	1593.1
25°	1045.0	1114.3	1179.5	1243.8	1307.0	1334.1	1363.3	1425.5	1477.7	1540.9	1604.2
27.5°	*1015.9*	*1087.2*	*1152.4*	*1210.7*	*1269.9*	*1307.0*	*1338.2*	*1403.4*	*1472.7*	*1541.9*	*1624.3*
30°	984.8	1052.1	1114.3	1171.5	1236.8	1274.9	1306.0	1382.3	1459.6	1548.0	1646.3
32.5°	951.7	1014.9	1068.1	1126.3	1195.6	1230.7	1272.9	1356.2	1447.6	1553.0	1676.5
35°	909.5	969.7	1016.9	1076.1	1145.4	1190.6	1234.8	1328.1	1434.5	1552.0	1693.5
37.5°	867.3	914.5	959.7	1022.9	1103.2	1144.4	1190.6	1293.0	1414.4	1549.0	1700.6
40°	817.1	863.3	902.5	966.7	1051.0	1098.2	1146.4	1253.8	1391.4	1537.9	1675.5
42.5°	767.0	806.1	849.3	916.5	997.8	1048.0	1099.2	1218.7	1361.2	1505.8	1606.2
45°	714.8	744.9	792.1	853.3	939.6	987.8	1046.0	1175.5	1319.1	1447.6	1497.8
47.5°	660.5	690.7	734.8	794.1	879.4	936.6	991.8	1121.3	1265.9	1365.3	1365.3
50°	608.3	632.4	675.6	734.8	821.2	873.4	929.6	1067.1	1183.6	1256.8	1191.6
52.5°	552.1	579.2	615.4	677.6	762.9	810.1	871.4	988.8	1099.2	1129.4	1029.0
55°	502.9	525.0	559.2	618.4	697.7	746.9	799.1	911.5	1004.9	1002.9	895.4
57.5°	451.7	469.8	505.9	560.2	633.4	677.6	729.8	827.2	903.5	876.4	775.0
60°	404.6	417.6	452.7	496.9	567.2	608.3	658.5	737.8	796.1	757.9	655.5
62.5°	355.4	370.4	398.5	441.7	503.9	537.1	574.2	654.5	691.7	657.5	553.1
65°	311.2	323.2	348.3	384.5	440.7	470.8	502.9	569.2	604.3	555.1	468.8
67.5°	267.0	281.1	299.2	331.3	375.4	403.6	431.7	488.9	504.9	460.8	388.5
70°	225.9	237.9	255.0	278.1	315.2	340.3	361.4	408.6	419.6	378.5	321.2
72.5°	185.7	193.7	207.8	226.9	261.0	275.1	297.1	329.3	343.3	306.2	265.0
75°	150.6	156.6	165.6	179.7	202.8	217.8	235.9	266.0	265.0	238.9	209.8
77.5°	116.4	117.5	127.5	140.5	154.6	167.6	176.7	197.8	199.8	183.7	159.6
80°	83.3	86.3	90.3	100.4	112.4	117.5	128.5	141.5	143.6	131.5	115.4
82.5°	53.2	55.2	58.2	64.2	72.3	78.3	84.3	89.3	94.4	87.3	74.3
85°	30.1	31.1	34.1	36.1	40.2	43.2	48.2	53.2	52.2	47.2	43.2
87.5°	15.1	15.1	15.1	17.1	19.1	19.1	21.1	22.1	23.1	21.1	19.1
90°	1.2	3.4	5.6	7.9	10.1	11.2	12.2	14.1	16.1	18.0	20.0
92.5°	37.4	38.8	40.2	41.6	43.0	43.7	44.9	47.4	49.9	52.4	54.9
95°	81.1	81.7	82.2	82.8	83.3	83.6	85.0	87.8	90.5	93.3	96.1
97.5°	124.8	125.1	125.3	125.6	125.9	126.0	127.9	131.8	135.7	139.6	143.5
100°	174.7	174.7	174.7	174.7	174.7	174.7	176.5	180.1	183.7	187.3	190.9
102.5°	228.4	229.8	231.2	232.5	233.9	234.6	235.3	236.7	238.1	239.5	240.9
105°	284.5	285.9	287.3	288.7	290.1	290.8	291.6	293.3	295.0	296.6	298.3
107.5°	345.7	347.1	348.5	349.8	351.2	351.9	352.6	354.0	355.4	356.8	358.2
110°	409.3	410.7	412.1	413.5	414.9	415.6	416.0	416.8	417.7	418.5	419.3

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	474.2	474.8	475.3	475.9	476.4	476.7	477.3	478.4	479.5	480.6	481.7
115°	537.9	539.0	540.1	541.2	542.3	542.9	543.2	543.7	544.2	544.8	545.3
117.5°	602.8	603.1	603.3	603.6	603.9	604.0	604.3	604.8	605.4	605.9	606.5
120°	662.7	664.1	665.5	666.8	668.2	668.9	669.0	669.3	669.6	669.8	670.1
122.5°	727.5	727.8	728.1	728.4	728.7	728.8	729.2	730.0	730.9	731.7	732.5
125°	785.0	786.6	788.3	789.9	791.6	792.4	792.5	792.8	793.1	793.4	793.7
127.5°	848.6	849.4	850.2	851.1	851.9	852.3	852.4	852.7	853.0	853.3	853.6
130°	904.8	906.2	907.6	908.9	910.3	911.0	911.3	911.8	912.4	912.9	913.5
132.5°	960.9	963.4	965.9	968.4	970.9	972.1	972.0	971.7	971.4	971.2	970.9
135°	1020.8	1022.5	1024.1	1025.8	1027.5	1028.3	1028.4	1028.7	1029.0	1029.2	1029.5
137.5°	1077.0	1078.7	1080.3	1082.0	1083.7	1084.5	1084.8	1085.3	1085.9	1086.4	1087.0
140°	1130.6	1132.0	1133.4	1134.8	1136.2	1136.9	1137.3	1138.1	1139.0	1139.8	1140.6
142.5°	1184.3	1185.4	1186.5	1187.6	1188.7	1189.3	1189.9	1191.0	1192.1	1193.2	1194.3
145°	1236.7	1237.8	1238.9	1240.0	1241.1	1241.7	1242.1	1242.9	1243.8	1244.6	1245.4
147.5°	1285.4	1286.2	1287.0	1287.9	1288.7	1289.1	1289.4	1289.9	1290.5	1291.0	1291.6
150°	1334.0	1333.7	1333.5	1333.2	1332.9	1332.8	1333.4	1334.5	1335.6	1336.7	1337.8
152.5°	1374.0	1374.6	1375.1	1375.7	1376.2	1376.5	1376.6	1376.9	1377.2	1377.4	1377.7
155°	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.3	1415.6	1415.9	1416.1	1416.4
157.5°	1452.6	1452.0	1451.5	1450.9	1450.4	1450.1	1450.2	1450.5	1450.8	1451.0	1451.3
160°	1485.0	1484.2	1483.4	1482.5	1481.7	1481.3	1481.4	1481.7	1482.0	1482.2	1482.5
162.5°	1513.7	1513.1	1512.6	1512.0	1511.5	1511.2	1511.2	1511.2	1511.2	1511.2	1511.2
165°	1538.7	1538.1	1537.6	1537.0	1536.5	1536.2	1536.3	1536.6	1536.9	1537.2	1537.5
167.5°	1561.2	1560.1	1559.0	1557.9	1556.8	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2
170°	1578.6	1577.5	1576.4	1575.3	1574.2	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6
172.5°	1591.1	1590.0	1588.9	1587.8	1586.7	1586.1	1586.1	1586.1	1586.1	1586.1	1586.1
175°	1599.9	1598.8	1597.7	1596.6	1595.5	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9
177.5°	1606.1	1605.0	1603.9	1602.8	1601.7	1601.1	1601.0	1600.7	1600.4	1600.2	1599.9
180°	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	*1182.6*	1182.6
2.5°	1236.8	1243.8	1249.8	1254.8	1258.8	1264.9	1260.9	1261.9	1263.9	*1267.9*	1267.9
5°	1317.1	1328.1	1334.1	1354.2	1359.2	1358.2	1355.2	1371.3	1370.3	*1364.3*	1363.3
7.5°	1395.4	1414.4	1431.5	1447.6	1452.6	1465.6	1468.7	1475.7	1473.7	*1483.7*	1478.7
10°	1466.6	1496.8	1512.8	1536.9	1542.9	1549.0	1557.0	1561.0	1570.0	*1569.0*	1569.0
12.5°	1521.9	1558.0	1579.1	1585.1	1608.2	1615.2	1622.2	1635.3	1632.3	*1633.3*	1639.3
15°	1565.0	1600.2	1618.2	1646.3	1662.4	1670.4	1682.5	1696.5	1694.5	*1703.6*	1701.6
17.5°	1597.2	1630.3	1663.4	1705.6	1706.6	1727.7	1755.8	1761.8	1774.8	*1765.8*	1765.8
20°	1623.3	1667.4	1714.6	1768.8	1774.8	1787.9	1822.0	1845.1	1860.2	*1855.1*	1858.2
22.5°	1651.4	1714.6	1769.8	1824.0	1853.1	1876.2	1909.4	1945.5	1958.5	*1966.6*	1964.6
25°	1687.5	1753.8	1835.1	1910.4	1940.5	1984.6	2028.8	2064.0	2074.0	*2096.1*	2076.0
27.5°	*1724.6*	*1818.0*	*1919.4*	*2007.7*	*2045.9*	*2082.0*	*2135.2*	*2161.3*	*2174.4*	*2184.4*	*2177.4*
30°	1755.8	1884.3	1994.7	2076.0	2103.1	2124.2	2154.3	2160.3	2155.3	*2163.3*	2173.4
32.5°	1803.9	1929.4	2022.8	2061.9	2058.9	2057.9	2034.8	2002.7	1995.7	*1976.6*	2002.7
35°	1830.0	1930.4	1966.6	1914.4	1893.3	1855.1	1781.9	1733.7	1691.5	*1682.5*	1684.5
37.5°	1815.0	1854.1	1811.0	1673.4	1639.3	1581.1	1483.7	1415.5	1384.3	*1360.2*	1391.4
40°	1733.7	1690.5	1572.1	1404.4	1355.2	1300.0	1208.7	1171.5	1127.3	*1118.3*	1159.5
42.5°	1599.2	1467.7	1300.0	1170.5	1119.3	1088.2	1011.9	976.8	945.6	*931.6*	954.7
45°	1416.5	1256.8	1088.2	981.8	938.6	901.5	856.3	819.2	799.1	*793.1*	812.1
47.5°	1227.7	1059.1	924.6	845.3	800.1	772.0	729.8	708.7	692.7	*694.7*	697.7
50°	1047.0	893.4	790.0	710.7	688.7	666.6	638.5	620.4	612.4	*615.4*	613.4
52.5°	891.4	767.0	679.6	618.4	608.3	587.3	564.2	549.1	546.1	*547.1*	550.1
55°	754.9	657.5	588.3	544.1	533.1	518.0	503.9	493.9	485.9	*488.9*	487.9
57.5°	651.5	566.2	513.0	476.8	468.8	459.8	446.7	441.7	438.7	*432.7*	437.7
60°	560.2	490.9	444.7	422.6	415.6	409.6	395.5	389.5	387.5	*384.5*	392.5
62.5°	473.8	424.6	389.5	369.4	362.4	356.4	349.3	344.3	345.3	*341.3*	345.3
65°	405.6	365.4	340.3	322.2	313.2	309.2	308.2	300.2	299.2	*300.2*	301.2
67.5°	342.3	308.2	289.1	278.1	271.0	267.0	264.0	259.0	263.0	*260.0*	262.0
70°	285.1	262.0	241.9	230.9	227.9	228.9	223.9	221.9	222.9	*220.9*	222.9
72.5°	229.9	210.8	202.8	194.8	190.7	189.7	186.7	183.7	186.7	*185.7*	185.7
75°	183.7	169.7	160.6	155.6	155.6	153.6	148.6	148.6	148.6	*147.6*	148.6
77.5°	141.5	129.5	125.5	120.5	120.5	117.5	116.4	116.4	114.4	*117.5*	115.4
80°	105.4	96.4	90.3	87.3	87.3	86.3	84.3	83.3	84.3	*83.3*	83.3
82.5°	68.3	64.2	61.2	58.2	57.2	58.2	57.2	55.2	56.2	*55.2*	57.2
85°	39.2	35.1	35.1	33.1	34.1	32.1	33.1	31.1	30.1	*33.1*	31.1
87.5°	17.1	16.1	16.1	14.1	14.1	14.1	13.1	14.1	13.1	*12.0*	13.1
90°	21.4	22.8	24.1	25.5	26.2	26.6	27.5	28.3	29.2	*30.0*	29.2
92.5°	56.8	58.8	60.7	62.6	63.6	63.9	64.4	65.0	65.5	*66.1*	65.5
95°	98.0	100.0	101.9	103.8	104.8	105.1	105.6	106.2	106.7	*107.3*	106.7
97.5°	145.2	146.8	148.5	150.2	151.0	151.1	151.4	151.7	151.9	*152.2*	151.9
100°	193.4	195.9	198.4	200.9	202.2	202.5	203.0	203.6	204.1	*204.7*	204.1
102.5°	243.7	246.4	249.2	251.9	253.3	253.7	254.6	255.4	256.3	*257.1*	256.3
105°	299.9	301.6	303.2	304.9	305.7	306.1	307.0	307.8	308.7	*309.5*	308.7
107.5°	359.0	359.8	360.7	361.5	361.9	361.9	361.9	361.9	361.9	*361.9*	361.9
110°	420.1	420.9	421.8	422.6	423.0	422.9	422.6	422.3	422.1	*421.8*	422.1

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	482.0	482.3	482.6	482.9	483.0	482.7	482.2	481.6	481.1	*480.5*	481.1
115°	545.0	544.8	544.5	544.2	544.1	544.0	543.7	543.4	543.2	*542.9*	543.2
117.5°	606.8	607.0	607.3	607.6	607.7	607.2	606.1	605.0	603.9	*602.8*	603.9
120°	670.1	670.1	670.1	670.1	670.1	669.5	668.4	667.3	666.2	*665.1*	666.2
122.5°	732.2	732.0	731.7	731.4	731.3	730.9	730.0	729.2	728.3	*727.5*	728.3
125°	793.1	792.6	792.0	791.5	791.2	791.1	790.8	790.5	790.2	*789.9*	790.2
127.5°	853.3	853.0	852.7	852.4	852.3	852.0	851.5	850.9	850.4	*849.8*	850.4
130°	913.2	912.9	912.6	912.3	912.2	911.9	911.4	910.8	910.3	*909.7*	910.3
132.5°	970.6	970.3	970.0	969.7	969.6	969.2	968.4	967.5	966.7	*965.9*	966.7
135°	1029.5	1029.5	1029.5	1029.5	1029.5	1029.0	1027.9	1026.8	1025.7	*1024.6*	1025.7
137.5°	1087.3	1087.5	1087.8	1088.1	1088.2	1087.5	1086.1	1084.8	1083.4	*1082.0*	1083.4
140°	1141.2	1141.7	1142.3	1142.8	1143.1	1142.4	1141.0	1139.7	1138.3	*1136.9*	1138.3
142.5°	1194.6	1194.8	1195.1	1195.4	1195.5	1194.8	1193.4	1192.1	1190.7	*1189.3*	1190.7
145°	1245.4	1245.4	1245.4	1245.4	1245.4	1245.0	1244.2	1243.3	1242.5	*1241.7*	1242.5
147.5°	1292.4	1293.3	1294.1	1295.0	1295.4	1294.3	1292.1	1289.8	1287.6	*1285.4*	1287.6
150°	1337.8	1337.8	1337.8	1337.8	1337.8	1337.5	1337.0	1336.4	1335.9	*1335.3*	1335.9
152.5°	1378.5	1379.4	1380.2	1381.1	1381.5	1380.9	1379.8	1378.7	1377.6	*1376.5*	1377.6
155°	1417.5	1418.6	1419.7	1420.8	1421.4	1420.7	1419.3	1418.0	1416.6	*1415.2*	1416.6
157.5°	1452.4	1453.5	1454.6	1455.7	1456.3	1455.3	1453.4	1451.5	1449.5	*1447.6*	1449.5
160°	1483.6	1484.7	1485.8	1486.9	1487.5	1486.8	1485.4	1484.1	1482.7	*1481.3*	1482.7
162.5°	1512.6	1514.0	1515.4	1516.8	1517.5	1516.7	1515.0	1513.3	1511.7	*1510.0*	1511.7
165°	1538.6	1539.7	1540.8	1541.9	1542.4	1541.6	1539.9	1538.3	1536.6	*1535.0*	1536.6
167.5°	1557.9	1559.5	1561.2	1562.9	1563.7	1562.9	1561.2	1559.5	1557.9	*1556.2*	1557.9
170°	1575.3	1576.9	1578.6	1580.3	1581.1	1580.1	1578.2	1576.3	1574.3	*1572.4*	1574.3
172.5°	1587.8	1589.4	1591.1	1592.8	1593.6	1592.8	1591.1	1589.4	1587.8	*1586.1*	1587.8
175°	1596.5	1598.2	1599.8	1601.5	1602.3	1601.3	1599.4	1597.5	1595.5	*1593.6*	1595.5
177.5°	1601.5	1603.2	1604.8	1606.5	1607.3	1606.3	1604.4	1602.5	1600.5	*1598.6*	1600.5
180°	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	*1603.6*	1603.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6
2.5°	1265.9	1258.8	1260.9	1258.8	1253.8	1250.8	1242.8	1232.7	1228.7	1223.7	1220.7
5°	1367.3	1362.2	1361.2	1353.2	1351.2	1339.2	1319.1	1309.0	1297.0	1284.9	1272.9
7.5°	1477.7	1471.7	1451.6	1448.6	1450.6	1435.5	1409.4	1389.4	1364.3	1347.2	1324.1
10°	1569.0	1557.0	1539.9	1540.9	1533.9	1513.8	1487.7	1466.6	1430.5	1408.4	1375.3
12.5°	1624.3	1614.2	1612.2	1602.2	1596.1	1570.0	1538.9	1511.8	1484.7	1454.6	1429.5
15°	1691.5	1678.5	1669.4	1655.4	1651.4	1624.3	1590.1	1559.0	1527.9	1499.8	1446.6
17.5°	1765.8	1751.7	1717.6	1714.6	1690.5	1664.4	1631.3	1585.1	1552.0	1511.8	1472.7
20°	1850.1	1830.0	1785.9	1774.8	1755.8	1712.6	1667.4	1616.2	1563.0	1521.9	1475.7
22.5°	1944.5	1909.4	1877.2	1842.1	1828.0	1774.8	1712.6	1650.4	1586.1	1529.9	1474.7
25°	2067.0	2020.8	1975.6	1940.5	1916.4	1847.1	1763.8	1681.5	1607.2	1533.9	1461.6
27.5°	*2163.3*	*2123.2*	*2074.0*	*2027.8*	*1996.7*	*1914.4*	*1819.0*	*1712.6*	*1620.2*	*1530.9*	*1453.6*
30°	2170.4	2158.3	2128.2	2103.1	2069.0	1980.6	1875.2	1754.8	1640.3	1531.9	1437.5
32.5°	2038.9	2062.9	2076.0	2080.0	2073.0	2021.8	1925.4	1792.9	1658.4	1522.9	1423.5
35°	1755.8	1820.0	1899.3	1929.4	1958.5	1985.6	1935.5	1820.0	1664.4	1520.9	1401.4
37.5°	1445.6	1503.8	1635.3	1695.5	1729.7	1837.1	1878.2	1816.0	1676.5	1522.9	1380.3
40°	1166.5	1258.8	1353.2	1434.5	1487.7	1608.2	1735.7	1749.7	1659.4	1503.8	1353.2
42.5°	981.8	1036.0	1107.3	1182.6	1229.7	1372.3	1545.0	1646.3	1606.2	1472.7	1320.1
45°	836.2	876.4	943.6	968.7	1029.0	1165.5	1348.2	1494.8	1514.8	1423.5	1281.9
47.5°	717.8	751.9	795.1	826.2	874.4	976.8	1131.4	1293.0	1389.4	1356.2	1228.7
50°	632.4	660.5	696.7	714.8	745.9	838.2	954.7	1115.3	1244.8	1255.8	1159.5
52.5°	561.2	577.2	605.3	625.4	650.5	706.7	812.1	944.6	1090.2	1150.4	1074.1
55°	498.9	512.0	537.1	550.1	563.2	611.4	693.7	814.1	950.7	1030.0	986.8
57.5°	442.7	453.7	474.8	486.9	493.9	540.1	603.3	697.7	820.2	916.5	892.4
60°	396.5	406.6	418.6	427.6	435.7	473.8	518.0	594.3	703.7	797.1	791.0
62.5°	347.3	356.4	369.4	378.5	385.5	409.6	446.7	504.9	598.3	684.6	701.7
65°	304.2	311.2	320.2	324.2	333.3	351.4	381.5	433.7	510.0	587.3	599.3
67.5°	265.0	267.0	273.1	282.1	284.1	300.2	327.3	366.4	425.6	488.9	508.0
70°	222.9	225.9	230.9	237.9	241.9	252.0	275.1	301.2	352.4	407.6	421.6
72.5°	185.7	189.7	191.7	195.8	197.8	213.8	223.9	250.0	285.1	331.3	346.3
75°	150.6	154.6	155.6	157.6	159.6	166.6	180.7	196.8	225.9	256.0	276.1
77.5°	119.5	118.5	120.5	123.5	122.5	128.5	137.5	151.6	170.7	195.8	208.8
80°	84.3	84.3	87.3	90.3	89.3	95.4	98.4	108.4	124.5	140.5	145.6
82.5°	56.2	56.2	59.2	59.2	61.2	62.2	66.3	71.3	84.3	92.4	95.4
85°	32.1	32.1	33.1	33.1	33.1	35.1	38.1	40.2	44.2	49.2	51.2
87.5°	13.1	14.1	14.1	14.1	14.1	16.1	16.1	18.1	19.1	21.1	21.1
90°	28.3	27.5	26.6	26.2	25.5	24.1	22.8	21.4	20.0	18.0	16.1
92.5°	65.0	64.4	63.9	63.6	62.6	60.7	58.8	56.8	54.9	52.4	49.9
95°	106.2	105.6	105.1	104.8	103.8	101.9	100.0	98.0	96.1	93.3	90.5
97.5°	151.7	151.4	151.1	151.0	150.2	148.5	146.8	145.2	143.5	139.6	135.7
100°	203.6	203.0	202.5	202.2	200.9	198.4	195.9	193.4	190.9	187.3	183.7
102.5°	255.4	254.6	253.7	253.3	251.9	249.2	246.4	243.7	240.9	239.5	238.1
105°	307.8	307.0	306.1	305.7	304.9	303.2	301.6	299.9	298.3	296.6	295.0
107.5°	361.9	361.9	361.9	361.9	361.5	360.7	359.8	359.0	358.2	356.8	355.4
110°	422.3	422.6	422.9	423.0	422.6	421.8	420.9	420.1	419.3	418.5	417.7

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	481.6	482.2	482.7	483.0	482.9	482.6	482.3	482.0	481.7	480.6	479.5
115°	543.4	543.7	544.0	544.1	544.2	544.5	544.8	545.0	545.3	544.8	544.2
117.5°	605.0	606.1	607.2	607.7	607.6	607.3	607.0	606.8	606.5	605.9	605.4
120°	667.3	668.4	669.5	670.1	670.1	670.1	670.1	670.1	670.1	669.8	669.6
122.5°	729.2	730.0	730.9	731.3	731.4	731.7	732.0	732.2	732.5	731.7	730.9
125°	790.5	790.8	791.1	791.2	791.5	792.0	792.6	793.1	793.7	793.4	793.1
127.5°	850.9	851.5	852.0	852.3	852.4	852.7	853.0	853.3	853.6	853.3	853.0
130°	910.8	911.4	911.9	912.2	912.3	912.6	912.9	913.2	913.5	912.9	912.4
132.5°	967.5	968.4	969.2	969.6	969.7	970.0	970.3	970.6	970.9	971.2	971.4
135°	1026.8	1027.9	1029.0	1029.5	1029.5	1029.5	1029.5	1029.5	1029.5	1029.2	1029.0
137.5°	1084.8	1086.1	1087.5	1088.2	1088.1	1087.8	1087.5	1087.3	1087.0	1086.4	1085.9
140°	1139.7	1141.0	1142.4	1143.1	1142.8	1142.3	1141.7	1141.2	1140.6	1139.8	1139.0
142.5°	1192.1	1193.4	1194.8	1195.5	1195.4	1195.1	1194.8	1194.6	1194.3	1193.2	1192.1
145°	1243.3	1244.2	1245.0	1245.4	1245.4	1245.4	1245.4	1245.4	1245.4	1244.6	1243.8
147.5°	1289.8	1292.1	1294.3	1295.4	1295.0	1294.1	1293.3	1292.4	1291.6	1291.0	1290.5
150°	1336.4	1337.0	1337.5	1337.8	1337.8	1337.8	1337.8	1337.8	1337.8	1336.7	1335.6
152.5°	1378.7	1379.8	1380.9	1381.5	1381.1	1380.2	1379.4	1378.5	1377.7	1377.4	1377.2
155°	1418.0	1419.3	1420.7	1421.4	1420.8	1419.7	1418.6	1417.5	1416.4	1416.1	1415.9
157.5°	1451.5	1453.4	1455.3	1456.3	1455.7	1454.6	1453.5	1452.4	1451.3	1451.0	1450.8
160°	1484.1	1485.4	1486.8	1487.5	1486.9	1485.8	1484.7	1483.6	1482.5	1482.2	1482.0
162.5°	1513.3	1515.0	1516.7	1517.5	1516.8	1515.4	1514.0	1512.6	1511.2	1511.2	1511.2
165°	1538.3	1539.9	1541.6	1542.4	1541.9	1540.8	1539.7	1538.6	1537.5	1537.2	1536.9
167.5°	1559.5	1561.2	1562.9	1563.7	1562.9	1561.2	1559.5	1557.9	1556.2	1556.2	1556.2
170°	1576.3	1578.2	1580.1	1581.1	1580.3	1578.6	1576.9	1575.3	1573.6	1573.6	1573.6
172.5°	1589.4	1591.1	1592.8	1593.6	1592.8	1591.1	1589.4	1587.8	1586.1	1586.1	1586.1
175°	1597.5	1599.4	1601.3	1602.3	1601.5	1599.8	1598.2	1596.5	1594.9	1594.9	1594.9
177.5°	1602.5	1604.4	1606.3	1607.3	1606.5	1604.8	1603.2	1601.5	1599.9	1600.2	1600.4
180°	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6
2.5°	1216.7	1211.7	1205.6	1205.6	1198.6	1195.6	1189.6	1187.6	1182.6	1174.5	1168.5
5°	1259.9	1246.8	1238.8	1231.7	1216.7	1205.6	1194.6	1182.6	1170.5	1156.5	1140.4
7.5°	1302.0	1277.9	1266.9	1254.8	1232.7	1209.7	1187.6	1171.5	1155.5	1133.4	1113.3
10°	1346.2	1316.1	1296.0	1279.9	1245.8	1216.7	1184.6	1161.5	1136.4	1108.3	1082.2
12.5°	1383.3	1344.2	1327.1	1297.0	1257.8	1222.7	1182.6	1147.4	1114.3	1081.2	1049.0
15°	1414.4	1377.3	1335.1	1323.1	1268.9	1218.7	1173.5	1128.3	1087.2	1054.1	1016.9
17.5°	1424.5	1377.3	1356.2	1327.1	1262.9	1210.7	1153.4	1104.3	1065.1	1015.9	986.8
20°	1427.5	1382.3	1353.2	1326.1	1268.9	1199.6	1143.4	1083.2	1036.0	986.8	940.6
22.5°	1419.5	1366.3	1338.2	1312.1	1247.8	1188.6	1123.3	1057.1	1001.9	956.7	910.5
25°	1404.4	1342.2	1315.1	1287.0	1225.7	1160.5	1089.2	1026.0	974.8	920.5	875.4
27.5°	*1384.3*	*1313.1*	*1281.9*	*1252.8*	*1192.6*	*1131.4*	*1064.1*	*998.8*	*941.6*	*884.4*	*842.2*
30°	1359.2	1276.9	1248.8	1210.7	1152.4	1094.2	1033.0	967.7	903.5	849.3	803.1
32.5°	1327.1	1240.8	1203.6	1167.5	1104.3	1051.0	992.8	931.6	869.3	816.1	768.0
35°	1298.0	1199.6	1158.5	1122.3	1052.1	995.8	947.7	890.4	835.2	780.0	736.8
37.5°	1258.8	1158.5	1109.3	1072.1	1000.9	943.6	898.5	854.3	796.1	742.9	702.7
40°	1217.7	1107.3	1061.1	1023.9	949.7	887.4	844.3	805.1	757.9	708.7	666.6
42.5°	1180.5	1058.1	1008.9	963.7	888.4	833.2	789.0	758.9	715.8	671.6	633.4
45°	1133.4	1005.9	952.7	905.5	833.2	773.0	730.8	706.7	674.6	631.4	598.3
47.5°	1085.2	949.7	894.4	848.3	770.0	716.8	675.6	652.5	630.4	596.3	563.2
50°	1021.9	890.4	840.2	787.0	709.7	655.5	621.4	598.3	581.2	557.1	529.0
52.5°	952.7	829.2	775.0	728.8	652.5	603.3	564.2	551.1	534.1	516.0	491.9
55°	879.4	762.9	710.7	665.6	595.3	545.1	513.0	498.9	485.9	471.8	455.8
57.5°	806.1	693.7	644.5	604.3	539.1	490.9	464.8	445.7	436.7	428.7	415.6
60°	714.8	619.4	581.2	545.1	480.9	436.7	411.6	397.5	389.5	385.5	379.5
62.5°	634.4	556.1	514.0	478.8	427.6	388.5	364.4	353.4	346.3	344.3	337.3
65°	549.1	481.9	448.7	418.6	374.4	339.3	319.2	306.2	301.2	300.2	300.2
67.5°	468.8	414.6	381.5	360.4	322.2	291.1	272.0	267.0	264.0	260.0	259.0
70°	393.5	350.3	321.2	303.2	269.0	245.9	230.9	222.9	222.9	219.8	217.8
72.5°	327.3	284.1	265.0	250.0	221.9	201.8	190.7	188.7	181.7	180.7	180.7
75°	256.0	223.9	210.8	197.8	176.7	162.6	153.6	148.6	144.6	144.6	145.6
77.5°	192.7	170.7	158.6	148.6	133.5	124.5	117.5	115.4	111.4	111.4	111.4
80°	136.5	124.5	115.4	107.4	96.4	88.3	84.3	80.3	80.3	79.3	80.3
82.5°	88.3	78.3	73.3	72.3	62.2	59.2	54.2	55.2	52.2	51.2	53.2
85°	51.2	46.2	40.2	38.1	34.1	30.1	28.1	29.1	28.1	27.1	28.1
87.5°	20.1	17.1	16.1	16.1	13.1	12.0	11.0	12.0	10.0	10.0	11.0
90°	14.1	12.2	11.2	10.1	7.9	5.6	3.4	1.2	3.4	5.6	7.9
92.5°	47.4	44.9	43.7	43.0	41.6	40.2	38.8	37.4	38.8	40.2	41.6
95°	87.8	85.0	83.6	83.3	82.8	82.2	81.7	81.1	81.7	82.2	82.8
97.5°	131.8	127.9	126.0	125.9	125.6	125.3	125.1	124.8	125.1	125.3	125.6
100°	180.1	176.5	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7	174.7
102.5°	236.7	235.3	234.6	233.9	232.5	231.2	229.8	228.4	229.8	231.2	232.5
105°	293.3	291.6	290.8	290.1	288.7	287.3	285.9	284.5	285.9	287.3	288.7
107.5°	354.0	352.6	351.9	351.2	349.8	348.5	347.1	345.7	347.1	348.5	349.8
110°	416.8	416.0	415.6	414.9	413.5	412.1	410.7	409.3	410.7	412.1	413.5

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	478.4	477.3	476.7	476.4	475.9	475.3	474.8	474.2	474.8	475.3	475.9
115°	543.7	543.2	542.9	542.3	541.2	540.1	539.0	537.9	539.0	540.1	541.2
117.5°	604.8	604.3	604.0	603.9	603.6	603.3	603.1	602.8	603.1	603.3	603.6
120°	669.3	669.0	668.9	668.2	666.8	665.5	664.1	662.7	664.1	665.5	666.8
122.5°	730.0	729.2	728.8	728.7	728.4	728.1	727.8	727.5	727.8	728.1	728.4
125°	792.8	792.5	792.4	791.6	789.9	788.3	786.6	785.0	786.6	788.3	789.9
127.5°	852.7	852.4	852.3	851.9	851.1	850.2	849.4	848.6	849.4	850.2	851.1
130°	911.8	911.3	911.0	910.3	908.9	907.6	906.2	904.8	906.2	907.6	908.9
132.5°	971.7	972.0	972.1	970.9	968.4	965.9	963.4	960.9	963.4	965.9	968.4
135°	1028.7	1028.4	1028.3	1027.5	1025.8	1024.1	1022.5	1020.8	1022.5	1024.1	1025.8
137.5°	1085.3	1084.8	1084.5	1083.7	1082.0	1080.3	1078.7	1077.0	1078.7	1080.3	1082.0
140°	1138.1	1137.3	1136.9	1136.2	1134.8	1133.4	1132.0	1130.6	1132.0	1133.4	1134.8
142.5°	1191.0	1189.9	1189.3	1188.7	1187.6	1186.5	1185.4	1184.3	1185.4	1186.5	1187.6
145°	1242.9	1242.1	1241.7	1241.1	1240.0	1238.9	1237.8	1236.7	1237.8	1238.9	1240.0
147.5°	1289.9	1289.4	1289.1	1288.7	1287.9	1287.0	1286.2	1285.4	1286.2	1287.0	1287.9
150°	1334.5	1333.4	1332.8	1332.9	1333.2	1333.5	1333.7	1334.0	1333.7	1333.5	1333.2
152.5°	1376.9	1376.6	1376.5	1376.2	1375.7	1375.1	1374.6	1374.0	1374.6	1375.1	1375.7
155°	1415.6	1415.3	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2	1415.2
157.5°	1450.5	1450.2	1450.1	1450.4	1450.9	1451.5	1452.0	1452.6	1452.0	1451.5	1450.9
160°	1481.7	1481.4	1481.3	1481.7	1482.5	1483.4	1484.2	1485.0	1484.2	1483.4	1482.5
162.5°	1511.2	1511.2	1511.2	1511.5	1512.0	1512.6	1513.1	1513.7	1513.1	1512.6	1512.0
165°	1536.6	1536.3	1536.2	1536.5	1537.0	1537.6	1538.1	1538.7	1538.1	1537.6	1537.0
167.5°	1556.2	1556.2	1556.2	1556.8	1557.9	1559.0	1560.1	1561.2	1560.1	1559.0	1557.9
170°	1573.6	1573.6	1573.6	1574.2	1575.3	1576.4	1577.5	1578.6	1577.5	1576.4	1575.3
172.5°	1586.1	1586.1	1586.1	1586.7	1587.8	1588.9	1590.0	1591.1	1590.0	1588.9	1587.8
175°	1594.9	1594.9	1594.9	1595.5	1596.6	1597.7	1598.8	1599.9	1598.8	1597.7	1596.6
177.5°	1600.7	1601.0	1601.1	1601.7	1602.8	1603.9	1605.0	1606.1	1605.0	1603.9	1602.8
180°	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6
2.5°	1166.5	1164.5	1159.5	1156.5	1146.4	1134.4	1130.4	1120.3	1124.3	1117.3	1117.3
5°	1135.4	1126.3	1120.3	1111.3	1092.2	1079.2	1065.1	1058.1	1054.1	1049.0	1045.0
7.5°	1095.2	1088.2	1082.2	1065.1	1044.0	1026.0	1008.9	1001.9	988.8	979.8	975.8
10°	1060.1	1050.0	1036.0	1015.9	993.8	970.7	955.7	940.6	930.6	925.6	914.5
12.5°	1023.9	1011.9	996.8	967.7	943.6	929.6	902.5	888.4	883.4	879.4	866.3
15°	986.8	973.8	955.7	928.6	907.5	874.4	858.3	847.3	835.2	834.2	824.2
17.5°	953.7	937.6	922.6	889.4	863.3	834.2	825.2	813.1	802.1	790.0	785.0
20°	911.5	896.5	885.4	849.3	820.2	802.1	787.0	777.0	770.0	757.9	755.9
22.5°	873.4	857.3	842.2	815.1	790.0	767.0	748.9	737.8	734.8	729.8	720.8
25°	836.2	820.2	802.1	777.0	750.9	734.8	718.8	711.7	705.7	697.7	690.7
27.5°	*805.1*	*790.0*	*773.0*	*741.9*	*719.8*	*707.7*	*690.7*	*682.6*	*674.6*	*670.6*	*667.6*
30°	768.0	750.9	737.8	713.7	689.7	673.6	661.5	654.5	647.5	643.5	641.5
32.5°	731.8	715.8	706.7	680.6	661.5	642.5	633.4	628.4	624.4	620.4	616.4
35°	702.7	686.6	672.6	648.5	629.4	616.4	609.3	601.3	598.3	594.3	594.3
37.5°	666.6	654.5	640.5	617.4	600.3	590.3	584.3	574.2	573.2	571.2	568.2
40°	635.4	623.4	610.4	590.3	575.2	563.2	555.1	550.1	547.1	545.1	543.1
42.5°	602.3	589.3	583.2	560.2	547.1	535.1	531.0	526.0	525.0	521.0	516.0
45°	570.2	559.2	547.1	530.0	519.0	509.0	502.9	498.9	493.9	492.9	489.9
47.5°	542.1	529.0	518.0	501.9	489.9	481.9	476.8	471.8	467.8	464.8	461.8
50°	505.9	495.9	486.9	469.8	459.8	451.7	444.7	440.7	436.7	436.7	436.7
52.5°	470.8	461.8	453.7	441.7	429.7	422.6	414.6	411.6	409.6	406.6	409.6
55°	436.7	427.6	419.6	410.6	396.5	390.5	382.5	379.5	380.5	380.5	383.5
57.5°	400.5	393.5	388.5	377.5	364.4	358.4	353.4	350.3	350.3	354.4	355.4
60°	365.4	358.4	349.3	339.3	331.3	324.2	321.2	322.2	322.2	324.2	329.3
62.5°	326.3	322.2	317.2	303.2	298.1	293.1	289.1	292.1	291.1	296.1	303.2
65°	290.1	286.1	279.1	272.0	266.0	261.0	260.0	261.0	263.0	268.0	276.1
67.5°	250.0	250.0	243.9	237.9	232.9	227.9	228.9	229.9	231.9	237.9	250.0
70°	216.8	212.8	206.8	202.8	198.8	196.8	194.8	198.8	204.8	208.8	217.8
72.5°	180.7	177.7	172.7	168.6	167.6	165.6	164.6	166.6	172.7	179.7	189.7
75°	142.5	143.6	140.5	137.5	137.5	134.5	136.5	136.5	142.5	149.6	157.6
77.5°	110.4	109.4	108.4	106.4	105.4	105.4	105.4	107.4	113.4	117.5	125.5
80°	78.3	79.3	76.3	77.3	76.3	77.3	77.3	81.3	84.3	89.3	95.4
82.5°	52.2	52.2	50.2	51.2	51.2	51.2	52.2	54.2	58.2	62.2	66.3
85°	29.1	30.1	28.1	30.1	30.1	30.1	31.1	32.1	35.1	36.1	40.2
87.5°	11.0	13.1	13.1	11.0	12.0	13.1	14.1	13.1	15.1	17.1	18.1
90°	10.1	11.2	12.2	14.1	16.1	18.0	20.0	21.4	22.8	24.1	25.5
92.5°	43.0	43.7	44.9	47.4	49.9	52.4	54.9	56.8	58.8	60.7	62.6
95°	83.3	83.6	85.0	87.8	90.5	93.3	96.1	98.0	100.0	101.9	103.8
97.5°	125.9	126.0	127.9	131.8	135.7	139.6	143.5	145.2	146.8	148.5	150.2
100°	174.7	174.7	176.5	180.1	183.7	187.3	190.9	193.4	195.9	198.4	200.9
102.5°	233.9	234.6	235.3	236.7	238.1	239.5	240.9	243.7	246.4	249.2	251.9
105°	290.1	290.8	291.6	293.3	295.0	296.6	298.3	299.9	301.6	303.2	304.9
107.5°	351.2	351.9	352.6	354.0	355.4	356.8	358.2	359.0	359.8	360.7	361.5
110°	414.9	415.6	416.0	416.8	417.7	418.5	419.3	420.1	420.9	421.8	422.6

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	476.4	476.7	477.3	478.4	479.5	480.6	481.7	482.0	482.3	482.6	482.9
115°	542.3	542.9	543.2	543.7	544.2	544.8	545.3	545.0	544.8	544.5	544.2
117.5°	603.9	604.0	604.3	604.8	605.4	605.9	606.5	606.8	607.0	607.3	607.6
120°	668.2	668.9	669.0	669.3	669.6	669.8	670.1	670.1	670.1	670.1	670.1
122.5°	728.7	728.8	729.2	730.0	730.9	731.7	732.5	732.2	732.0	731.7	731.4
125°	791.6	792.4	792.5	792.8	793.1	793.4	793.7	793.1	792.6	792.0	791.5
127.5°	851.9	852.3	852.4	852.7	853.0	853.3	853.6	853.3	853.0	852.7	852.4
130°	910.3	911.0	911.3	911.8	912.4	912.9	913.5	913.2	912.9	912.6	912.3
132.5°	970.9	972.1	972.0	971.7	971.4	971.2	970.9	970.6	970.3	970.0	969.7
135°	1027.5	1028.3	1028.4	1028.7	1029.0	1029.2	1029.5	1029.5	1029.5	1029.5	1029.5
137.5°	1083.7	1084.5	1084.8	1085.3	1085.9	1086.4	1087.0	1087.3	1087.5	1087.8	1088.1
140°	1136.2	1136.9	1137.3	1138.1	1139.0	1139.8	1140.6	1141.2	1141.7	1142.3	1142.8
142.5°	1188.7	1189.3	1189.9	1191.0	1192.1	1193.2	1194.3	1194.6	1194.8	1195.1	1195.4
145°	1241.1	1241.7	1242.1	1242.9	1243.8	1244.6	1245.4	1245.4	1245.4	1245.4	1245.4
147.5°	1288.7	1289.1	1289.4	1289.9	1290.5	1291.0	1291.6	1292.4	1293.3	1294.1	1295.0
150°	1332.9	1332.8	1333.4	1334.5	1335.6	1336.7	1337.8	1337.8	1337.8	1337.8	1337.8
152.5°	1376.2	1376.5	1376.6	1376.9	1377.2	1377.4	1377.7	1378.5	1379.4	1380.2	1381.1
155°	1415.2	1415.2	1415.3	1415.6	1415.9	1416.1	1416.4	1417.5	1418.6	1419.7	1420.8
157.5°	1450.4	1450.1	1450.2	1450.5	1450.8	1451.0	1451.3	1452.4	1453.5	1454.6	1455.7
160°	1481.7	1481.3	1481.4	1481.7	1482.0	1482.2	1482.5	1483.6	1484.7	1485.8	1486.9
162.5°	1511.5	1511.2	1511.2	1511.2	1511.2	1511.2	1511.2	1512.6	1514.0	1515.4	1516.8
165°	1536.5	1536.2	1536.3	1536.6	1536.9	1537.2	1537.5	1538.6	1539.7	1540.8	1541.9
167.5°	1556.8	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1557.9	1559.5	1561.2	1562.9
170°	1574.2	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1575.3	1576.9	1578.6	1580.3
172.5°	1586.7	1586.1	1586.1	1586.1	1586.1	1586.1	1586.1	1587.8	1589.4	1591.1	1592.8
175°	1595.5	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1596.5	1598.2	1599.8	1601.5
177.5°	1601.7	1601.1	1601.0	1600.7	1600.4	1600.2	1599.9	1601.5	1603.2	1604.8	1606.5
180°	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6
2.5°	1121.3	1114.3	1113.3	1115.3	1111.3	1117.3	1115.3	1117.3	1112.3	1117.3	1114.3
5°	1044.0	1042.0	1038.0	1033.0	1034.0	1035.0	1040.0	1035.0	1039.0	1040.0	1045.0
7.5°	971.7	967.7	970.7	968.7	959.7	957.7	959.7	962.7	968.7	972.7	975.8
10°	913.5	911.5	907.5	904.5	899.5	896.5	900.5	896.5	904.5	911.5	911.5
12.5°	869.3	861.3	856.3	855.3	844.3	846.3	850.3	853.3	862.3	866.3	866.3
15°	823.2	817.1	815.1	811.1	807.1	811.1	809.1	812.1	816.1	820.2	822.2
17.5°	783.0	782.0	783.0	773.0	776.0	771.0	772.0	777.0	774.0	777.0	783.0
20°	746.9	748.9	745.9	741.9	741.9	735.8	742.9	740.9	741.9	747.9	756.9
22.5°	719.8	718.8	715.8	712.7	708.7	709.7	710.7	708.7	716.8	721.8	722.8
25°	690.7	688.7	687.6	684.6	680.6	684.6	683.6	684.6	686.6	694.7	688.7
27.5°	*663.6*	*659.5*	*661.5*	*658.5*	*657.5*	*658.5*	*658.5*	*659.5*	*661.5*	*662.6*	*663.6*
30°	640.5	636.5	635.4	633.4	632.4	633.4	635.4	633.4	641.5	640.5	640.5
32.5°	615.4	612.4	610.4	610.4	609.3	608.3	609.3	610.4	616.4	612.4	616.4
35°	591.3	589.3	589.3	587.3	586.3	586.3	586.3	590.3	588.3	591.3	591.3
37.5°	568.2	568.2	567.2	565.2	564.2	565.2	564.2	566.2	565.2	566.2	567.2
40°	544.1	542.1	541.1	541.1	538.1	535.1	538.1	538.1	539.1	542.1	543.1
42.5°	515.0	516.0	516.0	512.0	512.0	512.0	513.0	514.0	514.0	516.0	516.0
45°	489.9	487.9	487.9	487.9	485.9	486.9	488.9	488.9	488.9	488.9	486.9
47.5°	461.8	461.8	462.8	462.8	465.8	464.8	464.8	463.8	461.8	461.8	462.8
50°	435.7	438.7	439.7	439.7	440.7	441.7	441.7	439.7	438.7	435.7	435.7
52.5°	410.6	412.6	414.6	417.6	419.6	418.6	418.6	416.6	412.6	411.6	410.6
55°	383.5	386.5	390.5	393.5	396.5	397.5	397.5	393.5	389.5	384.5	384.5
57.5°	358.4	361.4	368.4	371.4	375.4	375.4	373.4	370.4	364.4	360.4	357.4
60°	333.3	338.3	343.3	349.3	354.4	355.4	352.4	348.3	341.3	336.3	332.3
62.5°	306.2	311.2	321.2	327.3	331.3	331.3	331.3	326.3	317.2	310.2	304.2
65°	280.1	285.1	294.1	302.2	305.2	308.2	305.2	300.2	293.1	285.1	279.1
67.5°	253.0	259.0	268.0	274.1	278.1	281.1	279.1	275.1	266.0	255.0	251.0
70°	222.9	225.9	238.9	244.9	251.0	253.0	251.0	244.9	235.9	223.9	219.8
72.5°	194.8	197.8	209.8	214.8	219.8	221.9	218.8	214.8	206.8	195.8	190.7
75°	162.6	167.6	173.7	181.7	187.7	189.7	186.7	183.7	173.7	166.6	162.6
77.5°	128.5	133.5	141.5	148.6	154.6	153.6	149.6	150.6	139.5	131.5	128.5
80°	97.4	101.4	107.4	113.4	116.4	116.4	115.4	111.4	107.4	101.4	96.4
82.5°	67.3	72.3	77.3	81.3	81.3	82.3	80.3	79.3	75.3	70.3	69.3
85°	40.2	41.2	45.2	45.2	49.2	47.2	46.2	49.2	45.2	42.2	41.2
87.5°	18.1	17.1	18.1	18.1	17.1	19.1	19.1	18.1	19.1	18.1	18.1
90°	26.2	26.6	27.5	28.3	29.2	30.0	29.2	28.3	27.5	26.6	26.2
92.5°	63.6	63.9	64.4	65.0	65.5	66.1	65.5	65.0	64.4	63.9	63.6
95°	104.8	105.1	105.6	106.2	106.7	107.3	106.7	106.2	105.6	105.1	104.8
97.5°	151.0	151.1	151.4	151.7	151.9	152.2	151.9	151.7	151.4	151.1	151.0
100°	202.2	202.5	203.0	203.6	204.1	204.7	204.1	203.6	203.0	202.5	202.2
102.5°	253.3	253.7	254.6	255.4	256.3	257.1	256.3	255.4	254.6	253.7	253.3
105°	305.7	306.1	307.0	307.8	308.7	309.5	308.7	307.8	307.0	306.1	305.7
107.5°	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9	361.9
110°	423.0	422.9	422.6	422.3	422.1	421.8	422.1	422.3	422.6	422.9	423.0

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	483.0	482.7	482.2	481.6	481.1	480.5	481.1	481.6	482.2	482.7	483.0
115°	544.1	544.0	543.7	543.4	543.2	542.9	543.2	543.4	543.7	544.0	544.1
117.5°	607.7	607.2	606.1	605.0	603.9	602.8	603.9	605.0	606.1	607.2	607.7
120°	670.1	669.5	668.4	667.3	666.2	665.1	666.2	667.3	668.4	669.5	670.1
122.5°	731.3	730.9	730.0	729.2	728.3	727.5	728.3	729.2	730.0	730.9	731.3
125°	791.2	791.1	790.8	790.5	790.2	789.9	790.2	790.5	790.8	791.1	791.2
127.5°	852.3	852.0	851.5	850.9	850.4	849.8	850.4	850.9	851.5	852.0	852.3
130°	912.2	911.9	911.4	910.8	910.3	909.7	910.3	910.8	911.4	911.9	912.2
132.5°	969.6	969.2	968.4	967.5	966.7	965.9	966.7	967.5	968.4	969.2	969.6
135°	1029.5	1029.0	1027.9	1026.8	1025.7	1024.6	1025.7	1026.8	1027.9	1029.0	1029.5
137.5°	1088.2	1087.5	1086.1	1084.8	1083.4	1082.0	1083.4	1084.8	1086.1	1087.5	1088.2
140°	1143.1	1142.4	1141.0	1139.7	1138.3	1136.9	1138.3	1139.7	1141.0	1142.4	1143.1
142.5°	1195.5	1194.8	1193.4	1192.1	1190.7	1189.3	1190.7	1192.1	1193.4	1194.8	1195.5
145°	1245.4	1245.0	1244.2	1243.3	1242.5	1241.7	1242.5	1243.3	1244.2	1245.0	1245.4
147.5°	1295.4	1294.3	1292.1	1289.8	1287.6	1285.4	1287.6	1289.8	1292.1	1294.3	1295.4
150°	1337.8	1337.5	1337.0	1336.4	1335.9	1335.3	1335.9	1336.4	1337.0	1337.5	1337.8
152.5°	1381.5	1380.9	1379.8	1378.7	1377.6	1376.5	1377.6	1378.7	1379.8	1380.9	1381.5
155°	1421.4	1420.7	1419.3	1418.0	1416.6	1415.2	1416.6	1418.0	1419.3	1420.7	1421.4
157.5°	1456.3	1455.3	1453.4	1451.5	1449.5	1447.6	1449.5	1451.5	1453.4	1455.3	1456.3
160°	1487.5	1486.8	1485.4	1484.1	1482.7	1481.3	1482.7	1484.1	1485.4	1486.8	1487.5
162.5°	1517.5	1516.7	1515.0	1513.3	1511.7	1510.0	1511.7	1513.3	1515.0	1516.7	1517.5
165°	1542.4	1541.6	1539.9	1538.3	1536.6	1535.0	1536.6	1538.3	1539.9	1541.6	1542.4
167.5°	1563.7	1562.9	1561.2	1559.5	1557.9	1556.2	1557.9	1559.5	1561.2	1562.9	1563.7
170°	1581.1	1580.1	1578.2	1576.3	1574.3	1572.4	1574.3	1576.3	1578.2	1580.1	1581.1
172.5°	1593.6	1592.8	1591.1	1589.4	1587.8	1586.1	1587.8	1589.4	1591.1	1592.8	1593.6
175°	1602.3	1601.3	1599.4	1597.5	1595.5	1593.6	1595.5	1597.5	1599.4	1601.3	1602.3
177.5°	1607.3	1606.3	1604.4	1602.5	1600.5	1598.6	1600.5	1602.5	1604.4	1606.3	1607.3
180°	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6
2.5°	1123.3	1117.3	1124.3	1115.3	1117.3	1128.3	1127.3	1137.4	1143.4	1142.4	1147.4
5°	1049.0	1049.0	1052.1	1051.0	1061.1	1070.1	1082.2	1092.2	1103.2	1109.3	1116.3
7.5°	975.8	985.8	987.8	992.8	1004.9	1019.9	1032.0	1047.0	1063.1	1074.1	1082.2
10°	915.5	923.6	931.6	935.6	948.7	968.7	985.8	1009.9	1030.0	1042.0	1053.1
12.5°	862.3	871.4	875.4	893.4	902.5	915.5	939.6	965.7	987.8	1000.9	1009.9
15°	824.2	829.2	838.2	849.3	858.3	874.4	894.4	923.6	944.6	955.7	986.8
17.5°	792.1	798.1	803.1	808.1	822.2	839.2	858.3	883.4	910.5	929.6	945.6
20°	758.9	761.9	768.0	776.0	786.0	802.1	819.2	845.3	869.3	884.4	905.5
22.5°	719.8	728.8	734.8	740.9	751.9	770.0	786.0	805.1	835.2	852.3	874.4
25°	696.7	700.7	704.7	711.7	719.8	735.8	753.9	774.0	798.1	816.1	835.2
27.5°	*666.6*	*672.6*	*677.6*	*686.6*	*691.7*	*704.7*	*721.8*	*741.9*	*771.0*	*786.0*	*802.1*
30°	641.5	647.5	651.5	655.5	662.6	676.6	692.7	708.7	735.8	754.9	771.0
32.5°	616.4	622.4	627.4	630.4	637.5	646.5	659.5	679.6	702.7	715.8	736.8
35°	594.3	594.3	600.3	604.3	610.4	618.4	630.4	645.5	669.6	686.6	705.7
37.5°	569.2	570.2	575.2	578.2	584.3	592.3	604.3	618.4	638.5	651.5	670.6
40°	543.1	546.1	548.1	553.1	560.2	563.2	575.2	591.3	611.4	623.4	639.5
42.5°	517.0	519.0	524.0	528.0	534.1	539.1	547.1	562.2	577.2	595.3	608.3
45°	487.9	492.9	495.9	502.9	505.9	511.0	519.0	531.0	549.1	560.2	575.2
47.5°	462.8	464.8	466.8	475.8	481.9	484.9	492.9	499.9	519.0	529.0	543.1
50°	435.7	435.7	438.7	442.7	449.7	455.8	462.8	470.8	485.9	495.9	510.0
52.5°	410.6	407.6	409.6	411.6	418.6	424.6	431.7	442.7	456.8	462.8	474.8
55°	383.5	378.5	381.5	384.5	386.5	394.5	402.6	409.6	420.6	429.7	440.7
57.5°	354.4	353.4	351.4	352.4	357.4	362.4	368.4	377.5	390.5	397.5	403.6
60°	328.3	322.2	320.2	322.2	325.3	328.3	336.3	344.3	355.4	362.4	369.4
62.5°	301.2	295.1	291.1	288.1	291.1	298.1	303.2	309.2	318.2	326.3	332.3
65°	275.1	266.0	262.0	260.0	259.0	264.0	268.0	276.1	284.1	287.1	294.1
67.5°	245.9	237.9	232.9	229.9	229.9	229.9	233.9	241.9	250.0	251.0	258.0
70°	216.8	207.8	202.8	198.8	196.8	198.8	203.8	204.8	211.8	213.8	217.8
72.5°	185.7	177.7	171.7	166.6	167.6	169.7	169.7	171.7	175.7	180.7	180.7
75°	156.6	145.6	142.5	138.5	136.5	136.5	136.5	140.5	143.6	147.6	146.6
77.5°	123.5	117.5	111.4	109.4	106.4	105.4	107.4	107.4	109.4	112.4	113.4
80°	95.4	88.3	84.3	82.3	78.3	77.3	78.3	78.3	81.3	80.3	81.3
82.5°	66.3	61.2	58.2	55.2	53.2	54.2	53.2	53.2	54.2	53.2	53.2
85°	38.1	37.1	35.1	34.1	33.1	31.1	33.1	32.1	31.1	30.1	32.1
87.5°	18.1	17.1	17.1	15.1	15.1	14.1	15.1	15.1	14.1	14.1	14.1
90°	25.5	24.1	22.8	21.4	20.0	18.0	16.1	14.1	12.2	11.2	10.1
92.5°	62.6	60.7	58.8	56.8	54.9	52.4	49.9	47.4	44.9	43.7	43.0
95°	103.8	101.9	100.0	98.0	96.1	93.3	90.5	87.8	85.0	83.6	83.3
97.5°	150.2	148.5	146.8	145.2	143.5	139.6	135.7	131.8	127.9	126.0	125.9
100°	200.9	198.4	195.9	193.4	190.9	187.3	183.7	180.1	176.5	174.7	174.7
102.5°	251.9	249.2	246.4	243.7	240.9	239.5	238.1	236.7	235.3	234.6	233.9
105°	304.9	303.2	301.6	299.9	298.3	296.6	295.0	293.3	291.6	290.8	290.1
107.5°	361.5	360.7	359.8	359.0	358.2	356.8	355.4	354.0	352.6	351.9	351.2
110°	422.6	421.8	420.9	420.1	419.3	418.5	417.7	416.8	416.0	415.6	414.9

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	482.9	482.6	482.3	482.0	481.7	480.6	479.5	478.4	477.3	476.7	476.4
115°	544.2	544.5	544.8	545.0	545.3	544.8	544.2	543.7	543.2	542.9	542.3
117.5°	607.6	607.3	607.0	606.8	606.5	605.9	605.4	604.8	604.3	604.0	603.9
120°	670.1	670.1	670.1	670.1	670.1	669.8	669.6	669.3	669.0	668.9	668.2
122.5°	731.4	731.7	732.0	732.2	732.5	731.7	730.9	730.0	729.2	728.8	728.7
125°	791.5	792.0	792.6	793.1	793.7	793.4	793.1	792.8	792.5	792.4	791.6
127.5°	852.4	852.7	853.0	853.3	853.6	853.3	853.0	852.7	852.4	852.3	851.9
130°	912.3	912.6	912.9	913.2	913.5	912.9	912.4	911.8	911.3	911.0	910.3
132.5°	969.7	970.0	970.3	970.6	970.9	971.2	971.4	971.7	972.0	972.1	970.9
135°	1029.5	1029.5	1029.5	1029.5	1029.5	1029.2	1029.0	1028.7	1028.4	1028.3	1027.5
137.5°	1088.1	1087.8	1087.5	1087.3	1087.0	1086.4	1085.9	1085.3	1084.8	1084.5	1083.7
140°	1142.8	1142.3	1141.7	1141.2	1140.6	1139.8	1139.0	1138.1	1137.3	1136.9	1136.2
142.5°	1195.4	1195.1	1194.8	1194.6	1194.3	1193.2	1192.1	1191.0	1189.9	1189.3	1188.7
145°	1245.4	1245.4	1245.4	1245.4	1245.4	1244.6	1243.8	1242.9	1242.1	1241.7	1241.1
147.5°	1295.0	1294.1	1293.3	1292.4	1291.6	1291.0	1290.5	1289.9	1289.4	1289.1	1288.7
150°	1337.8	1337.8	1337.8	1337.8	1337.8	1336.7	1335.6	1334.5	1333.4	1332.8	1332.9
152.5°	1381.1	1380.2	1379.4	1378.5	1377.7	1377.4	1377.2	1376.9	1376.6	1376.5	1376.2
155°	1420.8	1419.7	1418.6	1417.5	1416.4	1416.1	1415.9	1415.6	1415.3	1415.2	1415.2
157.5°	1455.7	1454.6	1453.5	1452.4	1451.3	1451.0	1450.8	1450.5	1450.2	1450.1	1450.4
160°	1486.9	1485.8	1484.7	1483.6	1482.5	1482.2	1482.0	1481.7	1481.4	1481.3	1481.7
162.5°	1516.8	1515.4	1514.0	1512.6	1511.2	1511.2	1511.2	1511.2	1511.2	1511.2	1511.5
165°	1541.9	1540.8	1539.7	1538.6	1537.5	1537.2	1536.9	1536.6	1536.3	1536.2	1536.5
167.5°	1562.9	1561.2	1559.5	1557.9	1556.2	1556.2	1556.2	1556.2	1556.2	1556.2	1556.8
170°	1580.3	1578.6	1576.9	1575.3	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1574.2
172.5°	1592.8	1591.1	1589.4	1587.8	1586.1	1586.1	1586.1	1586.1	1586.1	1586.1	1586.7
175°	1601.5	1599.8	1598.2	1596.5	1594.9	1594.9	1594.9	1594.9	1594.9	1594.9	1595.5
177.5°	1606.5	1604.8	1603.2	1601.5	1599.9	1600.2	1600.4	1600.7	1601.0	1601.1	1601.7
180°	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6	1603.6

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1182.6	1182.6	1182.6	1182.6
2.5°	1154.4	1164.5	1171.5	1184.6
5°	1128.3	1146.4	1163.5	1181.6
7.5°	1102.2	1123.3	1150.4	1173.5
10°	1073.1	1100.2	1132.4	1163.5
12.5°	1044.0	1076.1	1111.3	1152.4
15°	1008.9	1050.0	1091.2	1135.4
17.5°	977.8	1019.9	1064.1	1119.3
20°	942.6	988.8	1037.0	1093.2
22.5°	911.5	962.7	1012.9	1072.1
25°	876.4	926.6	981.8	1045.0
27.5°	*847.3*	*893.4*	*947.7*	*1015.9*
30°	812.1	862.3	916.5	984.8
32.5°	779.0	827.2	884.4	951.7
35°	744.9	794.1	845.3	909.5
37.5°	712.7	754.9	806.1	867.3
40°	676.6	722.8	769.0	817.1
42.5°	643.5	685.6	728.8	767.0
45°	606.3	642.5	683.6	714.8
47.5°	572.2	604.3	636.5	660.5
50°	538.1	563.2	587.3	608.3
52.5°	497.9	526.0	539.1	552.1
55°	461.8	477.8	489.9	502.9
57.5°	426.6	433.7	439.7	451.7
60°	380.5	388.5	395.5	404.6
62.5°	340.3	344.3	346.3	355.4
65°	302.2	301.2	306.2	311.2
67.5°	261.0	260.0	265.0	267.0
70°	220.9	219.8	220.9	225.9
72.5°	182.7	182.7	183.7	185.7
75°	147.6	147.6	148.6	150.6
77.5°	111.4	113.4	112.4	116.4
80°	81.3	79.3	81.3	83.3
82.5°	53.2	55.2	55.2	53.2
85°	30.1	30.1	30.1	30.1
87.5°	13.1	13.1	14.1	15.1
90°	7.9	5.6	3.4	1.2
92.5°	41.6	40.2	38.8	37.4
95°	82.8	82.2	81.7	81.1
97.5°	125.6	125.3	125.1	124.8
100°	174.7	174.7	174.7	174.7
102.5°	232.5	231.2	229.8	228.4
105°	288.7	287.3	285.9	284.5
107.5°	349.8	348.5	347.1	345.7
110°	413.5	412.1	410.7	409.3

TEST NUMBER: P1035579
CATALOG NUMBER: S125DIW-B850D1340UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	475.9	475.3	474.8	474.2
115°	541.2	540.1	539.0	537.9
117.5°	603.6	603.3	603.1	602.8
120°	666.8	665.5	664.1	662.7
122.5°	728.4	728.1	727.8	727.5
125°	789.9	788.3	786.6	785.0
127.5°	851.1	850.2	849.4	848.6
130°	908.9	907.6	906.2	904.8
132.5°	968.4	965.9	963.4	960.9
135°	1025.8	1024.1	1022.5	1020.8
137.5°	1082.0	1080.3	1078.7	1077.0
140°	1134.8	1133.4	1132.0	1130.6
142.5°	1187.6	1186.5	1185.4	1184.3
145°	1240.0	1238.9	1237.8	1236.7
147.5°	1287.9	1287.0	1286.2	1285.4
150°	1333.2	1333.5	1333.7	1334.0
152.5°	1375.7	1375.1	1374.6	1374.0
155°	1415.2	1415.2	1415.2	1415.2
157.5°	1450.9	1451.5	1452.0	1452.6
160°	1482.5	1483.4	1484.2	1485.0
162.5°	1512.0	1512.6	1513.1	1513.7
165°	1537.0	1537.6	1538.1	1538.7
167.5°	1557.9	1559.0	1560.1	1561.2
170°	1575.3	1576.4	1577.5	1578.6
172.5°	1587.8	1588.9	1590.0	1591.1
175°	1596.6	1597.7	1598.8	1599.9
177.5°	1602.8	1603.9	1605.0	1606.1
180°	1603.6	1603.6	1603.6	1603.6

(END OF REPORT)